

SELECT SPEC™

Specification Grade Wiring Devices



restaurants...



hospitals...



retail stores...

plugs & connectors...

receptacles...




switches...

offices...



shopping malls...



locking devices...

schools...





Duplex Receptacles



Light Industrial Back and Side Wired



Description	Color	Catalog Numbers	UL	SF
Smooth Face	Brown	5252AB	UL	SF
	Gray	5252AG		
	Ivory	5252AI		
	White	5252AW		
	Almond	5252AAL		
	Black	5252ABLK		
Finder Groove Face	Brown	5262B	UL	SF
	Gray	5262G		
	Ivory	5262I		
	White	5262W		
	Almond	5262AL		
	Black	5262BLK		

Select Spec™ light industrial, commercial and hospital grade receptacles are ideal for any project where ease of wiring, durability and reliability are required. The impact resistant nylon face is available in a variety of colors to blend into the decor of office buildings, administrative areas, schools, government facilities and retail spaces. The Hospital Grade receptacle is specifically designed to provide safety and withstand demanding environments found in hospitals.

Hospital Grade Back and Side Wired



Finder Groove Face	Brown	8200B	8300B
	Gray	8200G	8300G
	Ivory	8200I	8300I
	Red	8200R	8300R
	White	8200W	8300W
	Almond	8200AL	8300AL

Commercial Back and Side Wired



Smooth Face	Brown	BR15B	BR20B
	Gray	BR15G	BR20G
	Ivory	BR15I	BR20I
	White	BR15W	BR20W
	Almond	BR15AL	BR20AL
	Black	BR15BLK	BR20BLK
Decorator Style Rectangular Smooth Face	Gray	D15G	D20G
	Ivory	D15I	D20I
	White	D15W	D20W
	Almond	D15AL	D20AL



5352AI



5262W



8200W



D15AL

Commercial Side Wired Only



Smooth Face	Brown	R15B	R20B
	Gray	R15G	R20G
	Ivory	R15I	R20I
	White	R15W	R20W
	Almond	R15AL	R20AL
	Black	R15BLK	R20BLK



R20G



IG15I

Isolated Ground Side Wired Only



Finder Groove Face	Ivory	IG15I	IG20I
	Orange	IG15O	IG20O



Locking Devices

Description	Catalog Numbers	Connector Receptacle Plug	
2P 3W 15A 125V Connector	L515C		
2P 3W Brown Duplex Receptacle	L515DR		
2P 3W Ivory Duplex Receptacle	L515DRI		
2P 3W 15A 125V Plug	L515P		
2P 3W 15A 125V Receptacle	L515R		
2P 3W 20A 125V Connector	L520C		
2P 3W 20A 125V Plug	L520P		
2P 3W 20A 125V Receptacle	L520R		
2P 3W 30A 125V Connector	L530C		
2P 3W 30A 125V Plug	L530P		
2P 3W 30A 125V Receptacle	L530R		
2P 3W 20A 250V Connector	L620C		
2P 3W 20A 250V Plug	L620P		
2P 3W 20A 250V Receptacle	L620R		
2P 3W 30A 250V Connector	L630C		
2P 3W 30A 250V Plug	L630P		
2P 3W 30A 250V Receptacle	L630R		
2P 3W 15A 277V AC Connector	L715C		
2P 3W 15A 277V AC Plug	L715P		
2P 3W 15A 277V AC Receptacle	L715R		
2P 3W 20A 277V AC Connector	L720C		
2P 3W 20A 277V AC Plug	L720P		
2P 3W 20A 277V AC Receptacle	L720R		
2P 3W 30A 277V AC Connector	L730C		
2P 3W 30A 277V AC Plug	L730P		
2P 3W 30A 277V AC Receptacle	L730R		
3P 4W 20A 125/250V AC Connector	L1420C		
3P 4W 20A 125/250V Plug	L1420P		
3P 4W 20A 125/250V AC Receptacle	L1420R		
3P 4W 30A 125/250V AC Connector	L1430C		
3P 4W 30A 125/250V AC Plug	L1430P		
3P 4W 30A 125/250V AC Receptacle	L1430R		
3P 4W 20A 3Ø250V AC Connector	L1520C		
3P 4W 20A 3Ø250V AC Plug	L1520P		
3P 4W 20A 3Ø250V AC Receptacle	L1520R		
3P 4W 30A 3Ø250V AC Connector	L1530C		
3P 4W 30A 3Ø250V AC Plug	L1530P		
3P 4W 30A 3Ø250V AC Receptacle	L1530R		
3P 4W 20A 3Ø480V AC Connector	L1620C		
3P 4W 20A 3Ø480V AC Plug	L1620P		
3P 4W 20A 3Ø480V AC Receptacle	L1620R		
3P 4W 30A 3Ø480V AC Connector	L1630C		
3P 4W 30A 3Ø480V AC Plug	L1630P		
3P 4W 30A 3Ø480V AC Receptacle	L1630R		

Select Spec™ locking devices provide a safe disconnect solution between an equipment load and a power source. These devices incorporate a locking interface that is engaged and disengaged simply by rotating the device assuring a safe and reliable electrical connection. Locking devices are used on a wide range of industrial, MRO & OEM, and construction applications for providing a secure electrical connection. Uses include plant floor equipment wiring, ceiling power drops, extension cords and portable equipment. The product line includes plugs, connectors and receptacles in 15, 20 and 30 amperages and common voltage ratings.



L730P



L730C



L730R

Light Industrial Receptacles

Features

- Multiple drive screws
- Pretensioned ground contacts
- Large oxide-cutting terminal screws
- High grade, bronze alloy triple wipe power contacts

Benefits

- Quick and easy installation
- Provides positive ground continuity
- Ensures reliable low resistance connections
- Superior plug blade retention

Commercial Receptacles

Features

- Smooth nylon face
- Nylon base
- Multiple drive screws
- Pre-tensioned ground contacts
- Large oxide-cutting terminal screws
- Brass alloy triple wipe power contacts

Benefits

- Provides high-impact resistance and a contemporary look
- Highly impact and abuse resistant
- Quick and easy installation
- Provides positive ground continuity
- Ensures reliable low resistance connections
- Superior plug blade retention

Locking Devices

Features

- Nylon construction
- Visible NEMA ratings
- Captive assembly screws
- Nickel plated receptacle strap

Benefits

- High impact resistance
- Plugs and connectors have NEMA number and electrical ratings molded in for easy identification
- Faster assembly and no screws to drop and lose
- Nickel plated steel strap prevents corrosion

Switches

Features

- Nylon toggle
- Integral ground terminal
- Silver alloy contacts
- Multiple drive screws
- One piece rivetless spring contact arm and terminal plate
- Ground terminal anchor hole

Benefits

- Resists abuse and chemical attack
- Allows compliance to NEC®
- Reduces contact erosion and helps prevent welding, providing long life
- Quick and easy installation
- Assures proper contact alignment, reducing heat rise
- Forms conductor around terminal screw and provides wiring ease and labor savings



Light Industrial - Back and Side Wired 15A, 120-277V AC



Description	Single Pole	Three Way	Four Way
Brown Toggle	1201B	1203B	Order 20A
Gray Toggle	1201G	1203G	Order 20A
Ivory Toggle	1201I	1203I	Order 20A
White Toggle	1201W	1203W	Order 20A
Almond Toggle	1201AL	1203AL	Order 20A
Black Toggle	1201BLK	1203BLK	Order 20A

20A, 120-277VAC

Brown Toggle	1221B	1223B	1224B
Gray Toggle	1221G	1223G	1224G
Ivory Toggle	1221I	1223I	1224I
White Toggle	1221W	1223W	1224W
Almond Toggle	1221AL	1223AL	1224AL
Black Toggle	1221BLK	1223BLK	1224BLK

Decorator Style - Rectangular Toggle Back and Side Wired - 15A, 120-277V AC



Gray	DS115G	DS315G	Order 20A
Ivory	DS115I	DS315I	Order 20A
White	DS115W	DS315W	Order 20A
Almond	DS115AL	DS315AL	Order 20A
Black	DS115BLK	DS315BLK	Order 20A

20A, 120-277V AC

Gray	DS120G	DS320G	DS420G
Ivory	DS120I	DS320I	DS420I
White	DS120W	DS320W	DS420W
Almond	DS120AL	DS320AL	DS420AL
Black	DS120BLK	DS320BLK	DS420BLK

Commercial - Back and Side Wired - 15A, 120-277V AC

Brown Toggle	BS115B	BS315B	Order 20A
Gray Toggle	BS115G	BS315G	Order 20A
Ivory Toggle	BS115I	BS315I	Order 20A
White Toggle	BS115W	BS315W	Order 20A
Almond Toggle	BS115AL	BS315AL	Order 20A
Black Toggle	BS115BLK	BS315BLK	Order 20A



20A, 120-277V AC

Brown Toggle	BS120B	BS320B	BS420B
Gray Toggle	BS120G	BS320G	BS420G
Ivory Toggle	BS120I	BS320I	BS420I
White Toggle	BS120W	BS320W	BS420W
Almond Toggle	BS120AL	BS320AL	BS420AL
Black Toggle	BS120BLK	BS320BLK	BS420BLK

Commercial - Side Wired Only - 15A, 120-277V AC

Brown Toggle	S115B	S315B	Order 20A
Gray Toggle	S115G	S315G	Order 20A
Ivory Toggle	S115I	S315I	Order 20A
White Toggle	S115W	S315W	Order 20A
Almond Toggle	S115AL	S315AL	Order 20A
Black Toggle	S115BLK	S315BLK	Order 20A



20A, 120-277V AC

Brown Toggle	S120B	S320B	S420B
Gray Toggle	S120G	S320G	S420G
Ivory Toggle	S120I	S320I	S420I
White Toggle	S120W	S320W	S420W
Almond Toggle	S120AL	S320AL	S420AL
Black Toggle	S120BLK	S320BLK	S420BLK



From a toggle switch to an AC rocker style switch, Select Spec™ switches are ideal for any commercial to light industrial construction project where ease of wiring, durability and reliability are required. The nylon toggle is exceptionally rugged and chemical resistant. The rocker switch low profile design reduces the chance of damage. Select Spec switches are available in a variety of colors to blend into the decor of office buildings, administrative areas, schools, government projects, retail spaces and any place a light industrial/commercial switch is needed.



1201I



1221B



DS115I



S315I



Single Receptacles and Straight Blade Plugs & Connectors

Single Receptacles Back and Side Wired



NEMA 5-15R
15A 125V
UL CSA



NEMA 5-20R
20A 125V
UL CSA

Description	Color	Catalog Numbers
Finder Groove Face	Gray	SR15G SR20G
	Ivory	SR15I SR20I
	White	SR15W SR20W
Isolated Ground	Orange	SR15IG SR20IG



Select Spec™ single receptacles are ideal for any commercial to light industrial construction projects.

Use Select Spec straight blade plugs and connectors in commercial areas such as offices and retail centers. The straight blade devices can also be used in light industrial areas such as on the plant floor.

Specialty Receptacles

Description	Color	Catalog Numbers
Clock Hanger	Brass Finish	R15CH —
Display Receptacle	Brass Finish	R15DIS —

Straight Blade Plugs and Connector

Description	Color	Catalog Numbers
Plug	Black	515P —
Nylon Plug	Black & White	515SP 520SP
Nylon Connector	Black & White	515SC 520SC

Range & Dryer Receptacles

Description	Color	NEMA Configuration	Catalog Numbers
2P 3W 20A 250V	Gray	6-20R	SR620G*
2P 3W 20A 250V	Ivory	6-20R	SR620I*
2P 3W 20A 250V	White	6-20R	SR620W*
2P 3W 30A 250V	Black	6-30R	SR630**
2P 3W 50A 250V	Black	6-50R	SR650**
3P 3W 30A 125/250V	Black	10-30R	SR1030***
3P 3W 50A 125/250V	Black	10-50R	SR1050***
3P 4W 30A 125/250V	Black	14-30R	SR1430**



Also Available Select Spec Counter Mats!

The Select Spec laminated counter mat is 22" x 17". This is a great quick reference to the Select Spec NEMA configurations and catalog numbers.

