

June 2014

RIP-TIE®

www.riptide.com

800/ 348-7600



RIP-TIE®

As a manager of a film and broadcast video equipment rental facility, Michael Paul Fennell wanted his products to be the most professionally prepared for this intense, fast paced industry. Frustrated with messy cables and annoying plastic ties, and unable to find any useful options on the market, Fennell set out to solve the problem on his own and came up with the first cable organizer using VELCRO® brand hook and loop fasteners - The Original Rip-Tie CableWrap. He wanted something that was reusable, quick, strong, neat, and wouldn't be lost. He worked on perfecting his invention, testing it on rental equipment and with his colleagues, until he knew he had it right. Little did he know that this handy device would become so popular.

Rip-Tie is the industry standard in reusable cable organization. The Rip-Tie line includes the CableWrap, CableCarrier, CableCarrier-LG, mini, CableCatch, CableHanger, CinchStrap, CinchStrap-EG, Rip-Tie Lite & WrapStrap, Econo Series Products, and we are a Preferred Converter of VELCRO® brand Hook & Loop. Rip-Tie is trusted to be the expert in both cable organization and VELCRO® brand products. After 29 years in business, Rip-Tie proudly boasts a customer base which includes high profile companies like Intel, Panavision and General Dynamics and the U.S. military. From Fortune 100 companies to home users, they all want the same thing - the best quality product available!



Mission

That we maintain the highest quality standards with our products and that all who contact us have a positive experience; including customers, suppliers, and our staff.



Background

We design, manufacture and distribute hook and loop reusable cable management products for virtually every function and market. We have the ability to customize and adapt products for specific needs. All Rip-Tie products are produced on site in our San Leandro facility.



Products

Most Rip-Tie products are available in the ten EIA color code. The hook and loop materials we use are reusable, and ideally suited for use with sensitive data cables and fiber optics. Rip-Tie is a Preferred Converter of VELCRO® brand Hook and Loop materials.



Services

Quality products, fairly priced, and prompt, courteous service are the Rip-Tie standards. With rare exceptions, we ship within 24 hours from receipt of the purchase order. Our goal; 100% customer satisfaction.

phone: (510) 577-0200 or (800) 348-7600

fax: (510) 553-0160











email: info@riptide.com

mailing: P. O. Box 549, San Leandro, CA 94577; Location: 883 San Leandro Boulevard, San Leandro, CA 94577





Rip-Tie Product Comparison Chart

Attach to the Cable








Choose the one that suits your application!

Pg	Product	How to use	Features	Application
4	 CableWrap	Attaches to Cable with Nylon Tie	10,000+ Cycles, Pull Tab for Easy Release	For frequently-used cables, such as extension cords, camera cables or any equipment cable. Once it is attached, you won't lose it.
5	 CableWrap Elastic	Attaches to Cable with Elastic Loop	10,000+ Cycles Pull Tab for Easy Release	Designed to attach the elastic loop directly on the power adapter or optical cable connector. The elastic-loop fits almost any shape.
5	 CableWrap Buckle	Attaches to Cable with Plastic Buckle	10,000+ Cycles Pull Tab for Easy Release	For frequently-used cables, extension cords, camera cables, and cables for equipment. The installation and removal can be done simply and quickly.
10	 EconoWrap Nylon Tie	Attaches to Cable with Nylon Tie	2,000+ refastening Economical and Easy to Use	For microphone cables and network cables.
10	 EconoWrap Elastic	Attaches to Cable with Elastic Loop	2,000+ Cycles Easy to Release	For microphone cables and network cables with diameters up to 1/2".
10	 EconoWrap Slip-on	Attaches to Cable with Hook & Loop	2,000+ Cycles Easy to Release	For use with cable diameters up to 3/4".
10	 EconoWrap Snap-on	Attaches to Cable with Plastic Rivet	2,000+ Cycles Easy to Slide on Cable	Use enclosed rivets for the attachment. Attaches to a cable with the maximum diameter of 3/8". Not a fixed mount type, it can slide freely.
12	 Rip-Tie Lite	Attaches by Inserting Strap through Slot	200+ Cycles Double-Sided Hook & Loop	The Rip-Tie Lite is ideal for bundling & organizing computer and network cables.
12	 Rip-Tie Lite PLUS	Attaches by Inserting Strap through Slot	200+ Cycles Double-Sided Hook & Loop with Low Profile Material	Same usage as Rip-Tie Lite. The thickness of the Rip-Tie Lite Plus is 0.03", suitable for cabling in limited space.
12	 Rip-Tie mini	Attaches by Inserting Strap through Slot	200+ Cycles Double-Sided Hook & Loop Designed for Small Cables	For small cables, such as charger cables, earphone cables and cell phone cables, etc.

Just Wrap

Pg	Product	How to use	Features	Application
10	 EconoWrap	Just wrap	2,000+ Cycles Economical	Easy to install and remove, durable, good for bundling cables and many other household uses!
13	 WrapStrap	Cut to Desired Length and Wrap	200+ Cycles Leaves no sticky residue	For cable racks, wiring under a server room and floor. Versatile and economical, just cut to desired length.
13	 WrapStrap PLUS	Cut to Desired Length and Wrap	200+ Cycles Economical - Low Profile	Same usage as WrapStrap, but with a lower profile (0.03"). Suitable for cabling in a limited space.
14	 RipWrap	Cut to Desired Length and Wrap	25+ Cycles Weather Resistant	Used instead of nylon wire ties. Can be used for outdoor applications. Inexpensive and expendable for a variety of uses.

Other Ways to Organize Cables

Pg	Product	How to use	Features	Application
8	 CableCarrier	Attaches to Belt for Easy Access to Cables	10,000+ Cycles Choose from 3 different Attachments	For carrying cables on the go. Also can be used for hanging temporary cable runs.
7	 CableCatch	Peel Backing and Apply to Smooth Surface	10,000+ Cycles Acrylic Based Adhesive, for high temperatures (225°F)	Adheres to most smooth surfaces. Used in computer server rooms, monitor wiring, and medical equipment.
11	 EconoCatch	Peel Backing and Apply to Smooth Surface	2,000+ Cycles Rubber Based Adhesive	Adheres to most surfaces. For use at work stations and many other uses.
7	 CinchStrap	Cinch with Buckle to Fasten	10,000+ Cycles Heavy Duty Utility Strap	For multiple uses; cables, tripods, luggage, boating, and many other household organizational uses.
11	 EconoCinch	Cinch with Buckle to Fasten	2,000+ Cycles Non-metallic Buckle	Same usage as CinchStrap, NOT for heavy use. For camera cables, tripod, and many other uses.
6	 CinchStrap-EG	Attaches to a Surface with Brass Grommet	10,000+ Cycles Oriented to Any Direction	For professional use, manage cable bundles inside wiring racks and closets.
11	 EconoCinch-EG	Attaches to a Surface with Brass Grommet	2,000+ Cycles Oriented to Any Direction	For cable management in component racks, Medium duty.

©2014 Rip-Tie, Inc. San Leandro CA 94577 MADE IN THE U.S.A. All rights reserved worldwide

CW Our highest quality wraps are extremely durable and tested for 10,000 release cycles. MADE IN THE U.S.A.



CableWrap

Our original patented wrap, one end semi-permanently attaches to a cable, the other end has a pull-tab to fasten and unfasten the Rip-Tie with one hand.


Two-Inch

The two inch wide Rip-Tie CableWrap has two grommetted holes and a flap to cover the heads of the 50 lb. nylon ties that attach the wrap to the cable.


With Webbing

Same great design as the Two-Inch CableWrap with the additional strength of heavy duty nylon webbing. INDUSTRIAL GRADE.

[5/8", 3/4" and 1" width]




[2" width]



CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
3/4" CableWrap - Available in 10 Standard Colors			
M-06-...-	1.5"	3/4" x 6"	1, 10, & 100 Pack
5/8" CableWrap - Available in 10 Standard Colors			
L-06-...-	1.5"	5/8" x 6"	1, 3, 10, & 100 Pack
1" CableWrap - Available in 10 Standard Colors + Neon Colors!			
H-03-...-	0.75"	1" x 3"	1, 3, 10, & 100 Pack
H-06-...-	1.5"	1" x 6"	1, 3, 10, & 100 Pack
H-09-...-	2.25"	1" x 9"	1, 3, 10, & 100 Pack
H-14-...-	3.75"	1" x 14"	1, 3, 10, & 100 Pack
H-21-...-	5.5"	1" x 21"	1, 3, 10, & 100 Pack

CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
2" CableWrap - Available in 10 Standard Colors			
E-18-...-	4.0"	2" x 18"	1, 10, & 50 Pack
E-24-...-	6.5"	2" x 24"	1, 10, & 50 Pack
E-30-...-	8.5"	2" x 30"	1, 10, & 50 Pack
E-36-...-	10.5"	2" x 36"	1, 10, & 50 Pack
2" CableWrap with Webbing *			
EW-12-...-	2.5"	2" x 12"	1, 10, & 50 Pack
EW-18-...-	4.0"	2" x 18"	1, 10, & 50 Pack
EW-24-...-	6.5"	2" x 24"	1, 10, & 50 Pack
EW-30-...-	8.5"	2" x 30"	1, 10, & 50 Pack
EW-36-...-	10.5"	2" x 36"	1, 10, & 50 Pack
*Black Webbing on Standard 10 Colors			




Our highest quality wraps are extremely durable and tested for 10,000 release cycles. MADE IN THE U.S.A. **CW**



CableWrap with Buckle

CableWrap with Buckle can be installed on a cable easily, and attached to a wide variety of cable diameters. The soft buckle fits gently, yet snugly, and won't damage sensitive cables. Available in four sizes. Colors available: black, brown, blue, green, grey, orange, red, violet, white, yellow, neon green, neon orange, neon pink, neon yellow.



CableWrap with Elastic

Quickly attaches to cable like a luggage tag. Will slide along cable for best location after coiling. Call 1-800-348-7600 for more information.



CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
1" CableWrap with Buckle			
HB-06-....	1.5"	1" x 6"	1, 10, & 100 Pack
HB-09-....	2.25"	1" x 9"	1, 10, & 100 Pack
HB-14-....	3.75"	1" x 14"	1, 10, & 100 Pack
HB-21-....	5.5"	1" x 21"	1, 10, & 100 Pack

Fast!
Installs in Seconds.

Easy!
Handy Pull Tab Release.


Tidy!
Keeps Cables Neat and Organized.

Your Logo Here
Custom Logo Info
page 9



*Actual colors may appear different.

Neon ONLY Available in One Inch



CinchStrap-EG

Cable Management for Professionals

EG Our highest quality wraps are extremely durable and tested for 10,000 release cycles. MADE IN THE U.S.A.



CinchStrap-EG





- Professional grade quality, durability and value for cable management.
- Perfect for managing cable bundles inside wiring racks, mobile carts, along walls, over doorways, and in wiring closets.
- Attach to any rack or surface. Use any fastener up to 1/4" diameter for mounting.
- Non-magnetic grommet spreads fastener load evenly without risk of ripping fabric.
- Can be oriented in any direction.
- One of our top sellers.

Two-Inch CinchStrap-EG

- 2" CinchStrap-EG has two brass spur grommets to support heavier cable runs.
- Grommets are spaced 7/8" on center.
- We can make them at 1-1/8" on center to match standard rack hole dimensions.

CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
CinchStrap-EG - Available in 10 Standard Colors + Neon Colors!			
N-07-...-	1.5"	1" x 7"	2, 10, & 50 Pack
N-10-...-	2.50"	1" x 10"	2, 10, & 50 Pack
N-16-...-	4.25"	1" x 16"	2, 10, & 50 Pack
N-22-...-	6.25"	1" x 22"	2, 10, & 50 Pack
N-28-...-	8.25"	1" x 28"	2, 10, & 50 Pack
N-34-...-	10.0"	1" x 34"	2, 10, & 50 Pack
N-46-...-	14.0"	1" x 46"	2, 10, & 50 Pack

CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
2-Inch CinchStrap-EG - Available in 10 Standard Colors			
O-16-...-	2.5"	2" x 16"	1, 10, & 50 Pack
O-22-...-	4.5"	2" x 22"	1, 10, & 50 Pack
O-28-...-	6.25"	2" x 28"	1, 10, & 50 Pack
O-34-...-	8.25"	2" x 34"	1, 10, & 50 Pack
O-46-...-	12.0"	2" x 46"	1, 10, & 50 Pack
O-70-...-	19.75"	2" x 70"	1, 10, & 50 Pack
O-94-...-	27.25"	2" x 94"	1, 10, & 50 Pack
2-Inch CinchStrap-EG with WEBBING*			
OW-16-...-	2.5"	2" x 16"	1, 10, & 50 Pack
OW-22-...-	4.5"	2" x 22"	1, 10, & 50 Pack
OW-28-...-	6.25"	2" x 28"	1, 10, & 50 Pack
OW-34-...-	8.25"	2" x 34"	1, 10, & 50 Pack
OW-46-...-	12.0"	2" x 46"	1, 10, & 50 Pack
OW-70-...-	19.75"	2" x 70"	1, 10, & 50 Pack
OW-94-...-	27.25"	2" x 94"	1, 10, & 50 Pack
*Black Webbing on Standard 10 Colors			



Our highest quality wraps are extremely durable and tested for 10,000 release cycles. MADE IN THE U.S.A.



CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
1-Inch CinchStrap - Available in 10 Standard Colors + Neon Colors			
N-09-...-	2.0"	1" x 9"	1, 10, & 100 Pack
N-12-...-	2.75"	1" x 12"	1, 10, & 100 Pack
N-18-...-	4.5"	1" x 18"	1, 10, & 100 Pack
N-24-...-	6.5"	1" x 24"	1, 10, & 100 Pack
N-30-...-	8.5"	1" x 30"	1, 10, & 100 Pack
N-36-...-	10.25"	1" x 36"	1, 10, & 100 Pack
N-48-...-	14.25"	1" x 48"	1, 10, & 100 Pack
2-Inch CinchStrap - Available in 10 Standard Colors			
O-18-...-	4.0"	2" x 18"	1, 10, & 50 Pack
O-24-...-	6.0"	2" x 24"	1, 10, & 50 Pack
O-30-...-	7.75"	2" x 30"	1, 10, & 50 Pack
O-36-...-	9.75"	2" x 36"	1, 10, & 50 Pack
O-48-...-	13.5"	2" x 48"	1, 10, & 50 Pack
O-72-...-	21.25"	2" x 72"	1, 10, & 50 Pack
O-96-...-	28.75"	2" x 96"	1, 10, & 50 Pack
2-Inch CinchStrap with Webbing*			
OW-18-...-	4.0"	2" x 18"	1, 10, & 50 Pack
OW-24-...-	6.0"	2" x 24"	1, 10, & 50 Pack
OW-30-...-	7.75"	2" x 30"	1, 10, & 50 Pack
OW-36-...-	9.75"	2" x 36"	1, 10, & 50 Pack
OW-48-...-	13.5"	2" x 48"	1, 10, & 50 Pack
OW-72-...-	21.25"	2" x 72"	1, 10, & 50 Pack
OW-96-...-	28.75"	2" x 96"	1, 10, & 50 Pack
*Black Webbing on Standard 10 Colors			






CinchStrap

Heavy duty utility strap with extra strength and holding power that exemplifies our exacting standards for the best quality. We use the highest quality hook and loop and double stitch to insure the CinchStrap will stand up to years of daily use.

2" CinchStrap

Many recreational uses like boating, camping, soccer nets, backstops and cycling. Use on suitcases and boxes when travelling - both as a closure and as a unique ID. Earthquake safety strapping for computer equipment. Use in the garden - around hoses and on tools.





Non-metallic buckle - can be used safely around computers without demagnetizing disks.



CableCatch



Anchor cords, cables and wires neatly along a surface and out of the way. Acrylic pressure sensitive adhesive securely attaches CableCatch to equipment racks, desks, or walls. Peel-away backing makes the CableCatch easy to install. CableCatch successfully maintains the integrity of cable performance, and offers an easy & reliable way to organize high performance data cable without using nylon ties. One quick pull of the tab releases the cable bundle for easy rearranging and quick equipment set-ups.



CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
1-Inch CableCatch - Available in 10 Standard Colors			
A-02-...-	0.75"	5/8" x 2"	2, 5, & 50 Pack
A-04-...-	1.5"	5/8" x 4"	2, 5, & 50 Pack
C-02-...-	0.75"	1" x 2"	2, 5, & 50 Pack
C-04-...-	1.5"	1" x 4"	2, 5, & 50 Pack
C-08-...-	3.25"	1" x 8"	2, 5, & 50 Pack
C-12-...-	4.5"	1" x 12"	2, 5, & 50 Pack
2-Inch CableCatch - Available in 10 Standard Colors			
C-E5-...-	1.75"	2" x 5"	2, 5, & 50 Pack
C-E9-...-	3.75"	2" x 9"	2, 5, & 50 Pack

CableCarrier

CR Our highest quality wraps are extremely durable, made of the best quality hook and loop, tested for 10,000 release cycles.
MADE IN THE U.S.A.

CableCarrier

Available Attachments



Snaphook
Max Opening: 1/4"
Overall height: 2-1/16"



Triangle Carabiner
Max Opening: 3/8"
Overall height: 2-3/16"



Carabiner
Max Opening: 1"
Overall height: 3-1/16"




CableCarrier attaches to a belt loop or tool belt for easy access to extra cables:

- Power cords
- Microphones
- Speaker
- Lighting cables

It can also be used as a temporary hanger for cable runs during events, construction or installations.

CATALOG NO.	MAX BUNDLE DIAMETER		PACKAGE UNIT
Swivelhook CableCarrier			
J-06-...-	1.5"	1" x 6"	2, 5, 10, & 50 Pack
J-09-...-	2.5"	1" x 9"	2, 5, 10, & 50 Pack
Black Carabiner CableCarrier			
J-B6-C..-	1.5"	1" x 6"	2, 5, 10, & 50 Pack
J-B9-C..-	2.5"	1" x 9"	2, 5, 10, & 50 Pack
Silver Carabiner CableCarrier			
J-S6-C..-	1.5"	1" x 6"	2, 5, 10, & 50 Pack
J-S9-C..-	2.5"	1" x 9"	2, 5, 10, & 50 Pack
Black Triangle Carabiner CableCarrier			
J-B6-T.-	1.5"	1" x 6"	2, 5, 10, & 50 Pack
J-B9-T.-	2.5"	1" x 9"	2, 5, 10, & 50 Pack
Silver Triangle Carabiner CableCarrier			
J-S6-T.-	1.5"	1" x 6"	2, 5, 10, & 50 Pack
J-S9-T.-	2.5"	1" x 9"	2, 5, 10, & 50 Pack
2-Inch CableCarrier (6" Carabiner w/ Max Opening 2-1/2")			
J-20-E.-	4.5"	2" x 20"	1, 5, 10, & 50 Pack
J-24-E.-	6.0"	2" x 24"	1, 5, 10, & 50 Pack
2-Inch with Webbing (6" Carabiner w/ Max Opening 2-1/2")			
JW-20-E.-	4.5"	2" x 20"	1, 5, 10, & 50 Pack
JW-24-E.-	6.0"	2" x 24"	1, 5, 10, & 50 Pack

*Carabiners non-load bearing; not for personal safety applications.




CableCarrier-LG



Heavy Duty 4.5" Locking Carabiner

- **Keep your cables together and separated!**
- **Store and carry an assortment of cables on one carabiner.**
- **Color code your cables easily.**
- **Available in ten colors.**


CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
CableCarrier-LG with Heavy Duty 4.5" Locking Carabiner			
LGC-09-G04-	2"	1.5" x 9"	4-Pack
LGC-12-G04-	3"	1.5" x 12"	4-Pack
LGC-16-G04-	4"	1.5" x 16"	4-Pack
CableCarrier-LG - Strap Only			
LG-09-G1P-	2"	1.5" x 9"	1-Pack
LG-09-G04-	2"	1.5" x 9"	4-Pack
LG-09-G10-	2"	1.5" x 9"	10-Pack
LG-09-G50-	2"	1.5" x 9"	50-Pack
LG-12-G1P-	3"	1.5" x 12"	1-Pack
LG-12-G04-	3"	1.5" x 12"	4-Pack
LG-12-G10-	3"	1.5" x 12"	10-Pack
LG-12-G50-	3"	1.5" x 12"	50-Pack
LG-16-G1P-	4"	1.5" x 16"	1-Pack
LG-16-G04-	4"	1.5" x 16"	4-Pack
LG-16-G10-	4"	1.5" x 16"	10-Pack
LG-16-G50-	4"	1.5" x 16"	50-Pack
Heavy Duty 4.5" Locking Carabiner - Matte Black			
HDC-1	N/A	4.5"	1-Pack



Program 1

One side (Front) / One ink color

- Pull-Tab Size:** **A** 1" X 3-5/8" folded in the middle
1" X 1-11/16" finished size
B 1" X 2-1/4" folded in the middle
1" X 1" finished size
- Pull Tab Color:** **A** Black & Color Pull-Tabs available
B Black Only
- Multi color Ink:** NOT available
- Minimum Qty:** 250 pieces
- Setup Charge:** \$75.00
- Printing Cost:**
- | | | |
|--------------------|-----------|---------|
| 250-499 | 500-1,999 | 2,000 + |
| (per print) \$0.32 | \$0.25 | \$0.20 |



Program 2

One side (Front & Back) / One ink color

- Pull-Tab Size:** **A** 1" X 3-5/8" folded in the middle
1" X 1-11/16" finished size
B 1" X 2-1/4" folded in the middle
1" X 1" finished size
- Pull Tab Color:** Black & Color Pull-Tabs available
- Multi color Ink:** Up to 3 colors available with additional fee
- Minimum Qty:** 2,000 pieces
- Setup Charge:** \$100.00
- Printing Cost:**
- | | | |
|--------------------|-------------|---------|
| 2,000-4,999 | 5,000-9,999 | 10,000+ |
| (per print) \$0.20 | \$0.12 | \$0.09 |

Program 3

EconoSeries & Lite Products / One ink color

- Multi color Ink:** NOT available
- Minimum Qty:** 250 pieces
- Setup Charge:** \$75.00
- Printing Cost:**
- | | | |
|--------------------|-----------|---------|
| 250-499 | 500-1,999 | 2,000 + |
| (per print) \$0.32 | \$0.25 | \$0.20 |



ES Our EconoSeries is designed for moderate use and a more budget driven user, tested for 2,000 release cycles. Available with a variety of attachments. **MADE IN THE U.S.A.**

EconoWrap



EconoWrap is designed for organizing cables and cords for the more budget driven user. Our economical design features a die cut rounded end to make it easier to release.

What is EconoSeries...

EconoSeries are designed for organizing cables and cords for the budget driven user.

EconoSeries are made out of medium duty hook & loop - good for 2000+ cycles.


EconoSeries straps are designed to meet medium usage applications. Our economical design features a die cut rounded end to make it easy to release .

Available Attachments




Nylon Tie

Semi-Permanently attached on the cable with nylon tie, so you won't lose it. Nylon tie included.



Snap-On

Install EconoWrap with enclosed rivets. This allows the wrap to slide freely on the cable.



Elastic Loop

EconoWrap with an elastic loop attaches quickly and easily to keep the wrap on the cable.




Slip-On

Install EconoWrap on a cable by peeling the hook away, then place the cable and mate the hook/loop strap.

CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
EconoWrap			
M-07-E..-	2.0"	3/4" x 7"	2, 5, 20, & 200 Pack
M-11-E..-	3.0"	3/4" x 11"	2, 5, 20, & 200 Pack
H-07-E..-BK	2.0"	1" x 7"	2, 5, 20, & 200 Pack
H-11-E..-BK	3.0"	1" x 11"	2, 5, 20, & 200 Pack
EconoWrap with Nylon Tie			
M-07-EP.-	1.5"	3/4" x 7"	2, 5, 20, & 200 Pack
M-11-EP.-	2.5"	3/4" x 11"	2, 5, 20, & 200 Pack
H-07-EP.-	1.5"	1" x 7"	2, 5, 20, & 200 Pack
H-11-EP.-	2.5"	1" x 11"	2, 5, 20, & 200 Pack
EconoWrap with Elastic Band			
M-07-EE.-	2.0"	3/4" x 7"	2, 5, 20, & 200 Pack
M-11-EE.-	3.0"	3/4" x 11"	2, 5, 20, & 200 Pack
H-07-EE.-	2.0"	1" x 7"	2, 5, 20, & 200 Pack
H-11-EE.-	3.0"	1" x 11"	2, 5, 20, & 200 Pack

CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
EconoWrap with Slip-on Attachment			
M-05-ESL.-	1.13"	3/4" x 5"	2, 5, 20, & 200 Pack
M-07-ESL.-	1.5"	3/4" x 7"	2, 5, 20, & 200 Pack
H-11-ESL.-	3.0"	1" x 11"	2, 5, 20, & 200 Pack
H-15-ESL.-	4.13"	1" x 15"	2, 5, 20, & 200 Pack
EconoWrap with Snap-on Attachment			
H-11-ESN.-	2.5"	1" x 11"	2, 5, 20, & 200 Pack
H-15-ESN.-	3.75"	1" x 15"	2, 5, 20, & 200 Pack
H-20-ESN.-	5.38"	1" x 20"	2, 5, 20, & 200 Pack
* Rainbow Pack is available for 20 & 200 Packs.			




Our EconoSeries is designed for moderate use and a more budget driven user, tested for 2,000 release cycles. Available with a variety of attachments. **MADE IN THE U.S.A.**




EconoCinch

EconoCinch has many uses; bundling cables, hoses, and strapping equipment to desks or carts. The loop lock acts like a pulley, giving you leverage to pull the strap as tight as needed. The non-metallic buckle is safe to use around electrical and magnetic equipment.




EconoCinch-EG

EconoCinch-EG has a brass grommet with an inside diameter of 1/4". It can be attached with a metal fastener to walls, carts, and equipment racks.



EconoCatch

EconoCatch organizes cables against any smooth surface. The rubber based adhesive back allows for attachment to desks, walls, computers and any smooth surface.



Your Logo Here!

See Page 9


CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
EconoCatch *Available in BLACK ONLY			
B-02-E..-BK	0.75"	3/4" x 2"	2, 5, 20, & 200 Pack
B-H3-E..-BK	1.0"	1" x 3"	2, 5, 20, & 200 Pack
EconoCinch			
K-12-E..-	2.75"	3/4" x 12"	2, 5, 20, & 200 Pack
K-18-E..-	4.75"	3/4" x 18"	2, 5, 20, & 200 Pack
K-36-E..-	10.50"	3/4" x 36"	2, 5, 20, & 200 Pack
EconoCinch-EG			
K-05-GE.-	0.75"	3/4" x 5"	2, 5, 20, & 200 Pack
K-07-GE.-	1.25"	3/4" x 7"	2, 5, 20, & 200 Pack
K-10-GE.-	2.25"	3/4" x 10"	2, 5, 20, & 200 Pack

* Rainbow Pack is available for 20 & 200 Packs only



*Actual product colors may appear different.

LT Our lite series are made of double-sided hook and loop, tested for at least 200+ release cycles. Perfect for use on equipment, home theater and audio systems, tools, appliances and more. **MADE IN THE U.S.A.**




Rip-Tie Lite

Rip-Tie Lite is ideal for bundling & organizing computer and network cables. Made of one piece of double-sided hook and loop. A die-cut slot allows for attachment to a single cable; **chads removed**. Rip-Tie Lite Screw Mount version has a larger head and a perforated "X" for driving a screw.

Rip-Tie mini is designed for small cables, such as USB adapter cables for mobile phones and earbud cords for portable music players. Finally an end to frustration with tangled cables in your bags and pockets. Available in black or white. Each package contains seven (7), 1/4 x 3-1/2" wraps; bulk packs available.

Plenum Rated Rip-Tie Lite

Meeting the requirements of these regulations allows these products to be used for wire and cable management above a hung ceiling or below a raised floor. Manufactured from Polypropylene and Nylon. UL (Underwriters Laboratories) 94-V2 FAR 2.5 853 A/B NEC Section 300-22 (C) & (D).




CATALOG NO.	MAX BUNDLE DIAMETER	SIZEe	PACKAGE UNIT
Rip-Tie Lite			
Y-05-...	1.00"	1/2" x 5"	10, 25, & 100 Pack
Y-06-...	1.25"	1/2" x 6"	10, 25, & 100 Pack
Y-08-...	1.75"	1/2" x 8"	10, 25, & 100 Pack
Y-12-...	2.75"	1/2" x 12"	10, 25, & 100 Pack
Y-18-...	4.75"	1/2" x 18"	10, 25, & 100 Pack
Plenum Rated Rip-Tie Lite *Available in BLACK & CRANBERRY			
F-05-...	1.00"	1/2" x 5"	10, 25, & 100 Pack
F-06-...	1.25"	1/2" x 6"	10, 25, & 100 Pack
F-08-...	1.75"	1/2" x 8"	10, 25, & 100 Pack
F-12-...	2.75"	1/2" x 12"	10, 25, & 100 Pack
F-18-...	4.75"	1/2" x 18"	10, 25, & 100 Pack
Rip-Tie Lite Screw Mount			
Y-10-H.-BK	2.00"	1" x 10"	10, 25, & 100 Pack
X-08-...-BK	1.75"	1/2" x 8"	10, 25, & 100 Pack
X-12-...-BK	2.75"	1/2" x 12"	10, 25, & 100 Pack
X-23-...-BK	6.00"	7/8" x 23"	10, 25, & 100 Pack
Available in 10-Pack, Roll of 10, Roll of 25, 10 Rolls of 10			





Rip-Tie Lite PLUS **LTP**

Rip-Tie Lite PLUS has the same durability as Rip-Tie Lite. Lower cost and lower profile than Rip-Tie Lite. Thickness .03"



CATALOG NO.	MAX BUNDLE DIAMETER	SIZEe	PACKAGE UNIT
Rip-Tie Lite PLUS *Available In BLACK/BLACK & BLACK/GREY			
Q-05-180-BK	1.0"	1/2" x 5"	1 Roll of 180
Q-08-050-BG	1.75"	1/2" x 8"	2 Rolls of 25
Q-08-100-BK	1.75"	1/2" x 8"	1 Roll of 100
Q-12-075-BK	2.75"	1/2" x 12"	1 Roll of 75
mini *Available In Black & White ONLY			
Q-35-007-	0.5"	1/4" x 3-1/2"	7-Pack



Our lite series are made of double-sided hook and loop, tested for at least 200+ release cycles. Perfect for use in building installations containing large bundles of network cables, home theater and audio systems, appliances and more. **MADE IN THE U.S.A.** 

WrapStrap

WrapStrap is a single strip of double sided hook and loop fastener that quickly and easily wraps around almost anything. One of our most popular items. You can cut it to any length desired. Professional installers choice.

Plenum Rated WrapStrap


Meeting the requirements of these regulations allows these products to be used for wire and cable management above a hung ceiling or below a raised floor. Manufactured from Polypropylene and Nylon. UL (Underwriters Laboratories) 94-V2 FAR 2.5 853 A/B NEC Section 300-22 (C) & (D).



*Actual product colors may appear different.

WrapStrap PLUS

WrapStrap PLUS has the same durability as Rip-Tie WrapStrap. Lower cost and lower profile than WrapStrap. Thickness .03"



CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
Pre-Cut WrapStrap			
W-12-...-	3.0"	1/2" x 12"	1, 10, & 100 Pack
WrapStrap			
W-...-QRL-		1/4"	10, 15, & 75 Foot Roll
W-60-QSP-		1/4"	600 Foot Spool
W-...-PRL-		3/8"	10, 15, & 75 Foot Roll
W-60-PSP-BK		3/8"	600 Foot Spool
W-...-1RL-		1/2"	10, 15, & 75 Foot Roll
W-60-1SP-		1/2"	600 Foot Spool
W-...-LRL-	N/A	5/8"	10, 15, & 75 Foot Roll
W-...-MRL-		3/4"	10, 15, & 75 Foot Roll
W-60-MSP-BK		3/4"	600 Foot Spool
W-...-HRL-		1"	10, 15, & 75 Foot Roll
W-45-HSP-BK		1"	450 Foot Spool
W-...-JRL-BK		1-1/2"	10, 15, & 75 Foot Roll
W-...-ERL-BK		2"	10, 15, & 75 Foot Roll
W-...-WRL-BK		4"	10, 15, & 75 Foot Roll

CATALOG NO.	MAX BUNDLE DIAMETER	WIDTH	PACKAGE UNIT
Plenum Rated WrapStrap Available in BLACK & CRANBERRY ONLY			
G-75-QRL-		1/4"	75 Foot Roll
G-75-PRL-		3/8"	75 Foot Roll
G-75-1RL-		1/2"	75 Foot Roll
G-60-1SP-		1/2"	600 Foot Roll
G-75-LRL-		5/8"	75 Foot Roll
G-75-MRL-	N/A	3/4"	75 Foot Roll
G-60-MSP-		3/4"	600 Foot Roll
G-75-HRL-		1"	75 Foot Roll
G-75-JRL-		1-1/2"	75 Foot Roll
G-75-ERL-		2"	75 Foot Roll
G-75-WRL-		4"	75 Foot Roll
WrapStrap Plus Available In Black/Black			
Q-75-1RL-BK		1/2"	75 Foot Roll
Q-75-LRL-BK	N/A	5/8"	75 Foot Roll
Q-75-MRL-BK		3/4"	75 Foot Roll
Q-75-HRL-BK		1"	75 Foot Roll



RipWrap

RIP-TIE Style Gaffer Tape!

Do you use Gaffer tape? Try RipWrap instead. Great value, reusable and leaves no sticky residue on your cables!

- RipWrap can be used to bundle low voltage cables INSTEAD of nylon wire ties or tape.
- Perfect for Home Theater, Security or Telecom applications.
- Very inexpensive and weather resistant, can be used in nurseries, vineyards, tree farms, florists, and for gardening.
- Both continuous and perforated rolls are available. Perforations allow tearing off pieces at predetermined lengths.
- Polyester construction makes this wrap ideal for marine and outdoor installations.
- Tested for 25+ release cycles.





CATALOG NO.	MAX BUNDLE DIAMETER	SIZE	PACKAGE UNIT
RipWrap			
G-05-...-		1/2"	30, 75, & 150 Foot Roll
G-10-...-	N/A	1"	30, 75, & 150 Foot Roll
G-15-...-		1-1/2"	30, 75, & 150 Foot Roll
G-20-...-		2"	30, 75, & 150 Foot Roll
Perforated RipWrap			
G-P8-045-	1.75"	1/2" x 8"	1 Roll of 45
G-P8-131-	1.75"	1/2" x 8"	1 Roll of 131
G-P8-225-	1.75"	1/2" x 8"	1 Roll of 225
*Orange & Violet are NOT stock colors. Minimum order may apply.			

Thickness .03"

RipWrap is available in Black, Blue, Green, Yellow, Orange, Violet and White.



*Actual product colors may appear different.




Unitag

Unitag cable identification labels were developed to provide a quick, easy method of clearly labeling cables 7/16" in diameter or smaller.

Unitag cable labels are easy to read. They can be oriented to be easily read in hard to reach areas, behind computer desks and crowded wiring closets.

The marking surface can be rotated 360 for easy viewing. Unitag labels are easily installed. They are interchangeable and reusable. A marking pen can be used directly on the surface or use your own label printer.



CATALOG NO.	COLOR	SIZE	PACKAGE UNIT
Unitag - Available in Orange, Yellow, Blue & White			
U-15-....	O, Y, BU, W	5/8" x 1.5"	10, 50, 100, & 1000-Pack
U-20-....	O, Y, BU, W	5/8" x 2.0"	10, 50, 100, & 1000-Pack
U-25-....	O, Y, BU, W	5/8" x 2.5"	10, 50, 100, & 1000-Pack
U-20-040-FC	10 of Each	5/8" x 2.0"	40-Pack

Write-On CableWrap

New RIP-TIE Write-On CableWrap



- Won't get lost, permanently attaches to cable
- CableWrap is reusable over 10,000 times
- Make your own custom labels
- Show Length of cable, use of cable, owner of cable, etc.

RIP-TIE

Distributor for Velcro USA

RIP-TIE carries the largest stock of VELCRO® brand industrial hook and loop fastening tape in the West.

- Cable management
- Sew-on, standard back
- Widths from 1/2" to 6"
- Adhesive hook and loop tape
- Adhesive hook and loop dots
- Veltex display fabric

RIP-TIE offers:

- Custom Printing
- Sewing
- Cutting
- Grommeting
- Punching
- Slitting
- Perforating
- Die Cutting
- Mated Pairs
- Ultrasonic Welding



www.riptide.com

US & CANADA 800/ 348-7600

INTL 510/ 577-0200