










# LIGHT BULB SELECTION & REFERENCE GUIDE

12 Volt

Bulb Type	Item Number		Bulb Type	Base Type	Watts Rated	Watts Consumed	Rated Life (Hours)	Approx Light (Lumen)	Approx Color (Temp °K)	
	<b>9727</b>		T3 1/4	Wedge	3	2.1	20,000	8	2,200	
	<b>9731</b>	Xenon	T3 1/4	Wedge	3	2.7	19,000	15	2,400	
	<b>9728</b>		T3 1/4	Wedge	5	4.0	9,000	23	2,300	
	<b>9729</b>		T3 1/4	Wedge	5	3.9	2,000	26	2,450	
	<b>9732</b>	Xenon	T3 1/4	Wedge	5	4.2	8,000	33	2,550	
	<b>9718-32</b>	Clear	Xenon	T3	Rigid Loop	5	4.2	16,000	33	2,550
	<b>9718-33</b>	Frosted	Xenon	T3	Rigid Loop	5	4.2	16,000	33	2,550
	<b>9719-32</b>	Clear	Xenon	T3	Rigid Loop	10	8.4	12,000	83	2,650
	<b>9719-33</b>	Frosted	Xenon	T3	Rigid Loop	10	8.4	12,000	83	2,650
	<b>9776</b>		T5	Wedge	8	8	2,500	57	2,650	
	<b>9777</b>		T5	Wedge	12	11.6	2,000	120	2,750	
	<b>9778</b>		T5	Wedge	18	16.2	2,000	210	2,800	
	<b>9774</b>	Xenon	T5	Wedge	18	16.2	10,000	210	2,800	
	<b>9782</b>	Halogen	T3	G4 Bi-Pin	5	5	2,000	60	2,850	
	<b>9783</b>	Halogen	T3	G4 Bi-Pin	10	10	2,000	120	2,850	
	<b>9784</b>	Halogen	T3	G4 Bi-Pin	20	20	2,000	320	2,850	
	<b>9703</b>	Open Lens	Halogen	MR11	GZ4 Bi-Pin	20	20	2,000	<b>NSP</b> 10°	3,000
	<b>9704</b>	Open Lens	Halogen	MR11	GZ4 Bi-Pin	20	20	2,000	<b>SP</b> 20°	3,000
	<b>9705</b>	Open Lens	Halogen	MR11	GZ4 Bi-Pin	20	20	2,000	<b>NFL</b> 30°	3,000
	<b>9787</b>	Glass Lens	Halogen	MRC11	GZ4 Bi-Pin	20	20	2,000	<b>NSP</b> 10°	3,000
	<b>9788</b>	Glass Lens	Halogen	MRC11	GZ4 Bi-Pin	20	20	2,000	<b>SP</b> 20°	3,000
	<b>9789</b>	Glass Lens	Halogen	MRC11	GZ4 Bi-Pin	20	20	2,000	<b>NFL</b> 30°	3,000
	<b>9792</b>	Halogen	T4	GY6.35 Bi-Pin	20	20	2,000	340	2,850	
	<b>9793</b>	Halogen	T4	GY6.35 Bi-Pin	35	35	2,000	650	2,900	
	<b>9794</b>	Halogen	T4	GY6.35 Bi-Pin	50	50	2,000	900	2,950	
	<b>9709</b>	Open Lens	Halogen	MR16	GX5.3 Bi-Pin	50	50	2,000	<b>NSP</b> 15°	3,050
	<b>9710</b>	Open Lens	Halogen	MR16	GX5.3 Bi-Pin	50	50	2,000	<b>NFL</b> 25°	3,050
	<b>9711</b>	Open Lens	Halogen	MR16	GX5.3 Bi-Pin	50	50	2,000	<b>FL</b> 40°	3,050
	<b>9765</b>	Halogen	Par 36	Screw Terminal	50	50	4,000	<b>NSP</b> 5°	3,050	
	<b>9766</b>	Halogen	Par 36	Screw Terminal	50	50	4,000	<b>SP</b> 8°	3,050	
	<b>9767</b>	Halogen	Par 36	Screw Terminal	50	50	4,000	<b>FL</b> 30°	3,050	

**NSP:** Narrow Spot, **SP:** Spot, **NFL:** Narrow Flood, **FL:** Flood.  
Light bulb data for low voltage products are based on manufacturers published information recalculated at approximately 12 volts for 12 volt systems and 23 volts for 24 volt systems.




# AMBIANCE®

## STEP, DECK, & BRICK LIGHTS


WET LOCATION 12 VOLT LIGHTING SYSTEM IS DESIGNED TO PROVIDE SAFE, FUNCTIONAL, EASY TO INSTALL ILLUMINATION. THE LOW PROFILE DESIGN ALLOWS IT TO FIT INTO VIRTUALLY ANY APPLICATION.

### RECESSED BRICK LIGHTS

- Die-cast aluminum brick lights fit into landscape walls and feature gasketed frosted glass lenses.
- (One) Access hole for 1/2" conduit on one end.
- Accommodates two 12v T5 wedge base, 18w Max. light bulbs.
- Black powdercoat finish.
- U.L., C.U.L. Listed for wet locations.




9241-12 Louver Trim



9242-12 Glass Trim

### SURFACE MOUNT DECK LIGHTS




#### 9329-12 Black Finish

Die-cast aluminum accent / deck light with black powdercoat finish and white polycarbonate diffuser. Includes one 9328-12 two light socket for use with 9373 105° Ambiance® Cable. Accommodates two 12V T3 1/4 wedge base, 3w Max. light bulbs. UL and C-UL listed for wet locations.

Select from the following available light bulbs:

- 9727 3w      9731 3w Xenon



#### 9396-12 Black Finish

Die-Cast Aluminum accent / deck light with black powdercoat finish. Socket adjusts up and down for desired effect. Complete with 36" 18/2 leads and connector for 12/2 cable. Use optional 9357 or 9399 gasket if desired. Accommodates one 12v T5 wedge base, 18w Max. light bulb.


### LINEAR LIGHTING

- Injection molded polycarbonate sockets.
- Corrosion resistant contacts pierce the specially designed cable with no tools required.
- Use with 9373 105° Ambiance® cable.
- Includes wire clip for easy installation.
- UL and C-UL listed for wet location.

#### 9328-12 Black Finish

Two Light Socket  
Minimum socket spacing 4" on center.  
Accommodates two, T3 1/4 wedge base, 3w Max. light bulbs. Select from the following available light bulbs:


- 9727 3w      9731 3w Xenon



#### 9429-12 Black Finish (shown) 9429-15 White Finish

One light socket. Minimum socket spacing 2" on center. Accommodates one, T3 1/4, wedge base 5w Max. light bulb. Select from the following available light bulbs:


- 9727 3w      9728 5w  
9731 3w Xenon      9729 5w  
9732 5w Xenon



See Ambiance® pages 347-365 for other components and fixtures that are U.L. Listed for wet location.

### RECESSED MOUNT DECK LIGHTS


- Aluminum trims with powdercoat finish.
- Complete with galvanized housing with powdercoat finish and 12v 18w T5 wedge base socket.



#### 9336-12 Black Finish (shown) 9336-40 Chestnut Finish

White glass lens trim. Select from the following available light bulbs:


- 9776 8w      9777 12w      9778 18w      9774 8w Xenon



#### 9337-12 Black Finish Louver Trim

Select from the following available light bulbs:

- 9776 8w      9777 12w      9778 18w      9774 8w Xenon



#### 9341-12 Black Finish 9341-40 Chestnut Finish (shown)

Louver / Step trim. Select from the following available light bulbs:

- 9776 8w      9777 12w      9778 18w      9774 18w Xenon



# AMBIANCE LAMPHOLDERS:

Minimum Spacing  
On Center

Item Number / Finishes

Dimensions

Lamp Data



9423-12 Black Finish    9423-15 White Finish



9427-12 Black Finish    9427-15 White Finish



9828-12 Black Finish    9828-15 White Finish



9428-12 Black Finish    9428-15 White Finish



9429-12 Black Finish    9429-15 White Finish










9432-15 White Finish



9433-15 White Finish



9498-12 Black Four Foot Kit    9498-15 White Four Foot Kit



### T3 Rigid Loop Xenon

9718-32	12V	5w	Clear	2"
9718-33	12V	5w	Frosted	2"
9719-32	12V	10w	Clear	4"
9719-33	12V	10w	Frosted	4"
9720-32	24V	5w	Clear	2"
9720-33	24V	5w	Frosted	2"
9721-32	24V	10w	Clear	4"
9721-33	24V	10w	Frosted	4"

### T3 1/4 Wedge Base

9727	12V	3w		4"
9731	12V	3w Xenon		4"
9728	12V	5w		4"
9729	12V	5w		4"
9732	12V	5w Xenon		4"

### T3 1/4 Wedge Base

9727	12V	3w		2"
9731	12V	3w Xenon		2"
9728	12V	5w		2"
9729	12V	5w		2"
9732	12V	5w Xenon		2"

### T5 Wedge Base

9776	12V	8w		6"
9777	12V	12w		6"
9778	12V	18w		6"
9774	12V	18w Xenon		6"
9775	24V	18w Xenon		6"

### T3 1/4 Wedge Base

9728	12V	5w	8 Included	4"
------	-----	----	------------	----

