

CUSTOM DECORATIVE
LUMINAIRE IDEA BOOK





WHAT SETS US APART

INNOVATION

We combine the latest energy efficient technology and design styles to create an extensive range of attractive and sustainable luminaires. We have over 5,000 products, including many high performance products that can't be found anywhere else. Our EcoTechnology solutions offer sustainable energy solutions that meet the qualitative needs of the visual environment with the least impact on the physical environment.



SUSTAINABILITY

At ConTech Lighting, our commitment to the environment is as important as our commitment to innovation, quality and our customers. We believe that lighting can be environmentally responsible and energy efficient, while providing high-quality performance and outstanding aesthetic design. EcoTechnology applies to our daily operation as well as to our products; from materials, manufacturing and transportation to the disposal process for our products and by-products.

QUALITY

We use the best components and manufacturing methods resulting in the highest quality fixtures. From cast housings and high performance reflectors, to the testing of each ballasted fixture before it ships, ConTech Lighting is defined by its quality. For consistency, we use only the most reliable LED chip makers including Cree, Nichia, Lumileds, Bridgelux and Sharp.

SERVICE

Our responsive, personalized customer focus, and market expertise represents an oasis of outstanding service in an industry that values it, but frequently doesn't receive it. We are here for you, live and in person, Monday through Friday 7:30am – 5:30pm CST.

PRODUCT AVAILABILITY AND SPEEDSHIP™

Most of our products are in stock and ready to ship. Our unique SpeedShip™ process helps us toward our goal of shipping 100% of placed orders within 48 hours; at no additional cost to you. Custom products may not be stocked.



MARKET EXPERTISE

Each market has its own unique lighting challenges. Designs can get tricky, having to verify every fixture, test every connector and make certain that every length of track is just right. We have an experienced staff of sales professionals to assist you with your projects from concept to completion.

At ConTech Lighting, we pride ourselves on supplying exactly what our clients need to create dynamic, successful projects, on time and within budget.

This decorative luminaire idea book illustrates ConTech's capabilities. Whether modifying an existing product or creating an entirely new luminaire, ConTech is uniquely qualified to handle all of your lighting needs. Our world class, in-house design team and manufacturing partners have years of experience bringing ideas to life. For more information on creating your own custom shade or luminaire, please contact your local ConTech representative or our Quotations Department.

To get started, please provide the following information:

Technical Specifications:

- Lamping
Lamp Type & Quantity
- Luminaire
Stem/Cord Length
Stem/Cord Color
Hardware/Canopy Finish
- Shade
Shape
Dimensions
Material
Color
Bottom Diffuser
Top Dust Cover

Project Specifications:

- Project Name
- Quantity
- Delivery Date
- Budget Per Fixture
- Special Requirements/Code Compliance

CUSTOM DECORATIVE LUMINAIRE IDEA BOOK • CONTECH LIGHTING



CYLINDER PENDANT 4



LINEN DRUM PENDANT 8



DOME PENDANT 11



ACRYLIC BOWL PENDANT 14



DRUM PENDANT 4



LINEN DRUM PENDANT 9



BASKET PENDANT 12




GLASS PENDANT 14



RECTANGULAR PENDANT 5



LINEN CYLINDER PENDANT 9



PERFORATED CYLINDER 13



FAT BEAT LIGHT PENDANT 15



WALL SCNCE 6



LOOSE FABRIC PENDANT 10



GLOBE PENDANT 13



TALL BEAT LIGHT PENDANT 15



FLOOR LAMP 6



CONCRETE CONE PENDANT 11



PATTERNED DRUM PENDANT 14



WIDE BEAT LIGHT PENDANT 15



CYLINDER PENDANT

Low profile canopy with 8' fabric wrapped SVT cord. Antique bronze finish. Shade available in ivory burlap with a chocolate fabric wrapped cord, woodgrain with a rust fabric wrapped cord, and dark burlap with an olive green fabric wrapped cord. Custom finishes available. One (1) E26 base socket, 18W max. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size	Shade	– Finish
RLM71CYA - Single lamp cylinder pendant, 6" Dia. x 20" H	1 - Ivory Burlap	AB - Antique Bronze
RLM72CYB - Dual lamp cylinder pendant, 10" Dia. x 36" H	2 - Woodgrain	
	3 - Dark Burlap	
		<p>woodgrain/rust ivory burlap/chocolate dark burlap/olive green</p>



DRUM PENDANT




Low profile canopy with 8' fabric wrapped SVT cord. Antique bronze finish. Shade available in ivory burlap with a chocolate fabric wrapped cord, woodgrain with a rust fabric wrapped cord, and dark burlap with an olive green fabric wrapped cord. Custom finishes available. One (1) or three (3) E26 base sockets, 18W max. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size	Shade	– Finish
RLM71DRD - Single lamp drum pendant, 10" Dia. x 12" H	1 - Ivory Burlap	AB - Antique Bronze
RLM71DRA - Single lamp drum pendant, 15" Dia. x 9" H	2 - Woodgrain	
RLM73DRB - Three lamp drum pendant, 24" Dia. x 9" H	3 - Dark Burlap	
RLM73DRE - Three lamp drum pendant, 36" Dia. x 12" H		
		<p>woodgrain/rust ivory burlap/chocolate dark burlap/olive green</p>



Low profile canopies with 8' fabric wrapped SVT cord. Antique bronze finish. Shade available in ivory burlap with a chocolate fabric wrapped cord, woodgrain with a rust fabric wrapped cord, and dark burlap with an olive green fabric wrapped cord. Custom finishes available. Four (4) E26 base sockets, 18W max. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

RECTANGULAR PENDANT

Size	Shade	– Finish
RLM74SQA - Four lamp rectangular pendant, 39"L x 10"W x 12"H	1 - Ivory Burlap 2 - Woodgrain 3 - Dark Burlap	AB - Antique Bronze  woodgrain/rust  ivory burlap/ chocolate  dark burlap/ olive green



WALL SCONCE

Low profile depth meets the requirements of ADA. Includes top and bottom acrylic diffusers. Custom finishes available. One (1) E26 base socket, 18W max. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size


WS71A - Single lamp wall sconce,
15" H x 4-1/2" W x 3-1/2" D

Shade

- 1 - Ivory Burlap
- 2 - Woodgrain
- 3 - Dark Burlap



woodgrain



ivory burlap



dark burlap



FLOOR LAMP

63" (5'3") floor lamp finished in antique bronze with 6ft cord and plug. Includes a top clear lens and bottom cream acrylic diffuser. Shade available in ivory burlap, woodgrain, and dark burlap. Antique Bronze hardware. Custom finishes available. One (1) E26 base socket, 18W max. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size

FL71DRA - Single lamp floor lamp,
15" Dia. x 9" H

Shade


- 1 - Ivory Burlap
- 2 - Woodgrain
- 3 - Dark Burlap

- Finish

AB - Antique Bronze



woodgrain



ivory burlap



dark burlap





LINEN DRUM PENDANT

Decorative fabric shade pendant with clear flexible cord and 6" brushed nickel decorative sleeve at the base of the fixture. Includes a 16" diameter x 16" tall white linen fabric drum shade with a bottom acrylic diffuser. Custom fabrics available. Canopy (4-3/4" dia. x 1/2" tall) and two-piece stem have a brushed nickel finish. Three (3) E26 Base sockets. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size

RLM603 - 10' Clear cable with canopy
RLM60315 - 15' Clear cable with canopy
RLM60320 - 20' Clear cable with canopy

– Finish

N - Nickel

Shade

DFS116-BR - 16" Dia. x 16" H White linen fabric



white linen

Decorative shade pendant adds a rich elegant feel to any interior space. Washable linen fabric. Low profile canopy and 6" rigid stem in an antique bronze finish. Includes top and bottom acrylic diffuser. Custom finishes available. Four (4) E26 Base sockets, 15W Max. Label. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.



LINEN DRUM PENDANT

Size	Finish
RLM294DRB1 - Washable fabric drum pendant, 36" Dia. x 18" H	AB - Antique Bronze
RLM594DRD1 - Washable fabric drum pendant, 36" Dia. x 12" H	



linen



LINEN DRUM PENDANT

Decorative shade pendant adds a rich elegant feel to any interior space. Washable linen fabric. Low profile canopy in an antique bronze finish. 10' Black SVT cord. Larger shades include aircraft cable supports. Includes top and bottom acrylic diffuser. Custom finishes available. Two (2) or four (4) E26 Base sockets, 15W Max. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size	Finish
RLM592DRB1 - Washable fabric drum pendant, (2) Socket, 24" Dia. x 12" H	AB - Antique Bronze
RLM592DRC1 - Washable fabric drum pendant, (2) Socket, 24" Dia. x 21" H	
RLM594DRE1 - Washable fabric drum pendant, (4) Socket, 36" Dia. x 30" H	
RLM594DRF1 - Washable fabric drum pendant, (4) Socket, 48" Dia. x 18" H	



linen



Decorative drum pendant features 24" diameter loose natural fabric shade with opaque acrylic dust cover. Includes antique bronze finish canopy, 10' black SVT cord wrapped in natural jute and one (1) energy efficient, 11W A21 LED E26 base lamp with 360° distribution. Color management system maintains color consistency over time and temperature. Correlated Color Temperature of 2700K, Color Rendering Index of 80. Lumen output = 1100 (100 Lumens per Watt). cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

LOOSE FABRIC DRUM PENDANT

Size

RLM71DRC4ML11-36027K - Drum Pendant, 24" Dia., with (1) Megaman A21 Lamp

– Canopy Finish

AB - Antique Bronze



natural gauze fabric

Decorative 6-1/4" diameter cone pendant in two-tone concrete finish variations. No two pendants are the same. Includes brushed nickel finish canopy, 10' black SJT cord and one (1) energy efficient, 11W A21 LED lamp with 360° distribution. Color management system maintains color consistency over time and temperature. Correlated Color Temperature of 2700K, Color Rendering Index of 80. Lumen output = 1100 (100 Lumens per Watt). (1) E26 base socket, 40W Max., 120V. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.




CONCRETE CONE PENDANT

Size

RLM71CNA8ML11-36027K - Concrete Cone Pendant, 6-1/4" Dia., with (1) Megaman A21 Lamp

– Canopy Finish

BN - Brushed Nickel



concrete/
brushed nickel

Decorative 11" diameter off-white metal dome pendant adds a rustic feel to any space. Dome shade is accented with wood mount and metal bracket. Includes antique bronze finish canopy, 10' brown, fabric covered cord with chain and one (1) energy efficient, 11W A21 LED lamp with 360° distribution. Color management system maintains color consistency over time and temperature. Correlated Color Temperature of 2700K, Color Rendering Index of 80. Lumen output = 1100 (100 Lumens per Watt). (1) E26 base socket, 40W Max., 120V. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.



DOME PENDANT

Size

RLM71DMA9ML11-36027K - Dome Pendant, 11" Dia., with (1) Megaman A21 Lamp

– Finish

WM - Wood and Metal



off-white metal



Decorative 22" diameter basket pendant adds a rustic exotic feel to any space. Woven rattan wicker shade features three (3) staggered suspended lamp positions to add interest and visual appeal. Includes antique bronze finish canopy, 10' brown, fabric covered cord with aircraft cable and three (3) energy efficient, 3W ST19 Filament LED lamps. Color management system maintains color consistency over time and temperature. Correlated Color Temperature of 2200K, Color Rendering Index of 80. Lumen output = 210 (70 Lumens per Watt). Three (3) E26 base sockets, 25W Max. each, 120V cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

BASKET PENDANT

Size


RLM73BKA8ML02-36022K - Basket Pendant, 22" Dia.,
with (3) Megaman ST19 Lamps

– Finish

WK - Wicker




natural wicker



Perforated metal shade with satin copper tone painted finish. Includes interior side diffuser and bottom diffuser. 8' UL Listed black SVT cord. Three (3) aircraft cable supports. One (1) E26 base socket. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

PERFORATED CYLINDER PENDANT

Size	Finish
RLM31CY - Perforated cylinder pendant, 9" Dia. x 18" H	CO - Copper



copper

Decorative globe pendant in natural wood adds warmth and style to any space. Premium plywood construction with 10 ft (120") brown fabric covered cord, monopoint wood canopy, and one (1) energy efficient, 3W G25 filament LED lamp, tinted glass, 360° distribution. Correlated Color Temperature of 2200K, Color Rendering Index of 80. Lumen output of 210 (70Lm/W). 120V E26 Base. If choosing incandescent lamps, 12" Pendant: One (1) Lamp with E26 Base, 40W Max.; 18" Pendant: One (1) Lamp with E26 Base, 60W Max. cCSAus Listed. NRTL Certified to UL Standards. Indoor use only.



GLOBE PENDANT

Size	Finish
RLM71GBA7MLG2-36022K - Globe Pendant, 12" Dia., with (1) Megaman G25 Filament Lamp	NW - Natural Wood
RLM71GGB7MLG2-36022K - Globe Pendant, 18" Dia., with (1) Megaman G25 Filament Lamp	



natural wood



PATTERNED DRUM PENDANT

The patterned fabric shade features a removable bottom diffuser. Custom fabrics available. Low profile canopy with 10' cord. Two (2) or three (3) E26 base sockets, 60W Max. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size	Finish
RLM142DRA1 - Two Socket Patterned Drum Pendant 13-1/2" Dia. x 10" H	NK - Nickel
RLM143DRB1 - Three Socket Patterned Drum Pendant 20" Dia. x 5-1/2" H	



ACRYLIC BOWL PENDANT

Decorative 36" diameter opal acrylic bowl pendant adds an elegant feel to any interior space. Brushed nickel canopy with 29" stem. Additional 8" stem and 12" stem also included. May only use one (1) stem per fixture. Four (4) E26 base sockets, 60W Max. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size	Finish
RLM274BLA1 - Acrylic Bowl Pendant	NK - Nickel



GLASS PENDANT

Decorative handcrafted glass shade (3-1/2" Dia. x 11-1/4" H) pendant with clear flexible cord and 5" brushed nickel decorative sleeve at the base of the fixture. Canopy (4-3/4" dia. x 1/2" tall) and fixture base with decorative sleeve have a brushed nickel finish. One (1) E26 base socket. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size	Finish
RLMGC50 - 10' Pendant	NK - Nickel
RLMGC5015 - 15' Pendant	

Shade	
MLA300-A - Amber Glass Cloud Shade 3-1/2" Dia. x 11-1/4" H	



fat



tall



wide

Spun aluminum shade with satin black exterior and satin copper tone hammered texture interior. 8' UL Listed black SVT cord. One (1) E26 base socket. Beat Light "FAT" is 9-1/2" diameter, Beat Light "TALL" is 7" in diameter, and Beat Light "WIDE" is 14" in diameter. cETLus Listed. NRTL Certified to UL Standards. Indoor use only.

Size — Finish

- RLM31F** - Beat Light "FAT" 9-1/2" Diameter **B** - Black
- RLM31T** - Beat Light "TALL" 7" Diameter
- RLM31W** - Beat Light "WIDE" 14" Diameter



satin black/hammered copper

BEAT LIGHTS



CONTECH[®]
LIGHTING | a **LEVITON**[®]
company

725 Landwehr Road
Northbrook, Illinois 60062
www.contechlighting.com
Phone: 847.559.5500
Fax: 847.559.5505

 **ecoTECHNOLOGY**
sustainable energy solutions



All specifications subject to change without notice.

LITCUS16