





12 VOLT SERIES

www.coronalighting.com

CORONA LANDSCAPE LIGHTING



12 VOLT SERIES

CL-650B • Cast Brass • T3 Halogen Lamp, 20W Max • Finish: AB	CL-651B • Cast Brass, 18" Stem • S. C. Bayonet Lamp, 27W Max • Finish: AB • 12" and 24" Stems Available	CL-652B • Cast Brass, 18" Stem • S. C. Bayonet Lamp, 27W Max • Finish: AB • 12" and 24" Stems Available	CL-654B • Cast Brass, 18" Stem • S. C. Bayonet Lamp, 27W Max • Finish: AB • 12" and 24" Stems Available	CL-714B • Solid Brass • S. C. Bayonet Lamp, 27W Max • Finish: AB	CL-718B • Cast Brass • T3 Halogen Lamp, 20W Max • Finish: AB	CL-719B • Cast Brass • S. C. Bayonet Lamp, 27W Max • Finish: AB	CL-722B • Solid Brass, 24" Riser • MR-16 Lamp, 35W Max • Finish: AB	CL-730B • Solid Brass, 24" Riser • MR-8 Lamp, 20W Max • Finish: AB, GM	CL-732B-T • Solid Brass, 24" Riser • MR-16 Lamp, 2x50W Max • Finish: AB, GM	CL-647C • Solid Copper • T3 Lamp, 20W Max • Finish: RC	CL-648C • Solid Copper • T3 Lamp, 20W Max • Finish: RC	CL-740C • Solid Copper, 24" Riser • MR-16 Lamp, 35W Max • Finish: RC	CL-602 • Cast Aluminum • T3/T4 Lamp, 50W Max • Finish: BK, GR, VG
CL-603 • Cast Aluminum • T3/T4 Lamp, 50W Max • Finish: BK, GR, VG	CL-604 • Cast Aluminum • T3/T4 Lamp, 50W Max • Finish: BK, GR, VG	CL-605 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, VG	CL-616 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, BZ, GR, RT, VG	CL-617 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, GR, VG	CL-620 • Cast Aluminum • T3 Lamp, 35W Max • Finish: BK, BZ	CL-624 • Cast Aluminum • T3 Lamp, 35W Max • Finish: BK, BZ, VG	CL-625 • Cast Aluminum • T3 Lamp, 35W Max • Finish: BK, BZ, VG	CL-630 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, VG	CL-631 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, VG	CL-632 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, VG	CL-635 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, VG	CL-636 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, VG	CL-637 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, VG
CL-638 • Cast Aluminum • T3 Lamp, 20W max. • Finish: BK, BZ • 12" Stems Available	CL-639 • Cast Aluminum • T3 Lamp, 20W max. • Finish: BK, BZ • 12" Stems Available	CL-708 • Cast Aluminum • S. C. Bayonet Lamp, 27W Max • Finish: BK, GR, VG	CL-366 • Alum, Brass, Copp Face Plates • S. C. Bayonet, 2 x 27W Max • Finish: BK, BZ, RT, WH, AB, OC, SI, RC	CL-367 • Alum, Brass, Copp Face Plates • S. C. Bayonet, 2 x 27W Max • Finish: BK, BZ, RT, WH, AB, SI, RC	CL-368B • Cast Brass • S. C. Bayonet Lamp 2x27W Max • Finish: AB, GM	CL-369B • Cast Brass • S. C. Bayonet Lamp 2x27W Max • Finish: AB, GM	CL-370B • Cast Brass • S. C. Bayonet Lamp 2x27W Max • Finish: AB, GM	CL-373B • Cast Brass Face Plate • S. C. Bayonet Lamp 2x27W Max • Finish: AB	CL-374B • Cast Brass Face Plate • S. C. Bayonet Lamp 2x27W Max • Finish: AB	CL-363B • Cast Brass • S. C. Bayonet Lamp, 27W Max • Finish: AB, GM	CL-364B • Cast Brass • S. C. Bayonet Lamp, 27W Max • Finish: AB, GM	CL-365B • Cast Brass • S. C. Bayonet Lamp, 27W Max • Finish: AB, GM	CL-371B • Cast Brass Face Plate • S. C. Bayonet Lamp 27W Max • Finish: AB
CL-372B • Cast Brass Face Plate • S. C. Bayonet Lamp 27W Max • Finish: AB	CL-360 • Alum, Brass, Copp Face Plates • S. C. Bayonet Lamp, 27W Max • Finish: BK, BZ, RT, WH, AB, OC, SI, RC	CL-361 • Alum, Brass, Copp Face Plates • S. C. Bayonet Lamp, 27W Max • Finish: BK, BZ, RT, WH, AB, OC, SI, RC	CL-362 • Alum, Brass, Copp Face Plates • S. C. Bayonet Lamp, 27W Max • Finish: BK, BZ, RT, WH, AB, OC, SI, RC	CL-346B • Cast Brass Face Plate • MR-16 Lamp, 50W Max • Finish: AB, GM • Adjustable Socket	CL-347B • Cast Brass Face Plate • MR-16 Lamp, 50W Max • Finish: AB, GM • Adjustable Socket	CL-348B • Cast Brass Face Plate • MR-16 Lamp, 50W Max • Finish: AB, GM • Adjustable Socket	CL-349B • Cast Brass Face Plate • MR-16 Lamp, 50W Max • Finish: AB, GM • Adjustable Socket	CL-375 • Composite • MR-16 Lamp, 50W Max • Finish: BK, BZ • Adjustable Socket	CL-376 • Composite • MR-16 Lamp, 50W Max • Finish: BK, BZ • Adjustable Socket	CL-377 • Composite • MR-16 Lamp, 50W Max • Finish: BK, BZ • Adjustable Socket	CL-378 • Composite • MR-16 Lamp, 50W Max • Finish: BK, BZ • Adjustable Socket	CL-342B • Cast Brass • T5 Wedge Lamp, 18W Max • Finish: AB, BR, GM, SI	CL-343B • Cast Brass • T5 Wedge Lamp, 18W Max • Finish: AB, BR, GM, SI
CL-308 • Cast Brass • MR-16 Lamp, 50W Max • Finish: AB, BR	CL-311-BR • Solid Brass • MR-16 Lamp, 50W Max • Finish: BR	CL-312-SS • Solid Stainless Steel • MR-16 Lamp, 50W Max • Finish: SS, 316 Marine Grade	CL-313-BR • Cast Brass • PAR-36 Lamp, 50W Max • Finish: BR	CL-320-NM • Composite • T3 Lamp, 35W Max • Finish: BK	CL-321-NM • Polycarbonate • T5 Wedge Lamp, 18W Max • Finish: BK	CL-310 • Cast Aluminum • MR-16 Lamp, 50W Max • Finish: BK	CL-398-BZ • Cast Aluminum, 7 inch • Integrated 1.5W LED Module • Finish: BZ	CL-399-BZ • Cast Aluminum, 13 inch • Integrated 2.5W LED Module • Finish: BZ	CL-384-RC • Solid Copper • S. C. Bayonet Lamp, 27W Max • Finish: RC	CL-385 • Cast Aluminum, 5.25" H • MR-11 Lamp, 35W Max • Finish: BK	CL-387 • Cast Aluminum, 8.25" H • MR-11 Lamp, 35W Max • Finish: BK	CL-389 • Cast Aluminum, 11.25" H • MR-11 Lamp, 35W Max • Finish: BK	CL-391 • Cast Aluminum, 14.25" H • MR-11 Lamp, 35W Max • Finish: BK

LIMITED WARRANTIES

- Limited lifetime warranty on: Brass, Copper and Stainless Steel Fixtures.
- Limited ten years warranty on composite fixtures.
- Limited one year warranty on aluminum fixtures.
- Limited ten years warranty on transformer's coils. Lifetime warranty on stainless steel enclosures.
- Limited five years warranty on LED lamps.
- Limited ten years warranty on integrated LED fixtures.

FINISH CHART

NATURAL TONING			
NATURAL			
PLATED			
POWDER COATED			

AB, GM & OC FINISHES ON SOME BRASS PRODUCTS ONLY.

CL-352-SS • Solid Stainless Steel • T5 Wedge Lamp, 18W Max • Finish: SS	CL-353-SS • Solid Stainless Steel • T5 Wedge Lamp, 18W Max • Finish: SS	CL-352 • Cast Aluminum • T5 Wedge Lamp, 18W Max • Finish: BK, BZ, WH	CL-353 • Cast Aluminum • T5 Wedge Lamp, 18W Max • Finish: BK, BZ, WH	CL-350 • Steel Face Plates • S. C. Bayonet Lamp, 18W Max • Finish: BK, BZ, WH, CU, PB, SI	CL-351 • Steel Face Plates • S. C. Bayonet Lamp, 18W Max • Finish: BK, BZ, WH, PB, SI	CL-307 • Cast Brass • MR-16 Lamp, 50W Max • Finish: AB, BR
CL-801-D • Cast Aluminum • T3 Lamp, 35W Max • Finish: BK	CL-802-D • Cast Aluminum • MR-11 Lamp, 35W Max • Finish: BK	CL-803-D • Cast Aluminum • MR-16 Lamp, 50W Max • Finish: BK	CL-806-D • Solid Brass, Chrome Plated • T3/5C Lamp, 20W Max • Finish: SI	CL-807-D • Cast Aluminum • MR-16 Lamp, 50W Max • Finish: BK, SI	T-ST300-TP • WATTAGE: 300,600,900W • MULTITAP: 12,13,14V • ENCLOSURE: Stainless Steel	LED LAMPS Please visit coronalighting.com for available LED LAMPS

CORONA Lighting
1633 Staunton Ave.
Los Angeles, California 90021

TEL: 800-727-9262 • 213-747-4500
FAX: 800-727-9957 • 213-747-3234
E-MAIL: sales@coronalighting.com
WEBSITE: www.coronalighting.com

© 2016 Corona Lighting Inc. - Reproduction of information, photographs and artwork used in this brochure without the written consent of Corona Lighting Inc. is strictly prohibited. Corona Lighting reserves the right to make any changes in the design and construction of the products listed in this brochure without notice. CL-1616 \$12.00