




PROJECT	TYPE
CATALOG NUMBER	

PRODUCT DESCRIPTION

A high output, 80+ CRI flexible LED linear ribbon that features a magnetic back for mounting to retail shelving, metal cabinets, commercial workspaces, grocery store shelving, or where magnetic / portable mounting is ideal. 3000K and 4200K. Available in a high output, high efficiency 16'-4" reel.

Custom cuts available - consult factory.



FEATURES

- 12VDC operation. Requires remote driver
- Dry location
- Dimmable
- Magnetic mounting strip on back
- Available with connectors (see below)
- 5 year warranty
- High output
- Available in 16'-4" reels

ELECTRICAL

- 12VDC
- 2.2W per foot
- 19 LED's per foot
- 36W per reel
- 50,000 hour LED life

OPTICS

- 3000K, 4200K
- Up to 222 lumens per foot
- 80+ CRI

LABEL

- ETL
- American Lighting Association

POWER SUPPLIES

- For a complete list of applicable 12VDC power supplies, please see our website at gmlighting.net.

MOUNTING CHANNELS

- GM Lighting manufactures lensed architectural mounting channels in a wide array of configurations. Please see our website at gmlighting.net.

PHOTOMETRICS

- Please see our website at gmlighting.net.

ORDERING INFORMATION

Catalog No.	Length	Output	LED Wattage	Lumens per Foot	Color Temp.*
MTR300-30	16'-4" reel	High	2.2W /ft.	195	3000K
MTR300-42	16'-4" reel	High	2.2W /ft.	222	4200K

16'-4" reel includes 24" of lead and (3) ribbon to power supply connectors. * Kelvin temperature (color) ±200K

SURE-TITE CONNECTORS

Catalog No.	Description
STC-1	RIBBON TO RIBBON CONNECTOR
STLK-60	RIBBON TO RIBBON CONNECTOR - ONE END WITH 60" 18 AWG LEAD AND EXTRA CONNECTOR. ADJUSTABLE TO ANY LENGTH DESIRED AND CUTTABLE IN FIELD.
STW-60	RIBBON TO POWER SUPPLY CONNECTOR - ONE END WITH 60" 18 AWG LEAD. ADJUSTABLE TO ANY LENGTH DESIRED AND CUTTABLE IN FIELD.

NOTE: STLK-60 and STW-60 are adjustable to any length desired, and cuttable in the field.