

Bay Lighter LED

150 Watt LED

Linear Series LED
FLUORESCENT REPLACEMENT



RECOMMENDED

ILH150LED4LS w/ GLARE FREE LENS

LUMENS: 17,410
WATTS: 150
LUMENS PER WATT: 113
CRI: 82
CCT: 4500K
DIMMING: 10-100%

ILH150LED4S No LENS

LUMENS: 18,590
WATTS: 150
LUMENS PER WATT: 120
CRI: 82
CCT: 4500K
DIMMING: 10-100%

Ordering Information


CATALOG #	DESCRIPTION	VOLTS
ILH150LED4LS	150W LED High Bay w/ Glare Free Lens	120-277
ILH150LED4S	150W LED High Bay - No Lens	120-277

Options

SUFFIX #	DESCRIPTION
3C*	3' Cord (No Plug)
3T*	3' 120V Cord & Plug
3E*	3' 208V Cord & Plug
3F*	3' 240V Cord & Plug
3S*	3' 277V Cord & Plug
F	Inline Fusing
EB	Emergency Back-Up
M	Motion Sensor
P	Pendant Mount
W	Wireguard
IC	Integrated Control**
4	480V Driver

Dimensions and Specifications

Overall Height: 3.30" (8.38 cm)
Overall Width: 7.17" (18.21 cm)
Length: 46.06" (116.99 cm)




**Tool-less
Snap On Lens**



Hanging Hooks Included

For more information including photometrics, Lighting Facts and DLC visit www.atlasled.com



*Also Available in 6', 10' and 20' lengths
**End Panel Mounted

**200,000+
HOURS**



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components



Features



Easy Access Driver Compartment



High Brightness LEDs



Quick Wire Access Panel

Superior Thermal Management

- Cooler Operating Temperatures
- Brighter, Whiter Light
- Longer Life 200,000+ Hours



Tool-less Snap On Lens

High Transmission Lens




- Protects LEDs
- No Glare - 91% Efficiency
- Provides Improved Visual Comfort
- High Impact with Scratch Resistant Surface
- Provides Wider, Smoother & Uniform Light Output



Accessories

CATALOG #	DESCRIPTION
CH36	Chain Set
CH36HFC	Chain Set w/Hammer-On Flange Clip
CA36	Cable Set
MS360	360° Motion Sensor
WG33	Wireguard

LED COMPARISON CHART

	400W METAL HALIDE	4 LAMP T5 FLUORESCENT	ATLAS 150W LED
HIGH BAY FIXTURES	 458 INPUT WATTS	 238 INPUT WATTS	 150 INPUT WATTS
TOTAL YEARLY COST INC. MAINT.	\$230	\$126	\$66
TOTAL YEARLY SAVINGS	-	\$104	\$164
POTENTIAL ONE TIME REBATE	\$0	\$50	\$170
TOTAL FIRST YEAR SAVINGS	-	\$154	\$334
DOLLAR RETURN IN 3 YEARS	-	\$362	\$662

Based on 12 hours per day | \$.10/kWh Utility Rates & Rebates Vary by Location

AMBIENT TEMPERATURE FIXTURE RATING

PART #	DESCRIPTION	12" CHAIN MOUNT
ILH150LED4LS	150W LED High Bay w/ Glare Free Lens	50°C (122°F)
ILH150LED4S	150W LED High Bay - No Lens	50°C (122°F)

48% ANNUAL SAVINGS*

Less Than 3 Year Payback*

*Based on premium paid - LED vs Fluorescent

