


Pass & Seymour



6207
shown with neoprene
sealing mat


Straight Blade Receptacles Dust & Moisture Resistant & Clock Hanger Receptacles

15 & 20A, 125V

Features – Dust & Moisture Resistant

- Duplex receptacle has face backed by neoprene gasket which is slit to provide wiping action on plug blades and to provide positive closure when not in use.
- Cellular neoprene sealing mat fits under wall plate.

Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
Dust & Moisture Resistant						
6207	15 125	Duplex, Dust and Moisture Resistant, Gray	5-15R	•	•	•
CR6207	15 125	Duplex, Corrosion, Dust and Moisture Resistant, Yellow	5-15R	•	•	•
6307	20 125	Duplex, Dust and Moisture Resistant, Gray	5-20R	•	•	•
6307RED	20 125	Duplex, Dust and Moisture Resistant, Red	5-20R	•	•	•
CR6307	20 125	Duplex, Corrosion, Dust and Moisture Resistant, Yellow	5-20R	•	•	•



S3713I

Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
Clock Hangers						
S3713I	15 125	Recessed Receptacle with Ivory Smooth Wall Plate	5-15R	•	•	•
S3713W	15 125	Recessed Receptacle with White Smooth Wall Plate	5-15R	•	•	•
S3713BK	15 125	Recessed Receptacle with Black Smooth Wall Plate	5-15R	•	•	•
S3713LA	15 125	Recessed Receptacle with Light Almond Smooth Wall Plate	5-15R	•	•	•
S3733SS	15 125	Recessed Receptacle with Stainless Steel Wall Plate	5-15R	•	•	•
S3733	15 125	Recessed Receptacle with Brass Wall Plate	5-15R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R