

LSER - Serrano® LED Architectural Luminaire



LED



10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

LSER				G			U	
MODEL		COLOR TEMP		CEILING TYPE		SHIELDING		OPTIONS
LSER Serrano® LED Architectural Luminaire		35 3500K 40 4000K		G Grid ¹		C Contour		C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack, 1400 Lumen ²
SIZE		LUMEN OUTPUT				DRIVER	VOLTAGE	
22 2' x 2'		LW Low Watt				E Fixed Output	U 120V-277V	
24 2' x 4'		ML Medium Lumen HL High Lumen VL Very High Lumen				ED 0-10V Dimming		

¹ For drywall, order G with Flange Kit Accessory.

² For compatibility with Dual-Life LiteGear® inverters in lieu of installed Battery Pack, contact Hubbell Lighting Representative.

FALL
2014



LTRE - Transition® Enclosed LED High Efficiency Architectural Lensed



LED




10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

LTRE				G		RFA		U	
MODEL		COLOR TEMP		CEILING TYPE		SHIELDING		OPTIONS	
LTRE Transition® Enclosed LED High Efficiency Architectural Lensed		35 3500K 40 4000K		G Grid Lay-in ¹		RFA Ribbed Frosted Acrylic		C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack, 1400 Lumen ²	
SIZE		LUMEN OUTPUT				DRIVER	VOLTAGE		
22 2' x 2'		LW Low Watt (2x4 only)				E Fixed Output	U 120V-277V		
24 2' x 4'		ML Medium Lumen HL High Lumen (2x2 only) VL Very High Lumen (2x2 only)				ED 0-10V Dimming			

¹ For drywall, order G with Flange Kit Accessory.

² For compatibility with Dual-Life LiteGear® inverters in lieu of installed Battery Pack, contact Hubbell Lighting Representative.



LJT - LED Lensed Troffer



Regional Distribution Center Stock List



Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93048975	LJT22-35HLG-FSA12-EDU	078531121228	LED 2X2 Lensed Troffer, 3500K, 3800 Lumens, 0-10V Dimming Driver	•	•	•	•	20.0	36	
93053880	LJT22-40HLG-FSA12-EDU	078531123185	LED 2X2 Lensed Troffer, 4000K, 3800 Lumens, 0-10V Dimming Driver		•		•	20.0	36	
93048976	LJT24-35MLG-FSA12-EDU	078531121235	LED 2X4 Lensed Troffer, 3500K, 4800 Lumens, 0-10V Dimming Driver	•	•	•	•	20.0	26	
93053881	LJT24-40MLG-FSA12-EDU	078531123192	LED 2X4 Lensed Troffer, 4000K, 4800 Lumens, 0-10V Dimming Driver		•		•	20.0	26	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

LJT		-			G	-	FS		-		U	-	
MODEL LJT LED Lensed Troffer	COLOR TEMP 35 3500K 40 4000K		CEILING TYPE G Grid ¹		SHIELDING A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal						OPTIONS C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack Installed, 1400 Lumen ²		
SIZE 22 2' × 2' 24 2' × 4'	LUMEN OUTPUT LW Low Watt (2x4 only) ML Medium Lumen HL High Lumen VL Very High Lumen XL Extra High Lumen (2x4 only)		DOOR FS White Flush Steel		DRIVER E Fixed Output ED 0-10V Dimming		VOLTAGE U 120V-277V						

¹ For hard ceilings use flange kit accessory.² For compatibility with Dual-Lite LiteGear[®] inverters in lieu of EL Battery Pack, contact Hubbell Lighting Representative.


LAW - LED Wraparound



Regional Distribution Center Stock List



Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93058502	LAW2-35LW-EDU	078531124229	LED 2' Wrap, 3500K, 2250 Lumens, 0-10V Dimming Driver		•			8.0	110	
93058503	LAW2-40LW-EDU	078531124236	LED 2' Wrap, 4000K, 2250 Lumens, 0-10V Dimming Driver		•		•	8.0	110	
93056100	LAW4-40ML-EDU	078531123840	LED 4' Wrap, 4000K, 4500 Lumens, 0-10V Dimming Driver		•		•	14.0	55	
93055614	LAW4-35ML-EDU	078531123635	LED 4' Wrap, 3500K, 4500 Lumens, 0-10V Dimming Driver		•			14.0	55	



LLHV - LED Lensed Troffers



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93052470	LLHV4-40M-WST-EDU	078531024000	LED 4'; 120-277V, 2 Drivers		•	•		20.0	30	
93052471	LLHV4-40H-WST-EDU	078531024017	LED 4'; 120-277V, 3 Drivers		•	•		20.0	24	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

LLHV	4	-		-		ST	-		U	-	
MODEL LLHV VersaBay® LED High Bay	COLOR TEMP 35 3500K 40 4000K		REFLECTOR N Narrow Distribution W Wide Distribution							OPTIONS C6TL15_ 6' Cord and Twist-Lock™ Plug 15A (Add Voltage: 1=120, 2=277) C6TL20_ 6' Cord and Twist-Lock™ Plug 20A (Add Voltage: 1=120, 2=277) C6P151 6' Cord and Straight Blade Plug 15A, 120V ELL14 Emergency Battery Pack Installed, 1400 Lumen¹	
SIZE 4 4'	LUMEN OUTPUT M Medium Lumen H High Lumen		UPLIGHT ST Solid Top (no uplight)		DRIVER E Fixed Output ED 0-10V Dimming		VOLTAGE U 120V-277V				

¹ ELL14 reduces max ambient temperature to 40°C. If combined with lens max is 30°C.



LCS - LED Striplight



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93052240	LCS4-35ML-EDU	078531122294	LED 4' Striplight, 3500K, 5000 Lumens, 0-10V Dimming Driver		•			9.0	66	
93056105	LCS4-40ML-EDU	078531123888	LED 4' Striplight, 4000K, 5000 Lumens, 0-10V Dimming Driver		•		•	9.0	66	



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93055613	LXEM4-35ML-RFA-EU	078531123666	LED 4'Vapor Tight, 3500K, 4900 Lumens		●			14.0	30	



SER - Serrano® Recessed Architectural Luminaire



Order Limit Per Fixture Selection: 100

SER			G	C					
MODEL	NO. OF LAMPS	CEILING TYPE			BALLAST	VOLTAGE	OPTIONS		
SER Serrano® Recessed Architectural Luminaire	1 One 2 Two 3 Three	G Grid			E Electronic T8, 0.88 Ballast Factor, Instant Start EP Electronic T5, T5HO, 1.0 Ballast Factor or T8, 0.88 Ballast Factor, Programmed Start ETT Electronic Twin Tube, Instant Start EPTT Electronic Twin Tube, Programmed Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8, Programmed Start	U 120V-277V 347 347V (T5 and T8 only)	EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex		
SIZE	LAMP TYPE	SHIELDING							
14 1' x 4'	17 2', T8: 17 Watt	C Contour							
22 2' x 2'	24 2', T5HO: 24 Watt								
24 2' x 4'	28 4', T5: 28 Watt 32 4', T8 ¹	REFLECTOR P Performance F Full							
	40TT Twin Tube Compact, 2G11 Base: 40 Watt								
						LAMPS			
						F830 30K 78+CRI T8 Lamps Installed F835 35K 78+CRI T8 Lamps Installed F841 41K 78+CRI T8 Lamps Installed FO830 30K 82CRI 32W T8 Lamps Installed FO835 35K 82CRI 32W T8 Lamps Installed FO841 41K 82CRI 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed			

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



EPC - Full Distribution Luminaire



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
EPC000007	EPC22-224G-SH-EPU-F5835	078531015848	2x2 24W T5HO 2-Lamp With 1.0 BF Ballast 24W T5HO Lamp, and Shield Lens			•		25.0	44	
EPC000031	EPC24-228G-SH-EPU-F5835	078531121266	2x4 28W T5 2-Lamp With 1.00 BF Ballast 28W T5 Lamp, and Shield Lens	•	•	•	•	25.0	22	
EPC000032	EPC24-232G-SH-EU-F0835	078531121273	2x4 32W T8 2-Lamp With 0.88 BF Ballast 80 CRI 32W T8 Lamp, and Shield Lens		•		•	25.0	22	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

EPC	24	-	2		G	-	SH	-		-		-	
MODEL	NO. OF LAMPS		CEILING TYPE	SHIELDING		VOLTAGE		OPTIONS					
EPC epec® Full Distribution Luminaire	2 Two		G Grid	SH Shield Profile		U 120V-277V 347 347V (E and EP only)		C388 3-Wire Flex EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8					
SIZE	LAMP TYPE		BALLAST				LAMPS INSTALLED (REQUIRED)						
24 2' x 4'	28 4', T5: 28 Watt 32 4', T8 ¹		E Electronic T8, 0.88 Ballast Factor, Instant Start E104 Electronic T8, 1.04 Ballast Factor, Instant Start (2-lamp only) EP Electronic T5, T5HO, 1.0 Ballast Factor or T8, 0.88 Ballast Factor, Programmed Start EP95 Electronic T5, 0.95 Ballast Factor, Programmed Start				F830 30K 78+CRI 32W T8 Lamps Installed F835 35K 78+CRI 32W T8 Lamps Installed F841 41K 78+CRI 32W T8 Lamps Installed FO830 30K 82CRI 32W T8 Lamps Installed FO835 35K 82CRI 32W T8 Lamps Installed FO841 41K 82CRI 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed						

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



STE - Stratus Recessed Direct/Indirect



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93029796	STE22-217G-MPO-EU	078531017415	2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast	●	●	●	●	12.0	24	
93029798	STE22-240TTG-MPO-EPTTU-C388	078531017477	2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V Twin Tube, Elec Prog Start Ballast, 3 Wire Flex		●			12.0	24	
93029800	STE22-240TTG-MPO-ETTU	078531017408	2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V Twin Tube, Elec Ballast	●	●	●		12.0	24	
93029801	STE22-317G-MPO-EU	078531017439	2 x 2, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast		●	●		12.0	24	
93029804	STE24-232G-MPO-EU	078531017385	2 x 4, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast	●	●	●	●	20.0	14	
93030408	STE24-232G-MPO-EPU	078531017446	2 x 4, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Prog Start Ballast	●	●	●	●	20.0	14	
93029803	STE24-332G-MPO-3EU	078531017378	2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast	●	●	●	●	20.0	14	
93030410	STE24-332G-MPO-3EPU	078531017460	2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Prog Start Ballast	●	●	●		20.0	14	
93029802	STE24-332G-MPO-EU	078531017392	2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec (2 Ballasts)	●	●	●	●	20.0	14	
93043912	STE24-332G-MPO-EU-FO841	078531023409	2x4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast (2 Ballasts), T8 Lamps installed		●			20.0	14	
93030962	Kit - STE/TRA 2x4 Dust Guard	078531017507	Dust Guard Kit, 4ft fixtures			●		1.0	N/A	



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

STE				G		MPO			U	
MODEL	NO. OF LAMPS IN CROSS SECTION	CEILING TYPE	BALLAST	OPTIONS	SIZE	LAMP TYPE	SHIELDING	VOLTAGE		
STE Stratus Recessed Indirect	2 Two 3 Three	G Grid Lay-in	E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8 or T5, Programmed Start	EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 F830 30K 78+CRI 17 or 32W T8 Lamps Installed F835 35K 78+CRI 17 or 32W T8 Lamps Installed F841 41K 78+CRI 17 or 32W T8 Lamps Installed FO830 30K 82CRI 17 or 32W T8 Lamps Installed FO835 35K 82CRI 17 or 32W T8 Lamps Installed FO841 41K 82CRI 17 or 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed C388 3-Wire Flex C488 4-Wire Flex	22 2' x 2' 24 2' x 4'	17 2', T8: 17 Watt 24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only)	MPO Metal Perf w/Overlay	U 120V-277V 347 347V (T5 and T8 only)		

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



TRA - Transition® High Efficiency Architectural Lensed




10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

TRA				G	CLO			
MODEL	NO. OF LAMPS IN CROSS SECTION	CEILING TYPE	BALLAST					OPTIONS
TRA Transition® High Efficiency Architectural Lensed	2 Two 3 Three	G Grid Lay-in	E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start EPTT Electronic Twin Tube, Programmed Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8 or T5, Programmed Start E104 Electronic T8, 1.04 Ballast Factor, Instant Start					EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 F830 30K 78+CRI 17 or 32W T8 Lamps Installed F835 35K 78+CRI 17 or 32W T8 Lamps Installed F841 41K 78+CRI 17 or 32W T8 Lamps Installed FO830 30K 82CRI 17 or 32W T8 Lamps Installed FO835 35K 82CRI 17 or 32W T8 Lamps Installed FO841 41K 82CRI 17 or 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed C388 3-Wire Flex C488 4-Wire Flex
SIZE	LAMP TYPE	SHIELDING				VOLTAGE		
22 2' x 2'	17 2', T8: 17 Watt	CLO Clear Linear Prism Acrylic with Overlay				U 120V-277V 347 347V (T5 and T8 only)		
24 2' x 4'	24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only)							

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



ZPT - Zero Plenum Troffer



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

ZPT		2		G			EP	U
MODEL	NO. OF LAMPS	CEILING TYPE	REFLECTOR					VOLTAGE
ZPT Zero Plenum® Troffer	2 Two	G Grid Lay-in	O Open (N/A with PRF) R Ribbed Curve S Smooth Curve					U 120V-277V 347 347V (T5 only)
SIZE	LAMP TYPE	SHIELDING	BALLAST					OPTIONS
22 2' x 2'	14 2', T5: 14 Watt	LSR Linear Prismatic Lens with Surface Relief Diffuser	EP Electronic T5, 1.00 Ballast Factor (28W or 54W)					C38890 3-Wire Flex, 90° Connector EL5 Emergency Battery Pack (N/A 2 x 2) F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed
24 2' x 4'	24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 54 4', T5HO: 54 or 51 Watt	PRF Metal Perf w/ Overlay						

ACCESSORIES (ORDER SEPARATELY)

ZPTSMK22 ZPT Surface Mounting Kit (2' x 2')

ZPTSMK24 ZPT Surface Mounting Kit (2' x 4')



P4D - High Performance Parabolic

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pal- let	Price
P4D00162	P4D22-232U6G-MA33-AV-EU	078531006501	2 x 2, 2-L, 9 Cell MA Lvr, 120-277V T8 Elec Ballast, Air w/Vanes			●		32.0	28	
P4D00120	P4D22-232U6G-MA33-S-EU	078531043445	2 x 2, 2-L, 9 Cell MA Lvr, 120-277V T8 Elec Ballast, Static	●	●	●	●	32.0	28	
P4D00156	P4D24-232G-MA26-S-EU	078531043704	2 x 4, 2-L, 12 Cell MA Lvr, 120-277V T8 Elec Ballast, Static	●	●	●	●	32.0	16	
P4D00157	P4D24-332G-MA36-AV-3EU	078531043711	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Air w/Vanes			●		33.0	16	
P4D00146	P4D24-332G-MA36-S-3EU	078531043483	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static	●	●	●	●	33.0	16	
93043905	P4D24-332G-MA36-S-3EPU	078531023331	2x4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Prog Start Ballast, Static		●			33.0	16	
P4D00138	P4D24-332G-MA36-S-EU	078531043414	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V T8 Elec (2 Ballasts), Static	●	●	●	●	35.0	16	
93057986	P4D24-332G-MA36-S-3EU- F835	078531124120	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static, T8 Lamps Installed		●	●	●	34.0	16	
93057987	P4D24-332G-MA36-S-3EU- F835-C388	078531124137	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Stat, T8 Lamps Installed, 3 Wire Flex	●	●		●	34.0	16	
93057988	P4D24-332G-MA36-S-3EU- F841	078531124144	2x4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static, T8 Lamps Installed		●			34.0	16	
P4D00147	P4D24-432G-MA48-S-4EU	078531043490	2 x 4, 4-L, 32 Cell, 120-277V 4-L T8 Elec Ballast, Static		●	●	●	34.0	16	
P4D019047.16PK1	LVR P4D24 3X6 MA HK BAG	078531044985	Louver for 2 x 4, 18 cell, MA		●	●		10.0	N/A	

QS75

5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

P4D		-			G	-	MA		-	S	-			U	-	
MODEL	NO. OF LAMPS		CEILING TYPE		CELLS WIDE BY CELLS LONG			BALLAST		VOLTAGE						
P4D High Performance Parabolic	2 Two 3 Three		G Grid		33 3 × 3 (2' × 2' only) 36 3 × 6 (2' × 4' 3-Lamp only)			E 2-Lamp Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start EP T8, Programmed Start 3EP 3-Lamp T8, Programmed Start		U 120V-277V 347 347V						
SIZE	LAMP TYPE		LOUVER FINISH		AIR HANDLING					OPTIONS						
22 2' × 2' 24 2' × 4'	17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-Lamp only)		MA Matte Anodized Low Iridescent Semi-Specular Aluminum (Std.)		S Static					F835 35K 78+CRI Full Wattage T8 Lamps Installed F841 41K 78+CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed C388 3-Wire Flex C488 4-Wire Flex EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8						
¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.																

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



ST8 - Shallow Specification Lensed Troffers



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
HS241519F000000	ST824-232G-FSA12125-EU	078531006853	2 x 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens	•	•	•	•	22.0	24	
HS341519G000000	ST824-332G-FSA12125-3EU	078531006884	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens		•	•	•	22.0	24	
93043895	ST824-332G-FSA12125-3EPU	078531023416	2x4, 3-L, 120-277V 3-L T8 Elec Prog Start Ballast, .125" Lens		•			22.0	24	
HS341519F000000	ST824-332G-FSA12125-EU	078531006877	2 x 4, 3-L, 120-277V T8 Elec (2 Ballasts), .125" Lens		•		•	25.0	24	
93043896	ST824-332G-FSA12125-EPU	078531023423	2x4, 3-L, 120-277V T8 Elec Prog Start (2) Ballasts, .125" Lens		•			22.0	24	



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 200

ST8				G		FS			U	
MODEL	NO. OF LAMPS	CEILING TYPE	SHIELDING	VOLTAGE						
ST8 Low Profile Specification Troffer	2 Two 3 Three (N/A 1 x 4) 4 Four (N/A 1 x 4 or 2 x 2)	G Grid	A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal	U 120V-277V 347 347V						
SIZE	LAMP TYPE	DOOR	BALLAST	OPTIONS						
14 1' x 4' 22 2' x 2' 24 2' x 4'	17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-lamp only)	FS White Flush Steel	E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start	F835 35K 78+CRI Full Wattage T8 Lamps Installed F841 41K 78+CRI Full Wattage T8 Lamps Installed F0835 35K 82CRI Full Wattage T8 Lamps Installed F0841 41K 82CRI Full Wattage T8 Lamps Installed EL Emergency Battery Pack ² EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex						

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.




JT8- Lensed Troffers



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
JT243119FTP0000	JT822-232U6G-FSA12-EU	078531005603	2 x 2, 2-L, 120-277V T8 Elec Ballast	●	●	●	●	16.0	36	
JT241519F000000	JT824-232G-FSA12125-EU	078531006914	2 x 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens	●	●	●	●	20.0	26	
JT24111BL000000	JT824-232G-FSA12-ELWU	078531011765	2x4, 2-L, 120-277V T8 Elec Low Wattage Ballast			●		20.0	26	
JT241119F000000	JT824-232G-FSA12-EU	078531005610	2 x 4, 2-L, 120-277V T8 Elec Ballast	●	●	●	●	20.0	26	
93057975	JT824-232G-FSA12-EU-F835-C388	078531124014	2 x 4, 2-L, 120-277V T8 Elec Ballast, 3 Wire Flex, T8 Lamps Installed	●			●	24.0	26	
JT341519G000000	JT824-332G-FSA12125-3EU	078531006815	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens		●	●	●	20.0	26	
JT34111BM000000	JT824-332G-FSA12-3ELWU	078531010867	2x4, 3-L, 120-277V 3-L T8 Elec Low Wattage Ballast			●		20.0	26	
93043898	JT824-332G-FSA12-3EPU	078531023447	2x4, 3-L, 120-277V 3-L T8 Elec Prog Start Ballast		●			20.0	26	
JT341119G000000	JT824-332G-FSA12-3EU	078531005627	2 x 4, 3-L, 120-277V 3-L T8 Elec Ball.	●	●	●	●	20.0	26	
93057976	JT824-332G-FSA12-3EU-F835	078531124021	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, T8 Lamps Installed		●		●	23.0	26	
93057977	JT824-332G-FSA12-3EU-F835-C388	078531124038	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, T8 Lamps Installed, 3 Wire Flex	●	●		●	24.0	26	
93057978	JT824-332G-FSA12-3EU-F841	078531124045	2 x 4, 3-L, 120-277V 3-L T8 Elec Ball., T8 Lamps Installed		●		●	23.0	26	
JT341119F000000	JT824-332G-FSA12-EU	078531005634	2 x 4, 3-L, 120-277V T8 Elec (2 Ballasts)	●	●	●	●	24.0	26	
93046045	JT824-332SM-FSA12-3EU	078531121105	2 x 4 Surface Mount, 3-L 120-277V T8 Elec Ballast		●			24.0	9	
JT441119H000000	JT824-432G-FSA12-4EU	078531005641	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast	●	●	●	●	18.0	26	
93057980	JT824-432G-FSA12-4EU-F835	078531124069	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 Lamps Installed		●	●	●	23.0	26	
93057981	JT824-432G-FSA12-4EU-F835-C388	078531124076	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 Lamps Installed, 3 Wire Flex	●	●		●	24.0	26	
93057982	JT824-432G-FSA12-4EU-F841	078531124083	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 41K Lamps Installed		●		●	23.0	26	
93057983	JT824-432G-FSA12-4EU-F841-C388	078531124090	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 41K Lamps Installed, 3 Wire Flex		●	●	●	24.0	26	
JT441119F000000	JT824-432G-FSA12-EU	078531005658	2 x 4, 4-L, 120-277V T8 Elec (2 Ballasts)	●	●	●	●	24.0	26	
93046044	JT824-432SM-FSA12-4EU	078531121099	2 x 4 Surface Mount, 4-L 120-277V T8 Elec Ballast		●			24.0	9	
JT2499000800000	DR&SHLD JT824 FS A12	078531012632	2 x 4 Replacement Door Assembly with Lens			●		5.0	N/A	
003334.00	A12.095 22.500-22.500	078531004781	2 x 2 Replacement Lens		●	●		1.0	N/A	
003335.00	A12.095 22.500-46.562	078531004774	2 x 4 Replacement Lens		●	●		2.0	N/A	
003312.00	A12.125	078531022891	2 x 4 Replacement Lens		●	●		2.5	N/A	



JT8 - Lensed Troffers




5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 200

JT8		-			G	-	FS		-		U	-				
MODEL	NO. OF LAMPS			CEILING TYPE			SHIELDING			VOLTAGE			OPTIONS			
JT8 Dedicated T8 Lensed Troffer	2	Two		G Grid			A12	Pattern 12 Acrylic Lens			U	120V-277V		F835	35K 78+CRI Full Wattage T8 Lamps Installed	
	3	Three					A12125	Pattern 12 Acrylic Lens, 0.125" Nominal			347	347V		F841	41K 78+CRI Full Wattage T8 Lamps Installed	
	4	Four (2 x 4 only)												F0835	35K 82CRI Full Wattage T8 Lamps Installed	
SIZE	LAMP TYPE			DOOR			BALLAST									
22 2' x 2'	17	2', T8: 17 Watt		FS White Flush Steel			E	Electronic T8, Instant Start								
24 2' x 4'	32	4', T8 ¹					3E	3-Lamp Electronic T8, Instant Start								
	32U6	U-Bent, 6" Leg Spacing T8: 32 Watt (2 lamps)					4E	4-Lamp Electronic T8, Instant Start								
							EP	Electronic T8, Programmed Start								
							3EP	3-Lamp Electronic T8, Programmed Start								
							4EP	4-Lamp Electronic T8, Programmed Start								

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.



4PS - Specification Grade Lensed Troffers



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
HW241519F000000	4PS24-232G-FSA12125-EU	078531009106	2 × 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens	•	•	•	•	22.0	18	
HW341519G000000	4PS24-332G-FSA12125-3EU	078531009113	2 × 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens		•			23.0	18	
HW341519F000000	4PS24-332G-FSA12125-EU	078531009120	2 × 4, 3-L, 120-277V T8 Elec (2 Ballasts), .125" Lens		•			25.0	18	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

4PS	-		G	-		-	U	-	
MODEL 4PS Specification Grade Static Troffer	NO. OF LAMPS 2 Two 3 Three 4 Four (2 × 4 only)	CEILING TYPE G Grid	SHIELDING A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal	VOLTAGE U 120V-277V 347 347V (T8 only)					
SIZE 22 2' × 2' 24 2' × 4'	LAMP TYPE 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2 lamps) 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2 or 3 lamps)	DOOR FS White Flush Steel RA White Regressed Aluminum	BALLAST E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start ETT Electronic Twin Tube, Instant Start	OPTIONS F835 35K 78+CRI Full Wattage T8 Lamps Installed F841 41K 78+CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed EL Emergency Battery Pack, T8 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex					

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



BIL - Integrated Sensor for Stairwell Applications



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
BIL000002	BIL4-232-EPU	078531016807	4', 2-L, 32W T8, Elec Ballast		•	•		9.0	N/A	



SA - Wall Brackets



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
34241019F000000	SA4-232-EU	078531006792	2-4' T8, 4', 120-277V Elec Ballast	•	•	•	•	13.0	24	



UC - Undercabinet



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93047671	UC24-117-EU	078531023690	2', 1-L, 17W T8, Elec Ballast		•	•	•	6.0	224	
93047672	UC36-125-EU	078531023706	3', 1-L, 25W T8, Elec Ballast	•	•	•	•	6.0	140	
93047673	UC48-132-EU	078531023713	4', 1-L, 32W T8, Elec Ballast	•	•	•	•	8.0	112	



W - Wall Mount Light



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
24222019F000000	W2-217-EU	078531010294	2-2' T8, 2', 120-277V T8 Elec Ballast Less Switch, Less Convenience Outlet	•	•	•	•	6.0	N/A	
24241019F000000	W4-232-EU	078531007287	2-4' T8, 4', 120-277V T8 Elec Ballast Less Switch, Less Convenience Outlet	•	•	•	•	13.0	N/A	

**WAL - Wall Mount****Regional Distribution Center Stock List**

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
DS241019F000000	WAL4-232-EU	078531006068	2-4' T8, 4', 120-277V T8 Elec Ballast	•	•	•	•	16.0	55	

**AD - Corridor Wraparounds****Regional Distribution Center Stock List**

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
22141019F000000	AD4-132-EU	078531006327	1-4'T8, 4', 120-277V T8 Elec Ballast			•		10.0	56	
22241019F000000	AD4-232-EU	078531006334	2-4'T8, 4', 120-277V T8 Elec Ballast	•		•		10.0	56	

**WC - Specification Grade Wraparounds****Regional Distribution Center Stock List**

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
CD241019F000000	WC4-232-EU	078531006075	2-4'T8, 4', 120-277V T8 Elec Ballast	•	•	•	•	13.0	48	
CD441019H000000	WC8-232-4EU	078531006822	4-4'T8, 8', 120-277V 4-L T8 Elec Ballast		•			26.0	36	
CF341019G000000	WCW4-332-3EU	078531006341	3-4'T8, 4', 120-277V 3-L T8 Elec Ballast	•		•		14.0	33	
CF441019H000000	WCW4-432-4EU	078531006082	4-4'T8, 4', 120-277V 4-L T8 Elec Ballast	•	•	•		16.0	28	
CD8013802000000	SHLD ASY WC 4FT	078531000998	WC Replacement Lens - 4'		•	•		3.1	54	
CF8013803000000	SHLD ASY WCW 4FT	078531001001	WCW Replacement Lens		•	•		10.0	80	



AW- Wraparounds



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
CY222019F000000	AWN2-217-EU	078531009984	2-2'T8, 2', 120-277V T8 Elec Ballast		●	●	●	8.0	110	
CY241019F000000	AWN4-232-EU	078531004859	2-4'T8, 4', 120-277V T8 Elec Ballast	●	●	●	●	14.0	55	
93043931	AWN4-232-EPU	078531023508	2-4'T8, 4', 120-277V T8 Elec Prog Start Ballast	●	●			14.0	55	
CY24101BL000000	AWN4-232-ELWU	078531011857	2-4'T8, 4', 120-277V T8 Elec Low Wattage Ballast	●		●		14.0	55	
CY441019H000000	AWN8-232-4EU	078531005979	4-4'T8, 8', 120-277V 4-L T8 Elec Ballast	●	●	●		26.0	30	
93015558	AWN8-232-4ELWU	078531012441	4-4'T8, 8', 120-277V 4-L T8 Elec Low Wattage Ballast			●		26.0	30	
CL341019G000000	AWW4-332-3EU	078531004866	3-4'T8, 4', 120-277V 3-L T8 Elec Ballast	●	●	●	●	14.0	33	
CL441019H000000	AWW4-432-4EU	078531004873	4-4'T8, 4', 120-277V 4-L T8 Elec Ballast	●	●	●	●	14.0	33	
CY8092746000000	SHLD AWN 4FT	078531001148	AWN Replacement Lens		●	●		10.0	100	
CL8092721000000	SHLD AWW 4FT	078531001155	AWW Replacement Lens		●	●		5.0	66	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

		-		32	-		U	-	EL
MODEL	SIZE		LAMP TYPE			VOLTAGE		OPTIONS	
AWN 8 ⁵ / ₁₆ " Wide	4 4'		32 4' T8 ¹			U 120V-277V		EL Emergency Battery Pack	
AWW 14 ⁵ / ₈ " Wide	8 8' (AWN only)					347 347V		EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8	
			NO. OF LAMPS IN CROSS SECTION	BALLAST					
			2 Two	E Electronic Instant Start					
			3 Three (AWW only)	3E 3-Lamp Electronic T8, Instant Start					
			4 Four (AWW only)	4E 4-Lamp Electronic T8, Instant Start					
				EP Electronic T8, Programmed Start					
				3EP 3-Lamp Electronic T8, Programmed Start					
				4EP 4-Lamp Electronic T8, Programmed Start					

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



CSR - Industrials



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
56241719F910000	CSR4-232-ST-EU	078531004934	2-4' T8, 4', 120-277V T8 Elec Ballast, Solid Reflector	•	•	•	•	11.0	48	
5624171BL910000	CSR4-232-ST-ELWU	078531011918	2-4' T8, 4', 120-277V T8 Elec Low Wattage Ballast, Solid Reflector			•		11.0	48	
55441719H910000	CSR8-232-ST-4EU	078531004941	2-4' T8, 8', 120-277V 4-L T8 Elec Ballast, Solid Reflector	•	•	•	•	20.0	27	
56275719F910000	CSR8-296T8-ST-EU	078531005986	2-4' T8, 8', 120-277V T8 Elec Ballast, Solid Reflector		•	•		26.0	27	
562092935000000	CSRWG4	078531740139	4' Wire Guard for CSR series	•	•	•	•	2.5	N/A	
985084348700000	CSZT	078531740146	Zip T-Hanger - 1/2" spacer		•	•	•	0.2	N/A	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

CSR		-			-		U	-	EL
MODEL CSR Industrial	NO. OF LAMPS 2 Two 3 Three (T8 only)		REFLECTOR TYPE ST Solid Top Reflector U Apertured Reflector for 5% Uplight (Solid Reflector not recommended with HO units)		VOLTAGE U 120V-277V 347 347V (T8 only)		OPTIONS EL Emergency Battery Pack (T8 only) EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8		
SIZE 4 4' 8 8'	LAMP TYPE 32 4', T8 ¹ 96HO 8', T12: 110 or 95 Watt	BALLAST E Electronic, Instant Start 3E 3-Lamp Electronic T8 (32W), Instant Start 4E 4-Lamp Electronic T8 (32W), Instant Start EP Electronic, Programmed Start, T8 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start							

1 Capable of operating 32, 30, 28 or 25 Watt T8 only.

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



LHA- Industrial Fluorescent High Bay



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
LHA000016	LHA4-454-NST-4EPU	078531022464	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Narrow Distribution, Solid Reflector		●	●		22.0	30	
LHA000017	LHA4-454-NU-4EPU	78531022112	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Narrow Distribution, Uplight Reflector	●	●	●	●	22.0	30	
LHA000019	LHA4-454-NU-4EPU-F554841	78531022129	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, 54 Watt Lamps Installed, Narrow Distribution, Uplight Reflector	●	●		●	23.0	30	
LHA000024	LHA4-632-NST-3EHLU	078531022471	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast, Narrow Distribution, Uplight Reflector		●			24.0	24	
LHA000025	LHA4-632-NU-3EHLU	78531022136	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast, Narrow Distribution, Uplight Reflector	●	●	●	●	24.0	24	
LHA000027	LHA4-632-NU-3EHLU-F0841	078531022143	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 82 CRI T8 Lamps Installed, Narrow Distribution, Uplight Reflector		●			25.0	24	
LHA000040	LHA4-654-NST-24EPU	078531022488	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, Narrow Distribution, Solid Reflector	●	●	●	●	26.0	24	
93043290	LHA4-654-NST-24EPU-F554841	078531023256	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, 54W-T5 Lamps Installed, Narrow Distribution, Solid Reflector			●		26.0	24	
LHA000041	LHA4-654-NU-24EPU	078531022150	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, Narrow Distribution, Uplight Reflector	●	●	●	●	26.0	24	
LHA000043	LHA4-654-NU-24EPU-F554841	078531022167	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, 54 Watt Lamps Installed, Narrow Distribution, Uplight Reflector	●	●	●	●	26.0	24	



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

LHA	4	-		-		-		-	U	-	
SIZE 4 4'	NO. OF LAMPS 4 Four 6 Six		REFLECTOR N Narrow Distribution W Wide Distribution	UPLIGHT ST Solid Top U Uplight		VOLTAGE U 120V-277V 347 347V		OPTIONS EL141 Emergency Battery Pack, T8, 1400 Lumens EL5H Emergency Battery Pack, T5, 1250 Lumens F3C5 3-Conductor Cord F4C5 4-Conductor Cord F3C10 3-Conductor Cord, 10' F4C10 4-Conductor Cord, 10'			
MODEL LHA Industrial Fluorescent High Bay	LAMP TYPE 32 4', T8 ¹ 54 4', T5HO: 54 or 51 Watt	BALLAST LHA4-454 4EP (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-654 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-432 4EHL (1) 4-Lamp Electronic T8, High Light Output, Instant Start (N/A 480V) LHA4-632 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start 3EPHL (2) 3-Lamp Electronic T8, High Light Output, Programmed Start				LAMPS INSTALLED T8 F841 4100K 78+CRI 32W T8 F850 5000K 78+CRI 32W T8 T5HO F554841 54 Watt, 85 CRI, 4100K F554850 54 Watt, 85 CRI, 5000K					

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



LHV - Linear High Bays

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93014378	LHV4-432-M4R-ST-4EHLU	078531019372	4-4' T8, 4', 120-277V 4-L T8 HL Elec Ballast		●			22.0	30	
93038457	LHV4-432-M4RU-4EHLU-FO850	078531022914	4-4' T8, 4', 120-277V 4-L T8 HL Elec Ballast 80 CRI T8 Lamps Installed		●			24.0	30	
LHV000004	LHV4-454-GWU-4EPU-F5841	078531011086	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, White Reflector T5 Lamps Installed		●			23.0	30	
93014379	LHV4-454-M4RST-4EPU	078531011703	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Solid Top Reflectors			●		22.0	30	
LHV000003	LHV4-454-M4RU-4EPU	078531011024	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Uplight Reflector	●	●	●	●	22.0	30	
LHV000002	LHV4-454-M4RU-4EPU-F5841	078531011079	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, T5 Lamps Installed		●	●	●	23.0	30	
93057984	LHV4-632-GWU-3EHLU-F841	078531124106	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast T8 Lamps Installed, White Reflector		●			23.0	24	
LHV000009	LHV4-632-M4RU-3EHLU	078531011048	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast,	●	●	●	●	24.0	24	
93057985	LHV4-632-M4RU-3EHLU-F841	078531124113	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 70CRI T8 Lamps Installed		●		●	25.0	24	
LHV000029	LHV4-632-M4RU-3EHLU-FO850	078531016845	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 80 CRI T8 Lamps Installed		●			25.0	24	
LHV000007	LHV4-654-GWU-24EPU-F5841	078531011109	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast T5 Lamps Installed, White Reflector		●		●	25.0	24	
93020453	LHV4-654-M4RST-24EPU-F5841	078531016296	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, T5 Lamps Installed Solid Top Reflector				●	26.0	24	
LHV000006	LHV4-654-M4RU-24EPU	078531011031	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast	●	●	●	●	26.0	24	
LHV000005	LHV4-654-M4RU-24EPU-F5841	078531011093	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, T5 Lamps Installed		●	●	●	26.0	24	
LHVOS1360	LHVOS1360	078531023584	Occupancy/Daylight Sensor, with a 360° lens, 120/277/347V, One Relay	●	●	●	●	25.0	N/A	
LHVQM10	LHVQM10	078531012526	Aircraft Cable Hangers, 10' (pair)	●	●	●	●	0.6	N/A	
LHVQM20	LHVQM20	078531012991	Aircraft Cable Hangers, 20' (pair)		●		●	1.2	N/A	
LHVQM5	LHVQM5	078531012670	Aircraft Cable Hangers, 5' (pair)	●	●	●	●	0.5	N/A	
LHVSP	LHVSP	078531011338	Side Panels (pair)		●			5.0	N/A	
LHVSPM5	LHVSPM5	078531012656	Single Point Mounting Kit, Includes Aircraft Cable, 5' (pair)		●	●		5.0	N/A	
LHVTH	LHVTH	078531012649	Tong Hanger (pair)	●	●	●	●	0.6	N/A	
LHVWG4-4	LHVWG4-4	078531012625	Cage Wireguard, 4-L, White	●	●	●	●	5.0	N/A	
LHVWG4-6	LHVWG4-6	078531012618	Cage Wireguard, 6-L, White	●	●	●	●	5.0	N/A	
C6P15-120	C6P15-120	078531016111	Cord and Plug Kit (white), 6 ft Straight Blade Nema 5-15P, 15 amp, 120V		●			0.8	N/A	
C6TL15-120	C6TL15-120	078531016098	Cord and Plug Kit (white), 6 ft Twist Lock Nema L5-15P, 15 amp, 120V		●			0.8	N/A	
C6TL15-277	C6TL15-277	078531016104	Cord and Plug Kit (white), 6 ft Twist Lock Nema L7-15P, 15 amp, 277V		●			0.8	N/A	



LHV - Linear High Bays



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
VersaBay Shielding Accessories										
LHVS4-CA	LHVS4-CA		LHV 4 lamp Shielding kit, includes frame and clear acrylic lens		●				N/A	
LHV4SPJ	LHV4SPJ	078531016142	Side Panels and End Jaw (pair) for 4 lamp		●			2.5	N/A	
LHV4CA	LHV4CA	078531016203	Clear Acrylic Lens for 4 lamp		●			2.5	N/A	
LHVS4-WG	LHVS4-WG		LHV 4 lamp Shielding kit, includes frame and flat wire guard		●				N/A	
LHV4SPJ	LHV4SPJ	078531016142	Side Panels and End Jaw (pair) for 4 lamp		●			2.5	N/A	
LHV4FWG	LHV4FWG	078531016173	Flat Wire Guard for 4 lamp		●			2.5	N/A	
LHVS4-CAWG	LHVS4-CAWG		4 lamp Shielding kit, includes frame, clear acrylic lens and flat wire guard		●					
LHV4SPJ	LHV4SPJ	078531016142	Side Panels and End Jaw (pair) for 4 lamp		●			2.5		
LHV4FWG	LHV4FWG	078531016173	Flat Wire Guard for 4 lamp		●			2.5	N/A	
LHVS6-CA	LHVS6-CA		LHV 6 lamp Shielding kit, includes frame and clear acrylic lens		●					
LHV6SPJ	LHV6SPJ	078531016159	Side Panels and End Jaw (pair) for 6 lamp		●			2.5	N/A	
LHV6CA	LHV6CA	078531016210	Clear Acrylic Lens for 6 lamp		●			2.5	N/A	
LHVS6-WG	LHVS6-WG		LHV 6 lamp Shielding kit, includes frame and flat wire guard		●					
LHV6SPJ	LHV6SPJ	078531016159	Side Panels and End Jaw (pair) for 6 lamp		●			2.5	N/A	
LHV6FWG	LHV6FWG	078531016180	Flat Wire Guard for 6 lamp		●			2.5	N/A	
LHVS6-CAWG	LHVS6-CAWG		6 lamp Shielding kit, includes frame, clear acrylic lens and flat wire guard		●				N/A	
LHV6SPJ	LHV6SPJ	078531016159	Side Panels and End Jaw (pair) for 6 lamp		●			2.5		
LHV6CA	LHV6CA	078531016210	Clear Acrylic Lens for 6 lamp		●			2.5	N/A	
LHV6FWG	LHV6FWG	078531016180	Flat Wire Guard for 6 lamp		●			2.5	N/A	



LHV - Linear High Bays



5-Day Quick Ship Ordering Guide


Order Limit Per Fixture Selection: 150

LHV	4	-		-		-		-		-	
SIZE 4 4'	NO. OF LAMPS 4 Four 6 Six	REFLECTOR M4R 95% Reflective Specular Aluminum (Narrow Beam) GW Gloss White (Wide Beam)		UPLIGHT ST Solid Top U Uplight		VOLTAGE U 120V-277V 347 347V 480 480V ²		OPTIONS EL141 Emergency Battery Pack, T8, 1400 Lumens (120-277V) EL5H Emergency Battery Pack, T5, 1250 Lumens (120-277V) F3C5 3-Conductor Cord F4C5 4-Conductor Cord F3C10 3-Conductor Cord, 10' F4C10 4-Conductor Cord, 10'			
MODEL LHV VersaBay® Fluorescent High Bay	LAMP TYPE 32 4', T8 ¹ 54 4', T5HO: 54 or 51 Watt	BALLAST LHV4-454 4EP (1) 4-Lamp Electronic T5HO, Programmed Start LHV4-654 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start LHV4-432 4EHL (1) 4-Lamp Electronic T8, High Light Output, Instant Start (N/A 480V) LHV4-632 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start 3EPHL (2) 3-Lamp Electronic T8, High Light Output, Programmed Start ³					LAMPS INSTALLED T8 F0841 4100K 82CRI 32W T8 F0850 5000K 82CRI 32W T8 T5HO F5841 4100K 85CRI F5850 5000K 85CRI				

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

² 480V option on T5HO units only.

³ N/A in 347V.



KL - Specification Grade Industrials



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
72241819F910000	KL4-232-U-EU	078531006471	2-4'T8, 4', 120-277V T8 Elec Ballast, Apertured Reflector	•	•	•	•	15.0	21	
820268450000000	KLWG4	078531007478	4' Wire Guard for KL series	•	•	•	•	3.2	N/A	
984084190000000	KHC	078531000875	Two 24" chain assemblies for K and KL	•	•	•	•	0.3	N/A	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50

KL					U	
MODEL KL Premium Industrial	NO. OF LAMPS 2 Two 3 Three	REFLECTOR TYPE U Apertured Uplight Reflector ST Solid Top	VOLTAGE U 120V-277V 347 347V (T8 only)	OPTIONS EL Emergency Battery Pack EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8		
SIZE 4 4' 8 8'	LAMP TYPE 32 4' T8 ¹ 54 4' T5HO: 54 or 51 Watt 96T8 8' T8: 59 Watt (2-Lamp only) 96T8HO 8' T8: 86 Watt (2-Lamp only)	BALLAST E Electronic, Instant Start 3E 3-Lamp Electronic T8 (32W), Instant Start 4E 4-Lamp Electronic T8 (32W), Instant Start EP Electronic, Programmed Start, T5HO or T8 3EP 3-Lamp Electronic T5HO or T8, Programmed Start 4EP 4-Lamp Electronic T5HO or T8, Programmed Start Instant Start ballasts available for 32 and 96T8. Programmed Start ballasts available for all except 96T8.				
ACCESSORIES (ORDER SEPARATELY) KLEC Full Depth Endcap (pair) KZT Zip-Tee Hanger KLRU4 4' 5% Uplight Reflector Only KTH Slide Clamp Tong Hanger						

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



K - Heavy Duty Striplights



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
80241009F910000	K4-232-EU	078531007034	2-4'T8, 4', 120-277V T8 Elec Ballast		•		•	16.0	72	
93025871	K8-296HO-EPU	078531016913	2-8'T12HO, 8', 120-277V Ballast	•	•	•	•	19.0	36	
93032673	K8-296T8HO-EPU	078531017699	2-8'T8HO, 8', 120-277V Elec.Prog Start Ballast		•			19.0	36	
984084190000000	KHC	078531000875	Two 24" chain assemblies for K and KL	•	•	•	•	0.3	N/A	



SS - Staggered Strips



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
FS000039	SS4-132-EU	078531044602	1-4' T8, 4', 120-277V T8 Elec Ballast				●	9.0	72	
FS000040	SS4-232-EU	078531044619	2-4' T8, 4', 120-277V T8 Elec Ballast				●	9.0	72	



CS - Striplights



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
04122009F910000	CS2-117-EU	078531008079	1-2' T8, 2', 120-277V T8 Elec Ballast			●		4.0	176	
04222009F910000	CS2-217-EU	078531004996	2-2' T8, 2', 120-277V T8 Elec Ballast		●	●	●	4.0	176	
041220007910000	CS2-220-L120	078531023164	2-2' T12, 2', 120V T12 LPF Ballast			●		4.0	176	
04231009F910000	CS3-225-EU	078531005009	2-3' T8, 3', 120-277V T8 Elec Ballast	●	●	●	●	7.0	88	
04141009F910000	CS4-132-EU	078531006280	1-4' T8, 4', 120-277V T8 Elec Ballast	●	●	●	●	9.0	77	
04241009F910000	CS4-232-EU	078531005016	2-4' T8, 4', 120-277V T8 Elec Ballast	●	●	●	●	9.0	77	
93022153	CS4-232-EPU	078531016609	2-4' T8, 4', 120-277V T8 Elec Prog Start Ballast	●	●			9.0	77	
93038454	CS4-254-EPU	078531022969	2-4' T5, 4', 120-277V T5 Elec Ballast		●	●		9.0	77	
0424100BL910000	CS4-232-ELWU	078531012458	2-4' T8, 4', 120-277V T8 Elec Low Wattage Ballast			●		9.0	77	
03241009F910000	CS8-132-EU	078531009151	2-8' T8, 8', 120-277V T8 Elec Ballast		●	●		17.0	77	
03441009H910000	CS8-232-4EU	078531005023	4-8' T8, 8', 120-277V 4-L T8 Elec Ballast	●	●	●	●	17.0	77	
0344100BN910000	CS8-232-4ELWU	078531011949	4-8' T8, 8', 120-277V 4-L T8 Elec Low Wattage Ballast			●		17.0	77	
04275009F910000	CS8-296T8-EU	078531005795	2-8' T8, 8', 120-277V T8 Elec Ballast	●	●	●	●	17.0	77	
0427500AS910000	CS8-296-EU120	078531008543	2-8' T12, 8', 120V Magnetic DOE Compliant Ballast		●			17.0	77	
93038455	CS8-254-4EPU	078531022976	4-8' T5, 8', 120-277V 4-L T5 Elec Ballast		●			17.0	77	
984084158000000	CSHC	078531000868	Two 14" chain assemblies for CS and CSR	●	●	●	●	0.2	N/A	
745013602000000	CSR4	078531001575	4' symmetric reflector, white, solid top	●	●	●	●	2.0	N/A	
745013603000000	CSRU4	078531001582	4' symmetric reflector, white, uplight		●			2.0	N/A	
982092925000000	CSWG4	078531000882	4' Wire Guard for CS series	●	●	●	●	1.0	N/A	
985084348700000	CSZT	078531740146	Zip T-Hanger - 1/2" spacer		●	●	●	0.2	N/A	



CS - Striplights



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

CS						U		EL
MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS		
CS Straight-Sided Utility Channel	2 2' 4 4' 8 8'	1 One 2 Two	17 2', T8: 17 Watt 32 4', T8 ¹	E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start	U 120V-277V 347 347V	EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8		
							ACCESSORIES (ORDER SEPARATELY)	
							CSRA4 4' Asymmetric Reflector CSRU4 4' Symmetric Reflector 5% Uplight	

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



CH-1-L Striplights



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
841120007000000	CH1.5-115-L120	078531840228	1-1.5' T12, 1.5', 120V T12 LPF Ballast			●		3.0	156	
84122009F910000	CH2-117-EU	078531005047	1-2' T8, 2', 120-277V T8 Elec Ballast		●	●	●	3.0	156	
841220007000000	CH2-120-L120	078531840235	1-2' T12, 2', 120V T12 LPF Ballast		●	●	●	3.0	156	
84131009F910000	CH3-125-EU	078531005054	1-3' T8, 3', 120-277V T8 Elec Ballast			●		7.0	156	
84141009F910000	CH4-132-EU	078531005061	1-4' T8, 4', 120-277V T8 Elec Ballast	●	●	●	●	7.0	156	
841410003910000	CH4-140-L120	078531840259	1-4' T12, 4', 120V T12 LPF Ballast			●		5.0	156	
83241009F910000	CH8-132-EU	078531005078	2-4' T8, 8', 120-277V T8 Elec Ballast			●		17.0	96	
845034020000000	CHRA4	078531011970	4' Asymmetric Reflector (1-lmp only)			●		1.9	N/A	
980929240000000	CHWG4	078531002954	Wire Guard, 4' for CH Strip	●	●	●		10.0	N/A	



XEW - Enclosed/Gasketed High Bay



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
XEW00021	XEW4-454-CA-W-4EPU	078531123598	4-4' T5, 4', 120-277V 4-L T5 Elec Program Start Ballast, Wide, Clear Acrylic Lens		●			25.0	21	
XEW00019	XEW4-454-CA-N-4EPU	078531123581	4-4' T5, 4', 120-277V 4-L T5 Elec Program Start Ballast, Narrow, Clear Acrylic Lens		●			25.0	21	
XEW00022	XEW4-654-CA-W-24EPU	078531123604	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Program Start Ballast, Wide, Clear Acrylic Lens		●			25.0	21	
XEW00023	XEW4-632-CA-W-3EHLU	078531123611	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast, Wide, Clear Acrylic Lens		●			25.0	21	
XEWFSBSS	XEWFSBSS	078531123659	Flexible Surface Mount Bracket, Pair		●			2.0		



XEM - Low Profile Enclosed/Gasketed Industrials



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
93049168	XEM4-232-RA-EU	078531023720	Vapor Tight 2-4'T8, 4', 120-277V T8 Elec Ballast, Fiberglass Housing	●	●	●	●	14.0	55	
93049169	XEM8-232-RA-4EU	078531023737	Vapor Tight 4-4'T8, 8', 120-277V 4-L T8 Elec Ballast, Fiberglass Housing	●	●	●	●	29.0	45	
93049170	XEM8-296T8HO-RA-EPU	078531023744	Vapor Tight 2-8'T8HO, 8', 120-277V 4-L T8 Elec Program Start Ballast, Fiberglass Housing		●	●		29.0	45	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50

XEM		2				U	
MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS	
XEM Low Profile Enclosed and Gasketed Fiberglass Industrial	4 4' 8 8'	2 Two	32 4'T8 ¹ 48T8HO 4'T8HO: 44 Watt 96T8 8'T8: 59 Watt 96T8HO 8'T8HO: 86 Watt	E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic, Programmed Start 4EP 4-Lamp Electronic, Programmed Start	U 120V-277V 347 347V (T8 only)	TP Tamper Proof Screws SSL Stainless Steel Latches	
			LENS TYPE	BALLAST FACTOR			
			RA Ribbed Acrylic (Standard)	Blank 0.88BF (Standard)			

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

Accessories



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	# on Pallet	Price
FK14	FK14	078531000745	1 × 4 Flange Kit	•	•	•	•	5.0	N/A	
FK22	FK22	078531000752	2 × 2 Flange Kit	•	•	•	•	5.0	N/A	
FK24	FK24	078531038991	2 × 4 Flange Kit	•	•	•	•	5.0	N/A	
GLH5	GLH5	078531012700	5' Adjustable Cable Kit	•	•	•	•	0.3	N/A	
GLH10	GLH10	078531013127	10' Adjustable Cable Kit	•	•		•	0.4	N/A	
980000011000000	S18	078531000790	18" Stem and Canopy	•	•	•	•	8.0	N/A	
980000010000000	SS18	078531003456	18" Stem only	•	•	•	•	5.0	N/A	
TBC10K	TBC	078531017606	Tall Ballast Cover, For Field Installed Battery Packs			•		8.0	N/A	