



Cat6A-Augmented Category 6 U/FTP, Riser/CMR



Product Construction

- Conductor:
- Solid Bare copper
- Insulation:
- Riser: PE (Polyethylene)
- Shield:
- Aluminum Foil
- Drain Wire:
- Yes
- Jacket:
- Riser: PVC (Polyvinyl Chloride)
- Ripcord:
- Yes

Applications

- 10GBASE-T Ethernet
- 1000BASE-T
- High-Throughput Wi-Fi
- High-Speed Internet

Standards

- ETL/UL Available
- UL444
- ISO/IEC11801
- EIA/TIA-568-C.2

Part #	AWG	Pairs	Nom. O.D.	Lbs./M'
J642304-02	23	4	.335"	44
J642304-05	23	4	.335"	44

Jacket Colors:

- 02 = White
- 05 = Blue

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.