

## HOOK UP WIRE

UL 1007, UL 1569  
80C to 105C -300 Volt



CONSTRUCTION	
Conductor	- Stranded tinned copper
Insulation	- Polyvinyl Chloride (PVC)

### Standards:

- UL Style 1007 80C AWM
- UL Style 1569 105C AWM
- VW-1
- RHS Compliant

### Additional Information:

- Standard put up 500 ft., 1000 ft., and bulk reels
- All colors can be striped upon request.
- Can be provided in twisted configurations

Part #	AWG	Stranding	Insulation Thickness	Nom. O.D.	Lbs./M'
L824ST-XX	24	7 <del>3</del> 0	.016"	.07"	4
L822ST-XX	22	7 <del>3</del> 0	.016"	.07"	4
L820ST-XX	20	10 <del>3</del> 0	.016"	.07"	7
L818ST-XX	18	16 <del>3</del> 0	.016"	.076"	7
L816ST-XX	16	26 <del>3</del> 0	.016"	.093"	10

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

Insert the color number in the -XX location:

- 01 = Black
- 02 = White
- 03 = Red
- 04 = Green
- 05 = Blue
- 06 = Gray
- 07 = Orange
- 08 = Yellow
- 09 = Purple
- 10 = Brown