

Panelboards

A-Series® Panelboards

Type AQ

240 Vac Bolt-On

Factory Assembled

Three-Phase, 3-Wire/4-Wire Pricing¹

GE Fastrac Program items are indicated in red²

Service Information:

3-ph, 3-w, 3-ph, 4-w;
240 Vac Max.

Bolt-On Branch Breakers:

15-100 amps, 1, 2, 3-poles
types THQB, THHQB, TXQB.

Service Entrance Equipment:

Service entrance rating is standard on all main breaker panels and 12 and 18 circuit, 225 amp max MLO devices. No need to specify on order.

Mains:

100-THQB, THHQB, TEY, SE
225-TQD, THQD, SF
400-TJD, SG
600-SG
800-SK
125-800 amp main lug

NOTE: Sizing dimensions to be used only for enclosure selection, not to determine interior length.

Main Lug Interiors^{3,4}

Use THQB Bolt-on Breakers		Single Main Lugs			Subfeed Main Lugs		
Panel Amps Max.	Branch Space Required	Interior Product Number	List Price, ⁵ GO-101	Sizing Dim. (in.)	Interior Product Number	List Price, ⁵ GO-101	Sizing Dim. (in.)
125	0-12	AQF3121MB	\$487.00	22.5	AQF3121SB	\$548.00	22.5
	13-18	AQF3181MB	\$523.00	25.5	AQF3181SB	\$584.00	25.5
	19-24	AQF3241MB	\$583.00	28.5	AQF3241SB	\$645.00	28.5
	25-30	AQF3301MB	\$644.00	31.5	AQF3301SB	\$705.00	31.5
	31-36	AQF3361MB	\$704.00	34.5	AQF3361SB	\$765.00	34.5
	37-42	AQF3421MB	\$763.00	37.5	AQF3421SB	\$824.00	37.5
225	0-12	AQF3122MB	\$529.00	28.5	AQF3122SB	\$591.00	28.5
	13-18	AQF3182MB	\$565.00	31.5	AQF3182SB	\$627.00	31.5
	19-24	AQF3242MB	\$626.00	34.5	AQF3242SB	\$687.00	34.5
	25-30	AQF3302MB	\$686.00	37.5	AQF3302SB	\$747.00	37.5
	31-36	AQF3362MB	\$746.00	40.5	AQF3362SB	\$807.00	40.5
	37-42	AQF3422MB	\$805.00	43.5	AQF3422SB	\$867.00	43.5
400	0-12	AQF3124MB	\$745.00	37.5	AQF3124SB	\$913.00	43.5
	13-18	AQF3184MB	\$796.00	43.5	AQF3184SB	\$966.00	49.5
	19-24	AQF3244MB	\$851.00	40.5	AQF3244SB	\$1023.00	46.5
	25-30	AQF3304MB	\$910.00	46.5	AQF3304SB	\$1083.00	52.5
	31-36	AQF3364MB	\$970.00	49.5	AQF3364SB	\$1143.00	55.5
	37-42	AQF3424MB	\$1030.00	52.5	AQF3424SB	\$1203.00	58.5
600	0-12	AQF3126MB	\$886.00	43.5	—	—	—
	13-18	AQF3186MB	\$957.00	49.5	—	—	—
	19-24	AQF3246MB	\$1014.00	46.5	—	—	—
	25-30	AQF3306MB	\$1074.00	52.5	—	—	—
	31-36	AQF3366MB	\$1134.00	55.5	—	—	—
	37-42	AQF3426MB	\$1194.00	58.5	—	—	—
800 ⁶	0-12	AQF3128MB	\$1190.00	43.5	—	—	—
	13-18	AQF3188MB	\$1316.00	46.5	—	—	—
	19-24	AQF3248MB	\$1433.00	49.5	—	—	—
	25-30	AQF3308MB	\$1554.00	52.5	—	—	—
	31-36	AQF3368MB	\$1710.00	55.5	—	—	—
	36-42	AQF3428MB	\$1815.00	58.5	—	—	—

¹For 3-ph, 3-wire applications, no neutral supplied.

²3-ph, 4-wire 240/120Vac Hi-leg Delta panels not available as GE Fastrac™ Program.

³Bottom feed furnished as standard-change last character in Product Number from B to T for Top Feed.

⁴Single section interiors available up to 84 circuits. Consult Speedi or sales office for details.

⁵Includes standard panelbox interior, box and front. Add price for options when required.

⁶Box is 30" wide x 7.81" deep.

SPLIT BUS—Refer to publication DE-81 or consult your local sales office



Publications and Reference: See Section 22 for a complete list of additional product-related publications