

# Wafer™ LED

Recessed Downlighting for Shallow Ceiling Plenum Applications

## Ultra-Thin Recessed Downlighting with Remote Driver Box for Quick, Simple and Housing-Free Installations.

The 3", 4" and 6" Wafer LED Downlights combine high quality light output and efficiency while eliminating the need for recessed housings for competitive affordability. The innovative, slim design allows for easy retrofit, remodel or new construction installation from below the ceiling. **With its narrow design, the Wafer can be installed in applications with only 2" plenum clearance.** The LED Wafer downlight and remote driver are wet location approved, making them ideal for a breadth of both indoor and outdoor residential, hospitality, commercial and multifamily applications.

### Key Features:

- No housing needed
- IC rated – safe to install in direct contact with insulation
- Edge-lit LED technology provides even illumination
- Available in 2700K (square only), 3000K and 4000K color temperatures
- Dimmable to 10%
- Wet location listed


Learn more about the Wafer LED recessed module at [www.lithonia.com](http://www.lithonia.com)



# Wafer LED Recessed Downlight

The ultra-thin Wafer LED redefines recessed downlighting installations. With the narrow design and remote driver box, the Wafer LED can be installed in confined, hard to reach spaces such as closets, bathrooms, hallways, stairwells, outside soffits and other areas that would have been nearly impossible with traditional recessed housings.










**Make installation quick and simple with the LED Wafer series.**



## Ordering Information

EXAMPLE: WF4 LED 30K MW

### Wafer LED

Series	Lamp	CCT/CRI/W/Lumens	Finish	Accessories: Order as separate catalog number.
WF3	3" wafer-thin round LED downlight	30K 3000K/80CRI/8W/550L 40K 4000K/80CRI/7.9W/590L	MW Matte White MB Matte Black BN Brushed Nickel ORB Oil-Rubbed Bronze	WF3 PAN R12 3" new construction pan, retail pack of 12 WF4 PAN R12 4" new construction pan, retail pack of 12 WF6 PAN R12 6" new construction pan, retail pack of 12 WFJB R4 Remodel joist bar for 4" & 6", retail pack of 4 WFEXC6 U 6' FT4 cable WFEXC10 U 10' FT4 cable WFEXC20 U 20' FT4 cable
WF4	4" wafer-thin round LED downlight	30K 3000K/80CRI/9.6W/675L 40K 4000K/80CRI/10W/765L		
WF6	6" wafer-thin round LED downlight	30K 3000K/80CRI/13W/1020L 40K 4000K/80CRI/13.6W/1200L	 Matte White	  
		LL LED Low Lumen LED 27K 2700K/80CRI/12.7W/780L 30K 3000K/80CRI/12.6W/865L 40K 4000K/80CRI/12.9W/944L		
WF4 SQ B	4" wafer-thin square LED downlight, baffle trim	27K 2700K/80CRI/10.4W/610L 30K 3000K/80CRI/10.3W/620L 40K 4000K/80CRI/10.28W/650L	 Matte Black	
WF4 SQ S	4" wafer-thin square LED downlight, smooth trim	27K 2700K/80CRI/10.7W/610L 30K 3000K/80CRI/10.3W/620L 40K 4000K/80CRI/10.4W/650L	 Brushed Nickel	 
WF6 SQ B	6" wafer-thin square LED downlight, baffle trim	27K 2700K/80CRI/13.9W/860L 30K 3000K/80CRI/13.4W/880L 40K 4000K/80CRI/13.9W/920L	 Oil Rubbed Bronze	
WF6 SQ S	6" wafer-thin square LED downlight, smooth trim	27K 2700K/80CRI/13.9W/860L 30K 3000K/80CRI/13.4W/880L 40K 4000K/80CRI/13.9W/920L		



Visit [www.lithonia.com](http://www.lithonia.com) for more information.