

DESIGN+SERIES
DEBUT



P400015-009

A new category of vintage modern fixtures takes center stage. Delicate details and warm finish options, including Graphite and Brushed Nickel, create statement making focal pieces for a variety of interiors. Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.

FINISHES

- Brushed Nickel - 009
- Graphite - 143

PAIR WITH

Wemberly Archives

ALSO AVAILABLE IN

Bath & Vanity



ONE-LIGHT WALL SCNCE

P300008-009 Brushed Nickel
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-009 Brushed Nickel
27-1/2" dia., 30" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-009 Brushed Nickel
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-009 Brushed Nickel
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.



P860002-001



P860003-001



P350036-009



P400015-009
shown with
P860003-001 shade



P400017-009
shown with
P860002-001 shade



P300008-009



P300008-009
shown with
P860002-001 shade



P400016-009



P400015-143 with
P860002-001 shade

DESIGN+SERIES DEBUT

ONE-LIGHT WALL SCNCE

P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-143 Graphite
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-143 Graphite
27-1/2" dia., 30" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-143 Graphite
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-143 Graphite
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.



P860002-001



P860003-001



P350036-143
shown with
P860002-001 shade



P400015-143



P400017-143
shown with
P860003-001 shade



P300008-143



P300008-143
shown with
P860003-001 shade



P400016-143

DESIGN+SERIES
DEBUT



P300009-143

A new category of vintage modern fixtures takes center stage. Delicate details and warm finish options, including Graphite and Brushed Nickel, create statement making focal pieces for a variety of interiors. Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.

FINISHES

- Brushed Nickel - 009
- Graphite - 143

ALSO AVAILABLE IN
Fixture Collections



P300008-009



P300008-009
Shown with seeded glass shade P860003-001



P300009-009



P300009-009
Shown with etched glass shade P860002-001



P300010-009
Shown with etched glass shade P860002-001



P300008-143



P300009-143



P300010-143
Shown with seeded glass shade P860003-001



P300011-143
Shown with etched glass shade P860002-001



P300010-009
Shown with seeded glass shade P860003-001



P300011-009

ONE-LIGHT BATH
P300008-009 Brushed Nickel
P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300009-009 Brushed Nickel
P300009-143 Graphite
14-1/4" W., 7-7/8" ht.
Extends 5-3/4". H/CTR 5-5/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300010-009 Brushed Nickel
P300010-143 Graphite
23-3/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300011-009 Brushed Nickel
P300011-143 Graphite
30-1/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Four medium base lamps,
each 60w max.

P860002-001
Etched glass shade.

P860003-001
Seeded glass shade.

Fixtures are shown with P7825-01 vintage lamps.



P860002-001



P860003-001

DESIGN+SERIES
DEBUT

Vintage modern design can be used with bare bulbs or with optional etched or clear seeded glass shades.



P350036-009



P350036-143

THREE-LIGHT SEMI-FLUSH

P350036-009 Brushed Nickel

P350036-143 Graphite

19-7/8" dia., 15" ht.

Overall ht. w/chain 52"; wire 10'.

Three medium base lamps, each 60w max.

ACCESSORY SHADE

P860002-001 Etched Seeded Glass

4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear Seeded Glass

4-1/4" dia., 5-7/8" ht.



P350036-009
*Shown with
P860002-001
optional shade*



P350036-143
*Shown with
P860003-001
optional shade*



P860002-001



P860003-001

*Shown with P7825-01
vintage lamps, page 832.*