



Straight Blade Devices
50 Ampere, 125/250 Volts, 3Ø 250 and 120/208 Volts AC
 3 Pole, 4 Wire Grounding and 4 Pole, 4 Wire Non-Grounding
Single Receptacles and Plugs




HBL9450A



HBL9451C



HBL9452C



HBL8350A

50A, 125/250V
3 Pole, 4 Wire Grounding
Receptacles and Plugs

IP20
SUITABILITY



50A 125/250V
NEMA 14-50R
 UL CSA
 3(2) HP



50A 125/250V
NEMA 14-50P
 UL CSA
 3(2) HP

Description	Cord Diameter	Catalog Numbers
Receptacle, black RTP.	-	HBL9450A -
Plug, nylon.	.625"-1.310" (15.9-33.3)	- HBL9451C
Plug, nylon, angle, 4-position.	.625"-1.310" (15.9-33.3)	- HBL9452C

50A, 3Ø 250V AC
3 Pole, 4 Wire Grounding
Receptacles and Plugs

IP20
SUITABILITY



50A 3Ø 250V AC
NEMA 15-50R
 UL CSA
 7.5 HP



50A 3Ø 250V AC
NEMA 15-50P
 UL CSA
 7.5 HP

Description	Cord Diameter	Catalog Numbers
Receptacle, black RTP.	-	HBL8450A -
Plug, nylon.	.625"-1.310" (15.9-33.3)	- HBL8451C
Plug, nylon, angle, 4-position.	.625"-1.310" (15.9-33.3)	- HBL8452C



50A, 3ØY 120/208V AC
4 Pole, 4 Wire Non-Grounding
Receptacles and Plugs

IP20
SUITABILITY



50A 3ØY
120/208V AC
NEMA 18-50R
 UL Listed
 7.5 HP



50A 3ØY
120/208V AC
NEMA 18-50P
 UL Listed
 7.5 HP

Description	Cord Diameter	Catalog Numbers
Receptacle, black RTP.	-	HBL8350A -
Plug, nylon, angle, 4-position.	.625"-1.310" (15.9-33.3)	- HBL8352C

Notes: See page A-47 for accessories.
 RTP is an abbreviation for reinforced thermoplastic polyester.