

naturalLED®

Turning Light into Savings ▶▶▶



G, A19, A21, Candle DECORATIVE

6W, 9W, 10W, 12W, 15W

With a full array of A lamps, naturalLED® offer various replacement for incandescent lamps. Direct replacement lamps for your decorative lighting, which is free of mercury and lead, UL listed and dimmability functions.

Our A19 comes in the choice of 6 watt, 9 watt, 10 watt and 12 watt to replace your existing incandescent up to 75 watt, saving up to 84% of energy. Introducing our new 15 watt A21 replaces your existing incandescent up to 100 watt. It is a great value energy efficient lamp, using less energy and lasts up to 25,000 hours average life.

naturalLED® lamps are ideal lighting solution for track lights, display lights, hotel boutiques, residential, retail, museum lighting and any hospitality applications.

Key Features & Benefits

- ▶ Direct replacement and Instant On
- ▶ Up to 84% energy savings
- ▶ Contains no mercury or lead
- ▶ UL/cUL Listed
- ▶ Rated 15,000~25,000 hours average life
- ▶ 3 Years Limited Warranty

Applications

- ▶ Display Case Lighting
- ▶ Track Lighting
- ▶ Recessed Downlight
- ▶ Accent Lighting
- ▶ General Lighting
- ▶ Residential Lighting
- ▶ Restaurant Lighting

Color Choice



White

Qualifications



Item Code	Description	Bulbs	Color Temp	Wattage	Lumen Output	Equivalent Wattage	CRI	Finish	Beam Angle	Rated Hours	Dimmable	
-----------	-------------	-------	------------	---------	--------------	--------------------	-----	--------	------------	-------------	----------	---

A19

5946	LED6A19/48L/827	A19	2700K	6	450	40	>80	Coated	Omni	25,000	•	•
5919	LED6A19/48L/830	A19	3000K	6	450	40	>80	Coated	Omni	25,000	•	•
5947	LED6A19/48L/840	A19	4000K	6	450	40	>80	Coated	Omni	25,000	•	•
5948	LED6A19/48L/850	A19	5000K	6	450	40	>80	Coated	Omni	25,000	•	•
5920	LED9A19/80L/827	A19	2700K	9	800	60	>80	Coated	Omni	25,000	•	•
5976	LED9A19/80L/830	A19	3000K	9	800	60	>80	Coated	Omni	25,000	•	•
5921	LED9A19/80L/840	A19	4000K	9	800	60	>80	Coated	Omni	25,000	•	•
5922	LED9A19/80L/850	A19	5000K	9	800	60	>80	Coated	Omni	25,000	•	•
5859	LED10A19/80L/927	A19	2700K	10	800	60	>80	Coated	Omni	25,000	•	•
5860	LED12A19/110L/827	A19	2700K	12	1,100	75	>80	Coated	Omni	25,000	•	•
5977	LED12A19/110L/830	A19	3000K	12	1,100	75	>80	Coated	Omni	25,000	•	•
5831	LED12A19/110L/840	A19	4000K	12	1,100	75	>80	Coated	Omni	25,000	•	•
5832	LED12A19/110L/850	A19	5000K	12	1,100	75	>80	Coated	Omni	25,000	•	•

A19-GU24

5923	LED9A19/80L/GU24/827	A19	2700K	9	800	60	>80	Coated	Omni	25,000	•	•
------	----------------------	-----	-------	---	-----	----	-----	--------	------	--------	---	---

A19 for Enclosed Fixture

5918	LED9A19/EC/80L/GU24/827	A19	2700K	9	800	60	>80	Coated	Omni	25,000	•	•
5980	LED9A19/EC/80L/827	A19	2700K	9	800	60	>80	Coated	Omni	25,000	•	•
5981	LED9A19/EC/80L/840	A19	4000K	9	800	60	>80	Coated	Omni	25,000	•	•






A21

5957	LED15A21/160L/827	A21	2700K	15	1,600	100	>80	Coated	Omni	25,000	•	•
5962	LED15A21/160L/830	A21	3000K	15	1,600	100	>80	Coated	Omni	25,000	•	•
5963	LED15A21/160L/840	A21	4000K	15	1,600	100	>80	Coated	Omni	25,000	•	•
5964	LED15A21/160L/850	A21	5000K	15	1,600	100	>80	Coated	Omni	25,000	•	•

Candelabra / Globe

5837	LED5CAB/32L/E12/27K	Candle	2700K	5	325	40	>80	Clear	Candle	15,000	•	•
5838	LED5CAB/32L/E12/30K	Candle	3000K	5	325	40	>80	Clear	Candle	15,000	•	•
5839	LED5CAB/32L/E12/50K	Candle	5000K	5	325	40	>80	Clear	Candle	15,000	•	•
5814	LED6G25/45L/27K	G25	2700K	6	450	40	>80	Coated	Flood	15,000	•	•

► Dimensions

	Item	A	B		Weight (lbs)
	6 watt	2.35-in	4.30-in	--	0.20
	9 watt	2.35-in	4.60-in	--	0.30
	GU24 Base	3.10-in	4.70-in	--	0.30
	12/15 watt	3.10-in	4.70-in	--	0.30
	Globe	3.10-in	4.70-in	--	0.30
	Candle	1.50-in	3.70-in	--	0.10

► Master Carton Package

