

ELXN400 LED Series

Low energy and low maintenance for moderate budget application



Housing

- UV stabilized thermoplastic body
- Fully adjustable Cluster™ LED glare-free heads
- 6 inch EXIT lettering legend, available in red or green
- Field selectable chevrons

Mounting

- Surface mount
- Canopy included for ceiling mount applications
- Universal J-box mounting finishes

Type of battery

- 3.6V nickel-cadmium battery

Lamp head source

- White LED 3.6V-1.8W each

Electronics

- Optional Advanced Diagnostics
- 120/277 60Hz

Approvals


- UL 924 listed
- Damp location 50°F to 104°F (10°C to 40°F)
- UL 94, 5VA flame rated

Warranty (subject to proper installation and maintenance)

- Unit has a three-year warranty
- Detailed warranty terms located on page 178 or online at:
www.emergi-lite.com/usa/files/EL_Warranty.pdf


Photometric performance

Spacing center-to-center (feet)	
7' mounting height	15' mounting height
15'	4'



Dimensions

Dimensions are approximate and subject to change.



Power consumption

Model	Current (A) / Power (W) 120/277VAC, 60Hz
ELXN400R-2LED	0.044/0.017A
ELXN400G-2LED	0.032/0.015A
ELXN400R-2LEDR	0.037/4.06A
ELXN400G-2LEDR	0.036/3.8A
ELXN400R_2LEDR-AD	0.038/0.017A
ELXN400G_2LEDR-AD	0.038/0.017A

How to order

Series	Legend color	Lamp	Options	Color
ELXN400= ELX Combo Series	R= Red exit G= Green exit	-2LED= Round LED array	Blank= No option R= 3.6W remote capacity to power one double head remote ¹ R-AD= 3.6W remote capacity to power one double head dedicated remote with Advanced-Diagnostics ¹	Blank= White B= Black

Example: ELXN400R-2LED

¹Remote capacity can only be used to power the EF43D or EF44D remote fixtures or to extend the battery units emergency run time beyond the standard 90 minutes.

Accessories (order as a separate item)

Description	Suffix
Wire guard	WG10-E
Battery	850.0110-E

EF43D & EF44D Series

Low energy and low maintenance for moderate budget application




The Cluster™ LED EF43D-LED or EF44D-LEDWP

The Cluster™ LED EF43D-LED or EF44D-LEDWP Remote head can ONLY be powered from the ELXN400 LED series combo or EL-2LED battery units of the same family. Used for internal or external applications, the indoor remote head draws 3.6V-3.6W and Weather-Proof head draws 3.6V-3.8W.




Photometric performance

Spacing center-to-center (feet)	15' mounting height
7' mounting height	4'
15'	4'



Dimensions

Dimensions are approximate and subject to change.



How to order

Series	# of lamps	Lamp	Option
EF43= Indoor series	D= 2	-LED= round LED array	Blank= Indoor remote
EF44= Outdoor weather-proof series			WP= Outdoor weather proof remote

Example: EF43D-LED