

naturalLED®

Turning Light into Savings ▶▶▶



SAL Slim Area Light

29W, 50W, 75W, 100W
180W, 240W, 360W

naturalLED® Slim Area Light constructed with durable, die-cast aluminum housing and excellent thermal design. Our SAL series are low profile replacements for up to 1,000 watt existing Metal Halide and HPS area lighting. Our SAL features a high efficiency LED driver with high lumens and long life LED chip. With excellent optical design improves light distribution and evenness. Perfect for parking lots, streets, walkways, streetscape, and providing you with uniform and consistent color.

Our fixtures are DLC 4.0 Premium and IP65 rated with four installation methods including: Swivel Bracket, Slip Fitter, 6" Extruded Arm and Yoke Mount. Compatible Integrated autonomous and photocell motion sensors are available as options to address your needs.



Key Features & Benefits

- ▶ DLC 4.0 Premium
- ▶ IP65
- ▶ Uniform and consistent color
- ▶ Aluminum die cast housing
- ▶ Excellent thermal design
- ▶ CRI:70
- ▶ Universal Voltage 120-277V
- ▶ Operating Temp: -22°F~122°F
- ▶ 50,000 Hours rated average life
- ▶ 1-10V dimming
- ▶ Motion sensor compatible
- ▶ Photocell sensor compatible

Applications

- ▶ Parking Lot Lighting
- ▶ Street Lighting
- ▶ Site Lighting
- ▶ Streetscape Lighting
- ▶ Area Lighting

2 Color Choices






















































































































































Dark Bronze






























White

Qualifications




Item Code	Description	Color Temp	Wattage	Lumen Output	Equivalent Wattage	Voltage (V)	CRI	Beam Angle	Color			
29W - 100W												
7616	LED-FXSAL29/40K/DB/3S	4000K	29	3190	100-150	120-277	70	Type 3	Dark Bronze			
7617	LED-FXSAL29/50K/DB/3S	5000K	29	3190	100-150	120-277	70	Type 3	Dark Bronze			
7618	LED-FXSAL29/40K/WH/3S	4000K	29	3190	100-150	120-277	70	Type 3	White			
7619	LED-FXSAL29/50K/WH/3S	5000K	29	3190	100-150	120-277	70	Type 3	White			
7620	LED-FXSAL50/40K/DB/3S	4000K	50	5750	250	120-277	70	Type 3	Dark Bronze			
7621	LED-FXSAL50/50K/DB/3S	5000K	50	5750	250	120-277	70	Type 3	Dark Bronze			
7622	LED-FXSAL50/40K/WH/3S	4000K	50	5750	250	120-277	70	Type 3	White			
7623	LED-FXSAL50/50K/WH/3S	5000K	50	5750	250	120-277	70	Type 3	White			
7624	LED-FXSAL75/40K/DB/3S	4000K	75	8625	250-400	120-277	70	Type 3	Dark Bronze			
7625	LED-FXSAL75/50K/DB/3S	5000K	75	8625	250-400	120-277	70	Type 3	Dark Bronze			
7626	LED-FXSAL75/40K/WH/3S	4000K	75	8625	250-400	120-277	70	Type 3	White			
7627	LED-FXSAL75/50K/WH/3S	5000K	75	8625	250-400	120-277	70	Type 3	White			
7628	LED-FXSAL100/40K/DB/3S	4000K	100	12000	400	120-277	70	Type 3	Dark Bronze			
7629	LED-FXSAL100/50K/DB/3S	5000K	100	12000	400	120-277	70	Type 3	Dark Bronze			
7630	LED-FXSAL100/40K/WH/3S	4000K	100	12000	400	120-277	70	Type 3	White			
7631	LED-FXSAL100/50K/WH/3S	5000K	100	12000	400	120-277	70	Type 3	White			
7644	LED-FXSAL29/40K/DB/5S	4000K	29	3190	100-150	120-277	70	Type 5	Dark Bronze			
7645	LED-FXSAL29/50K/DB/5S	5000K	29	3190	100-150	120-277	70	Type 5	Dark Bronze			
7646	LED-FXSAL29/40K/WH/5S	4000K	29	3190	100-150	120-277	70	Type 5	White			
7647	LED-FXSAL29/50K/WH/5S	5000K	29	3190	100-150	120-277	70	Type 5	White			
7648	LED-FXSAL50/40K/DB/5S	4000K	50	5750	250	120-277	70	Type 5	Dark Bronze			
7649	LED-FXSAL50/50K/DB/5S	5000K	50	5750	250	120-277	70	Type 5	Dark Bronze			
7650	LED-FXSAL50/40K/WH/5S	4000K	50	5750	250	120-277	70	Type 5	White			
7651	LED-FXSAL50/50K/WH/5S	5000K	50	5750	250	120-277	70	Type 5	White			
7652	LED-FXSAL75/40K/DB/5S	4000K	75	8625	250-400	120-277	70	Type 5	Dark Bronze			
7653	LED-FXSAL75/50K/DB/5S	5000K	75	8625	250-400	120-277	70	Type 5	Dark Bronze			
7654	LED-FXSAL75/40K/WH/5S	4000K	75	8625	250-400	120-277	70	Type 5	White			
7655	LED-FXSAL75/50K/WH/5S	5000K	75	8625	250-400	120-277	70	Type 5	White			
7656	LED-FXSAL100/40K/DB/5S	4000K	100	12000	400	120-277	70	Type 5	Dark Bronze			
7657	LED-FXSAL100/50K/DB/5S	5000K	100	12000	400	120-277	70	Type 5	Dark Bronze			
7658	LED-FXSAL100/40K/WH/5S	4000K	100	12000	400	120-277	70	Type 5	White			
7659	LED-FXSAL100/50K/WH/5S	5000K	100	12000	400	120-277	70	Type 5	White			
180W - 360W												
7632	LED-FXSAL180/40K/DB/3S	4000K	180	21600	400-575	120-277	70	Type 3	Dark Bronze			
7633	LED-FXSAL180/50K/DB/3S	5000K	180	21600	400-575	120-277	70	Type 3	Dark Bronze			
7634	LED-FXSAL180/40K/WH/3S	4000K	180	21600	400-575	120-277	70	Type 3	White			
7635	LED-FXSAL180/50K/WH/3S	5000K	180	21600	400-575	120-277	70	Type 3	White			
7636	LED-FXSAL240/40K/DB/3S	4000K	240	28800	750-1000	120-277	70	Type 3	Dark Bronze			
7637	LED-FXSAL240/50K/DB/3S	5000K	240	28800	750-1000	120-277	70	Type 3	Dark Bronze			
7638	LED-FXSAL240/40K/WH/3S	4000K	240	28800	750-1000	120-277	70	Type 3	White			
7639	LED-FXSAL240/50K/WH/3S	5000K	240	28800	750-1000	120-277	70	Type 3	White			
7640	LED-FXSAL360/40K/DB/3S	4000K	360	43200	1000-1250	120-277	70	Type 3	Dark Bronze			
7641	LED-FXSAL360/50K/DB/3S	5000K	360	43200	1000-1250	120-277	70	Type 3	Dark Bronze			
7642	LED-FXSAL360/40K/WH/3S	4000K	360	43200	1000-1250	120-277	70	Type 3	White			
7643	LED-FXSAL360/50K/WH/3S	5000K	360	43200	1000-1250	120-277	70	Type 3	White			
7660	LED-FXSAL180/40K/DB/5S	4000K	180	21600	400-575	120-277	70	Type 5	Dark Bronze			
7661	LED-FXSAL180/50K/DB/5S	5000K	180	21600	400-575	120-277	70	Type 5	Dark Bronze			
7662	LED-FXSAL180/40K/WH/5S	4000K	180	21600	400-575	120-277	70	Type 5	White			
7663	LED-FXSAL180/50K/WH/5S	5000K	180	21600	400-575	120-277	70	Type 5	White			

Item Code	Description	Color Temp	Wattage	Lumen Output	Equivalent Wattage	Voltage (V)	CRI	Beam Angle	Color			
7664	LED-FXSAL240/40K/DB/5S	4000K	240	28800	750-1000	120-277	70	Type 5	Dark Bronze			
7665	LED-FXSAL240/50K/DB/5S	5000K	240	28800	750-1000	120-277	70	Type 5	Dark Bronze			
7666	LED-FXSAL240/40K/WH/5S	4000K	240	28800	750-1000	120-277	70	Type 5	White			
7667	LED-FXSAL240/50K/WH/5S	5000K	240	28800	750-1000	120-277	70	Type 5	White			
7668	LED-FXSAL360/40K/DB/5S	4000K	360	43200	1000-1250	120-277	70	Type 5	Dark Bronze			
7691	LED-FXSAL360/50K/DB/5S	5000K	360	43200	1000-1250	120-277	70	Type 5	Dark Bronze			
7670	LED-FXSAL360/40K/WH/5S	4000K	360	43200	1000-1250	120-277	70	Type 5	White			
7671	LED-FXSAL360/50K/WH/5S	5000K	360	43200	1000-1250	120-277	70	Type 5	White			

Mounting

P10101	MT-SAL/SF/DB	Slip Fitter
P10103	MT-SAL/SB/DB	Swivel Bracket
P10105	MT-SAL/EA6/DB	6" Extended Arm Dark
TBD	TBD	Yoke Mount

► Dimensions

	Wattage	A	B	C	Weight
	29 50 75 100	13.38-in	8.66-in	2.56-in	- lbs
<p style="text-align: center;">Coming soon</p>	Wattage	A	B	C	Weight
	180 240 360				

► Master Carton Package

