

UNION SQUARE

Originally inspired by historical reproduction gas lanterns, Union Square now offers a four-light chandelier and five-light linear island fixture. The simple geometric form features a Stainless Steel frame that is paired with vintage-style light bulbs. Mechanical details such as exaggerated knobs provide character to the form.

ALSO AVAILABLE IN

- Bath & Vanity
- Outdoor



P400112-135



P400112-135

FINISH
 ● Stainless Steel - 135

FOUR-LIGHT CHANDELIER
P400112-135 Stainless Steel
 20" W., 9-3/4" ht.
 Overall ht. w/stem 76-1/2", wire 15'.
 Four medium base lamps,
 each 60w max.

FIVE-LIGHT ISLAND
P400145-135 Stainless Steel
 38" W., 9-3/4" ht., 8-1/2" d.
 Overall ht. w/stem 76", wire 15'.
 Five medium base lamps,
 each 60w max.



P400145-135

UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open bottom on wall lanterns provides easy access for cleaning and relamping.



ALSO AVAILABLE IN
Bath Collections



P560005-135



P560004-135



P560005-135



P560006-135



P550018-135



P550007-135

FINISH
● Stainless Steel - 135

FLUSH MOUNT
P550007-135 Stainless Steel
12-3/8" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

SMALL WALL-LANTERN
P560004-135 Stainless Steel
6-1/2" W., 15-7/8" ht.
Extends 5-1/2". H/CTR 6-1/4".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN
P560005-135 Stainless Steel
7-7/8" W., 19-3/8" ht.
Extends 6-1/2". H/CTR 7-3/4".
One medium base lamp,
100w max.

LARGE WALL-LANTERN
P560006-135 Stainless Steel
9-3/4" W., 23-5/8" ht.
Extends 8". H/CTR 9-5/8".
One medium base lamp,
100w max.

OUTDOOR HANGING LANTERN
P550018-135 Stainless Steel
7" sq., 27-3/8" ht.
Overall ht. w/chain 102-1/2", wire 10'.
One medium base lamp,
100w max.

*Fixtures shown with P7827-01
vintage lamps*

UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open top and bottom on fixture provides easy access for cleaning and relamping.



ALSO AVAILABLE IN

Outdoor



P300135-135
shown with P7825-01
vintage lamps



P710038-135
shown with P7825-01
vintage lamp



P710038-135
shown with P7827-01
vintage lamp



P300135-135
shown with P7825-01
vintage lamps



P300135-135
shown with P7827-01
vintage lamps



P300135-135
shown with P7825-01
vintage lamps



P300136-135
shown with P7825-01
vintage lamps



P300136-135
shown with P7827-01
vintage lamps

FINISH

● Stainless Steel - 135

TWO-LIGHT BATH

P300135-135 Stainless Steel
16" W., 4-1/2" ht.
Extends 5". H/CTR 2-1/4".
Two medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300136-135 Stainless Steel
30" W., 4-1/2" ht.
Extends 5". H/CTR 2-1/4".
Four medium base lamps,
each 60w max.

ONE-LIGHT BRACKET

P710038-135 Stainless Steel
5-1/4" sq., 12" ht.
Extends 5". H/CTR 6".
One medium base lamp,
60w max.

Mounts horizontal or vertical.



P300136-135
shown with P7827-01
vintage lamps