


TWIST-LOCK® Devices

3 Pole, 4 Wire Grounding

50 Ampere, 125/250 Volts, 3Ø 250 and 3Ø 480V AC

Receptacles, Connector Bodies, Plugs and Flanged Inlets




CS6369



CS6364C



CS6365C



CS6375



HBL7774WO



**50A
125/250V
UL/CSA**



**50A 3Ø
250V AC
UL/CSA**



**50A 3Ø
480V AC
UL/CSA**

Receptacles

Description	Catalog Numbers		
Black melamine.	CS6369	CS8369	CS8169

Connector Bodies IP20 SUITABILITY

Description	Catalog Numbers		
Nylon cover, Rynite® interior.	CS6364C	CS8364C	CS8164C

Note: Cord clamp range .920"-1.2" (23.681-30.48).



**50A
125/250V
UL/CSA**



**50A 3Ø
250V AC
UL/CSA**



**50A 3Ø
480V AC
UL/CSA**

Plugs IP20 SUITABILITY

Description	Catalog Numbers		
Nylon cover, Rynite interior.	CS6365C	CS8365C	CS8165C

Note: Cord clamp range .920"-1.2" (23.681-30.48).

Flanged Inlets

Description	Catalog Numbers		
Zinc plated steel casing, Rynite interior.	CS6375***	CS8375	CS8175

Note: ***See page V-12 for weatherproof inlet.

Accessories

Weatherproof Boots IP55** SUITABILITY

Description	Catalog Numbers
Seal-Tite® triple seal black elastomeric cover for plugs when used in a cord set and connector bodies when used with flanged inlets.	HBL7716C*
Seal-Tite triple seal black elastomeric cover for connector bodies when used with cord sets.	HBL7717C*

Note: Boots shown on page B-74.

Weatherproof Receptacle Cover Plates

Description	Catalog Numbers
Gray thermoplastic, corrosion resistant.	HBL7774WO
Yellow thermoplastic, corrosion resistant.	HBL7774WO

Receptacle Wall Plate & Box Cover

Description	Catalog Number
Stainless steel 302/304, smooth.	S750
Galvanized Steel fits 4" square, 4 11/16" or 2 gang box	HBL50SC

Closure Plug for 50A Inlets

Description	Catalog Number
Black closure plug.	HBL4892*

Notes: For additional accessories see page B-74.

For technical information see page B-85.

**When installed and used properly with plug and connector body combination.

* Not UL Listed, CSA Certified.

®Rynite is a registered trademark of E. I. Dupont