



Temporary Lighting

When day turns to night, light the site with Coleman Cable's temporary job-site lighting for general, commercial or industrial construction sites. CCI offers a complete line of temporary lighting products. Choose from Luma-Site® 400W NEC Compliant metal halide or Cord-O-Lite™ incandescent string lights.

The Luma-Site® pulse start metal halide lamp saves energy and labor costs with a NEC Compliant Type "O" 400W bulb that lasts over 20,000 hours and emits 36,000 initial lumens. It substantially increases light levels without increasing energy costs. This makes them ideal for convention centers, retail, commercial and industrial applications or wherever high light output is required.

Cord-O-Lite™ string lights are durable indoor/outdoor temporary lighting systems, available in 50 ft. and 100 ft. lengths, and 12 or 14 gauge cords. They come in coated metal or easy to open, snap-on plastic guards to meet contractor demands.



Features & Benefits


- UL Listed, NEC Compliant and OSHA Compliant
- Meets Energy Independence Security Act of 2007 - EISA (pt# 07605)
- Provides Easy, Fast and Secure Installations
- Heavy-Duty Design to Withstand Harsh Job-Site Conditions
- Metal Halide or Incandescent

LUMA-SITE®
CORD-O-LITE™

Metal Halide Temporary Lights

LUMA-SITE®

- Pulse start lamp
- NEC Compliant
- UL/cUL Listed
- Energy Independence Security Act 2007 (EISA)
- 36,000 initial lumens
- 20,000 hours of bulb life
- Fast plug-in installation & spring loaded hook
- Knock-outs for hard wire & local codes



Part #	Length	Watts	Guard	Bulb	Pallet Qty
07605-88-00	6 ft	400	10" Wire Guard	Type "O"	16

NOW IN STOCK

NEW Pulse Start Metal Halide Lamp Features:

- Energy Independence Security Act 2007 (EISA)
- 50% faster warm-up
- Hot restart in less than half the time of a standard probe start metal halide system
- Longer lamp life

Incandescent Temporary Lighting

CORD-LITE™

- NEC Compliant
- UL Listed
- OSHA Compliant
- Pre-assembled guards onto molded sockets save time and labor expense on the job-site
- Easy and fast installation
- Heavy-duty design able to withstand harsh job-site conditions



Part #	Length	Description	Guard	Bulb	Pallet Qty
07538-88-02	50 ft.	12/3 SJTW 300V	Coated Metal	A-23	30
07539-88-02	100 ft.	12/3 SJTW 300V	Coated Metal	A-23	20
07548-88-02	50 ft.	12/3 SJTW 300V	Plastic	A-23	30
07549-88-02	100 ft.	12/3 SJTW 300V	Plastic	A-23	20
07145-88-02	100 ft.	14/2 SJTW 300V	Plastic	A-23	20

Cross Reference

Coleman Cable	07145	07548	07549	07538	07539
Ericson®	142100	12350STWY-1L	123100STWY-1L	12350STWY-1W	123100STWY-1W
Woodhead®	5000	-	5002	5003	-
McGill®	2252-0012	-	2252-0026	-	-
CEP	94132	96135	96132	-	-

07145 Installation is a Snap!

