



GTL LED Recessed Troffer

LBL LED Wraparound

## Step up to LED without breaking the bank!

The Contractor Select® GTL LED recessed troffer and LBL LED surface-mount wraparound from Lithonia Lighting® present two affordable LED options for general-purpose ambient lighting. Built on tried-and-true GT troffer and LB low-profile basket wraparounds, these LED luminaires are priced for the budget-conscious.

LED technology ensures reliable color consistency and extended service life of at least 50,000 hours. Less input watts and no lamp maintenance minimize your total cost of ownership.

- Common appearances to complement existing design applications
- 2'x4' GTL LED replaces 2-lamp T8; 2'x2' GTL LED replaces 2- to 4-lamp T8; and, LBL LED replaces 2-lamp T8
- LED technology with MVOLT (120-277V) driver
- 0-10V Dimming on the GTL LED Troffer
- Multiple lumen packages
- *Best Value in Lighting®*



CONTRACTOR  
**SELECT**



## Affordable LED from the company you have relied on for over 65 years. What will you light next?



### GTL LED Recessed Troffer

- Available in 2'x2' and 2'x4' configurations, 3700 and 4000 lumens, respectively
- 3500K and 4000K
- 0-10V dimming
- DLC qualified product
- Pattern 12 prismatic lens
- Ideal for grid ceilings

50,000 HOURS | MVOLT | 3700 LUMENS | 4000 LUMENS | 43 INPUT WATTS | 3500K TEMP | 4000K TEMP | 82 CRI



### LBL LED Surface-Mount Wraparound

- Available in 2' and 4' configurations, 2000 and 4000 lumens, respectively
- 3500K and 4000K
- 4' configuration is a DLC qualified product
- Lift and shift diffuser
- Pattern 12 acrylic with linear side prisms
- Suitable for all surface-mount applications

50,000 HOURS | MVOLT | 2000 LUMENS | 4000 LUMENS | 50 INPUT WATTS | 26 INPUT WATTS | 3500K TEMP | 4000K TEMP | 82 CRI

#### ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Example: 2GTL4 LP835

Contractor Select <b>GTL LED Recessed Troffer</b>									
Series	Door	Lens	Voltage	Color Temperature	Options				
<b>2GTL2</b>	2'x2' recessed LED Luminaire Nominal 3700 lumens, 43 input watts <sup>1</sup> .	(blank) Flush steel, white	(blank) #12 pattern acrylic	(blank) MVOLT (120-277V) 347V 347V	<b>LP835</b> 82 CRI, 3500 Kelvin <b>LP840</b> 82 CRI, 4000 Kelvin				
<b>2GTL4</b>	2'x4' recessed LED Luminaire Nominal 4000 lumens, 43 input watts <sup>1</sup> .								

Example: LBL2 LP835

Contractor Select <b>LBL LED Wraparound</b>						
Series	Lens	Voltage	Color Temperature	Options		
<b>LBL2</b>	2' surface-mount LED Wraparound Nominal 2000 lumens, 26 input watts <sup>1</sup> .	(blank) #12 pattern acrylic with linear side prisms	(blank) MVOLT (120-277V) 347V 347V	<b>LP835</b> 82 CRI, 3500 Kelvin <b>LP840</b> 82 CRI, 4000 Kelvin		
<b>LBL4</b>	4' surface-mount LED Wraparound Nominal 4000 lumens, 50 input watts <sup>1</sup> .					

Notes: <sup>1</sup> Actual wattage may differ by +/- 5% when operating between 120-277V +/- 10%.

Need more out of your LED luminaire? Don't forget our specification TL Series LED troffer!

### NOT QUITE READY FOR LED?

Be sure to check out our competitive fluorescent Contractor Select Lensed Troffers and Curved-Basket Wraps on [Lithonia.com](http://Lithonia.com).

