





Kindorf® Pipe Supports



Interchangeable strap fits both 1 1/2" and 1 3/4"



All Kindorf Straps are pre-assembled for easy handling and sorting

C-105 and C-106 Pipe Straps

Kindorf Pipe Straps are designed to be bolt twist inserted anywhere along the slot side of the channel. Pipes can be placed as closely as pipe couplings permit.

Some unique features of the straps include:

- Bolt head is combination slot and hex head for flexibility of attachment.

- Square nut is captivated on the shoulder for easy one-handed tightening.
- Straps are interchangeable with 1 5/8" strut, for broader application.
- Straps are shipped assembled so counting and sorting are easier.
- Pipe or conduit sizes are shown on the strap for easy identification.



Kindorf Straps for Rigid Conduit, IMC and Pipe

Steel Straps – Galv-Kröm Finish

Cat. No.	Rigid Conduit or Pipe Size	O.D. Size (In.)	Steel Strap Thickness	Design Load (lbs.)	Wt. lbs./C
C-105-3/8	3/8"	0.675	14 ga.	750	12
C-105-1/2	1/2"	0.840	14 ga.	750	13
C-105-3/4	3/4"	1.050	14 ga.	750	15
C-105-1	1"	1.315	14 ga.	750	17
C-105-1-1/4	1 1/4"	1.660	14 ga.	800	19
C-105-1-1/2	1 1/2"	1.900	12 ga.	800	28
C-105-2	2"	2.375	12 ga.	800	31
C-105-2-1/2	2 1/2"	2.875	12 ga.	1000	36
C-105-3	3"	3.500	12 ga.	1650	42
C-105-3-1/2	3 1/2"	4.000	11 ga.	1650	56
C-105-4	4"	4.500	11 ga.	1650	64
C-105-4-1/2	4 1/2"	5.000	11 ga.	1650	72
C-105-5	5"	5.563	11 ga.	1650	76
C-105-6	6"	6.625	11 ga.	1650	89
C-105-8	8"	8.625	11 ga.	1650	114
C-105-10	10"	10.750	10 ga.	1650	160
C-105-12	12"	12.750	10 ga.	1650	165





Figure 1




Figure 2

C105, C106 and C107 pipe straps are specifically designed to work with all brands of channel that have a rolled lip design (figure 1). Should you need to install pipe straps on old style Kindorf channel (figure 2) see table on page K40 to determine the strap to use with each diameter of conduit pipe.

K

Kindorf®