


# Lamp Guards




## Cat# BC-200 "Standard Cage"

- High strength, impact-resistant thermoplastic
- Standard collar
- Fits most Temporary Light lampholders
- Fits pigtail lampholders
- Designed for easy installation & faster re-lamping
- New tight fitting locking device
- 200 watt max type "A" bulb
- Packaged 100 per carton



## Cat# EC-200 "Keyless Cage"

- High strength, impact-resistant thermoplastic
- Adjustable collar
- Fits ceiling lampholders
- Fits metal shell lampholders
- Fits pigtail lampholders
- Fits sign & scoreboard Attachon lampholders
- Easy-open guard for relamping without removing guard
- 200 watt max type "A" bulb
- Packaged 100 per carton



## Cat# SG-200 "Small Wire Guard"

- Keyless Lamp Guard
- Easy "open close" design for re-lamping
- Fits most Temporary Light and keyless sockets
- Rust resistant zinc plating
- Screw's and nuts included
- 200 watt max type "A" bulb
- Packaged 20 per carton



## Cat# MC-200 "Metal Cage"

- Heavy duty 10-guage Vinyl coated
- Bronze plated 1 1/2" universal collar
- Fits most Temporary Light and keyless sockets
- Rust resistant zinc plating
- Open bottom for easy re-lamping
- Screw's and nuts included
- 200 watt max type "A" bulb
- Packaged 20 per carton

**BERGEN**  
INDUSTRIES

www.bergeninc.com  
800-875-1846

*Lighting  
Job Sites  
For Over  
35 Years*

