

COS-E SERIES

RESIDENTIAL FAN-FORCED ZONAL WALL HEATER



IDEAL SPACES

- Bedrooms
- Living/Family Rooms
- Kitchens
- Bathrooms
- Basements
- Offices
- Hallways
- Lobbies
- Waiting Rooms

COLORS

- Northern White

DIMENSIONS

- Grille: 12"H x 9"W x 0.9"D
- Back Box: 8-1/2"H x 6-9/25"W x 4"D

TEMP RANGE

- 40°– 90°F

CFM

- 50



- Patented CLIP-N-FIT® feature allows installer to change the desired wattage output without moving the jumper wire
- Dual Protection: self-hold limit with one-time thermal fuse
- Dual voltage and wattage ratings help reduce inventory levels
- Contemporary look and compact size ideal for new residential or commercial installations where space is limited
- Quick installation and easy service with heater/fan assembly fitting into back box with a single screw
- Double-pole thermostat on all models
- Efficient quiet operation from smooth running multi-layer impeller
- Adaptable for retrofits (such as provided with UL-approved COS-E and CS Models)*
- Thermostat with positive OFF position for added safety



*Adaptable for retrofits into 7-7/8 in. x 11-1/2 in. x 4 in. back-box (such as provided with UL-approved C OS-E and CS Models) and same rough-in opening if new box is desired.

www.qmarkmep.com

For Technical Services, Call 800-642-4328

ITEM# QFLY_COSE_1217-1



COS-E SERIES

RESIDENTIAL FAN-FORCED ZONAL WALL HEATER

MODELS & SPECIFICATIONS

CATALOG NO.	UPC	VOLTS (1)	VOLTS (2)	WATTS (1)	WATTS (2)	AMPS (1)	AMPS (2)	SHIP WT. (LBS.)
CZ1512T	6 85360 16164 8	120	–	1500/750	–	12.5/6.3	–	11
CZ1012T	6 85360 16165 5	120	–	1000/500	–	8.4/4.2	–	8.1
CZ1048T	6 85360 16163 1	208	240	750/350	1000/500	7.2/3.6	8.4/4.2	11
CZ1548T	6 85360 16162 4	208	240	1125/570	1500/750	5.4/2.7	6.3/3.2	5.6
CZ2048T	6 85360 16161 7	208	240	1500/750	2000/1000	3.6/1.8	4.2/2.1	11

MOTOR AND GRILLE ONLY

CZ1512IF*	6 85360 16172 3	120	–	1500/750	–	12.5/6.3	–	5.7
CZ1012IF*	6 85360 16173 0	120	–	1000/500	–	8.4/4.2	–	5.7
CZ1048IF*	6 85360 16176 1	208	240	750/375	1000/500	7.2/3.6	8.4/4.2	5.6
CZ1548IF*	6 85360 16175 4	208	240	1125/570	1500/750	5.4/2.7	6.3/3.2	5.6
CZ2048IF*	6 85360 16174 7	208	240	1500/750	2000/1000	3.6/1.8	4.2/2.1	11

NOTE: *"IF" models include heater motor/assembly and grille only with no back box.

ACCESSORIES

CATALOG NO.	UPC	DESCRIPTION	SHIP WT. (LBS.)
CZBB	6 85360 16333 8	Back Box Only (Used with "IF" suffix models)	2
CZBB6	6 85360 16334 5	Back Box Multi-Pack (Used with "IF" suffix models)	10.5
CZTDP	6 85360 16332 1	Double-Pole Built-in Thermostat Kit (Range: 40-85°F)	1
CZSM	6 85360 16335 2	Surface Mounting Frame (Used with "IF" suffix models)	2
CZ2CRAKIT	6 85360 16519 6	Retrofit Kit CRA to COS-E	2

