

Hole Plugs *HP Series*

Features



- Designed to seal unused pushbutton holes, conduit openings and knockout holes against dust, oil and water.
- Standard Pushbutton size is 30.5mm
- **Steel Hole Plug**
 - Available in 12 sizes.
 - Finished in gray.
 - Oil resistant gasket.
 - Secured with an 10-24 x 0.55" threaded stud and plated wing nut.
- **Stainless Steel Hole Plugs**
 - Available in 8 sizes.
 - Finished in brushed natural 304 stainless steel finish.
 - Oil resistant gasket.
 - Secured with an 10-24 x 0.55" threaded stud and plated wing nut.

Steel

Part No.	Description	Max Hole Diameter	Plug Diameter
HP22	22mm Pushbutton	0.88	1.22
HP50	.5" Conduit	0.88	1.38
HP75	.75" Conduit	1.06	1.56
HPB	Std. Pushbutton	1.25	1.75
HP100	1" Conduit	1.38	1.88
HP125	1.25" Conduit	1.69	2.19
HP150	1.5" Conduit	2.00	2.50
HP200	2" Conduit	2.50	3.00
HP250	2.5" Conduit	3.00	3.50
HP300	3" Conduit	3.62	4.12
HP350	3.5" Conduit	4.12	4.62
HP400	4" Conduit	4.62	5.12

Stainless Steel

Part No.	Description	Max Hole Diameter	Plug Diameter
HP22SS	22mm Pushbutton	0.88	1.22
HP50SS	.5" Conduit	0.88	1.38
HP75SS	.75" Conduit	1.06	1.56
HPBSS	Std. Pushbutton	1.25	1.75
HP100SS	1" Conduit	1.38	1.88
HP125SS	1.25" Conduit	1.69	2.19
HP150SS	1.5" Conduit	2.00	2.50
HP200SS	2" Conduit	2.50	3.00

