

Cobra Rechargeable Task Lights



Description

Flexible LED luminaire for task lighting when and where needed. Portable and durable with integrated stand. High quality body and clips to retain the head(s) in the desired positions.

Features

- Super Bright SMD LED's
- Single or twin head operation
- Independently adjustable heads, rotate and tilt
- Fold flat for storage or transport
- Supplied with a mains charger and in-car charger
- Rated life of 20,000 hours

Range

Wattage	Head	Charge Time	Work Time	Output (lumens)	Product Code
1x 8W	Single	4 Hours	3 Hours	1x 600lm	S3150
1x 18W	Single	4 Hours	3 Hours	1x 1200lm	S3160
2x 8W	Twin	4 Hours	3 Hours	2x 600lm	S3170
2x 18W	Twin	per head	per head	2x 1200lm	S3180

Technical Specification

Housing	Die-cast aluminum
Diffuser	Tempered glass
Lumen Efficiency	75lm/W
Colour Temperature	Daylight, 5500K
Beam Angle	100°
Type of Protection	Class I
Degree of Protection	IP54

Standards

- EN 60598-1:2015
- EN 60598-2-4:1997
- EN 62031:2008+A1:2013+A2:2015
- EN 62493:2015
- EN 62471:2008
- EN 55015:2013+A1:2015
- EN 61547:2009