

CADDY[®]





CADDY[®] Featured Products

Latin America



ERICO[®]

CADDY® Featured Products

	Part No.	Description	Size 1	Size 2	Working Load (Kgs)	
One Piece Strut						
SK Series			EMT	Rigid		
	SK85I	One-Piece Strut Clamp	1/2"	1/2"	90.7	100
	SK125I	One-Piece Strut Clamp	3/4"	3/4"	90.7	100
	SK165I	One-Piece Strut Clamp	1"	1"	90.7	100
	SK205I	One-Piece Strut Clamp	1 1/4"	1 1/4"	90.7	100
	SK245I	One-Piece Strut Clamp	1 1/2"	1 1/2"	90.7	50
	SK325I	One-Piece Strut Clamp	2"	2"	90.7	50
	SK405I	One-Piece Strut Clamp	2 1/2"	2 1/2"	158.7	50
	SK485I	One-Piece Strut Clamp	3"	3"	158.7	50
	SK565I	One-Piece Strut Clamp	3 1/2"	3 1/2"	158.7	25
	SK645I	One-Piece Strut Clamp	4"	4"	158.7	25
SCH Series			EMT	Rigid		
	SCH8	One-Piece Strut Clamp	1/2"	—	90.7	100
	SCH12	One-Piece Strut Clamp	3/4"	1/2"	90.7	100
	SCH16	One-Piece Strut Clamp	1"	3/4"	90.7	100
	SCH20	One-Piece Strut Clamp	1-1/4"	1"	90.7	100
	SCH6B	One-Piece Strut Clamp	3/8" MC/AC	—	90.7	100
	SCH8B	One-Piece Strut Clamp	1/2"	—	90.7	100
	SCH12B	One-Piece Strut Clamp	3/4"	1/2"	90.7	100
	SCH16B	One-Piece Strut Clamp	1"	3/4"	90.7	100
	SCH20B	One-Piece Strut Clamp	1-1/4"	1"	90.7	100
	SCH24B	One-Piece Strut Clamp	1-1/2"	1-1/4"	158.7	50
	SCH32B	One-Piece Strut Clamp	2"	1-1/2"	158.7	50
	SCH40B	One-Piece Strut Clamp	—	2"	158.7	25
	SCH48B	One-Piece Strut Clamp	2-1/2"	2-1/2"	158.7	25
	SCH56B	One-Piece Strut Clamp	3"	3"	158.7	25
	SCH64B	One-Piece Strut Clamp	3-1/2"	3-1/2"	158.7	10
	SCH72B	One-Piece Strut Clamp	4"	4"	158.7	10
CADDY® SPEED LINK						
CADDY SPEED LINK			Wire Ø	Length		
	SLD2L1	CADDY® SPEED LINK 2mm/1M	2mm	1M	45.0	100
	SLD2L1BP	CADDY SPEED LINK 2mm/1M	2mm	1M	45.0	1
	SLD2L2	CADDY SPEED LINK 2mm/2M	2mm	2M	45.0	100
	SLD2L2BP	CADDY SPEED LINK 2mm/2M	2mm	2M	45.0	1
	SLD2L3	CADDY SPEED LINK 2mm/3M	2mm	3M	45.0	100
	SLD2L3BP	CADDY SPEED LINK 2mm/3M	2mm	3M	45.0	1
	SLD2L5	CADDY SPEED LINK 2mm/5M	2mm	5M	45.0	50
	SLD2L5BP	CADDY SPEED LINK 2mm/5M	2mm	5M	45.0	1
	SLD2L7	CADDY SPEED LINK 2mm/7M	2mm	7M	45.0	20
	SLD2L10	CADDY SPEED LINK 2mm/10M	2mm	10M	45.0	25
	SLD2L10BP	CADDY SPEED LINK 2mm/10M	2mm	10M	45.0	1
	SLD3L1	CADDY SPEED LINK 3mm/1M	3mm	1M	90.0	100
	SLD3L1BP	CADDY SPEED LINK 3mm/1M	3mm	1M	90.0	1
	SLD3L2	CADDY SPEED LINK 3mm/2M	3mm	2M	90.0	100
	SLD3L2BP	CADDY SPEED LINK 3mm/2M	3mm	2M	90.0	1
	SLD3L2SS	CADDY SPEED LINK 3mm/2M	3mm	2M	90.0	100
	SLD3L3	CADDY SPEED LINK 3mm/3M	3mm	3M	90.0	50
	SLD3L3BP	CADDY SPEED LINK 3mm/3M	3mm	3M	90.0	1
	SLD3L3SS	CADDY SPEED LINK 3mm/3M	3mm	3M	90.0	50
	SLD3L5	CADDY SPEED LINK 3mm/5M	3mm	5M	90.0	50
SLD3L5BP	CADDY SPEED LINK 3mm/5M	3mm	5M	90.0	1	
SLD3L7	CADDY SPEED LINK 3mm/7M	3mm	7M	90.0	20	
SLD3L10	CADDY SPEED LINK 3mm/10M	3mm	10M	90.0	25	
SLD3L10BP	CADDY SPEED LINK 3mm/10M	3mm	10M	90.0	1	



CADDY® Featured Products

	Part No.	Description	Size 1	Size 2	Working Load (Kgs)	
CADDY® SPEED LINK LD						
	SLD15L1	CADDY® SPEED LINK 1.5mm/1M	1.5mm	1M	20.0	100
	SLD15L1TP	CADDY SPEED LINK 1.5mm/1M	1.5mm	1M	20.0	2
	SLD15L2	CADDY SPEED LINK 1.5mm/2M	1.5mm	2M	20.0	100
	SLD15L2S	CADDY SPEED LINK 1.5mm/2M	1.5mm	2M	20.0	2
	SLD15L2TP	CADDY SPEED LINK 1.5mm/2M	1.5mm	2M	20.0	2
	SLD15L3	CADDY SPEED LINK 1.5mm/3M	1.5mm	3M	20.0	100
	SLD15L3TP	CADDY SPEED LINK 1.5mm/3M	1.5mm	3M	20.0	2
	SLD15L5	CADDY SPEED LINK 1.5mm/5M	1.5mm	5M	20.0	100
	SLD15L5S	CADDY SPEED LINK 1.5mm/5M	1.5mm	5M	20.0	2
	SLD15L5TP	CADDY SPEED LINK 1.5mm/5M	1.5mm	5M	20.0	2
	SLD15L7	CADDY SPEED LINK 1.5mm/7M	1.5mm	7M	20.0	100
SLD15L10	CADDY SPEED LINK 1.5mm/10M	1.5mm	10M	20.0	100	
SLD15L10S	CADDY SPEED LINK 1.5mm/10M	1.5mm	10M	20.0	2	
CADDY® SPEED LINK TOGGLES						
	SLD15L1T	CADDY® SPEED LINK 1.5mm/1M	1.5mm	1M	20.0	20
	SLD15L1TTP	CADDY SPEED LINK 1.5mm/1M	1.5mm	1M	20.0	2
	SLD15L2T	CADDY SPEED LINK 1.5mm/2M	1.5mm	2M	20.0	20
	SLD15L2TTP	CADDY SPEED LINK 1.5mm/2M	1.5mm	2M	20.0	2
	SLD15L3T	CADDY SPEED LINK 1.5mm/3M	1.5mm	3M	20.0	20
	SLD15L3TTP	CADDY SPEED LINK 1.5mm/3M	1.5mm	3M	20.0	2
	SLD15L5T	CADDY SPEED LINK 1.5mm/5M	1.5mm	5M	20.0	20
	SLD15L5TTP	CADDY SPEED LINK 1.5mm/5M	1.5mm	5M	20.0	2
	SLD15L7T	CADDY SPEED LINK 1.5mm/7M	1.5mm	7M	20.0	20
	SLD15L10T	CADDY SPEED LINK 1.5mm/10M	1.5mm	10M	20.0	20
	SLD15L10TTP	CADDY SPEED LINK 1.5mm/10M	1.5mm	10M	20.0	2
CADDY® SPEED LINK Y HOOKS						
	SLD2YH500	CADDY® SPEED LINK 2mm/500mm	2mm	500mm	45.0	100
	SLD2YH800	CADDY SPEED LINK 2mm/800mm	2mm	800mm	45.0	100
	SLD3YH500	CADDY SPEED LINK 3mm/500mm	3mm	500mm	90.0	100
	SLD3YH800	CADDY SPEED LINK 3mm/800mm	3mm	800mm	90.0	100
CADDY® SPEED LINK Y TOGGLES						
	SLD15Y200	CADDY® SPEED LINK 1.5mm/200mm	1.5mm	200mm	20.0	20
	SLD15Y300	CADDY SPEED LINK 1.5mm/300mm	1.5mm	300mm	20.0	20
	SLD15Y500	CADDY SPEED LINK 1.5mm/500mm	1.5mm	500mm	20.0	20
	SLD15Y500TP	CADDY SPEED LINK 1.5mm/500mm	1.5mm	500mm	20.0	2
	SLD15Y800	CADDY SPEED LINK 1.5mm/800mm	1.5mm	800mm	20.0	20
	SLD15Y800TP	CADDY SPEED LINK 1.5mm/800mm	1.5mm	800mm	20.0	2
	SLD2Y300	CADDY SPEED LINK 2mm/300mm	2mm	300mm	45.0	100
CADDY® SPEED LINK INTEGRAL Y TOGGLES						
	SLD15Y300L3	CADDY® SPEED LINK 1.5mm/300mm/3M	1.5mm	300mm/3M	20.0	100
	SLD2Y300L2	CADDY SPEED LINK 2mm/300mm/2M	2mm	300mm/2M	45.0	100
	SLD2Y300L3	CADDY SPEED LINK 2mm/300mm/3M	2mm	300mm/3M	45.0	100
	SLD2Y300L5	CADDY SPEED LINK 2mm/300mm/5M	2mm	300mm/5M	45.0	100
	SLD2Y300L7	CADDY SPEED LINK 2mm/300mm/7M	2mm	300mm/7M	45.0	100
	SLD2Y300L10	CADDY SPEED LINK 2mm/300mm/10M	2mm	300mm/10M	45.0	50
CADDY® SPEED LINK INTEGRAL Y HOOKS						
	SLD2YH500L2	CADDY® SPEED LINK 2mm/500mm/2M	2mm	500mm/2M	45.0	100
	SLD2YH500L2TP	CADDY SPEED LINK 2mm/500mm/2M	2mm	500mm/2M	45.0	2
	SLD2YH500L3	CADDY SPEED LINK 2mm/500mm/3M	2mm	500mm/3M	45.0	100
	SLD2YH500L3TP	CADDY SPEED LINK 2mm/500mm/3M	2mm	500mm/3M	45.0	2
	SLD2YH500L7	CADDY SPEED LINK 2mm/500mm/7M	2mm	500mm/7M	45.0	100
	SLD2YH500L7TP	CADDY SPEED LINK 2mm/500mm/7M	2mm	500mm/7M	45.0	2

CADDY® Featured Products















	Part No.	Description	Size 1	Size 2	Working Load (Kgs)	
CADDY® SPEED LINK QUAD TOGGLES						
	SLD15QT250	CADDY® SPEED LINK 1.5 mm / 250 mm	1.5mm	250mm	20.0	100
MULTI-FUNCTION CLIPS			Flange	Wire/Rod		
	4Z34	MULTI-FUNCTION CLIP	1/8"-3/8"	#12 WIRE THRU 1/4" PLAIN ROD	N/A	100
	6Z34	MULTI-FUNCTION CLIP	3/8"-7/16"	3/8" PLAIN OR THREADED ROD	N/A	100
	4Z34812M	MULTI-PLUS 1/2" OR 3/4" CONDUIT	1/8"-3/8"	#12 WIRE THRU 1/4" PLAIN ROD	N/A	100
	6Z34812M	MULTI-PLUS 1/2" OR 3/4" CONDUIT	3/8"-7/16"	3/8" PLAIN OR THREADED ROD	N/A	100
CONDUIT CLIPS			Flange	Conduit		
	8P	CONDUIT CLIPS	-	1/2"	11.3 vertical; 6.8 horizontal	100
	12P	CONDUIT CLIPS	-	3/4"	11.3 vertical; 6.8 horizontal	100
	16P	CONDUIT CLIPS	-	1"	11.3 vertical; 6.8 horizontal	100
	8P24	CONDUIT CLIPS	1/8"-1/4"	1/2"	11.3	100
	12P24	CONDUIT CLIPS	1/8"-1/4"	3/4"	11.3	100
	16P24	CONDUIT CLIPS	1/8"-1/4"	1"	11.3	100
	8P24SM	CONDUIT CLIPS	1/8"-1/4"	1/2"	6.8	-
	12P24SM	CONDUIT CLIPS	1/8"-1/4"	3/4"	6.8	100
	16P24SM	CONDUIT CLIPS	1/8"-1/4"	1"	6.8	100
		812M	CONDUIT CLIPS	-	1/2" - 3/4"	45.0 vertical; 11.4 horizontal
16M		CONDUIT CLIPS	-	1"	45.0 vertical; 11.4 horizontal	100
20M		CONDUIT CLIPS	-	1-1/4"	45.0 vertical; 11.4 horizontal	100
24M		CONDUIT CLIPS	-	1-1/2"	45.0 vertical; 11.4 horizontal	100
32M		CONDUIT CLIPS	-	2"	45.0 vertical; 11.4 horizontal	100
	812M24	CONDUIT CLIPS	1/8"-1/4"	1/2" - 3/4"	34.0	100
	16M24	CONDUIT CLIPS	1/8"-1/4"	1"	34.0	100
	812M24SM	CONDUIT CLIPS	1/8"-1/4"	1/2" - 3/4"	11.3	100
	16M24SM	CONDUIT CLIPS	1/8"-1/4"	1"	11.3	100
CONDUIT CLAMPS			EVT	RIGID		
	CD0B	CONDUIT CLAMPS WITH BOLTS	1/2"	1/2"	50 vertical; 22 horizontal	100
	CD1B	CONDUIT CLAMPS WITH BOLTS	3/4"	3/4"	50 vertical; 22 horizontal	100
	CD2B	CONDUIT CLAMPS WITH BOLTS	1"	1"	50 vertical; 22 horizontal	100
	CD2.5B	CONDUIT CLAMPS WITH BOLTS	1-1/4"	-	50 vertical; 22 horizontal	100



CADDY® Featured Products










	Part No.	Description	Size 1	Size 2	Working Load (Kgs)	
	CD3B	CONDUIT CLAMPS WITH BOLTS	1-1/2"	1-1/4"	50 vertical; 22 horizontal	100
	CD4B	CONDUIT CLAMPS WITH BOLTS	-	1-1/2"	50 vertical; 22 horizontal	50
	CD5B	CONDUIT CLAMPS WITH BOLTS	2"	2"	50 vertical; 22 horizontal	50
	CD6B	CONDUIT CLAMP- 2-1/2" RIGID OR EMT; 5/16" MOUNTING HOLE	2-1/2"	2-1/2"	159 vertical; 22 horizontal	25
	CD7B	CONDUIT CLAMP- 3" RIGID OR EMT; 5/16" MOUNTING HOLE	3"	3"	159 vertical; 22 horizontal	25
	CD8B	CONDUIT CLAMP- 3-1/2" RIGID OR EMT; 5/16" MOUNTING HOLE	3-1/2"	3-1/2"	159 vertical; 22 horizontal	10
	CD9B	CONDUIT CLAMP- 4" RIGID OR EMT; 5/16" MOUNTING HOLE	4"	4"	159 vertical; 22 horizontal	10
BEAM CLAMPS			Flange	Rod		
	3000037EG	REVERSIBLE BEAM CLAMPS	3/4"	3/8" - #16	113.3	100
	3100037EG	REVERSIBLE BEAM CLAMPS	1-1/4"	3/8" - #16	113.3	50
	M24	HAMMER ON FLANGE CLIP	1/8" - 1/4"	-	Refer to Catalog	100
	M58	HAMMER ON FLANGE CLIP	5/16" - 1/2"	-	Refer to Catalog	100
	M912	HAMMER ON FLANGE CLIP	9/16" - 3/4"	-	Refer to Catalog	100
	BC	BEAM CLAMPS	up to 1/2"	1/4" and 3/8"	45.0	100
	BCISN375	BEAM CLAMPS (BUILT IN SMART NUT)	up to 1/2"	3/8"	45.0	100
	BC200	BEAM CLAMPS	1/8" - 5/8"	1/4"	45.0	50
	BC400	BEAM CLAMPS	up to 3/4"	3/8"	90.0	25
CADDY® CABLECAT CABLE SUPPORT						
	CAT12	CABLE SUPPORT	-	3/4"	-	50
	CAT21	CABLE SUPPORT	-	1-5/16"	-	80
	CAT32	CABLE SUPPORT	-	2"	-	60
	CAT64	CABLE SUPPORT	-	4"	-	25
	CAT324Z34	CABLE SUPPORT WITH CLIP	-	2"	-	40
	CATMTLS	CADDY® MILLE-TIE™ - LOW SMOKE/ZERO HALOGEN	304mm	-	N/A	100 BAG/ 1000 BOX
	CATMTP	CADDY MILLE-TIE - PLENUM RATED	304mm	-	N/A	100 BAG/ 1000 BOX
	CATMTH	CADDY MILLE-TIE - HEAVY DUTY	558mm	-	N/A	100 BAG/ 1000 BOX
	CAT16HP	1 INCH J-HOOK HIGH PERFORMANCE	-	1"	27.2	50
	CAT32HP	2 INCH J-HOOK HIGH PERFORMANCE	-	2"	27.2	50
	CAT48HP	3 INCH J-HOOK HIGH PERFORMANCE	-	3"	27.2	25
	CAT64HP	4 INCH J-HOOK HIGH PERFORMANCE	-	4"	27.2	25
	CATHPAN	ANGLE BRACKET, 3/16 IN MOUNTING HOLE	-	3/16"	72.6	50
	CATHPA4	ANGLE BRACKET, 1/4 IN ROD MOUNTING HOLE	-	1/4"	90.8	50
	CATHPA6	ANGLE BRACKET, 3/8 IN ROD MOUNTING HOLE	-	3/8"	90.8	50

CADDY® Featured Products

	Part No.	Description	Size 1	Size 2	Working Load (Kgs)	
	CATHPS4	STRAIGHT BRACKET, 0.283 IN HOLE	-	.283"	90.8	50
	CATHPTM	TREE MOUNTING BRACKET	-	-	90.8	50
	CATHP24	HAMMER-ON ASSY, ROTAT. 1/8-1/4 INCH FLANGE	-	1/8" - 1/4"	34.1	25
	CATHP58	HAMMER-ON ASSY, ROTAT. 5/16-1/2 INCH FLANGE	-	5/16" - 1/2"	34.1	25
	CATHP912	HAMMER-ON ASSY, ROTAT. 1/2-3/4 INCH FLANGE	-	1/2" - 3/4"	34.1	25
	CATHPBCB	SCREW-ON BEAM ASSY. 1/8-1/2 INCH FLANGE, ROT.	-	1/8" - 1/2"	27.2	50 50
	CATHPBC200B	SCREW-ON BEAM ASSY. 1/8-5/8 INCH FLANGE, ROT.	-	1/8" - 5/8"	45.4	25
	CATHP24SM	HAMMER-ON ASSY, 1/8-1/4 INCH FLANGE	-	1/8" - 1/4"	90.8	50
	CATHP58SM	HAMMER-ON ASSY, 5/16-1/2 INCH FLANGE	-	5/16" - 1/2"	90.8	50
	CATHP912SM	HAMMER-ON ASSY, 1/2-3/4 INCH FLANGE	-	9/16" - 3/4"	90.8	25
	CATHPBC	SCREW-ON BEAM ASSY. 1/8-1/2 INCH FLANGE	-	1/8" - 1/2"	45.4	50
	CATHPBC200	SCREW-ON BEAM ASSY. 1/8-5/8 INCH FLANGE	-	1/8" - 5/8"	45.4	25
	CATHPAF14	Z PURLIN ASSY. 1/16-1/4 INCH FLANGE	-	1/16" - 1/4"	45.4	50
	CATHPVF14	C PURLIN VERTICAL ASSY. 1/16-1/4 INCH FLANGE	-	1/16" - 1/4"	72.6	50
	CATHPESC	EASY STRUT ASSY.	-	-	45.4	50
	CATHP4Z34	ROD/FLANGE ASSY. 1/4 INCH ROD/3/8 INCH FL.	1/4"	3/8"	-	50
	CATHP6Z34	ROD/FLANGE ASSY. 3/8 INCH ROD/9/16 INCH FL.	3/8"	9/16"	-	50
	CATHPCD0B	UNDERFLOOR ASSY TO PED.. 3/4 INCH ROUND	-	3/4" round	-	25
	CATHPCD1B	UNDERFLOOR ASSY TO PED.. 1 IN ROUND, 3/4 IN SQUARE	-	1" round - 3/4" square	-	25
	CATHPCD2B	UNDERFLOOR ASSY TO PED.. 7/8 INCH SQUARE	-	7/8" square	-	25
	CATHPCD2.5B	UNDERFLOOR ASSY TO PED.. 1 INCH SQUARE	-	1" square	-	25



CADDY® Featured Products

	Part No.	Description	Size 1	Size 2	Working Load (Kgs)	
	CAT16HPTS	ACOUSTICAL TEE BAR ASSY.	-	-	-	25
	CATHPPLR	CABLE PULLER	-	-	-	2
VERTICAL MOUNT CONCRETE HANGER						
	HMZG730	VERTICAL MOUNT CONCRETE HANGER	7.9mm X 57.1mm anchor	3/8" - 10	990 kg for f'c 250kg/cm ²	50
	HMZG365	CONCRETE APPLICATIONS-VERTICAL MOUNT	7.9mm X 57.1mm anchor	1/4-20 ROD	990 kg for f'c 250kg/cm ²	50
	HMZE220	CONCRETE APPLICATIONS-RECESSED DRIVE SLEEVE	-	-	-	1
	HMZE350	CONCRETE APPLICATIONS-ANSI 1/4" SDS DRILL BIT	-	-	-	1
ISN SMART NUT/ISSP STRUT PLATE						
	ISSPK	ISSP STRUT PLATE	-	3/8" - 16	99 kg	SETS
MOUNTING PLATE BRACKET						
	MP1P	SINGLE GANG MOUNTING PLATE	-	-	N/A	100
	MPAL2	DOUBLE GANG MOUNTING PLATE	-	-	N/A	100
	MP34P	3 OR 4 GANG MOUNTING PLATE	-	-	N/A	2
CADDY® SLICK STRUT NUT						
	SLICK250	CADDY® SLICK STRUT NUT	-	1/4"-20	Refer to Catalog	100
	SLICK375	CADDY SLICK STRUT NUT	-	3/8"-16	Refer to Catalog	100
	SLICK500	CADDY SLICK STRUT NUT	-	1/2"-13	Refer to Catalog	100
BOX BRACKETS			LENGTH	BOX SIZE		
	TSGB16	TELESCOPING SCREW GUN BRACKET	279mm - 457mm	1-1/2" - 2-1/8"	N/A	50
	TSGB24	TELESCOPING SCREW GUN BRACKET	431mm - 660mm	1-1/2" - 2-1/8"	N/A	50
PURLIN CLIPS						
	VF14	PURLIN CLIP	1/16" - 1/4"	-	72	100
	VF144TI	PURLIN CLIP	1/16" - 1/4"	1/4"	72	100
	VF146T	PURLIN CLIP (nuts required)	1/16" - 1/4"	3/8"	72	100
	VF146TI	PURLIN CLIP	1/16" - 1/4"	3/8"	72	100

Mille-Tie is a trademark of Millepede International Ltd.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

WARRANTY

ERICO products are warranted to be free from defects in material and workmanship at the time of shipment. NO OTHER WARRANTY, WHETHER EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), SHALL EXIST IN CONNECTION WITH THE SALE OR USE OF ANY ERICO PRODUCTS. Claims for errors, shortages, defects or nonconformities ascertainable upon inspection must be made in writing within 5 days after Buyer's receipt of products. All other claims must be made in writing to ERICO within 6 months from the date of shipment or transport. Products claimed to be nonconforming or defective must, upon ERICO's prior written approval in accordance with its standard terms and procedures governing returns, promptly be returned to ERICO for inspection. Claims not made as provided above and within the applicable time period will be barred. ERICO shall in no event be responsible if the products have not been stored or used in accordance with its specifications and recommended procedures. ERICO will, at its option, either repair or replace nonconforming or defective products for which it is responsible or return the purchase price to the Buyer. THE FOREGOING STATES BUYER'S EXCLUSIVE REMEDY FOR ANY BREACH OF ERICO WARRANTY AND FOR ANY CLAIM, WHETHER SOUNDING IN CONTRACT, TORT OR NEGLIGENCE, FOR LOSS OR INJURY CAUSED BY THE SALE OR USE OF ANY PRODUCT.

LIMITATION OF LIABILITY

ERICO excludes all liability except such liability that is directly attributable to the willful or gross negligence of ERICO's employees. Should ERICO be held liable its liability shall in no event exceed the total purchase price under the contract. ERICO SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS OF BUSINESS OR PROFITS, DOWNTIME OR DELAY, LABOR, REPAIR OR MATERIAL COSTS OR ANY SIMILAR OR DISSIMILAR CONSEQUENTIAL LOSS OR DAMAGE INCURRED BY BUYER.

Mexico: 52-55-52-60-59-91
Chile: 56-2-370-29-08
www.erico.com


ERICO®



www.erico.com



AUSTRALIA
Phone 1-800-263-508
Fax 1-800-423-091



CHINA
Phone +86-21-3430-4878
Fax +86-21-5831-8177



HUNGARY
Phone 06-800-16538
Fax +39-0244-386-107



NORWAY
Phone 800-100-73
Fax 800-100-66



SWITZERLAND
Phone 0800-55-86-97
Fax 0800-55-96-15



BELGIUM
Phone 0800-757-48
Fax 0800-757-60



DENMARK
Phone 808-89-372
Fax 808-89-373



INDONESIA
Phone +62-21-575-0941
Fax +62-21-575-0942



POLAND
Phone +48-71-349-04-60
Fax +48-71-349-04-61



THAILAND
Phone +66-2-267-5776
Fax +66-2-636-6988



BRAZIL
Phone +55-11-3623-4333
Fax +55-11-3621-4066



FRANCE
Phone 0-800-901-793
Fax 0-800-902-024



ITALY
Phone 800-870-938
Fax 800-873-935



SINGAPORE
Phone +65-6-268-3433
Fax +65-6-268-1389



UNITED ARAB EMIRATES
Phone +971-4-881-7250
Fax +971-4-881-7270



CANADA
Phone +1-800-677-9089
Fax +1-800-677-8131



GERMANY
Phone 0-800-189-0272
Fax 0-800-189-0274



MEXICO
Phone +52-55-5260-5991
Fax +52-55-5260-3310



SPAIN
Phone 900-993-154
Fax 900-807-333



UNITED KINGDOM
Phone 0808-2344-670
Fax 0808-2344-676



CHILE
Phone +56-2-370-2908
Fax +56-2-369-5657



HONG KONG
Phone +852-2764-8808
Fax +852-2764-4486



NETHERLANDS
Phone 0800-0200-135
Fax 0800-0200-136



SWEDEN
Phone 020-790-908
Fax 020-798-964



UNITED STATES
Phone 1-800-753-9221
Fax +1-440-248-0723