



For a complete listing of solid wall dimensional details, see page B-4.




A



Front view with cover



Bottom view



Side view

Cat. no.	Description	Size (W x H)		Cover cat. no.	Duct std. ctn. qty.	Cover std. ctn. qty.	Length (ft.)
		In.	mm				
TYD75X1SP[ _ ]6	0.75 x 1 Solid wall duct	0.94 x 1.14	23.9 x 27.7	TYD75CP[ _ ]6	120	120	6
TYD75X15SP[ _ ]6	0.75 x 1.5 Solid wall duct	0.94 x 1.60	23.9 x 39.6				
TYD75X2SP[ _ ]6	0.75 x 2 Solid wall duct	0.94 x 2.10	23.9 x 52.6				
TYD1X1SP[ _ ]6	1 x 1 Solid wall duct	1.25 x 1.14	31.8 x 27.7	TYD1CP[ _ ]6	120	120	6
TYD1X15SP[ _ ]6	1 x 1.5 Solid wall duct	1.25 x 1.60	31.8 x 39.9				
TYD1X2SP[ _ ]6	1 x 2 Solid wall duct	1.25 x 2.10	31.8 x 52.8				
TYD1X3SP[ _ ]6	1 x 3 Solid wall duct	1.25 x 3.05	31.8 x 77.7	TYD15CP[ _ ]6	60	120	6
TYD1X4SP[ _ ]6	1 x 4 Solid wall duct	1.25 x 4.37	31.8 x 111.3				
TYD15X1SP[ _ ]6	1.5 x 1 Solid wall duct	1.75 x 1.14	44.5 x 27.7				
TYD15X15SP[ _ ]6	1.5 x 1.5 Solid wall duct	1.75 x 1.60	44.5 x 39.9	TYD15CP[ _ ]6	60	120	6
TYD15X2SP[ _ ]6	1.5 x 2 Solid wall duct	1.75 x 2.10	44.5 x 52.8				
TYD15X3SP[ _ ]6	1.5 x 3 Solid wall duct	1.75 x 3.05	44.5 x 77.7				
TYD15X4SP[ _ ]6	1.5 x 4 Solid wall duct	1.75 x 4.37	44.5 x 111.3	TYD2CP[ _ ]6	60	120	6
TYD2X1SP[ _ ]6	2 x 1 Solid wall duct	2.25 x 1.24	57.2 x 28.4				
TYD2X15SP[ _ ]6	2 x 1.5 Solid wall duct	2.25 x 1.70	57.2 x 40.4				
TYD2X2SP[ _ ]6	2 x 2 Solid wall duct	2.25 x 2.19	57.2 x 53.3	TYD25CP[ _ ]6	60	120	6
TYD2X3SP[ _ ]6	2 x 3 Solid wall duct	2.25 x 3.14	57.2 x 78.2				
TYD2X4SP[ _ ]6	2 x 4 Solid wall duct	2.25 x 4.46	57.2 x 111.8				
TYD2X5SP[ _ ]6	2 x 5 Solid wall duct	2.25 x 5.15	57.2 x 129.3	TYD25CP[ _ ]6	60	120	6
TYD25X2SP[ _ ]6	2.5 x 2 Solid wall duct	2.75 x 2.19	69.9 x 53.6				
TYD25X3SP[ _ ]6	2.5 x 3 Solid wall duct	2.75 x 3.14	69.9 x 78.2				
TYD25X4SP[ _ ]6	2.5 x 4 Solid wall duct	2.75 x 4.46	69.9 x 111.8	TYD3CP[ _ ]6	60	120	6
TYD3X1SP[ _ ]6	3 x 1 Solid wall duct	3.25 x 1.24	82.6 x 29.0				
TYD3X2SP[ _ ]6	3 x 2 Solid wall duct	3.25 x 2.19	82.6 x 54.9				
TYD3X3SP[ _ ]6	3 x 3 Solid wall duct	3.25 x 3.14	82.6 x 79.8	TYD3CP[ _ ]6	60	120	6
TYD3X4SP[ _ ]6	3 x 4 Solid wall duct	3.25 x 4.46	82.6 x 113.5				
TYD3X5SP[ _ ]6	3 x 5 Solid wall duct	3.25 x 5.15	82.6 x 130.6				
TYD4X15SP[ _ ]6	4 x 1.5 Solid wall duct	4.25 x 1.70	108.0 x 42.4	TYD4CP[ _ ]6	60	120	6
TYD4X2SP[ _ ]6	4 x 2 Solid wall duct	4.25 x 2.19	108.0 x 55.1				
TYD4X3SP[ _ ]6	4 x 3 Solid wall duct	4.25 x 3.14	108.0 x 80.0				
TYD4X4SP[ _ ]6	4 x 4 Solid wall duct	4.25 x 4.46	108.0 x 113.8	TYD4CP[ _ ]6	30	120	6
TYD4X5SP[ _ ]6	4 x 5 Solid wall duct	4.25 x 5.15	108.0 x 130.8				
TYD6X4SP[ _ ]6	6 x 4 Solid wall duct	6.25 x 4.46	158.8 x 114.0				
TYD6CP[ _ ]6				TYD6CP[ _ ]6	30	60	6

[ ] = space for color identifier:


- G = Gray
- W = White
- B = Black
- I = Intrinsic blue

- Standard lengths are 6 feet.
- + Catalog number must be completed by adding suffix G for gray, W for white, I for intrinsic blue, B for black.
- Example: TYD75X1SPG6 is a 0.75" x 1" solid wall gray duct.
- To order duct without mounting holes, add suffix NM to catalog number.
- Example: TYD75X1SPGNM6 is a 0.75" x 1" solid wall gray duct with no mounting holes.
- To order adhesive-backed duct, add suffix A to catalog number.
- Example: TYD75X1SPGA6 is a 0.75" x 1" solid wall gray duct with adhesive backing. Shelf life for adhesive is 1 year.
- PVC vinyl duct is UL® Recognized , CSA certified and CE compliant.


For a complete listing of wide slot dimensional details, see page B-5.




A



Front view with cover



Bottom view



Side view

Cat. no.	Description	Size (W x H)		Cover cat. no.	Duct std. ctn. qty.	Cover std. ctn. qty.	Length (ft.)	
		In.	mm					
TYD75X1WP[ _ ]6	0.75 x 1 Wide slot duct	0.94 x 1.14	23.9 x 27.7	TYD75CP[ _ ]6	120	120	6	
TYD75X15WP[ _ ]6	0.75 x 1.5 Wide slot duct	0.94 x 1.60	23.9 x 39.6					
TYD75X2WP[ _ ]6	0.75 x 2 Wide slot duct	0.94 x 2.10	23.9 x 52.6					
TYD1X1WP[ _ ]6	1 x 1 Wide slot duct	1.25 x 1.14	31.8 x 27.7	TYD1CP[ _ ]6	120	120	6	
TYD1X15WP[ _ ]6	1 x 1.5 Wide slot duct	1.25 x 1.60	31.8 x 39.9					
TYD1X2WP[ _ ]6	1 x 2 Wide slot duct	1.25 x 2.10	31.8 x 52.8					
TYD1X3WP[ _ ]6	1 x 3 Wide slot duct	1.25 x 3.05	31.8 x 77.7					
TYD1X4WP[ _ ]6	1 x 4 Wide slot duct	1.25 x 4.37	31.8 x 111.3	TYD15CP[ _ ]6	60	120	6	
TYD15X1WP[ _ ]6	1.5 x 1 Wide slot duct	1.75 x 1.14	44.5 x 27.7					
TYD15X15WP[ _ ]6	1.5 x 1.5 Wide slot duct	1.75 x 1.60	44.5 x 39.9					
TYD15X2WP[ _ ]6	1.5 x 2 Wide slot duct	1.75 x 2.10	44.5 x 52.8					
TYD15X3WP[ _ ]6	1.5 x 3 Wide slot duct	1.75 x 3.05	44.5 x 77.7					
TYD15X4WP[ _ ]6	1.5 x 4 Wide slot duct	1.75 x 4.37	44.5 x 111.3	60	TYD2CP[ _ ]6	120	120	6
TYD2X1WP[ _ ]6	2 x 1 Wide slot duct	2.25 x 1.24	57.2 x 28.4					
TYD2X15WP[ _ ]6	2 x 1.5 Wide slot duct	2.25 x 1.70	57.2 x 40.4					
TYD2X2WP[ _ ]6	2 x 2 Wide slot duct	2.25 x 2.19	57.2 x 53.3					
TYD2X3WP[ _ ]6	2 x 3 Wide slot duct	2.25 x 3.14	57.2 x 78.2					
TYD2X4WP[ _ ]6	2 x 4 Wide slot duct	2.25 x 4.46	57.2 x 111.8					
TYD2X5WP[ _ ]6	2 x 5 Wide slot duct	2.25 x 5.15	57.2 x 129.3	60	TYD25CP[ _ ]6	120	120	6
TYD25X2WP[ _ ]6	2.5 x 2 Wide slot duct	2.75 x 2.19	69.9 x 53.6					
TYD25X3WP[ _ ]6	2.5 x 3 Wide slot duct	2.75 x 3.14	69.9 x 78.2					
TYD25X4WP[ _ ]6	2.5 x 4 Wide slot duct	2.75 x 4.46	69.9 x 111.8	60	TYD3CP[ _ ]6	120	120	6
TYD3X1WP[ _ ]6	3 x 1 Wide slot duct	3.25 x 1.24	82.6 x 29.0					
TYD3X2WP[ _ ]6	3 x 2 Wide slot duct	3.25 x 2.19	82.6 x 54.9					
TYD3X3WP[ _ ]6	3 x 3 Wide slot duct	3.25 x 3.14	82.6 x 79.8					
TYD3X4WP[ _ ]6	3 x 4 Wide slot duct	3.25 x 4.46	82.6 x 113.5					
TYD3X5WP[ _ ]6	3 x 5 Wide slot duct	3.25 x 5.15	82.6 x 130.6	60	TYD4CP[ _ ]6	120	120	6
TYD4X15WP[ _ ]6	4 x 1.5 Wide slot duct	4.25 x 1.70	108.0 x 42.4					
TYD4X2WP[ _ ]6	4 x 2 Wide slot duct	4.25 x 2.19	108.0 x 55.1					
TYD4X3WP[ _ ]6	4 x 3 Wide slot duct	4.25 x 3.14	108.0 x 80.0					
TYD4X4WP[ _ ]6	4 x 4 Wide slot duct	4.25 x 4.46	108.0 x 113.8	30	TYD6CP[ _ ]6	30	60	6
TYD4X5WP[ _ ]6	4 x 5 Wide slot duct	4.25 x 5.15	108.0 x 130.8					
TYD6X4WP[ _ ]6	6 x 4 Wide slot duct	6.25 x 4.46	158.8 x 114.0					

[ ] = space for color identifier:


- G = Gray
- W = White
- B = Black
- I = Intrinsic blue

- Standard lengths are 6 feet.
- + Catalog number must be completed by adding suffix G for gray, W for white, I for intrinsic blue, B for black.
- Example: TYD75X1WPG6 is a 0.75" x 1" wide slot gray duct.
- To order duct without mounting holes, add suffix NM to catalog number.
- Example: TYD75X1WPGNM6 is a 0.75" x 1" wide slot gray duct with no mounting holes.
- To order adhesive-backed duct, add suffix A to Catalog Number.
- Example: TYD75X1WPGA6 is a 0.75" x 1" wide slot gray duct with adhesive backing. Shelf life for adhesive is 1 year.
- PVC vinyl duct is UL® Recognized , CSA certified and CE compliant.


For a complete listing of narrow slot dimensional details, see page B-6.




A



Front view with cover



Bottom view



Side view

Cat. no.	Description	Size (W x H)		Cover cat. no.	Duct std. ctn. qty.	Cover std. ctn. qty.	Length (ft.)
		In.	mm				
TYD75X15NP[_]6	0.75 x 1.5 Narrow slot duct	0.94 x 1.60	23.9 x 39.6	TYD75CP[_]6	120	120	6
TYD1X1NP[_]6	1 x 1 Narrow slot duct	1.25 x 1.14	31.8 x 27.7	TYD1CP[_]6	120	120	6
TYD1X15NP[_]6	1 x 1.5 Narrow slot duct	1.25 x 1.60	31.8 x 39.9				
TYD1X2NP[_]6	1 x 2 Narrow slot duct	1.25 x 2.10	31.8 x 52.8				
TYD1X3NP[_]6	1 x 3 Narrow slot duct	1.25 x 3.05	31.8 x 77.7				
TYD1X4NP[_]6	1 x 4 Narrow slot duct	1.25 x 4.37	31.8 x 111.3				
TYD15X1NP[_]6	1.5 x 1 Narrow slot duct	1.75 x 1.14	44.5 x 27.7	TYD15CP[_]6	120	120	6
TYD15X15NP[_]6	1.5 x 1.5 Narrow slot duct	1.75 x 1.60	44.5 x 39.9				
TYD15X2NP[_]6	1.5 x 2 Narrow slot duct	1.75 x 2.10	44.5 x 52.8				
TYD15X3NP[_]6	1.5 x 3 Narrow slot duct	1.75 x 3.05	44.5 x 77.7				
TYD15X4NP[_]6	1.5 x 4 Narrow slot duct	1.75 x 4.37	44.5 x 111.3	TYD2CP[_]6	120	120	6
TYD2X1NP[_]6	2 x 1 Narrow slot duct	2.25 x 1.24	57.2 x 28.4				
TYD2X15NP[_]6	2 x 1.5 Narrow slot duct	2.25 x 1.70	57.2 x 40.4				
TYD2X2NP[_]6	2 x 2 Narrow slot duct	2.25 x 2.19	57.2 x 53.3				
TYD2X3NP[_]6	2 x 3 Narrow slot duct	2.25 x 3.14	57.2 x 78.2				
TYD2X4NP[_]6	2 x 4 Narrow slot duct	2.25 x 4.46	57.2 x 111.8	TYD25CP[_]6	120	120	6
TYD2X5NP[_]6	2 x 5 Narrow slot duct	2.25 x 5.15	57.2 x 129.3				
TYD25X2NP[_]6	2.5 x 2 Narrow slot duct	2.75 x 2.19	69.9 x 53.6				
TYD25X3NP[_]6	2.5 x 3 Narrow slot duct	2.75 x 3.14	69.9 x 78.2	TYD3CP[_]6	120	120	6
TYD25X4NP[_]6	2.5 x 4 Narrow slot duct	2.75 x 4.46	69.9 x 111.8				
TYD3X1NP[_]6	3 x 1 Narrow slot duct	3.25 x 1.24	82.6 x 29.0	TYD4CP[_]6	60	120	6
TYD3X2NP[_]6	3 x 2 Narrow slot duct	3.25 x 2.19	82.6 x 54.9				
TYD3X3NP[_]6	3 x 3 Narrow slot duct	3.25 x 3.14	82.6 x 79.8				
TYD3X4NP[_]6	3 x 4 Narrow slot duct	3.25 x 4.46	82.6 x 113.5				
TYD3X5NP[_]6	3 x 5 Narrow slot duct	3.25 x 5.15	82.6 x 130.6	TYD4CP[_]6	60	120	6
TYD4X2NP[_]6	4 x 2 Narrow slot duct	4.25 x 2.19	108.0 x 55.1				
TYD4X3NP[_]6	4 x 3 Narrow slot duct	4.25 x 3.14	108.0 x 80.0				
TYD4X4NP[_]6	4 x 4 Narrow slot duct	4.25 x 4.46	108.0 x 113.8				
TYD4X5NP[_]6	4 x 5 Narrow slot duct	4.25 x 5.15	108.0 x 130.8				

[ ] = space for color identifier:

- G = Gray
- W = White
- B = Black
- I = Intrinsic blue

- Standard lengths are 6 feet.
- + Catalog number must be completed by adding suffix G for gray, W for white, I for intrinsic blue, B for black.
- Example: TYD75X1WPG6 is a 0.75" x 1" wide slot gray duct.
- To order duct without mounting holes, add suffix NM to catalog number.
- Example: TYD75X1WPGNM6 is a 0.75" x 1" wide slot gray duct with no mounting holes.
- To order adhesive-backed duct, add suffix A to Catalog Number.
- Example: TYD75X1WPGA6 is a 0.75" x 1" wide slot gray duct with adhesive backing. Shelf life for adhesive is 1 year.
- PVC vinyl duct is UL® Recognized , CSA certified and CE compliant.