

NEW



C-Lite™ Product Catalog

May 2017

C-LITE™
LED LIGHTING BY CREE



EFFICIENCY YOU NEED. QUALITY YOU TRUST.

C-Lite™ LED Lighting by Cree offers a broad range of reliable, easy to install LED lighting products with all the options you need and backed by Cree.

SIMPLE

Our mission is simple: provide high performance, go-to LED lighting at incredible value. Contractors have enough to worry about—C-Lite™ products make lighting projects one less hurdle in a day full of them.

EASY

From easy installation to making sure our products are always in stock, easy to find and ready to work, we make jobs of all sizes quick, easy and painless. C-Lite™ LED Lighting by Cree is your no hassle, “hey, that was easy” choice.

QUALITY

Cree won’t put their name on just any box. Engineered to deliver great energy savings and powerful performance, C-Lite™ LED Lighting by Cree is backed by a great warranty and Cree’s world-class live customer support. You can relax knowing that with this, Cree has got your back.



C-LITE™ STOCK & FLOW PRODUCTS

C-LITE™ - LED OUTDOOR

LED Area Lights, 120-277V.....	3
Shoebox LED Area, Lights 120-277V	3
LED Area Light Accessories, 120-277V.....	4
LED Canopy, 120-277V	5
Compact LED Floodlights, 120-277V.....	6
High Performance LED Floodlights & Accessories, 120-277V	7
LED Wall Mounts, 120V	8
Slimline LED Wall Packs, 120-277V.....	9
Slimline LED Wall Pack Accessories, 120-277V.....	10
LED Wall Packs, 120-277V.....	11
LED Vapor Tights, 120V.....	12

C-LITE™ - LED INDOOR

LED Round High Bays & Low Bays, 120-277V.....	13
LED Linear High Bays, 120-277V	14
LED High & Low Bay Accessories, 120-277V.....	15
General LED Accessories, 120-277V.....	16



LED AREA LIGHTS, 120-277V

Stylish Modern Design, Type III Optimized Distribution



LED Area Light (4LD)



LED Area Light (2LD)

- Category: LED Outdoor Area Light
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- High LPW: up to 103
- Watts: 117 to 228
- Non-Dimmable

Item	SKU	Replaces	CCT	Lumens	Finish Color
LED Area Light	C-AR-A-2LD-12L-40K-DB	250W PSMH	4000K	12,000	Dark Bronze
LED Area Light	C-AR-A-2LD-12L-50K-DB	250W PSMH	5000K	12,000	Dark Bronze
LED Area Light	C-AR-A-4LD-23L-40K-DB	400W PSMH	4000K	23,000	Dark Bronze
LED Area Light	C-AR-A-4LD-23L-50K-DB	400W PSMH	5000K	23,000	Dark Bronze

SHOEBOX LED AREA LIGHTS, 120-277V

Stylish, Modern Design; Type III, V and VII Optimized Distributions



LED Shoebox Area Light

- Category: LED Outdoor Area Light
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- High LPW: up to 143
- Watts: 119
- Non-Dimmable
- Finish Color: Dark Bronze

Item	SKU	Replaces	CCT	Lumens	Size
LED Area Light	C-AR-A-SQT3-16L-40K-DB	320W PSMH / 400W MH	4000K	16000	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT3-17L-50K-DB	320W PSMH / 400W MH	5000K	17000	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT5-15L-50K-DB	320W PSMH / 400W MH	5000K	15000	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT5-16L-40K-DB	320W PSMH / 400W MH	4000K	16000	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT7-17L-50K-DB	320W PSMH / 400W MH	4000K	17000	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT7-17L-40K-DB	320W PSMH / 400W MH	5000K	17000	16-1/5" x 16-1/5"



LED Adjustable U-Bracket



LED 6" Mounting Arm



LED Mount Slipfitter 2in

LED AREA LIGHT ACCESSORIES, 120-277V

Accessories for C-Lite™ Area Lights

• Category: LED Outdoor Accessories

Product/Item	SKU	Finish Color	Size/Fits
LED Adjustable U-Bracket, 2" x 5" x 6"	C-ACC-A-AUB-2X5X6-DB	Dark Bronze	Fits C-AR-A-2LD Series 2" x 5" x 6"
LED 6" Mounting Arm	C-ACC-A-MTARM-6IN-DB	Dark Bronze	6", Fits C-AR-A-2LD Series, C-AR-A-4LD Series
LED Adjustable U-Bracket, 3" x 5" x 5"	C-ACC-A-AUB-3X5X5-DB	Dark Bronze	Fits C-AR-A-4LD Series 3" x 5" x 5"
LED Mount Slipfitter 2"	C-ACC-A-MTSL-2IN-DB	Dark Bronze	2", Fits C-AR-A-2LD, C-AR-A-4LD, C-AR-A-SQT5, C-AR-A-SQT7 Series
LED Adjustable U-Bracket	C-ACC-A-SBMTARM-6IN-DB	Dark Bronze	Fits C-AR-A-SQT3, C-AR-A-SQT5, C-AR-A-SQT7 Series
LED 2" Mounting Arm	C-ACC-A-MTARM-2IN-DB	Dark Bronze	2", Fits C-AR-A-SQT3 C-AR-A-SQT5, C-AR-A-SQT7 Series



Square Canopy

LED CANOPY LIGHTS, 120-277V

Traditional Style; Easy Installation

- Category: LED Outdoor Canopy
- CRI: >70
- Location Type: Wet
- High LPW: Up to 136
- Watts: 36 to 67
- Non-Dimmable

Item	SKU	Replaces	CCT	Lumens	Finish Color	Size/Fits
Square LED Canopy	C-CP-A-SQ-49L-40K-DB	100W PSMH	4000K	4900	Dark Bronze	Hole Size: 7-3/8" x 7-3/8"
Square LED Canopy	C-CP-A-SQ-49L-40K-WH	100W PSMH	4000K	4900	White	Hole Size: 7-3/8" x 7-3/8"
Square LED Canopy	C-CP-A-SQ-49L-50K-DB	100W PSMH	5000K	4900	Dark Bronze	Hole Size: 7-3/8" x 7-3/8"
Square LED Canopy	C-CP-A-SQ-49L-50K-WH	100W PSMH	5000K	4900	White	Hole Size: 7-3/8" x 7-3/8"
Square LED Canopy	C-CP-A-SQ-79L-40K-DB	150W PSMH	4000K	7900	Dark Bronze	Hole Size: 10-7/8" x 10-7/8"
Square LED Canopy	C-CP-A-SQ-79L-40K-WH	175W MH	4000K	7900	White	Hole Size: 10-7/8" x 10-7/8"
Square LED Canopy	C-CP-A-SQ-79L-50K-DB	150W PSMH	5000K	7900	Dark Bronze	Hole Size: 10-7/8" x 10-7/8"
Square LED Canopy	C-CP-A-SQ-79L-50K-WH	175W MH	5000K	7900	White	Hole Size: 10-7/8" x 10-7/8"



Premium LED Compact Flood



Premium LED Directional Flood

COMPACT LED FLOODLIGHTS, 120-277V

High Quality; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Floodlights/Spot Lights
- CRI: >70
- Location Type: Wet
- Non-Dimmable
- High LPW: Up to 106
- Watts: 9 to 35

Item	SKU	Replaces	CCT	Lumens	Finish Color	Size/Fits
Premium LED Compact Flood	C-FL-A-RC-2L-40K-DB	50W MH	4000K	1,600	Dark Bronze	4-3/4" H x 6-1/8" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-2L-40K-WH	50W MH	4000K	1,600	White	4-3/4" H x 6-1/8" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-40K-DB	70W MH	4000K	3,000	Dark Bronze	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-40K-WH	70W MH	4000K	3,000	White	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-50K-DB	70W MH	5000K	3,000	Dark Bronze	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-50K-WH	70W MH	5000K	3,000	White	6" H x 7-3/4" W x 4-3/4" D
Premium LED Directional Flood	C-FL-A-RDC-1L-40K-BK	50W Halogen	4000K	700	Black	4" H x 4" W x 4-5/8" D
Premium LED Directional Flood	C-FL-A-RDC-1L-40K-WH	50W Halogen	4000K	700	White	4" H x 4" W x 4-5/8" D
Premium LED Directional Flood	C-FL-A-RDW-3L-40K-DB	70W MH	4000K	3,100	Dark Bronze	8-1/2" H x 6-1/2" W x 7-3/4" D
Premium LED Directional Flood	C-FL-A-RDW-3L-50K-DB	70W MH	5000K	3,300	Dark Bronze	8-1/2" H x 6-1/2" W x 7-3/4" D
Premium LED Directional Flood	C-FL-A-RDM-3L-40K-DB	70W MH	4000K	3,500	Dark Bronze	8-1/2" H x 6-1/2" W x 7-3/4" D
Premium LED Directional Flood	C-FL-A-RDM-4L-50K-DB	70W MH	4000K	3,800	Dark Bronze	8-1/2" H x 6-1/2" W x 7-3/4" D

*See lighting.cree.com/warranty for details

HIGH PERFORMANCE LED FLOODLIGHTS & ACCESSORIES, 120-277V

High Quality; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Floodlights & Accessories
- CRI: >70
- Location Type: Wet
- Non-Dimmable
- Finish Color: Dark Bronze
- High LPW: Up to 118
- Watts: 74 to 234



Premium LED Floodlight-Large



High-Output LED Floodlight



Premium LED Floodlight-Small



LED Photocell 120V, <1000W

Item	SKU	Replaces	CCT	Lumens	Size/Fits
Premium LED Floodlight-Small	C-FL-A-RTF1-8L-40K-DB	150W PSMH / 175W MH	4000K	8,000	11" H x 9-4/9" W x 5-1/2" D
Premium LED Floodlight-Small	C-FL-A-RTF1-7L-50K-DB	150W PSMH / 175W MH	5000K	7,400	11" H x 9-4/9" W x 5-1/2" D
Premium LED Floodlight-Small	C-FL-A-RTS1-8L-40K-DB	150W PSMH / 175W MH	4000K	8,000	11" H x 9-4/9" W x 5-1/2" D
Premium LED Floodlight-Small	C-FL-A-RTS1-7L-50K-DB	150W PSMH / 175W MH	5000K	7,400	11" H x 9-4/9" W x 5-1/2" D
Premium LED Floodlight-Large	C-FL-A-RTF2-12L-40K-DB	250W PSMH	4000K	12,000	14-5/8" H x 12-3/4" W x 7-3/8" D
Premium LED Floodlight-Large	C-FL-A-RTF2-12L-50K-DB	250W PSMH	5000K	12,000	14-5/8" H x 12-3/4" W x 7-3/8" D
Premium LED Floodlight-Large	C-FL-A-RTS2-13L-40K-DB	250W PSMH	4000K	13,500	14-5/8" H x 12-3/4" W x 7-3/8" D
Premium LED Floodlight-Large	C-FL-A-RTS2-14L-50K-DB	250W PSMH	5000K	13,900	14-5/8" H x 12-3/4" W x 7-3/8" D
High-Output LED Floodlight	C-FL-A-RTF4-26L-40K-DB	400W PSMH	4000K	26,500	16-1/16" H x 17-3/4" W x 7-5/16" D
High-Output LED Floodlight	C-FL-A-RTF4-26L-50K-DB	400W PSMH	5000K	26,300	16-1/16" H x 17-3/4" W x 7-5/16" D
High-Output LED Floodlight	C-FL-A-RTS4-23L-40K-DB	400W PSMH	4000K	22,900	16-1/16" H x 17-3/4" W x 7-5/16" D
High-Output LED Floodlight	C-FL-A-RTS4-23L-50K-DB	400W PSMH	5000K	22,800	16-1/16" H x 17-3/4" W x 7-5/16" D

ACCESSORIES	SKU	SIZE/FITS
LED Photocell 120V, <1000W	C-ACC-A-PCELL-LV	120V, <1000W, Fits C-FL-A-RTF2, C-FL-A-RTS2, C-FL-A-RTF4, C-FL-A-RTS4, C-WP-A Series
LED Photocell 208-240V, <1000W	C-ACC-A-PCELL-HV	208-240V, <1000W, Fits C-FL-A-RTF2, C-FL-A-RTS2, C-FL-A-RTF4, C-FL-A-RTS4, C-WP-A Series

*See lighting.cree.com/warranty for details



Architectural Wall Mount (120-277V)



Premium LED Directional Flood



LED Wall Mounts



LED High-Output Wall Mount



LED Wall Mounts

LED WALL MOUNTS, 120V

Easy Installation; Versatile; Efficient

- Category: LED Outdoor Wall Mounts with Photo Cell
- CRI: >70
- Location Type: Wet
- Non-Dimmable
- High LPW: Up to 97
- Watts: 14 to 36

Item	SKU	Replaces	CCT	Lumens	Finish Color	Size/Fits
Architectural Wall Mount (120-277V)	C-WM-A-WLAR-11L-50K-MB	100W Incandescent	5000K	1,100	Medium Bronze	Size: 6" H x 5-2/5" W x 7-2/7" D
Wall Mount	C-WM-A-WLCY-6L-40K-WH	60W Incandescent	4000K	600	White	
Wall Mount	C-WM-A-WLCY-6L-40K-DB	60W Incandescent	4000K	600	Dark Bronze	
Wall Mount	C-WM-A-WLHR-10L-40K-MB	100W Incandescent	4000K	1,000	Medium Bronze	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-10L-40K-WH	100W Incandescent	4000K	1,000	White	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-12L-40K-MB	120W Incandescent	4000K	1,200	Medium Bronze	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-12L-40K-WH	120W Incandescent	4000K	1,200	White	Size: 9" H x 5-3/4" W x 4" D
High-Output Wall Mount	C-WM-A-WLHO-36L-50K-MB	100W MH	5000K	3,600	Medium Bronze	Size: 11" H x 7-1/7" W x 4-1/4" D
High-Output Wall Mount	C-WM-A-WLHO-34L-40K-MB	100W MH	4000K	3,377	Medium Bronze	Size: 11" H x 7-1/7" W x 4-1/4" D
Wall Mount	C-WM-A-WLSL-14L-50K-MB	120W Incandescent	5000K	1,500	Medium Bronze	Size: 12-3/5" H x 7-3/4" W x 4-3/5" D
Wall Mount	C-WM-A-WLSP-8L-40K-WH	75W I Incandescent	4000K	800	White	Size: 9-4/5" H x 4-2/5" W x 5-4/5" L
Wall Mount	C-WM-A-WLSP-8L-40K-DB	75W Incandescent	4000K	800	Dark Bronze	Size: 9-4/5" H x 4-2/5" W x 5-4/5" L



Architectural Slim Wall Packs

SLIMLINE LED WALL PACKS, 120-277V

Efficient; Architectural Design; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Wall Packs
- CRI: >70
- Location Type: Wet
- Non-Dimmable
- Finish Color: Dark Bronze
- High LPW: Up to 105
- Watts: 40 to 150

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
Architectural Slim	C-WP-A-SL-4L-50K-DB	100W MH	5000K	3,900	40	Size: 8" H x 7-1/2" W x 2-4/5" L
Architectural Slim	C-WP-A-SL-4L-40K-DB	100W MH	4000K	3,900	40	Size: 8" H x 7-1/2" W x 2-4/5" L
Architectural Slim	C-WP-A-SL-8L-50K-DB	250W MH	5000K	8,110	80	Size: 12-4/5" H x 14-1/5" W x 5" L
Architectural Slim	C-WP-A-SL-8L-40K-DB	250W MH	4000K	8,110	80	Size: 12-4/5" H x 14-1/5" W x 5" L
Architectural Slim	C-WP-A-SL-16L-50K-DB	320W PSMH / 400W MH	5000K	15,800	150	Size: 12-4/5" H x 14-1/5" W x 5" L
Architectural Slim	C-WP-A-SL-16L-40K-DB	320W PSMH / 400W MH	4000K	15,800	150	Size: 12-4/5" H x 14-1/5" W x 5" L

*See lighting.cree.com/warranty for details



LED Photocell, 120V <1000W



Adjustable U-Bracket Mount Kit



Adjustable Slip Fitter



Adjustable Swivel Fitter



Adjustable U-Bracket



Surface Mounting Box

SLIMLINE LED WALL PACK ACCESSORIES, 120-277V

Efficient; Architectural Design; Easy Installation; 5 Year Limited Warranty*

• Category: LED Outdoor Accessories

Item	SKU	Size/Fits
LED Photocell, 120V <1000W	C-ACC-A-PCCELL-LV	120V, <1000W, Fits C-FL-A-RTF2, C-FL-A-RTS2, C-FL-A-RTF4, C-FL-A-RTS4, C-WP-A Series
LED Photocell, 208-240V, <1000W	C-ACC-A-PCCELL-HV	208-240V, <1000W, Fits C-FL-A-RTF2, C-FL-A-RTS2, C-FL-A-RTF4, C-FL-A-RTS4, C-WP-A Series
Adjustable U-Bracket	C-ACC-A-AUBAS-LG-DB	For Slimline Wallpacks C-WP-A-SL-8L Series
Adjustable Slip Fitter	C-ACC-A-2SFAS-SM-DB	2", For Slimline Wallpacks C-WP-A-SL-4L Series
Adjustable Swivel Fitter	C-ACC-A-12SFAS-SM-DB	1/2" NPS, For Slimline Wallpacks C-WP-A-SL-4L Series
Adjustable U-Bracket	C-ACC-A-AUBAS-LG-DB	For Slimline Wallpacks C-WP-A-SL-8L Series
Adjustable Slip Fitter	C-ACC-A-2SFAS-LG-DB	2", For Slimline Wallpacks C-WP-A-SL-8L Series
Surface Mounting Box	C-ACC-A-SMBAS-DB	For Slimline Wallpacks C-WP-A-SL-4L, C-WP-A-SL-8L Series

*See lighting.cree.com/warranty for details

LED WALL PACKS, 120-277V

Efficient; Easy Installation; 5 Year Limited Warranty*

- Category: LED Outdoor Wall Packs
- CR1: >70
- Location Type: Wet
- Non-Dimmable
- Finish Color: Dark Bronze
- High LPW: Up to 144
- Watts: 20 to 160



LED Wall Pack Traditional (non cutoff)



LED Wall Pack Premium (full cutoff)



LED Wall Pack Traditional (full cutoff)

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
Traditional (non cutoff)	C-WP-A-TR-12L-50K-DB	250W MH	5000K	12,500	87	Size: 9-5/6" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TR-12L-40K-DB	250W MH	4000K	12,500	87	Size: 9-5/6" H x 18" W x 9-3/8" D
Premium (full cutoff)	C-WP-A-FCT3-6L-50K-DB	150W PSMH / 175W MH	5000K	6,200	75	Size: 4-11/16" H x 10" W x 10-5/16" D
Premium (full cutoff)	C-WP-A-FCT3-6L-40K-DB	150W PSMH / 175W MH	4000K	6,200	75	Size: 4-11/16" H x 10" W x 10-5/16" D
Traditional (non cutoff)	C-WP-A-TR-15L-50K-DB	320W PSMH / 400W MH	5000K	15,300	160	Size: 9-7/8" H x 18" W x 13" D
Traditional (non cutoff)	C-WP-A-TR-15L-40K-DB	320W PSMH / 400W MH	4000K	15,300	160	Size: 9-7/8" H x 18" W x 13" D
Traditional (full cutoff)	C-WP-A-TRFC-6L-50K-DB	150W PSMH / 175W MH	5000K	6,600	70	Size: 14-1/4" D x 9-1/4" W x 9" H
Traditional (full cutoff)	C-WP-A-TRFC-6L-40K-DB	150W PSMH / 175W MH	4000K	6,600	70	Size: 14-1/4" D x 9-1/4" W x 9" H
Traditional (non cutoff) 120V only	C-WP-A-TR-1L-40K-DB	50W MH	4000K	1,300	20	Size: 8-9/16" H x 7-3/16" W x 7-5/16" L
Premium (full cutoff)	C-WP-A-FCT3-3L-50K-DB	100W MH	5000K	3,600	36	Size: 4-1/2" H x 8-3/4" W x 9-1/2" D
Premium (full cutoff)	C-WP-A-FCT3-3L-40K-DB	100W MH	4000K	3,600	36	Size: 4-1/2" H x 8-3/4" W x 9-1/2" D
Traditional (non cutoff)	C-WP-A-TR-3L-50K-DB	100W MH	5000K	3,400	47	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TR-3L-40K-DB	100W MH	4000K	3,400	47	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TR-8L-50K-DB	150W PSMH / 175W MH	5000K	8,900	96	Size: 9-3/4" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TR-8L-40K-DB	150W PSMH / 175W MH	4000K	8,900	96	Size: 9-3/4" H x 18" W x 9-3/8" D

*See lighting.cree.com/warranty for details



LED Vapor Pendant Mounts



LED Wall Mounts



LED Vapor Ceiling Mounts

LED VAPOR TIGHTS, 120V

Efficient; Traditional Design; Easy To Install; 5 Year Limited Warranty*

- Category: LED Outdoor Vapor Tights
- CRI: >70
- Location Type: Wet
- Non-Dimmable
- High LPW: Up to 98
- Watts: 14 to 48

Item	SKU	Replaces	CCT	Lumens	Finish Color	Size/Fits
LED Vapor Tight, Small Ceiling Mount	C-VT-A-SMCL-9L-40K-GR	100W Incandescent	4000K	900	GR = Gray	9-1/3" H x 4-1/2" Diameter
LED Vapor Tight, Small Pendant Mount	C-VT-A-SMPD-9L-40K-GR	100W Incandescent	4000K	900	GR = Gray	10" H x 4-1/2" Diameter
LED Vapor Tight, Small Wall Mount	C-VT-A-SMWL-9L-40K-GR	100W Incandescent	4000K	900	GR = Gray	10" H x 4-2/5" W x 5-4/5" L
LED Vapor Tight, Large Ceiling Mount	C-VT-A-LGCL-12L-40K-GR	120W Incandescent	4000K	1200	GR = Gray	11-3/5" H x 5-4/5" Diameter
LED Vapor Tight, Large Pendant Mount	C-VT-A-LGPD-12L-40K-GR	120W Incandescent	4000K	1200	GR = Gray	12-2/5" H x 5-4/5" Diameter
LED Vapor Tight, Large Wall Mount	C-VT-A-LGWL-12L-40K-GR	120W Incandescent	4000K	1200	GR = Gray	Large - Wall Mount 12-2/5" H x 5-4/5" W x 9" L



LED Vapor Tight Shroud

LED VAPOR TIGHT ACCESSORIES

Accessories for C-Lite LED Vapor Tights

Item	SKU	Finish Color	Size/Fits
LED Vapor Tight, Small Shroud	C-ACC-A-VTSHR-SM-GR	GR = Gray	Small, For C-VT-A-SMCL, C-VT-A-SMPD Series
LED Vapor Tight, Large Shroud	C-ACC-A-VTSHR-LG-GR	GR = Gray	Large, For C-VT-A-LGCL, C-VT-A-LGPD Series

*See lighting.cree.com/warranty for details



LED Round High Bay



LED Round Low Bay

LED ROUND HIGH BAYS & LOW BAYS, 120-277V

Easy Installation; High Efficiency; 5 Year Limited Warranty*

- Category: LED Indoor High Bays and Low Bays
- CRI: >70
- Location Type: Damp
- Non-Dimmable
- Finish Color: White
- High LPW: Up to 124
- Watts: 79 to 210

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
LED Round High Bay	C-HB-A-RDAL-18L-50K-WH	250W MH	5000K	18,000	160	Includes White 16" Aluminum Reflector
LED Round High Bay	C-HB-A-RDPC-18L-50K-WH	250W MH	5000K	18,000	160	Includes 16" Polycarbonate Prismatic Diffuser
LED Round High Bay	C-HB-A-RDAL-26L-50K-WH	400W MH	5000K	26,000	210	Includes 16" Polycarbonate Prismatic Diffuser
LED Round High Bay	C-HB-A-RDPC-26L-50K-WH	400W MH	5000K	26,000	210	Includes White 16" Aluminum Reflector
LED Round Low Bay	C-LB-A-RDAL-8L-50K-WH	150W PSMH 175W MH	5000K	8,000	79	10" H x 14" W x 14" L
LED Round Low Bay	C-LB-A-RDAL-8L-40K-WH	150W PSMH 175W MH	4000K	8,000	79	10" H x 14" W x 14" L
LED Round Low Bay	C-LB-A-RDAC-8L-50K-WH	150W PSMH 175W MH	5000K	8,000	79	10" H x 14" W x 14" L
LED Round Low Bay	C-LB-A-RDAC-8L-40K-WH	150W PSMH 175W MH	4000K	8,000	79	10" H x 14" W x 14" L

*See lighting.cree.com/warranty for details



LED Linear High Bay



Premium LED Linear High Bay



Premium LED Linear High Bay

LED LINEAR HIGH BAYS, 120-277V

Easy Installation; High Efficiency; 5 Year Limited Warranty*

- Category: LED Indoor Linear High Bays
- CRI: 80
- Location Type: Damp
- Non-Dimmable, 0-10V
- White
- High LPW: Up to 129
- Watts: 108 to 220

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
Linear High Bay	C-HB-A-L4F-20L-50K-WH	4-lamp T5HO 54W 8-lamp T8 32W	5000K	20,500	160	3-1/2" H x 12" W x 47-1/2" L
Linear High Bay	C-HB-A-L4F-28L-50K-WH	6-lamp T5HO 54W	5000K	28,500	220	3-1/2" H x 12" W x 47-1/2" L
Premium Linear High Bay	C-PHB-A-L2F-13L-40K-WH	8-lamp T8 32W	4000K	13,000	108	3-3/5" H x 12-3/5" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L2F-13L-50K-WH	6-lamp T8 32W	5000K	13,000	108	3-3/5" H x 12-3/5" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L2F-20L-40K-WH	4-lamp T5HO 54W 8-lamp T8 32W	4000K	20,000	160	3-3/5" H x 17-3/10" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L2F-20L-50K-WH	4-lamp T5HO 54W 8-lamp T8 32W	5000K	20,000	160	3-3/5" H x 17-3/10" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L4F-27L-40K-WH	6-lamp T5HO 54W	4000K	27,000	220	3-3/5" H x 12-3/5" W x 46" L
Premium Linear High Bay	C-PHB-A-L4F-27L-50K-WH	6-lamp T5HO 54W	5000K	20,000	160	3-3/5" H x 12-3/5" W x 46" L

*See lighting.cree.com/warranty for details




Premium Linear High Bay PIR Sensor



Premium Linear High Bay Pendant Mount Kit



Linear High Bay Frosted Lens



Premium Linear High Bay Wire Guard



LED Hook & Cord Kits



1/2" Hook

LED HIGH & LOW BAY ACCESSORIES

Accessories for C-Lite LED High & Low Bays

Item	SKU	Size/Fits
Premium Linear High Bay PIR Sensor	C-PHB-A-HBPIR	Suits C-PHB Series
Premium Linear High Bay Pendant Mount Kit	C-PHB-A-HBPM	Suits C-PHB Series
Linear High Bay Frosted Lens	C-HB-A-LHBFL-12X48	Suits C-HB Series 12" x 47-1/2" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-12X24	Suits C-PHB Series 12-3/5" x 23-4/5" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-18X24	Suits C-PHB Series 17-3/10" x 23-4/5" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-12X46	Suits C-PHB Series 12-3/5" x 46" Fixtures
LED Hook & Cord Kit, 6 ft, 120-277V, No Plug	C-ACC-A-HKCRD-6FT-LV-NP	6ft, 120V-277V, No Plug, Fits 120-277V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 120V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits 120V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 120V, Straight Blade Plug	C-ACC-A-HKCRD-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits 120V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 277V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits 277V High Bays / Low Bays
LED Hook & Cord, 208-240V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits 208-240V High Bays / Low Bays
1/2" Hook	C-ACC-A-HK12	1/2", Fits High Bays / Low Bays



Cord, 6 ft. Straight Blade Plug



Cord, 6 ft, Twist Lock Plug



Receptacle, 15A, Twist Lock

GENERAL LED ACCESSORIES, 120-277V

Quality; Reliability

Item	SKU	Size/Fits
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits any 120V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits any 120V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits any 277V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits any 208-240V Fixture
LED Cord	C-ACC-A-CRD-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits any 120V Fixture
LED Cord	C-ACC-A-CRD-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits any 120V Fixture
LED Cord	C-ACC-A-CRD-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits any 208-240V Fixture
LED Cord	C-ACC-A-CRD-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits any 277V Fixture
LED Receptacle	C-ACC-A-RECEP-LV-TL	3-Wire, 15A / 120V, Twist Lock
LED Receptacle	C-ACC-A-RECEP-HV-TL	3-Wire, 15A / 277V, Twist Lock
LED Receptacle	C-ACC-A-RECEP-MV-TL	3-Wire, 15A / 208-240V, Twist Lock

Learn more at: c-lite.com | 800.236.6800

©2017 Cree, Inc. All rights reserved. For informational purposes only. Not a warranty or specification. C-Lite™ and the C-Lite logo are trademarks of Cree Inc. CAT/C-LITE-0514 Rev. Date 05/01/2017

C-LITE[™]
LED LIGHTING BY **CREE**