

MEDIUM & MOGUL BASED METAL HALIDE HID LAMPS

Enclosed Fixture • Med. & Mogul Base • 50-1500 Watts



- **Long Life**
Less frequent re-lamping reduces maintenance costs
- **High Output & Efficiency**
Reduced power consumption saves money on electricity costs
- **Low Color Shift**
Produces consistent lighting over the life of the lamp
- **Superior Lumen Maintenance**
More usable light over time extends the useful life of the lamp
- **Universal Burn**
Reduces SKU count in inventory
- **Heavy Gauge Glass, Metal & Connections**
Commercial grade lamps for long term durability and reliability
- **RoHS Compliant**



Selection. Solutions. Simplicity.

23220 W. 84th St., Shawnee, KS 66227 • Ph: 1.800.852.2217 • Fax: 1.913.441.6679 • Email: eiko@eiko.com
EiKO CANADA: 81 King Street, Barrie, ON L4N 6B5, Canada • Ph: 705-721-5189 • Fax: 705-721-7855

www.eiko.com

HID LAMPS

Appendix A – Warnings

WARNING: This lamp can cause serious skin burn and eye inflammation from shortwave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available.