



Enhancing  
the Lighting  
Experience



---

**2017/2018**  
CATALOG

---

COMMERCIAL  
INDUSTRIAL  
RESIDENTIAL



## ETi Solid State Lighting means value, quality, and performance.

Our parent company, Elec-Tech Solid State Lighting (HK) Ltd., is a 100% vertically integrated global supplier of LED components, lamps, and luminaires to many of the largest lighting brands and retailers in the world. The company's scale, attention to quality, and ability to bring products to market quickly has allowed us to emerge as a leader in the LED lighting industry, with an extensive and growing line of products for the residential, commercial, and industrial markets. With a tireless focus on customer satisfaction, ETi is continuously striving to provide the latest in LED lighting technology, while delivering value to our distributor customers, the product installer, and the end-user.

---

### TO ORDER:

**Find a sales representative near you at [www.ETiSSL.com/contact-us/](http://www.ETiSSL.com/contact-us/)**

---

- Customer Service Hours: 8:00AM – 5:00PM CST  
(1.855.384.7754) 855.ETi.SSLI  
Fax: 847.383.6256
- Standard shipping turnaround time is 24 to 48 hours
- Midwest and West Coast shipping locations

### ETi SSL PRODUCT OFFERINGS

Flushmounts.....	1
Recessed Downlights ....	2
Spin Lights™.....	3
Ceiling Fixtures .....	4
Vapor Tights .....	5
Strip Lights .....	6
Security Lights .....	7
Shop Lights .....	8
Wrap Lights.....	9
Under Cabinet Lights....	10
LED Tubes .....	11
Flat Panels .....	12
High Bays .....	13
Wall Packs .....	14
Emergency Lighting ....	15
Accessories .....	16

# Flushmounts



These luminaires can replace most fixture types in residential and commercial retail spaces and are ideal for hallways, corridors, utility spaces and work areas. Available in round or square in a variety of color temperatures, these fixtures are designed for most applications.

The addition of Color Preference® technology to some items allows the installer to select the color temperature through a switch on the unit.

- Easy installation
- ENERGY STAR® certified
- Rated life: 50,000 hours
- 5 year limited warranty
- Color Preference® technology featured on select items
- Multi-volt, dimming, and step dimming motion sensor options available



12in. & 16in. Low Profile



I-Series Brushed Nickel



7in. Low Profile



Reva Stepped Lens

## ETi LED Flushmounts

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54436201	FM-12-14-827-MV-N-B	12" Round Low Profile - Non-Dimmable	14	980	2700	120-277	6
54436241	FM-12-14-840-MV-N-B	12" Round Low Profile - Non-Dimmable	14	1000	4000	120-277	6
54437201	FM-16-22-827-MV-N-B	16" Round Low Profile - Non-Dimmable	22	1500	2700	120-277	4
54437241	FM-16-22-840-MV-N-B	16" Round Low Profile - Non-Dimmable	22	1600	4000	120-277	4
54437261	FM-16-22-850-MV-N-B	16" Round Low Profile - Non-Dimmable	22	1600	5000	120-277	4
54663142	FM-7-11-840-SV-N-0	7" Round Low Profile - Non-Dimmable	11.5	810	4000	120	6
54643142	FM-11-14-840-SV-D-C	11" Round I-Series Brushed Nickel Trim - Dimmable	14	980	4000	120	4
54620142	FM-15-22-840-SV-D-C	15" Round I-Series Brushed Nickel Trim - Dimmable	22	1550	4000	120	3
54074343	FM-12-14-840-SV-D-E	12" Round Reva Stepped Lens - Dimmable	14	1000	4000	120	4
54075343	FM-16-22-840-SV-D-E	16" Round Reva Stepped Lens - Dimmable	22	1640	4000	120	3
54618244	FM-20-30-840-SV-D-E	20" Round Reva Stepped Lens - Dimmable	30	2200	4000	120	2
54614142	FM-24-40-840-SV-D-E	24" Round Reva Stepped Lens - Dimmable	40	2900	4000	120	2
54436511*	FM-12-16-902-MV-D-B	12" Round Color Preference® Low Profile - 0-10V Dimmable (T24) Compatible with Motion Sensor accessory	16	1000	3000/4000/5000	120-277	6
54437511*	FM-16-24-902-MV-D-B	16" Round Color Preference® Low Profile - 0-10V Dimmable (T24) Compatible with Step Dimming Motion Sensor accessory	24	1600	3000/4000/5000	120-277	4

\* Available in Q4 2017



# Recessed Downlights



Our offering of recessed downlight retrofits provides high quality replacements for traditional incandescent and halogen downlights reducing both energy consumption and maintenance. These products are great in both residential and commercial applications.

The addition of Color Preference® technology to some items allows the installer to select the color temperature through a switch on the unit.

- 5 year limited warranty
- Rated life: 50,000 hours
- ENERGY STAR certified
- IC Rated for direct contact with insulation
- ASTM Certified Airtight product available
- Color Preference® technology featured on select items
- All 4" and 5" / 6" are wet location rated for showers and exterior use
- Dimmable
- T24 qualified product available
- 80 and 90 CRI available



Color Preference™  
Recessed Retrofit Downlight Kit



Recessed Retrofit  
Downlight Kit



AC Power Recessed  
Retrofit Downlight Kit



8in. High Output Downlight

## ETi LED Recessed Downlights

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
<b>Color Preference® Retrofit Downlight Kits</b>							
53185143	DL-4-10-902-SV-D	4" Color Preference® Downlight - Dimmable (T24)	10	625	3000/4000/5000	120	4
53186143	DL-6-11-902-SV-D	5"/6" Color Preference® Downlight - Dimmable (T24)	11	670	3000/4000/5000	120	4
53185142	DL-4-10-901-SV-D	4" Color Preference® Downlight - Dimmable (T24)	10	625	2700/3000/4000	120	4
53186401*	DL-6-11-901-SV-D	5"/6" Color Preference® Downlight - Dimmable (T24)	11	800	2700/3000/4000	120	4
53186311*	DL-6-11-902-SV-D	5"/6" Color Preference® Downlight Kit - Dimmable (T24)	11	800	3000/4000/5000	120	4
<b>Multi-Volt Downlights</b>							
53192211*	DL-6-14-902-MV-D	5"/6" Color Preference® Downlight, 0-10V Dimmable (T24)	14	800	3000/4000/5000	120-277	4
53189111*	DL-8-40-902-MV-D	8"/10" Color Preference® Downlight, 0-10V Dimmable (T24)	40	3000	3000/4000/5000	120-277	4
90600193*	DL-10TR	10" Downlight Trim for Color Preference® Downlight	—	—	—	—	—
53081141	DL-8-26-840-MV-D	8" High Output Downlight - 0-10V Dimmable	26	2025	4000	120-277	12
<b>Basic Retrofit Downlight Kits</b>							
53181101	DL-4-10-927-SV-D	4" Recessed Retrofit Downlight Kit - Dimmable (T24)	10	625	2700	120	4
53167103	DL-6-10-927-SV-D	5"/6" Recessed Retrofit Downlight Kit - Dimmable (T24)	10.5	670	2700	120	4
53179111	DL-6-18-930-SV-D	5"/6" Recessed Retrofit Downlight Kit - Dimmable (T24)	18	1300	3000	120	4
53182201*	DL-4-10-827-SV-D	4" AC Power Recessed Retrofit Downlight Kit - Dimmable	10.5	625	2700	120	4
53193101*	DL-6-11-827-SV-D	5"/6" AC Power Recessed Retrofit Downlight Kit - Dimmable	11	670	2700	120	4
53193141*	DL-6-11-840-SV-D	5"/6" AC Power Recessed Retrofit Downlight Kit - Dimmable	11	670	4000	120	4

\* Available in Q4 2017





Our patented Spin Light™ is the easiest way to convert a plain lampholder into an attractive, energy efficient LED flushmount fixture. Installation is literally as easy as screwing in a light bulb. Without doing any wiring, you can replace exposed sockets and bare bulbs in basements, garages, closets and other areas with high quality LED lighting. This versatile product can also be used in new work applications with the provided hardware and adapter.

The addition of Color Preference® technology to some items allows the installer to select the color temperature through a switch on the unit.

- Rated life: 50,000 hours
- ENERGY STAR certified
- Passive infrared motion sensor (PIR) option available
- Damp location rated
- 5 year limited warranty
- Available in keyless or pull chain models
- Color Preference® technology featured on select items

Patented! Spin Lights™ install in seconds!



7in. Spin Light



7in. Spin Light with pull chain



11in. Spin Light

## ETi LED Spin Lights™

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54606211	SL-7-11-830-SV-N	7" Spin Light	11.5	810	3000	120	5
54606242	SL-7-11-840-SV-N	7" Spin Light	11.5	830	4000	120	5
54617141	SLP-7-11-840-SV-N	7" Spin Light - Pull Chain	11.5	830	4000	120	5
54652141	SL-11-22-840-SV-N	11" Spin Light	22	1600	4000	120	4
54690112	SL-7-11-802-SV-N	7" Color Preference® Spin Light	11.5	810	3000/4000/5000	120	5
54606342*	SL-7-11-840-SV-N-OS	7" Spin Light with PIR Motion Sensor	11.5	830	4000	120	5
54652144**	SL-11-22-840-SV-N-BN	11" Spin Light Brushed Nickel	22	1600	4000	120	4



\* Available in Q4 2017 \*\* Available in Q1 2018 <sup>1</sup> Patents: 9500352, 9541270, D776326, 169113

# Ceiling Lights



Stylish and sophisticated, the ETi ceiling light series brings elegant LED lighting solutions to commercial, retail, hospitality and office spaces. Available in soft rectangular forms with pleasing design features, the ETi ceiling light series offers exceptional performance for precision lighting applications, while reducing energy and maintenance costs when compared with conventional light sources.

- 2' and 4' sizes available
- Stepped or traditional smooth lenses
- Rated life: 50,000 hours
- ENERGY STAR certified
- Damp location rated
- 5 year limited warranty
- Dimmable



Reva Stepped Lens



Traditional Smooth Lens

## ETi LED Ceiling Lights

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54648142	CL-12-20-840-SV-D-G	Reva Stepped Lens 1' x 2' - Dimmable	20	1500	4000	120	1
54647142	CL-14-40-840-SV-D-G	Reva Stepped Lens 1' x 4' - Dimmable	40	3000	4000	120	1
54649142	CL-14-75-840-SV-D-G	Reva Stepped Lens 1.5' x 4' - Dimmable	75	5500	4000	120	1
54644142	CL-14-40-840-SV-D-H	Traditional Smooth Lens 1' x 4' - Dimmable	40	3000	4000	120	1
54645142	CL-14-75-840-SV-D-H	Traditional Smooth Lens 1.5' x 4' - Dimmable	75	5500	4000	120	1



# Vapor Tights



Our 4-foot Vapor Tight LED fixtures are a durable industrial solution for tough environments. These fixtures are ideal for canopies, enclosed parking decks, garages or other industrial applications.

- One person installation
- Captive stainless steel latches
- UV, IR and mercury free
- 5 year limited warranty
- Rated life: 50,000 hours
- Battery Back-up (BBU) option
- DLC® Qualified
- Starts reliably in cold environments to -13°F (-25°C)
- Compatible motion sensor available
- IP65 wet location rated



## ETi LED Vapor Tights

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54656142	VT-4-43-840-MV	4' Vapor Tight	43	3600	4000	120-277	2
54656241	VT-4-34-840-MV	4' Vapor Tight - Compatible with Motion Sensor accessory	34	3600	4000	120-277	2
54656341*	VT-4-40-840-MV-EM	4' Vapor Tight - Built-in BBU Compatible with Motion Sensor accessory	40	3600	4000	120-277	2
54465141**	VT-4-51-840-MV	4' High Lumen Output Vapor Tight - Compatible with Motion Sensor accessory	51	5400	4000	120-277	2



\* Available in Q4 2017 \*\* Available in Q1 2018

# Strip Lights



ETi LED Strip Lights offer exceptional performance as high quality replacements for traditional fluorescent light fixtures. Lasting more than 5 times longer than fluorescent alternatives, these strip lights reduce energy and maintenance costs.

Perhaps the best aspect of these LED strip lights is their versatility. With a variety of available options, ETi LED Strip Lights are perfect for both residential and industrial uses. Typically used in work shops, garages and utility rooms, common commercial applications include manufacturing facilities, offices, retail stores, restaurants, schools, hospitals, and hotel/motel locations. Some models include a linking feature, allowing multiple fixtures to be connected via the included linking cable or end-to-end connector. Whether individual or linked together, standard or high lumen output, plug-in or direct wire, 120V or multi-volt, surface mounted or suspended, these slim, low profile fixtures provide the right amount of light where it is needed.



- Patent pending linking feature with cable or end-to-end connectors
- Connect up to 360 total watts (32 2ft. units or 16 4ft. units)
- Rated life: 50,000 hours
- Damp location rated
- UV, IR and mercury free
- Direct wire or plug-in options
- 5 year limited warranty
- ENERGY STAR certified
- Starts reliably in cold environments to -4° F (-20° C)

## ETi LED Strip Lights

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54263143	ST-2-10-840-SV-N	2' Linkable Strip Light (Direct Wire or Plug-In)	10	900	4000	120	6
54261143	ST-4-20-840-SV-N	4' Linkable Strip Light (Direct Wire or Plug-In)	20	1800	4000	120	4
54260144	ST-2-20-840-MV-N	2' Strip Light (Direct Wire)	20	1800	4000	120-277	6
54283144	ST-4-40-840-MV-N	4' Strip Light (Direct Wire)	40	3600	4000	120-277	4
54573161	ST-4-45-850-MV-D	4' Linkable High Lumen Output Strip Light - 0-10V Dimmable, also compatible with suspension mounting hardware sold separately	45	5000	5000	120-277	6



# Security Lights



Designed with rugged all metal construction for long life and optimal performance, our security lights provide even, bright light to protect your home or business while saving money with energy efficient integrated LEDs. With a built-in photocell for dusk to dawn light or a passive infrared motion sensor (PIR), you can count on a safe and securely illuminated space with minimal maintenance.

- Wet location rated for exterior use
- Passive infrared motion sensor (PIR) option
- Dusk to dawn control
- 5 year limited warranty
- Toolless adjustable heads
- Rated life: 50,000 hours
- ENERGY STAR certified
- Starts reliably in cold environments to -13° F (-25° C)



Dark Bronze Security Light



White Security Light

## ETi LED Security Lights

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
51401142	SC-20-840-SV-BZ	2-head Dusk to Dawn Security Light (Bronze)	20	1200	4000	120	2
51401144	SC-20-840-SV-W	2-head Dusk to Dawn Security Light (White)	20	1200	4000	120	2
51402241**	SC-20-840-SV-OS-BZ	2-head Security Light with PIR Motion Sensor (Bronze)	20	1800	4000	120	2
51402242**	SC-20-840-SV-OS-W	2-head Security Light with PIR Motion Sensor (White)	20	1800	4000	120	2



\*\* Available in Q1 2018

# Shop Lights



Our slim LED shop lights are designed to be used anywhere a traditional fluorescent fixture is used. Typical applications include work shops, workbenches, craft tables, light manufacturing areas, and general utility spaces.

- Linking feature available
- Replaces most applications using T8 fluorescent lamps
- Damp location rated
- ENERGY STAR certified
- 5 year limited warranty
- Rated life: 50,000 hours
- Starts reliably in cold environments to -4° F (-20° C)



Linkable Shop Light



Shop Light Bar



Shop Light with Bluetooth Speakers

## ETi LED Shop Lights

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54568143	SH-2-18-840-SV	2' Linkable Shop Light	18	1600	4000	120	2
54103162	SH-4-35-840-SV	4' Linkable Shop Light	35	3200	4000	120	4
54255142	SH-3-18-840-SV	3' Shop Light Bar	18	1500	4000	120	6
54254142	SH-3-42-840-SV	3' Slim Shop Light	42	3200	4000	120	4
54569143	SH-40-50-840-SV-BT	40" Shop Light with Bluetooth Speakers	50	3500	4000	120	2



# Wrap Lights



Traditional fluorescent wrap light fixtures are common in commercial and institutional buildings. The ETi family of LED wrap lights offers attractive, energy efficient alternatives, with low profile designs and even white light. Available in 2' or 4' lengths, in a variety of lumen outputs, these fixtures can also be modified in the field with our motion sensor or battery back-up accessories.

- 2' and 4' sizes
- T24 available
- Damp location rated
- Dimmable and non-dimmable versions
- Battery Back-up (BBU) option
- Compatible motion sensor available
- 5 year limited warranty
- Rated life: 50,000 hours
- ENERGY STAR certified



2ft. Wrap Light



4ft. Wrap Light



4ft. High Lumen Output Wrap Light

## ETi LED Wrap Lights

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54655242	WR-2-22-840-SV-N	2' Wrap Light	22	1800	4000	120	4
54654242	WR-4-40-840-SV-N	4' Wrap Light	40	3600	4000	120	4
54676142	WR-4-40-940-SV-N-OS	4' Wrap Light with Motion Sensor	40	3600	4000	120	2
54677143	WR-4-57-940-MV-N	4' High Lumen Output Wrap Light	57	5200	4000	120-277	2
54655441*	WR-2-20-840-MV-D	2' Wrap Light - 0-10V Dimmable [T24] - Compatible with Motion Sensor accessory	20	1800	4000	120-277	4
54676241	WR-4-40-840-MV-D	4' Wrap Light - 0-10V Dimmable [T24] - Compatible with Motion Sensor accessory	40	3600	4000	120-277	2
54676341*	WR-4-45-840-MV-D-EM	4' Wrap Light - 0-10V Dimmable [T24], Built-in BBU, Compatible with Motion Sensor accessory	45	3600	4000	120-277	2
54677441**	WR-4-57-840-MV-D	4' Wrap Light - 0-10V Dimmable [T24], Compatible with Motion Sensor accessory	57	5200	4000	120-277	2



\* Available in Q4 2017 \*\* Available in Q1 2018

# Under Cabinet Lights



An excellent replacement for traditional fluorescent or xenon lights, ETi LED Under Cabinet lights come in three sizes, so you can easily customize to your cabinet layout. Link up to 30 from one power source using the included linking cable or end-to-end connector. Typical uses include laundry rooms, work shops, desks, or shelving in residential or commercial buildings. You can also install above cabinets or under lower cabinets to illuminate the toe kick area.

- Beam adjustable option
- Plug-in and direct wire options available
- UV, IR and mercury free
- Dimming options allow you to set the light level for tasks or for ambience
- ENERGY STAR certified
- Rated life: 35,000 hours
- Damp location rated
- 5 year limited warranty
- Linkable



Linkable Under Cabinet Light



Linkable, Beam Adjustable Under Cabinet Light

## ETi LED Under Cabinets

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54196112	UC-12-6-830-SV	12" Linkable Under Cabinet Light - Step Dimming	6	350	3000	120	5
54195112	UC-18-8-830-SV	18" Linkable Under Cabinet Light - Step Dimming	8	500	3000	120	5
54194112	UC-24-11-830-SV	24" Linkable Under Cabinet Light - Step Dimming	11	700	3000	120	5
53502111*	UC-12-5-930-SV-D	12" Linkable, Beam Adjustable Under Cabinet Light - Dim to Warm CCT (Direct Wire or Plug-in)	5.5	300	2200-3000	120	5
53503111*	UC-18-9-930-SV-D	18" Linkable, Beam Adjustable Under Cabinet Light - Dim to Warm CCT (Direct Wire or Plug-in)	9	500	2200-3000	120	5
53504111*	UC-24-12-930-SV-D	24" Linkable, Beam Adjustable Under Cabinet Light - Dim to Warm CCT (Direct Wire or Plug-in)	12.5	700	2200-3000	120	5



\* Available in Q4 2017



ETi LED tubes are manufactured with glass sheathed in a shatter resistant sleeve. ETi offers both direct replacement and integral driver replacements to traditional fluorescent tubes that can be used in many residential and commercial applications. But, unlike fluorescent tubes, LED tubes contain no mercury, which is safer for you and better for the environment.

- 330° light output
- Damp location rated
- DLC qualified, NSF certified
- Starts reliably in cold environments to -13°F (-25°C)
- Multi-volt (Integral Driver)
- 5 year limited warranty
- Rated life: 50,000 hours

## ETi Direct Replacement/Ballast Compatible LED Tubes

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54140241	T8BC-4-20-840-MV	4' T8 Direct Replacement Shatter Resistant Glass Tube (DLC, NSF)	20	2160	4000	Ballast Driven	15
54140261	T8BC-4-20-850-MV	4' T8 Direct Replacement Shatter Resistant Glass Tube (DLC, NSF)	20	2200	5000	Ballast Driven	15
54217141	T8BC-4-16-840-MV	4' T8 Direct Replacement Shatter Resistant Glass Tube (DLC)	16	2000	4000	Ballast Driven	15
54217161	T8BC-4-16-850-MV	4' T8 Direct Replacement Shatter Resistant Glass Tube (DLC)	16	2000	5000	Ballast Driven	15

## ETi Integral Driver LED Tubes

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54296141	T8BP-4-15-840-MV-18	4' T8 Integral Shatter Resistant Glass Tube (DLC, NSF)	15	1800	4000	120-277	20
54296161	T8BP-4-15-850-MV-18	4' T8 Integral Shatter Resistant Glass Tube (DLC, NSF)	15	1800	5000	120-277	20
54296143	T8BP-4-15-840-MV (IP)	4' T8 Integral Shatter Resistant Glass Tube (DLC, NSF) (Individual Pack)	15	1800	4000	120-277	10
54296163	T8BP-4-15-850-MV (IP)	4' T8 Integral Shatter Resistant Glass Tube (DLC, NSF) (Individual Pack)	15	1800	5000	120-277	10
54222241	T8BP-4-12-840-MV	4' T8 Integral Shatter Resistant Glass Tube (DLC, NSF)	12	1800	4000	120-277	24
54222261	T8BP-4-12-850-MV	4' T8 Integral Shatter Resistant Glass Tube (DLC, NSF)	12	1800	5000	120-277	24
54296441	T8BP-4-15-840-MV-22	4' T8 Integral Shatter Resistant Glass Tube (DLC, NSF)	15	2200	4000	120-277	24
54296461	T8BP-4-15-850-MV-22	4' T8 Integral Shatter Resistant Glass Tube (DLC NSF)	15	2200	5000	120-277	24
54222131	T8BP-4-13-835-MV	4' T8 Integral Shatter Resistant Glass Tube (DLC)	13	1800	3500	120-277	24
54216141	T5BP-4-22-840-MV	4' T5 Integral Shatter Resistant Glass Tube (NSF)	22	3300	4000	120-277	24
54216161	T5BP-4-22-850-MV	4' T5 Integral Shatter Resistant Glass Tube (NSF)	22	3300	5000	120-277	24
54293141	T8-U-15-840-MV	6" Leg Spacing Integral U-Bent Tube	15	1800	4000	120-277	6

## ETi LED Retrofit Kits

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54296168	RK-60-850-MV	LED Retrofit Kit for Fluorescent Fixtures, LED Tubes included	60	7200	5000	120-277	2



# Flat Panels



Flat panels provide excellent aesthetics at an affordable cost, resulting in fast payback. Whether the installation is new construction or a retrofit project, our flat panels can replace lay-in troffers, baskets, and parabolic fixtures. ETi's basic flat panel offering has a back side driver for drop-in and grid ceiling applications, while our premium flat panels are available with an integrated driver, allowing for a true surface mount installation.

- 2' x 2' and 2' x 4' sizes available
- Surface mounting and suspension kits available
- Rated life: 50,000 hours
- UV, IR and mercury free
- 5 year limited warranty
- Damp location rated
- DLC qualified



2' X 2' Premium Flat Panel



2' X 4' Premium Flat Panel

## ETi LED Flat Panels

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
54320141	FPI-22-42-840-MV-D	2'x2' Premium Flat Panel, 0-10V Dimmable (DLC)	42.5	4250	4000	120-277	1
54320161	FPI-22-42-850-MV-D	2'x2' Premium Flat Panel, 0-10V Dimmable (DLC)	42.5	4250	5000	120-277	1
54321141	FPI-24-42-840-MV-D	2'x4' Premium Flat Panel, 0-10V Dimmable (DLC)	42.5	4250	4000	120-277	1
54321161	FPI-24-42-850-MV-D	2'x4' Premium Flat Panel, 0-10V Dimmable (DLC)	42.5	4250	5000	120-277	1
54320142*	FPE-22-40-840-MV-D	2'x2' Flat Panel, 0-10V Dimmable (DLC)	40	4000	4000	120-277	4
54320162*	FPE-22-40-850-MV-D	2'x2' Flat Panel, 0-10V Dimmable (DLC)	40	4000	5000	120-277	4
54321142*	FPE-24-50-840-MV-D	2'x4' Flat Panel, 0-10V Dimmable (DLC)	50	5000	4000	120-277	2
54321162*	FPE-24-50-850-MV-D	2'x4' Flat Panel, 0-10V Dimmable (DLC)	50	5000	5000	120-277	2



\* Available in Q4 2017

# High Bays



Our round high bay brings energy savings with an aesthetically pleasing look to a category filled with legacy offerings. Replacing HID, fluorescent, and induction fixtures with these powerful, low wattage high bays provides quick payback in a variety of indoor spaces. The ETi series of round high bays come in lumen packages from 15,000 lumens to 38,000 lumens.

- DLC qualified
- Motion sensor compatible
- Emergency Battery Back-up (BBU) compatible
- Rated life: 50,000 hours
- Rated for a temperature range of -40°F to 113°F
- 5 year limited warranty



## ETi LED High Bays

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
50228161	HB-143-850-MV	Round High Bay (DLC) Compatible with Motion Sensor accessory	143	15,000	5000	120-277	1
50228261	HB-115-850-MV-EM	Round High Bay (DLC Premium) Compatible with Battery Back-Up and Motion Sensor accessories	115	15,000	5000	120-277	1
50228461	HB-115-850-MV	Round High Bay (DLC Premium) Compatible with Motion Sensor accessory	115	15,000	5000	120-277	1
50228361	HB-185-850-MV	Round High Bay (DLC Premium) Compatible with Motion Sensor accessory	185	24,000	5000	120-277	1
50228561	HB-270-850-MV	Round High Bay (DLC Premium) Compatible with Motion Sensor accessory	270	38,000	5000	120-277	1



# Wall Packs



Ideal for new or retrofit applications, ETi's Wall Pack series provides cost effective security lighting with a traditional look. When used as a replacement to metal halide or HPS fixtures, these products will match your existing footprint, preventing unsightly mismatched paint or fading issues. Cut off shields for glare reduction and photocell sensors for automatic dusk to dawn operation are available as accessories to our wall pack products.

- Durable metal housing
- Easy to mount
- 100W - 400W MH equivalent
- Glare free lenses
- Wet location rated
- DLC qualified
- Photocell sensor and cut off shield accessories available
- Rated life: 50,000 hours
- 5 year limited warranty



Small Wall Pack



14in. Wall Pack



18in. Wall Pack

## ETi Wall Packs

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Product Dimension	Case Pack
53305161	WP-20-850-MV	Small Wall Pack - 100W MH equivalent, with photocell sensor	20	2000	5000	120-277	6.85" x 10.43" x 3.7"	4
53304261	WP-32-850-MV	14in. Wall Pack - 150W MH equivalent, compatible with photocell accessory	32	3500	5000	120-277	14.21" x 9.25" x 7.44"	1
53304161	WP-54-850-MV	14in. Wall Pack - 250W MH equivalent, compatible with photocell accessory	54	6000	5000	120-277	14.21" x 9.25" x 7.44"	1
53304361	WP-74-850-MV	14in. Wall Pack - 400W MH equivalent, compatible with photocell accessory	74	8000	5000	120-277	14.21" x 9.25" x 7.44"	1
53303161	WP-90-850-MV	18in. Wall Pack - 400W MH equivalent, compatible with photocell accessory	90	10000	5000	120-277	18.31" x 9.29" x 9.06"	1



# Emergency Lighting



When looking for complete building lighting solutions, ETi's LED exit signs and emergency back-up lights are ready. Our rugged, best-in-class emergency lighting products combine state-of-the-art LED technology, advanced optical performance, and durability in a visually pleasing package.

- Damp or wet rated options
- Supports emergency light heads
- ENERGY STAR certified
- 5 year limited warranty
- Rated life: 50,000 hours



## ETi Emergency Lights

Model #	Part #	Description	Wattage	Lumens	CCT	Input Voltage	Case Pack
55301101	EM-EX-R	LED EXIT Sign (Red Letter)	—	—	—	120-277	6
55502101	EM-ELC-R	Emergency Light/EXIT Sign Combo (Red Letter)	—	—	—	120-277	6
55502201	EM-ECL-R-RC	Emergency Light/EXIT Sign Combo w/ Remote Compatibility (Red Letter)	—	—	—	120-277	6
55501101	EM-EL	Emergency Light (2-head)	2.4	—	—	120-277	6
55501201	EM-EL-RC	Emergency Light w/ Remote Compatibility (2-head)	2.4	—	—	120-277	6
55503101	RM-ELR-H1	Emergency Light - Single (Wet Rated)	1.2	—	—	—	12
55503201	EM-ELR-112	Emergency Light - Double (Wet Rated)	2.4	—	—	—	12



# Accessories

Designed to enhance your lighting experience, these add-on accessories will transform your lighting design and create the end result you seek. Whether for a flushmount panel, strip light conversion or motion sensor add-on, ETi has your lighting needs covered.



BIPIN-20



90600017



90600046



90600121



90600143



54296301



90600018



90600019



90600144



90600145

## ETi Accessories

Model #	Part #	Description	Wattage	Input Voltage	Case Pack
BIPIN-20	NA	Universal NON Shunted Bi-Pin T8 Tombstone	—		20
BIPIN-12	NA	U-bent NON Shunted Bi-Pin T8 Tombstone	—		12
54296301	NA	8' to 4' Strip T8 Conversion Kit w/ Non Shunted Sockets and Bridges	—		10
54657102	NA	Junction Box Cover Plate	—		10
54242102	NA	5' Linking Cable	—		10
90600017	NA	2'x2' Surface Mounting Kit	—		6
90600018	NA	2'x4' Surface Mounting Kit	—		4
90600019	NA	Earthquake Clip Kit (10-pack, 4 clips/pk)	—		10
95457326101	NA	Aircraft Cable for Suspension Mounting (Two 10' pieces)	—		84
90600046	NA	Junction Box for Highbay Motion Sensor	—		20
90600121	NA	Motion Sensor (External)	—	120-277	60
90600143	NA	Battery Back-up	25	120-277	6
90600144	NA	Step Dimming Motion Sensor (Internal)	—	120-277	60
90600145	NA	Motion Sensor (Internal)	—	120-277	60
20170001*	PE-MV-01	Photocell for Wall Pack	—	120-277	10
20170002*	CS-WP-14	Cut off Shield for 14in Wall Pack	—	—	5
20170003*	CS-WP-18	Cut off Shield for 18in Wall Pack	—	—	5

\* Available in Q4 2017



# A UNIQUE APPROACH. EXTRAORDINARY RESULTS.



ETi Solid State Lighting, Inc. provides the latest in LED lighting technology for today's extremely competitive and fast-paced marketplace.

Our North American headquarters in Vernon Hills, IL, represents a formidable global organization. ETi Solid State

Lighting, Inc., a wholly owned subsidiary of Elec-Tech Solid State Lighting (HK) Ltd., offers a growing line of products that includes LED tubes, a broad range of LED fixtures, LED downlights, and portable LED lights. With Jadestone managed funds holding 100% interest in Elec-Tech Solid State Lighting (HK) Ltd., the company is well-positioned for future growth, building on its established manufacturing capabilities, end-user driven product innovation, global management team, and robust customer base.



## CONTACT US

1.855.384.7754

[ETiSSL.com](http://ETiSSL.com)

ETi Solid State Lighting, Inc.  
720 Corporate Woods Parkway  
Vernon Hills, IL 60061  
Fax: 847.383.6256

ETi Solid State Lighting, Inc. is a wholly owned subsidiary of Elec-Tech Solid State Lighting (HK) Ltd.



**SOLID STATE  
LIGHTING INC.**

---

**FOR MORE INFORMATION,  
VISIT [ETiSSL.com](http://ETiSSL.com)**

---

**TO ORDER:**

[www.ETiSSL.com/contact-us/](http://www.ETiSSL.com/contact-us/)

Call: 1.855.ETi.SSLI (1.855.384.7754)



Standard shipping turnaround time is 24 to 48 hours

Midwest and West coast shipping locations

Customer Service Hours: 8:00AM – 5:00PM CST

(1.855.384.7754) 855.ETi.SSLI

Fax: 847.383.6256