



HEXAGON NUTS

STOCK NO.	UPC NO.	SIZE	BOLT SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER	
GRADE 2 STEEL ZINC PLATED							
JN157	79957	4-40	7/64	.16	100/500	4.48/c	NEW
JN159	80427	6-32	1/8	.26	100/500	2.68/c	
JN160	80428	8-32	5/32	.32	100/500	3.00/c	
JN161	80429	10-24	3/16	.38	100/500	3.20/c	
JN162	80430	10-32	3/16	.36	100/500	3.20/c	
JN163	80431	1/4-20	1/4	.75	100/500	3.85/c	
JN164	80432	5/16-18	5/16	1.09	100/500	6.93c	
JN165	80433	3/8-16	3/8	1.55	100/500	8.90/c	
JN170	83140	7/16-14	7/16	2.81	100/500	18.63/c	NEW
JN166	80434	1/2-13	1/2	1.80	50/250	18.10/c	
JN167	80435	5/8-11	5/8	1.81	25	32.20/c	
JN168	80436	3/4-10	3/4	2.91	25	44.92/c	
HEAVY HEX NUT GRADE 2 STEEL ZINC PLATED							
JHFN38	80437	3/8-16	3/8	2.86	100	12.50/c	
JHFN12	80438	1/2-13	1/2	6.07	100	24.25/c	
JHFN58	86658	5/8-11	5/8	2.61	25/125	46.20/c	NEW
JHFN34	86489	3/4-10	3/4	4.73	25/125	129.00/c	NEW
GRADE 5 HARDENED STEEL ZINC PLATED							
JG5N163	80439	1/4-20	1/4	.75	100/500	4.03/c	
JG5N164	80440	5/16-18	5/16	1.10	100/500	5.98/c	
JG5N165	80441	3/8-16	3/8	1.59	100/500	9.68/c	
JG5N170	83915	7/16-14	7/16	11.9	100/500	57.40/c	NEW
JG5N166	80442	1/2-13	1/2	1.82	50	19.40/c	
JG5N167	80443	5/8-11	5/8	1.83	25	39.40/c	
JG5N168	80444	3/4-10	3/4	2.92	25	65.80/c	
GRADE 8 HARDENED STEEL ZINC PLATED							
JG8N163	80445	1/4-20	1/4	.74	100/500	5.70/c	
JG8N164	80446	5/16-18	5/16	1.10	100/500	8.48/c	
JG8N165	80447	3/8-16	3/8	1.60	100/500	12.33/c	
JG8N169	81482	7/16-14	7/16	2.81	100/500	20.89/c	NEW
JG8N166	80448	1/2-13	1/2	1.85	50	28.06/c	
JG8N167	80449	5/8-11	5/8	1.87	25	55.20/c	
JG8N168	80450	3/4-10	3/4	2.87	25	87.32/c	
STAINLESS STEEL 18-8 TYPE							
JSN10	80451	6-32	1/8	.26	100/500	7.23/c	
JSN11	80452	8-32	5/32	.30	100/500	7.73/c	
JSN12	80453	10-24	3/16	.36	100/500	8.35/c	
JSN13	80454	10-32	3/16	.35	100/500	8.35/c	
JSN14	80455	1/4-20	1/4	.77	100/500	10.68/c	
JSN15	80456	5/16-18	5/16	1.10	100/500	21.80/c	
JSN16	80457	3/8-16	3/8	1.63	100/500	23.50/c	
JSN20	82279	7/16-14	7/16	2.85	100/500	37.53/c	NEW
JSN18	80458	1/2-13	1/2	1.92	50	50.80c	
JSN19	82278	5/8-11	5/8	7.34	100/500	118.93/c	NEW

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST

CONTINUED ON NEXT PAGE

B

NUTS



CONTINUED HEXAGON NUTS

STOCK NO.	UPC NO.	SIZE	BOLT SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER	
SILICON BRONZE							
J5BN6	73306	6-32	1/8	.25	100/500	27.68/c	NEW
J5BN8	73308	8-32	5/32	.38	100/500	31.93c	NEW
J5BN24	73324	10-24	3/16	.36	100/500	40.53/c	NEW
J5BN32	73332	10-32	3/16	.38	100/500	40.53/c	NEW
J5BN14	80459	1/4-20	1/4	.46	50	29.36/c	
J5BN516	80460	5/16-18	5/16	.63	50	41.36/c	
J5BN38	80461	3/8-16	3/8	.91	50	53.86/c	NEW
J5BN12	80462	1/2-13	1/2	1.06	25	126.12/c	
J5BN58	84340	5/8-11	5/8	1.81	25	375.38/c	NEW
BRASS							
JN159BR	80463	6-32	1/8	.26	100/500	7.10/c	
JN160BR	80464	8-32	5/32	.33	100/500	7.60/c	
JN161BR	62272	10-24	3/16	.38	100/500	15.40/c	NEW
JN162BR	80465	10-32	3/16	.38	100/500	9.70/c	
JN163BR	80466	1/4-20	1/4	1.82	100/500	15.53/c	
JN165BR	62276	3/8-16	3/8	1.73	100/500	48.73/c	NEW
NEW 316 TYPE STAINLESS STEEL							
JSN14316SS	89341	1/4-20	1/4	.66	100/500	PLEASE CALL FOR TRADE LIST PRICING	NEW
JSN15316SS	89315	5/16-18	5/16	.65	100/500		NEW
JSN16316SS	96716	3/8-16	3/8	.82	50/250		NEW
JSN20316SS	89320	7/16-14	7/16	1.44	50		NEW
JSN25316SS	89325	1/2-13	1/2	1.82	50		NEW
JSN19316SS	96719	5/8-11	5/8	3.67	50		NEW
NEW GALVANIZED							
JN163G	83163	1/4-20	1/4	.81	100/500	12.10/c	NEW
JN165G	83165	3/8-16	3/8	1.60	100/500	16.10/c	NEW
JN166G	83166	1/2-13	1/2	1.92	50/250	36.00/c	NEW
JN167G	83167	5/8-11	5/8	3.66	50/250	68.20/c	NEW
NEW JAM NUT STEEL ZINC							
JN163J	83713	1/4-20	1/4	.55	100/500	7.03/c	NEW
JN165J	83715	3/8-16	3/8	1.55	100/500	49.75/c	NEW

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST



STAINLESS STEEL NUT KIT **NEW!** 18-8 SERIES TYPE

STOCK NO.	UPC NO.	DESCRIPTION OF CONTENTS	STD. PKG./MSTR. CARTON	WT. EACH	SUGGESTED TRADE LIST PRICE PER
SNK1	90210	400 pcs - Hexagon Nuts 100 - 6-32, 100 - 8-32, 100 - 10-32 50 - 1/4-20, 30 - 5/16-18, 20 - 3/8-16	1/25	1.90	31.08/ea kit



HEX LOCK NUTS

WITH EXTERNAL TOOTH LOCK WASHER ATTACHED

STOCK NO.	UPC NO.	SIZE	BOLT SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER	
STEEL ZINC CHROMATE							
JTLN1	80467	6-32	1/8	.28	100/500	7.25/c	
JTLN2	80468	8-32	5/32	.33	100/500	7.73/c	
JTLN3	80469	10-24	3/16	.39	100/500	8.25/c	
JTLN4	80470	10-32	3/16	.40	100/500	8.35/c	
JTLN5	80471	1/4-20	1/4	.72	100/500	9.75/c	
JTLN6	80472	5/16-18	5/16	1.20	100/500	15.80/c	
JTLN7	80473	3/8-16	3/8	1.72	100/500	20.35/c	
NEW STAINLESS STEEL 18-8 TYPE							
JTLN5SS	90095	1/4-20	1/4	0.73	100/500	PLEASE CALL	NEW
JTLN7SS	90097	3/8-16	3/8	1.70	100/500		NEW

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST




NYLON INSERT LOCK NUTS

For use in areas of high vibration • Eliminates the need for a lockwasher
Not for use in high heat situations.

STOCK NO.	UPC NO.	SIZE	BOLT SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER	
STEEL ZINC CHROMATE							
JNYN159	80474	6-32	1/8	.30	100/500	7.25/c	
JNYN160	80475	8-32	5/32	.44	100/500	7.73/c	
JNYN161	80476	10-24	3/16	.54	100/500	8.35/c	
JNYN162	80477	10-32	3/16	.53	100/500	8.35/c	
JNYN163	80478	1/4-20	1/4	.80	100/500	9.75/c	
JNYN164	80479	5/16-18	5/16	1.18	100/500	15.80/c	
JNYN165	80480	3/8-16	3/8	1.77	100/500	20.35/c	
JNYN166	80481	1/2-13	1/2	2.26	50	25.40/c	
JNYN167	80482	5/8-11	5/8	2.19	25	44.72/c	
JNYN168	80483	3/4-10	3/4	3.10	25	84.80/c	
NEW STAINLESS STEEL 18-8 TYPE							
JNYN160SS	84471	8-32	3/32	.45	100/500	PLEASE CALL FOR TRADE LIST PRICING	NEW
JNYN161SS	84472	10-24	3/16	.53	100/500		NEW
JNYN162SS	84473	10-32	3/16	.52	100/500		NEW
JNYN163SS	84474	1/4-20	1/4	.84	100/500		NEW
JNYN164SS	84475	5/16-18	5/16	1.15	100/500		NEW
JNYN165SS	84476	3/8-16	3/8	1.81	100/500		NEW
JNYN172SS	84483	7/16-14	7/16	2.41	100/500		NEW
JNYN166SS	84477	1/2-13	1/2	2.30	50/250		NEW
JNYN167SS	84478	5/8-11	5/8	4.42	50/250		NEW

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST



SERRATED HEX FLANGE LOCK NUTS

FOR USE IN HIGH VIBRATION AREAS

STOCK NO.	UPC NO.	SIZE	BOLT SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER	
STEEL ZINC CHROMATE							
JSFN832	82060	8-32	3/32	.60	100/500	3.65/c	
JSFN1024	82062	10-24	3/16	.66	100/500	3.83/c	
JSFN1032	82064	10-32	3/16	.65	100/500	3.83/c	
JSFN1420	82066	1/4-20	1/4	.93	100/500	4.60/c	
JSFN51618	82068	5/16-18	5/16	1.30	100/500	8.93/c	
JSFN3816	82070	3/8-16	3/8	1.90	100/500	11.23/c	
NEW STAINLESS STEEL 18-8 TYPE							
JSFN1213SS	93818	1/2-13	1/2	2.29	50/250	PLEASE CALL	NEW

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST

NUTS



WING NUTS

General purpose nuts designed for rapid assembly and disassembly by hand

STOCK NO.	UPC NO.	SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE
ZINC PLATED					
JWN3	79899	8-32	.86	100/500	12.38/c NEW
JWN4	79900	10-24	.92	100/500	14.90/c NEW
JWN5	79901	10-32	.92	100/500	16.20/c NEW
JWN6	80484	1/4-20	1.28	100/500	17.65/c
JWN7	80485	5/16-18	1.47	100/500	24.43/c
JWN8	80486	3/8-16	2.75	100/500	37.63c
JWN9	80487	1/2-13	3.40	50/250	89.43/c
NEW STAINLESS STEEL 18-8 TYPE					
JWN2SS	90782	6-32	.80	100/500	PLEASE CALL FOR TRADE LIST PRICING NEW
JWN3SS	90783	8-32	.84	100/500	
JWN4SS	90793	10-24	.93	100/500	
JWN6SS	90785	1/4-20	1.36	100/500	
JWN7SS	90786	5/16-18	1.99	100/500	
JWN8SS	90787	3/8-16	3.35	100/500	



CAP NUTS

Provides a proper finish when covering exposed threaded bolt ends

STOCK NO.	UPC NO.	SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE
NICKEL PLATED					
JCN160	81798	6-32	.30	100/500	26.13/c NEW
JCN163	80488	1/4-20	.75	100/500	10.75/c
JCN164	80489	5/16-18	1.42	100/500	20.83/c
JCN165	80490	3/8-16	1.88	100/500	27.05/c
NEW STAINLESS STEEL 18-8 TYPE					
JCN163SS	90916	1/4-20	1.31	100/500	PLEASE CALL NEW
JCN164SS	92917	5/16-18	2.18	100/500	
JCN165SS	92918	3/8-16	3.36	100/500	



SQUARE NUTS

ZINC PLATED

Used for channel and strut applications

STOCK NO.	UPC NO.	THREAD DIAMETER	WIDTH "A"	THICKNESS "B"	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE
JSQ2	80491	6/32	5/16	7/64	.12	100/500	3.33/c
JSQ3	80492	8/32	11/32	1/8	.36	100/500	3.45/c
JSQ4	80493	10/24	3/8	1/8	.43	100/500	3.65/c
JSQ5	80494	10/32	3/8	1/8	.44	100/500	3.70/c
JSQ6	80495	1/4-20	7/16	3/16	.79	100/500	5.78/c
JSQ7	80496	5/16-18	9/16	7/32	.47	100/500	9.03/c
JSQ8	80497	3/8-16	5/8	1/4	2.45	100/500	14.53/c
JSQ9	81069	1/2-13	13/16	7/16	2.90	50/250	77.23/c NEW



HEXAGON NUT KIT

STEEL ZINC CHROMATE

Six popular sizes!

STOCK NO.	UPC NO.	DESCRIPTION OF CONTENTS	STD. PKG./MSTR. CARTON	WEIGHT EACH	SUGGESTED TRADE LIST PRICE PER
NK1	10506	400 pcs - Hexagon Nuts 100 - 6-32, 100 - 8-32, 100 - 10-32, 50 - 1/4-20, 30 - 5/16-18, 20 - 3/8-16	1/25	1.92	18.80/ea kit

MASTER PLUG® SYSTEM

THREADED INSERT-FASTENING, SEALING, CUSHIONING SYSTEM




ADAPTABILITY

- Fastens blind holes and closed-end holes
- Cushions and seals similar and non-similar materials
- Absorbs vibration and seals both sides
- Tapered design enhances fastening installation
- Won't crack with ozone and ultraviolet exposure

VERSATILITY

- Removable and re-insertable
- Installs with conventional tools
- Works as a system with MASTER SEAL® washers
- Flange thickness always in proportion to size
- Grip range covers all dimensions



MASTER PLUG® IS A REGISTERED TRADEMARK
MASTER SEAL® IS A REGISTERED TRADEMARK

FOR STEEL BUILDING CONSTRUCTION

PACKAGED IN A PLASTIC BOX

STOCK NO.	UPC NO.	SIZE	BODY DIA.	OVERALL LENGTH	FLANGE O.D.	FLANGE THICKNESS	STD. PKG.	WT. PER PKG.	SUGGESTED TRADE LIST PRICE PER
MPS10	10383	6-32L	.250	1.062	.500	.062	25	.14	19.03/ ea pkg
MPS11	10384	10-32S	.375	.625	.562	.062	25	.20	19.13/ ea pkg
MPS12	10385	10-32R	.375	1.062	.562	.062	25	.16	22.50/ ea pkg
MPS13	10386	1/4-20S	.500	.855	.875	.090	20	.13	19.03/ ea pkg
MPS14	10387	1/4-20R	.500	1.276	.875	.100	15	.19	16.98/ ea pkg

PACKAGED IN A POLY BAG

STOCK NO.	UPC NO.	SIZE	BODY DIA.	OVERALL LENGTH	FLANGE O.D.	FLANGE THICKNESS	STD. PKG.	WT. PER PKG.	SUGGESTED TRADE LIST PRICE PER
MPS15	10388	6-32L	.250	1.062	.500	.062	100	.58	57.08/c
MPS16	10389	10-32S	.375	.625	.562	.062	100	.50	57.43/c
MPS17	10390	10-32R	.375	1.062	.562	.062	100	.56	67.43/c
MPS18	10391	1/4-20S	.500	.855	.875	.090	100	.94	71.50/c
MPS19	10392	1/4-20R	.500	1.276	.875	.100	100	1.18	84.93/c