



Tools & Accessories Corp.

Toll Free: 1-800-796-4716

8975 Henkels Lane Suite 710 Annapolis Junction, MD 20701

Baltimore: 410-735-8800

Washington: 301-369-9191

Fax: 301-498-7628

Email: Sales@tatool.net

WWW.TATOOLSONLINE.COM



Nothing but **HEAVY DUTY.**

OFFERS VALID THROUGH APRIL 30, 2018 OR WHILE SUPPLIES LAST

\$100 TRADE-IN

M18 FUEL

GET \$100 OFF OF PURCHASE OF A QUALIFYING M18 FUEL™ KIT WHEN YOU TRADE IN A PROFESSIONAL GRADE CORDLESS TOOL AND (2) BATTERIES.

QUALIFYING KITS:

2703-22	2704-22	2705-22	2706-22	2897-22	2894-22	2896-22	2899-22	2795-22	2796-22	2866-22	2760-22	2753-22	2754-22
2755-22	2755B-22	2766-22	2767-22	2768-22	2765-22	2860-22	2861-22	2862-22	2863-22	2757-22	2758-22	2759-22	2759B-22

\$399 - \$100 =
\$299



M18 FUEL™
2-Tool Combo Kit
(2897-22)

\$279 - \$100 =
\$179



M18 FUEL™ 1/2"
Drill/Driver Kit
(2703-22)

\$449 - \$100 =
\$349



M18 FUEL™ High Torque
1/2" Impact Wrench
with Friction Ring Kit
(2767-22)

\$329 - \$100 =
\$229



M18 FUEL™ 1/2"
Compact Impact
Wrench w/ Pin
Detent Kit (2755-22)

E-REBATES

TO REDEEM GO TO WWW.MILWAUKEETOOL.COM/ER/IC

BUY KNOCKOUT OR EXACT™ SETS



GET A FREE GOODS PACKAGE VIA E-REBATE



BUY A PEX PRESS/CRIMP TOOL



BUY



(2633-22)

GET A FREE GOODS PACKAGE VIA E-REBATE



48-22-4202, 48-22-7125,
48-22-7214, & 49-22-8202

GET FREE VIA E-REBATE



(48-21-2050)

BUY



(2632-22XC)

OR



(2432-22XC)

GET THESE FREE VIA E-REBATE



(2688-20)

(2470-20)

(48-11-1850)



Tools & Accessories Corp.

Toll Free: 1-800-796-4716

8975 Henkels Lane Suite 710 Annapolis Junction, MD 20701

Baltimore: 410-735-8800

Washington: 301-369-9191

Fax: 301-498-7628

Email: Sales@tatool.net

WWW.TATOOLSONLINE.COM



Nothing but **HEAVY DUTY.**

OFFERS VALID THROUGH APRIL 30, 2018 OR WHILE SUPPLIES LAST

DUST EXTRACTION SOLUTIONS

(CALL FOR SPECIAL PRICING)

M18 FUEL™ 1" SDS Plus Rotary Hammer w/ Dust Extractor Kit (2712-22DE)



M12™ Universal HAMMervac™ Kit (2306-22)



HAMMervac™ Dedicated Dust Extractor (2712-DE)

For use with 2712-20



8 Gallon Dust Extractor (8960-20)



NOW AVAILABLE!

SDS+ DUST TRAP™ DRILLING SHROUD

- Industries First OSHA Compliant solution without a Vacuum
- Universal Fit on ALL SDS Plus Hammers • Low cost Solution, under \$20 Retail

OBJECTIVE DATA WITHOUT A DUST EXTRACTOR

Maximum Number of Holes per Day

Hole Depth	Maximum Number of Holes per Day							
	3/16"	1/4"	3/8"	1/2"	5/8"	3/4"	7/8"	
1"	1,200	675	300	169	108	75	55	
1-1/2"	800	450	200	113	72	50	37	
2"	600	338	150	84	54	38	28	
2-1/2"	480	270	120	68	43	30	22	
3"	400	225	100	56	39	25	18	
3-1/2"	343	193	86	48	31	21	16	
4"	300	169	75	42	27	19	14	

OR

TABLE 1 WITH A DUST EXTRACTOR



8960-20 or equivalent dust extractors

49-90-1957 Hose Adapter

DUST TRAP™

NO LIMITATIONS ON MAXIMUM NUMBER OF HOLES PER DAY

The user must drill the same number or fewer holes than those listed above for the given application in order to be considered compliant with the objective data clause of 29 CFR 1926.1153 OSHA regulation on crystalline silica dust.

ITEM	DESCRIPTION
48-03-3035	SDS+ DUST TRAP DRILLING SHROUD
48-03-3135	SDS+ DUST TRAP DRILLING SHROUD - BULK 10
48-03-3235	SDS+ DUST TRAP SLEEVE - BULK 5