

OUTDOOR/INDOOR EXTENSION CORDS

American Insulated Wire stocks various types of outdoor/indoor extension cords to meet the most demanding needs and requirements. From standard cords, to GFCI adapters, to power block, to locking connection, American has the cord to get the perfect connection.

Our SJTW is an outdoor/indoor cord that is UL listed and cUL certified for all weather, -40°C at 300V. It is available in 16, 14, 12, and 10 AWG and 25', 50', and 100' lengths.

Tuf-Flex® is available in 300V (SJEOOW). It is UL listed for oil and water resistance plus all weather conditions. This extra flexible cord is rated for extreme temperatures, -50°C to +105°C. It is cUL certified as SJTOOW.

Our portable GFCI adapters reduce shock hazard due to ground faults and complies with UL requirements and the National Electric Code.

- Heavy duty SJTW/STW
- Portable GFCI adapters
- Heavy duty STW
- Tuf-Flex® SJEOOW/SJTOOW
- Locking Connection
- Pro-Grade
- Quick Check®
- Wild Wire™



OUTDOOR/INDOOR EXTENSION CORDS

New Part Number	Old AIW Part No.	Cord Size	Length	Cord Color	Rating	Standard Carton Qty. Lbs.
-----------------	------------------	-----------	--------	------------	--------	-----------------------------

TRU-RUBBER™ SJOOW - 300 VOLT

All weather rubber extension cords for industrial and contractor use. Provides extra flexibility and durability. -40°C to +90°C. Features Tru-Link™ locking connector. Locking rubber connector securely locks cords. NEMA 5-15. Limited lifetime warranty.



C3424025BL	35868	14/3	25'	BLACK	15A 125V 1875W	14 38
C3424050BL06D	35869	14/3	50'	BLACK	15A 125V 1875W	6 31
C3424100BL	35870	14/3	100'	BLACK	13A 125V 1875W	5 51
C3422025BL	35871	12/3	25'	BLACK	15A 125V 1875W	10 37
C3422050BL	35872	12/3	50'	BLACK	15A 125V 1875W	6 46
C3422100BL	35873	12/3	100'	BLACK	15A 125V 1875W	3 47
C3420050BL	35874	10/3	50'	BLACK	15A 125V 1875W	2 26
C3420100BL	35875	10/3	100'	BLACK	15A 125V 1875W	2 50

TRU-RUBBER™ SJOOW WITH LOCKING CONNECTION - NEMA L5-20

A9212050BL	35876	12/3	50'	BLACK	20A 125V 2500W	3 23
A9212100BL	35877	12/3	100'	BLACK	15A 125V 1875W	3 48

TRU-RUBBER™ SOOW 600 VOLT WITH LOCKING CONNECTION - NEMA L5-20

A9213050BL	35878	12/3	50'	BLACK	20A 125V 2500W	2 26
A9213100BL	35879	12/3	100'	BLACK	15A 125V 1875W	2 47



TUF-FLEX® SJEOOW/SJTOOW - 300 VOLT

All weather with oil and water resistant jacket and insulation. Quick Check® power indicator lighted end. Stays flexible in extreme cold or hot conditions. Light weight, -50°C to +105°C (-58°F to 221°F). NEMA 5-15.



C3316015BULTE	02432	16/3	15'	BLUE	13A 125V 1625W	15 16
C3316025BULTE	02433	16/3	25'	BLUE	13A 125V 1625W	12 20
C3316050BULTE	02434	16/3	50'	BLUE	13A 125V 1625W	12 38
C3316100BULTE	02435	16/3	100'	BLUE	10A 125V 1250W	6 38
C3314025BULTE	02443	14/3	25'	BLUE	15A 125V 1875W	14 32
C3314050BULTE	02444	14/3	50'	BLUE	15A 125V 1875W	10 43
C3314100BULTE	02445	14/3	100'	BLUE	13A 125V 1625W	5 44
C3312025BULTE	--	12/3	25'	BLUE	15A 125V 1875W	10 35
C3312050BULTE	02454	12/3	50'	BLUE	15A 125V 1875W	8 53
C3312100BULTE	02455	12/3	100'	BLUE	15A 125V 1875W	3 40
C3310050BULTE	--	10/3	50'	BLUE	15A 125V 1875W	1 11
C3310100BULTE	--	10/3	100'	BLUE	15A 125V 1875W	1 23



TUF-FLEX® SJEOOW/SJTOOW, 3-OUTLET POWER BLOCK 300 VOLT

All weather with oil and water resistant jacket and insulation. Quick Check® power indicator lighted end. Stays flexible in extreme cold or hot conditions. Light weight, -50°C to +105°C (-58°F to 221°F). NEMA 5-15.



C3512100BULTE	02478	12/3	100'	BLUE	15A 125V 1875W	3 40
---------------	-------	------	------	------	----------------	--------



OUTDOOR/INDOOR EXTENSION CORDS

New Part Number	Old AIW Part No.	Cord Size	Length	Cord Color	Rating	Standard Carton Qty. Lbs.	
-----------------	------------------	-----------	--------	------------	--------	-----------------------------	--

PRO-GRADE CONTRACTOR CORDS - SJTW (-50°C, -58°F) 300V

For contractor and industrial users, water and weather resistant yellow jacket, Quick Check® light indicator, limited lifetime warranty. NEMA 5-15.



C3444025YP	34385	14/3	25'	YELLOW	15A 125V 1875W	14	38
C3444050YP	34384	14/3	50'	YELLOW	15A 125V 1875W	10	52
C3444100YP	34383	14/3	100'	YELLOW	13A 125V 1625W	5	49
C3442025YP	34382	12/3	25'	YELLOW	15A 125V 1875W	10	36
C3442050YP	34381	12/3	50'	YELLOW	15A 125V 1875W	6	43
C3442100YP	34380	12/3	100'	YELLOW	15A 125V 1875W	3	44
C3440050YP	34379	10/3	50'	YELLOW	15A 125V 1875W	2	26
C3440100YP	34378	10/3	100'	YELLOW	15A 125V 1875W	2	49

PRO-GRADE POWER BLOCK - SJTW (-50°C, -58°F) 300V, NEMA 5-15

A8442050YP	35996	12/3	50'	YELLOW	15A 125V 1875W	4	32
A8442100YP	35997	12/3	100'	YELLOW	15A 125V 1875W	3	45

PRO-GRADE COMPACT FLUORESCENT WORKLIGHT - SJT

For contractor and industrial users, transformer and outlet in the handle, super durable construction, vertical and horizontal mounting hooks, limited lifetime warranty. NEMA 5-15. 13 Amp bulb only.



C2816006YP	34376	16/3	6'	YELLOW	13A 125V 1625W	12	26
------------	-------	------	----	--------	----------------	----	----

WILD WIRE™ - SJTW 300V, UL/OSHA

High visibility all weather cords available in wild and crazy colors. Contractor quality. Plugs and connectors are same color as stripe. NEMA 5-15.



C4312050GK	36000	12/3	50'	FL. GRN W/BLK STRIPE	15A 125V 1875W	6	41
C4312100GK	36001	12/3	100'	FL. GRN W/BLK STRIPE	15A 125V 1875W	3	43
C4312050HP*	36002	12/3	50'	HOT PINKW/GRN STRIPE	15A 125V 1875W	6	41
C4312100HP*	36003	12/3	100'	HOT PINKW/GRN STRIPE	15A 125V 1875W	3	43
C4312050PD	36004	12/3	50'	PURPLE W/GOLD STRIPE	15A 125V 1875W	6	41
C4312100PD	36005	12/3	100'	PURPLE W/GOLD STRIPE	15A 125V 1875W	3	43
C4312050RK	36006	12/3	50'	RED W/BLK STRIPE	15A 125V 1875W	6	41
C4312100RK	36007	12/3	100'	RED W/BLK STRIPE	15A 125V 1875W	3	43
C4312050RR	36008	12/3	50'	GRAY W/RED STRIPE	15A 125V 1875W	6	41
C4312100RR	36009	12/3	100'	GRAY W/RED STRIPE	15A 125V 1875W	3	43
C4312050YA	36010	12/3	50'	YELLOW W/BLUE STRIPE	15A 125V 1875W	6	41
C4312100YA	36011	12/3	100'	YELLOW W/BLUE STRIPE	15A 125V 1875W	3	43
C4312050WA	36012	12/3	50'	BLUE W/WHITE STRIPE	15A 125V 1875W	6	41
C4312100WA	36013	12/3	100'	BLUE W/WHITE STRIPE	15A 125V 1875W	3	43
C4312050YB	36070	12/3	50'	YELLOW W/BLK STRIPE	15A 125V 1875W	6	41
C4312100YB	36071	12/3	100'	YELLOW W/BLK STRIPE	15A 125V 1875W	3	43

*Plug and connectors are black

OUTDOOR/INDOOR EXTENSION CORDS

New Part Number	Old AIW Part No.	Cord Size	Length	Cord Color	Rating	Standard Carton Qty. Lbs.	
-----------------	------------------	-----------	--------	------------	--------	-----------------------------	--

EXTREME WILD WIRE™ - SJTW 300V, UL/OSHA

High visibility all weather cords available in wild and crazy neon colors. Contractor quality. NEMA 5-15.



C4312050XB	--	12/3	50'	EXTREME BLUE	15A 125V 1875W	6	45
C4312100XB	--	12/3	100'	EXTREME BLUE	15A 125V 1875W	3	46
C4312050XN	--	12/3	50'	EXTREME GREEN	15A 125V 1875W	6	45
C4312100XN	--	12/3	100'	EXTREME GREEN	15A 125V 1875W	3	46
C4312050XO	--	12/3	50'	EXTREME ORANGE	15A 125V 1875W	6	45
C4312100XO	--	12/3	100'	EXTREME ORANGE	15A 125V 1875W	3	46
C4312050XP	--	12/3	50'	EXTREME PINK	15A 125V 1875W	6	45
C4312100XP	--	12/3	100'	EXTREME PINK	15A 125V 1875W	3	46
C4312050XY	--	12/3	50'	EXTREME YELLOW	15A 125V 1875W	6	45
C4312100XY	--	12/3	100'	EXTREME YELLOW	15A 125V 1875W	3	46

COLD WEATHER EXTENSION CORD - SJTW

With Quick Check® power indicator light, -40°C. NEMA 5-15.



C4422050CB	--	12/3	50'	BLUE	15A 125V 1875W	6	43
C4422100CB	--	12/3	100'	BLUE	15A 125V 1875W	3	43

SJTW — 300 VOLT

All weather, extra flexible, -40°C. Applications include construction, industrial, and maintenance. NEMA 5-15.



C2316025OR	02271	16/3	25'	ORANGE	13A 125V 1625W	24	47
C2316050OR	02273	16/3	50'	ORANGE	13A 125V 1625W	12	46
C2316100OR	02275	16/3	100'	ORANGE	10A 125V 1250W	6	43
C4314025BO	02281	14/3	25'	ORG/BLK STRIPE	15A 125V 1875W	14	31
C4314050BO	02283	14/3	50'	ORG/BLK STRIPE	15A 125V 1875W	10	50
C4314100BO	02285	14/3	100'	ORG/BLK STRIPE	13A 125V 1625W	5	41
C4312025YW	02292	12/3	25'	YELLOW	15A 125V 1875W	10	40
C4312050YW	02293	12/3	50'	YELLOW	15A 125V 1875W	6	44
C4312100YW	02294	12/3	100'	YELLOW	15A 125V 1875W	3	42
C4310050YB	32490	10/3	50'	YEL/BLK STRIPE	15A 125V 1875W	1	12
C4310100YB	32491	10/3	100'	YEL/BLK STRIPE	15A 125V 1875W	1	24

SJTW — 300 VOLT

Green jacketing blends in with grass, shrubs and trees to hide the cord, NEMA 5-15.



C2316025GN	32363	16/3	25'	GREEN	13A 125V 1625W	24	47
C2316050GN	32362	16/3	50'	GREEN	13A 125V 1625W	12	44

OUTDOOR/INDOOR EXTENSION CORDS

New Part Number	Old AIW Part No.	Cord Size	Length	Cord Color	Rating	Standard Carton Qty. Lbs.	
-----------------	------------------	-----------	--------	------------	--------	-----------------------------	--

SJTW, 3 OUTLET POWER BLOCK - 300 VOLT

Extra flexible, all weather, -40°C. Provides additional outlets from one source. NEMA 5-15.



C4514025BO	02311	14/3	25'	ORG/BLK STRIPE	15A 125V 1875W	14	39
C4514050BO	02312	14/3	50'	ORG/BLK STRIPE	15A 125V 1875W	10	50
C4514100BO	02313	14/3	100'	ORG/BLK STRIPE	13A 125V 1625W	5	46
C4512025YW	02321	12/3	25'	YELLOW	15A 125V 1875W	10	39
C4512050YW	02322	12/3	50'	YELLOW	15A 125V 1875W	6	46
C4512100YW	02323	12/3	100'	YELLOW	15A 125V 1875W	3	43
C4510050YB	--	10/3	50'	YEL/BLK STRIPE	15A 125V 1875W	1	13
C4510100YB	--	10/3	100'	YEL/BLK STRIPE	15A 125V 1875W	1	25

SJTW, 300 VOLT LOCKING CONNECTION

Extra heavy capacity, all weather industrial outdoor/indoor. NEMA L5-20.



A9318050YW	36030	12/3	50'	YELLOW	20A 125V 2500W	6	44
A9318100YW	36031	12/3	100'	YELLOW	15A 125V 1875W	3	44

SJTW, 4-OUTLET JUNCTION BOX - 300 VOLT

Rugged ABS housing. Converts single outlet to four grounded outlets. NEMA 5-15.

C1489050OR*	02366	12/3	50'	ORANGE	15A 125V 1875W	5	39
C1489100OR*	02367	12/3	100'	ORANGE	15A 125V 1875W	3	45

*Not UL listed, but made to acceptable industry standards.



STW, HEAVY DUTY RHINO-HIDE® - 600 VOLT

Extra flexible, abrasion resistant, -40°C. Construction and industrial job site cords. NEMA 5-15.



A7312050YW	02378	12/3	50'	YELLOW	15A 125V 1875W	2	22
A7312100YW	02379	12/3	100'	YELLOW	15A 125V 1875W	1	21

STW, HEAVY DUTY 3-OUTLET POWER BLOCK RHINO-HIDE® 600 VOLT

Extra flexible, all weather, -40°C. Plugs three into one outlet. NEMA 5-15.



A8312025YW	02394	12/3	25'	YELLOW	15A 125V 1875W	4	24
A8312050YW	02395	12/3	50'	YELLOW	15A 125V 1875W	2	22
A8312100YW	02396	12/3	100'	YELLOW	15A 125V 1875W	1	21

OUTDOOR/INDOOR EXTENSION CORDS

New Part Number	Old AIW Part No.	Cord Size	Length	Cord Color	Rating	Standard Carton Qty. Lbs.	
-----------------	------------------	-----------	--------	------------	--------	-----------------------------	--

STW, HEAVY DUTY LOCKING CONNECTION *RHINO-HIDE®* - 600 VOLT

Extra flexible, all weather, -40°C. NEMA L5-20.



A9315050YW	02382	12/3	50'	YELLOW	20A 125V 2500W	2	22
A9315100YW	02383	12/3	100'	YELLOW	15A 125V 1875W	1	22
A9310100YB	02385	10/3	100'	YEL/BLK STRIPE	20A 125V 2500W	1	27

STW, HEAVY DUTY LOCKING CONNECTION - 600 VOLT

With extra female connector near male plug end, -40°C. NEMA L5-20.



A1551100YW	02388	12/3	100'	YELLOW	15A 125V 1875W	1	23
------------	-------	------	------	--------	----------------	---	----