

# GE Modular Metering – Connecticut Market

### Main Breaker Module

Main Ampere Rating	Single-Phase, 3 Wire 120/240 Vac		Three-Phase, 4 Wire Single-Phase, 3 Wire 120/240 Vac, 208Y/120 Vac	
	Catalog No.	Breaker Frame	Catalog No.	Breaker Frame
		Catalog No.		Catalog No.
400	TMPSB4R	SGH 400	TMP3SB4R	SGH 400
	TMPSHB4R	SGL 400	TMP3SHB4R	SGL 400
600	TMPSB6R	SGH 600	TMP3SB6R	SGH 600
	TMPSHB6R	SGL 600	TMP3SHB6R	SGL 600
800	TMPSB8R	SKH 800	TMP3SB8R	SKH 800
1000	TMPSB10R	SKH 1000	TMP3SB10R	SKH 1000
1200	TMPSB12R	SKH 1200	TMP3SB12R	SKH 1200
1400	TMPBB14R	RGH	TMP3BB14R	RGH
	TMPBT14R		TMP3BT14R	
1600	TMPBB16R	RGH	TMP3BB16R	RGH
	TMPBB16RST		TMP3BB16RCLL	
	TMPBT16R		TMP3BB16RST	
	TMPBT16RST		TMP3BT16R	
	—	—	TMP3BT16RST	
2000	TMPBT20R	RGH	TMP3BT20R	RGH
	TMPBB20R		TMP3BB20R	
		—	TMP3BB20RCLL	
		—	TMP3BT20RST	
			TMP3BB20RST	

### Main Lug, Single-Phase, 3 Wire 120/240 Vac

Main Ampere Rating	Catalog No.	Wire Entry	Stud Sets per Phase and Neutral
400	Use Three-Phase	Top / Bottom	—
600			—
800	TMPL8R		2
1200	TMPL12R		3
1600	TMPL16R		3

### Main Lug, Three-Phase, 4 Wire / Single-Phase, 3 Wire 120/240 Vac, 208Y/120 Vac

Main Ampere Rating	Catalog No.	Wire Entry	Stud Sets per Phase and Neutral
400	TMP3L4R	Top / Bottom	1
	TMP3L4RCU		
600	TMP3L6R		1
	TMP3L6RCU		
800	TMP3L8R		2
	TMP3L8RCU		
1200	TMP3L12R	2	
1600	TMP3L16R	3	

### Meter Stack Modules, Single-Phase, Ringless Type, Socket with Lever Bypass

Socket Amps	No. of Sockets	Catalog No.
225	1	TMPR12122R
	2	TMPR12222R
	3	TMPR12322R
	4	TMPR12422R
400	1	TMPR12140RB
	2	TMPR12240RB
	1	TMPK12140RB
	1	TMPK12140RBA

### Commercial Meter Stack Modules, Three-Phase, Ringless Type, Socket with Lever Bypass

Socket Amps	No. of Sockets	Catalog No.
225	1	TMPR312122R
	2	TMPR312222R
	3	TMPR312322R
	4	TMPR312422R
400	1	TMPR312140TR
	1	TMPR312140RB
	2	TMPR312240RB
	1	TMPK312140RB
	1	TMPK312140RBA

### Main Fusible Switch, Single-Phase, 3 Wire 120/240 Vac

Main Ampere Rating	Catalog No.	Fuse Type	Wire Entry	Stud Sets per Phase and Neutral
400	TMPFT4R	T Fuse	Top	1
600	TMPFT6R			
800	TMPFT8R			
1200	TMPFT12R	T or L Fuse		—
400	TMPFB4R	T Fuse	Bottom	1
600	TMPFB6R			
800	TMPFB8R	T or L Fuse		
1200	TMPFB12RT	T Fuse	Bottom	—
	TMPFB12R	T or L Fuse		

### Main Fusible Switch, Three-Phase, 4 Wire / Single-Phase, 3 Wire 120/240 Vac, 208Y/120 Vac

Main Ampere Rating	Catalog No.	Fuse Type	Wire Entry	Stud Sets per Phase and Neutral
400	TMP3FT4R	T Fuse	Top	1
600	TMP3FT6R			
800	TMP3FT8R			
1200	TMP3FT12R	T or L Fuse		—
1600	TMP3FT16R	L Fuse		—
2000	TMP3FT20R			
400	TMP3FB4R	T Fuse		1
600	TMP3FB6R			
800	TMP3FB8R	T or L Fuse		
1200	TMP3FB12RT	T Fuse	Bottom	—
1200	TMP3FB12R	T or L Fuse		
1600	TMP3FB16R	L Fuse		
2000	TMP3FB20R			
1200	TMP3FB12RST	T or L Fuse		
1600	TMP3FB16RST	L Fuse		
2000	TMP3FB20RST			

### Commercial Meter Modules, 1200A Horizontal Bussing

Socket Amps	AIC	Ampere Rating	Tenant Main Breakers for 1PH	Tenant Main Breakers for 3PH		
			Catalog No.	Catalog No.		
225	10,000	15	TEB122015	TEB132015		
		20	TEB122020	TEB132020		
		25	TEB122025	TEB132025		
		30	TEB122030	TEB132030		
		35	TEB122035	TEB132035		
		40	TEB122040	TEB132040		
		45	TEB122045	TEB132045		
		50	TEB122050	TEB132050		
		60	TEB122060	TEB132060		
		70	TEB122070	TEB132070		
		80	TEB122080	TEB132080		
		90	TEB122090	TEB132090		
		100	TQD22100	TEB132100		
		125	TQD22125	TQD32125		
		150	TQD22150	TQD32150		
		175	TQD22175	TQD32175		
		200	TQD22200	TQD32200		
		225	Use TMQD	Use TMQD		
		225	22,000	100	THQD22100	THQD32100
				125	THQD22125	THQD32125
				150	THQD22150	THQD32150
				175	THQD22175	THQD32175
200	THQD22200			THQD32200		
225	Use TMQD			Use TMQD		
70	TMQD22070			TMQD32070		
80	TMQD22080			TMQD32080		
90	TMQD22090			TMQD32090		
100	TMQD22100			TMQD32100		
100,000	100,000	125	TMQD22125	TMQD32125		
		150	TMQD22150	TMQD32150		
		175	TMQD22175	TMQD32175		
		200	TMQD22200	TMQD32200		
		225	TMQD22225	TMQD32225		

### Accessories

Description	Catalog No.
Barrel Lock Bracket and Guard Kit	TMBL
Bypass Kit Totalizing Jumper Type	TMBPT320
Individual Meter Socket Barrier Kit (includes 6) <b>Required in CT</b>	TMBR3
Blank Meter Socket Cover	TMCB322A
Elbow, 16-inch x 16-inch, 4 cross bus rated 1200A	TMPE12
Elbow, 12-inch x 12-inch, 4 cross bus rated 1200A	TMPE12A
Spacer, 4-inch, 4 cross bus rated 1200A	TMPS12
TEB Breaker Mounting Kit	TMTEB
Mounting Z-Rail, 4-foot	TMZR