

# Rittal – The System.

Faster – better – everywhere.

## ▶ WM Wallmount Enclosures



Rittal WM enclosures set the standard for maximum use of space and ease of installation. WM compact enclosures can be used for virtually any application. NEMA protection ratings are ensured through a secure locking system, foamed-in-place gasket and knife-edge perimeter. Features include a body constructed of cold rolled steel, steel doors and zinc-plated mounting panels. WM enclosures are readily available in all of the most popular sizes, protection categories and configurations – including universal disconnect cutout.

For complete details on the entire line, go to [www.rittal.us](http://www.rittal.us).

- One-piece welded cold-rolled steel body
- Available in carbon and stainless steel
- Zinc-plated mounting panel standard
- Available with universal disconnect cutout
- Foamed-in-place gasket
- Quick-release hidden 130° door hinges
- Electrophoresis dip-coat primer with powder-coat surface
- Flange-trough collar opening channels liquids and dust away from enclosure gasket and enclosure interior
- Left-hand hinged door (the single door configuration is reversible)

- Wall-mounting holes
- Single door enclosures less than 20" in height have one ¼ turn latch with screwdriver insert
- Single door enclosures 20 - 40" in height have two ¼-turn latches with screwdriver inserts
- Single door enclosures greater than or equal to 42" in height have a 3-point latching L-handle
- Double door and disconnect enclosures have a 2- or 3-point latching L-handle

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



**Note:** measurements are approximate.

**Carbon Steel, Single Door – UL/cUL Type 12, 3R, 4**

Part No.	H x W x D
WM121206NC	12x12x6
WM161206NC	16x12x6
WM161606NC	16x16x6
WM162006NC	16x20x6
WM201606NC	20x16x6
WM202006NC	20x20x6
WM241606NC	24x16x6
WM242006NC	24x20x6
WM242406NC	24x24x6
WM302406NC	30x24x6
WM161208NC	16x12x8
WM161608NC	16x16x8
WM162008NC	16x20x8
WM201608NC	20x16x8
WM202008NC	20x20x8
WM202408NC	20x24x8
WM241608NC	24x16x8
WM242008NC	24x20x8
WM242408NC	24x24x8
WM243008NC	24x30x8
WM302008NC	30x20x8
WM302408NC	30x24x8
WM303008NC	30x30x8
WM362408NC	36x24x8
WM423608NC	42x36x8
WM483608NC	48x36x8
WM202010NC	20x20x10
WM242010NC	24x20x10

**Carbon Steel, Double Door – UL/cUL Type 12**

Part No.	H x W x D
WM244208NC	24x42x8
WM304210NC	30x42x10
WM304810NC	30x48x10
WM364212NC	36x42x12

**Carbon Steel Disconnect – UL/cUL Type 12, 3R, 4**

Part No.	H x W x D
WM202208XC	20x22x8
WM242208XC	24x22x8
WM242608XC	24x26x8
WM302608XC	30x26x8
WM363208XC	36x32x8
WM363210XC	36x32x10
WM603810XC	60x38x10
WM302612XC	30x26x12

**Carbon Steel, Single Door – UL/cUL Type 12, 3R, 4**

Part No.	H x W x D
WM363008NC	36x30x8
WM363608NC	36x36x8
WM423008NC	42x30x8
WM242410NC	24x24x10
WM302410NC	30x24x10
WM303010NC	30x30x10
WM362410NC	36x24x10
WM363010NC	36x30x10
WM423610NC	42x36x10
WM483610NC	48x36x10
WM603610NC	60x36x10
WM202012NC	20x20x12
WM242012NC	24x20x12
WM242412NC	24x24x12
WM302412NC	30x24x12
WM303012NC	30x30x12
WM362412NC	36x24x12
WM363012NC	36x30x12
WM363612NC	36x36x12
WM423612NC	42x36x12
WM483612NC	48x36x12
WM603612NC	60x36x12
WM363016NC	36x30x16
WM483616NC	48x36x16
WM603616NC	60x36x16
WM302420NC	30x24x20
WM483620NC	48x36x20

**Carbon Steel, Double Door – UL/cUL Type 12**

Part No.	H x W x D
WM364812NC	36x48x12
WM366012NC	36x60x12
WM426012NC	42x60x12
WM484812NC	48x48x12

**Carbon Steel Disconnect – UL/cUL Type 12, 3R, 4**

Part No.	H x W x D
WM363212XC	36x32x12
WM423212XC	42x32x12
WM423812XC	42x38x12
WM483812XC	48x38x12
WM603812XC	60x38x12
WM483816XC	48x38x16
WM603816XC	60x38x16

**Rittal Corporation**

Woodfield Corporate Center  
 425 North Martingale Road, Suite 400 • Schaumburg, Illinois 60173 • USA  
 Phone: 937-399-0500 • Toll-free: 800-477-4000  
 Email: rittal@rittal.us • Online: www.rittal.us