

Video Accessories | RG6 Coax Cables, Splitters & Termination Cap

RG6 Coax Cable, gold plated

Description	Part No.
RG6 Coax Cable, gold plated	C6851-xx*

xx = Length: 3' (G3), 6' (G6), 12' (1G), 25' (2G), 50' (5G) or 100' (GC).

* = Colors: Choose from any of the colors below.

RG6 Coax Cable, nickel

Description	Part No.
RG6 Coax Cable, nickel	C6851-xx*

xx = Length: 3' (03), 6' (06), 12' (12), 25' (25), 50' (50) or 100' (0C).

* = Colors: Choose from any of the colors below.

Two-Way Splitter | One 75 Ohm input to two 75 Ohm outputs

Description	Part No.
Two-Way Splitter, carded unit pack	C5002-000
Two-Way Splitter, gold plated, carded unit pack	C5002-0G0
Two-Way Splitter, gold plated, individual polybag pack	40987-002

Three-Way Splitter | One 75 Ohm input to three 75 Ohm outputs

Description	Part No.
Three-Way Splitter, carded unit pack	C5003-000
Three-Way Splitter, gold plated, individual polybag pack	40987-003

Four-Way Splitter | One 75 Ohm input to four 75 Ohm outputs

Description	Part No.
Four-Way Splitter, carded unit pack	C5004-000
Four-Way Splitter, gold plated, carded unit pack	C5004-0G0
Four-Way Splitter, gold plated, individual polybag pack	40987-004

75 Ohm Termination Cap for F-connector jacks

Description	Part No.
75 Ohm Termination Cap, 25 per polybag pack	40984-000



White (W)



Black (E)



C6851-G3W



C6851-03E



C5002-0G0



40987-003



C5004-000



40984-000