

## Aluminum Service Poles

- Poles with three service capability ideal for delivering power, fiber, and data cabling from the ceiling to the floor
- Available in three standard lengths to accommodate a variety of applications
- Available in five attractive durable paint colors and clear anodized aluminum finish to suit every need
- Factory ordered custom pole lengths and configurations available for special applications

Hubbell offers a line of attractive and durable Aluminum Service Poles which distribute power and telecommunications wiring from above the ceiling to workstations below.

They are offered in lengths of 10' 2", 12' 2", and 15' 2" with a variety of electrical wiring devices.

Poles with three service capability have a divider to separate power and low voltage wiring.

These customizable power poles effectively distribute power, fiber, and data cabling from the ceiling to the floor. Available in varying lengths and colors, custom options maximize space and allow workstations, retail checkout areas, collaboration areas, digital signage, vending machines, appliances, and kiosks to be pulled away from the wall.



### FEATURES

- Available in gray, ivory, black, white and office white painted and clear anodized aluminum finishes
- Style Line® decorator duplex receptacles and two Style Line® knockouts for communications
- Includes ceiling trim mounting plate and bottom scuff boot

### SPECIFICATIONS

- UL listed
- Suitable for retail checkout areas application



# Aluminum Service Poles



## ORDERING INFORMATION

Three Service Aluminum Service Poles		Height Feet (m)		
Description	Color	10' 2" (3.10m)	12' 2" (3.71m)	15' 2" (4.62m)
(2) 20A 125V Style Line® duplex receptacles; one circuit	Black	<b>HBLPP10BK</b>	<b>HBLPP12BK</b>	<b>HBLPP15BK</b>
	Gray	<b>HBLPP10A</b>	<b>HBLPP12A</b>	<b>HBLPP15A</b>
	Ivory	<b>HBLPP10AI</b>	<b>HBLPP12AI</b>	<b>HBLPP15AI</b>
	Office White	<b>HBLPP10OW</b>	<b>HBLPP12OW</b>	<b>HBLPP15OW</b>
	White	<b>HBLPP10W</b>	<b>HBLPP12W</b>	<b>HBLPP15W</b>
	Clear Anodized Aluminum	<b>HBLPP10AAL</b>	<b>HBLPP12AAL</b>	<b>HBLPP15AAL</b>
(1) Orange isolated ground 20A 125V Style Line® duplex receptacle; (1) 20A 125V Style Line® duplex receptacle; two circuits	Black	<b>HBLPP10IGBK</b>	—	—
	Gray	<b>HBLPP10IGA</b>	—	—
	Ivory	<b>HBLPP10IGAI</b>	—	—
	Office White	<b>HBLPP10IGOW</b>	—	—
	White	<b>HBLPP10IGW</b>	—	—
	Clear Anodized Aluminum	<b>HBLPP10IGAL</b>	—	—
(2) Orange isolated ground 20A 125V Style Line® duplex receptacles; (1) isolated ground surge suppression 20A 125V duplex receptacle; one circuit	Black	<b>HBLPP10SBK</b>	—	—
	Gray	<b>HBLPP10SA</b>	—	—
	Ivory	<b>HBLPP10SAI</b>	—	—
	Office White	<b>HBLPP10SOW</b>	—	—
	White	<b>HBLPP10SW</b>	—	—
	Clear Anodized Aluminum	<b>HBLPP10SAL</b>	—	—
(1) 20A 125V GFCI Self Test duplex receptacle with (2) ground fault protected 20A 125V Style Line® duplex receptacles; one circuit.	Black	<b>HBLPP10GFBK</b>	<b>HBLPP12GFBK</b>	<b>HBLPP15GFBK</b>
	Gray	<b>HBLPP10GF</b>	<b>HBLPP12GF</b>	<b>HBLPP15GF</b>
	Ivory	<b>HBLPP10GFI</b>	<b>HBLPP12GFI</b>	<b>HBLPP15GFI</b>
	Office White	<b>HBLPP10GFW</b>	<b>HBLPP12GFW</b>	<b>HBLPP15GFW</b>
	White	<b>HBLPP10GFW</b>	<b>HBLPP12GFW</b>	<b>HBLPP15GFW</b>
	Clear Anodized Aluminum	<b>HBLPP10GFAL</b>	<b>HBLPP12GFAL</b>	<b>HBLPP15GFAL</b>
Blank pole; divider; (4) Style Line® device knockouts	Black	<b>HBLPPOBK</b>	<b>HBLPPO12BK</b>	<b>HBLPPO15BK</b>
	Gray	<b>HBLPPOA</b>	<b>HBLPPO12A</b>	<b>HBLPPO15A</b>
	Ivory	<b>HBLPPOAI</b>	<b>HBLPPO12AI</b>	<b>HBLPPO15AI</b>
	Office White	<b>HBLPPOOW</b>	<b>HBLPPO12OW</b>	<b>HBLPPO15OW</b>
	White	<b>HBLPPOW</b>	<b>HBLPPO12W</b>	<b>HBLPPO15W</b>
	Clear Anodized Aluminum	<b>HBLPPOAAL</b>	<b>HBLPPO12AAL</b>	<b>HBLPPO15AAL</b>

See catalog section for custom pole configurations.

## Accessories

Description	
Adjustable T-bar assembly for mounting poles in the middle of ceiling tile.	<b>ATB*</b>
Replacement service pole trim kit (office white).	<b>PPTRIM1*</b>

Note: \*Not UL listed.



## DIMENSIONS Inches (mm)

