


SPATIAL

Spatial showcases a modern form that complements Urban Industrial, Mid-Century Modern and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.


ALSO AVAILABLE IN
Bath & Vanity



P500083-031
shown with P7826-01
vintage lamp



P500082-031
shown with P7827-01
vintage lamp



P500083-031
shown with P7826-01
vintage lamp



P500084-031
shown with P7826-01
vintage lamp



P400077-031



P500096-031



P400084-031

FINISHES

● Black - 31

SEMI-FLUSH CONVERTIBLE

P400077-031 Black
Hanging and ceiling mount hardware included.
19-5/8" dia., 14" ht.
Overall ht. w/chain 52", wire 10'.
Three candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER

P400084-031 Black
26" dia., 32" ht.
Overall ht. w/chain 101", wire 15'.
Six medium base lamps, each 60w max.

MINI-PENDANT

P500082-031 Black
12" dia., 11-1/4" ht.
Overall ht. w/chain 85", wire 10'.
One medium base lamp, 100w max.

FOUR-LIGHT PENDANT

P500083-031 Black
23-1/2" dia., 19" ht.
Overall ht. w/chain 93-1/2", wire 15'.
Four candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT

P500084-031 Black
28" dia., 26" ht.
Overall ht. w/chain 101", wire 15'.
Six candelabra base lamps, each 60w max.


THREE-LIGHT FOYER

P500096-031 Black
23-3/4" dia., 25-1/2" ht.
Overall ht. w/chain 100-1/2", wire 15'.
Three candelabra base lamps, each 60w max.

SPATIAL

Spatial showcases a modern form that complements Urban Industrial, Mid-Century and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. A Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.

ALSO AVAILABLE IN
Fixture Collections



P300112-031



P300113-031



P300114-031



P300115-031

FINISH

● Black - 031

ONE-LIGHT BATH

P300112-031 Black
5-3/8" W., 6-1/2" ht.
Extends 8". H/CTR 3-3/8".
One G16.5 candelabra base lamp,
60w max.

TWO-LIGHT BATH

P300113-031 Black
14-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Two G16.5 candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P300114-031 Black
22" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Three G16.5 candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P300115-031 Black
31-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Four G16.5 candelabra base lamps,
each 60w max.

Mounts up or down.

P300113-031