



# FLEXCOR® WIRE MESH GRIPS

## Strain Relief Grips



**Wide Range, Straight Male, Dust Tight**



**Turnlok/EHU Strain Relief Grips**

### Description

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and power centers. Includes insulated bushing.

CATALOG NUMBER	NPT SIZE	CABLE DIAMETER RANGE
<b>WIDE RANGE, STRAIGHT MALE, DUST TIGHT GRIPS</b>		
<b>BOX22</b>	1/2"	0.220"-0.320"
<b>BOX30</b>	1/2"	0.300"-0.430"
<b>BOX40</b>	1/2"	0.400"-0.540"
<b>BOX52</b>	3/4"	0.520"-0.730"
<b>BOX70</b>	1"	0.700"-1.000"
<b>BOX94</b>	1-1/4"	0.940"-1.250"
<b>BOX120</b>	1-1/2"	1.200"-1.500"
<b>BOX140</b>	2"	1.400"-1.750"

### Description

Wire mesh grips for Turnlok and EHU straight blade plugs and connectors provide additional strain-relief for wiring device plugs and connectors used on portable equipment in commercial and institutional applications, and industrial plant and construction site areas, which incur abnormally high abuse.

CATALOG NUMBER	CABLE DIAMETER RANGE	MESH LENGTH
<b>TURNLOK®/EHU STRAIN RELIEF GRIPS</b>		
<b>FC22GL</b>	0.220"-0.320"	4.00"
<b>FC30GL</b>	0.300"-0.430"	5.00"
<b>FC40GL</b>	0.400"-0.560"	5.00"
<b>FC52GL</b>	0.520"-0.730"	9.00"
<b>FC70GL</b>	0.700"-0.940"	7.50"
<b>FC94GL</b>	0.940"-1.250"	11.50"