

FIXTURE HANGING ACCESSORIES

HEX ROD COUPLINGS

STEEL ZINC • 18-8 STAINLESS • 316 STAINLESS • GALVANIZED



PART#	UPC#	ROD SIZE	HEX SIZE	LENGTH	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER PER
STEEL ZINC							
RCT25	21700	10-24	1/4	3/4	1.44	100	56.78/c
RCT26	21705	1/4 -20	3/8	7/8	1.02	50	41.46/c
RCTL26 (1 3/4 LONG)	23326	1/4 -20	3/8	1 3/4	3.06	50	124.88/c
RCT27	21710	5/16 -18	3/8	7/8	1.21	50	50.62/c
RCT28	21715	3/8 -16	1/2	1	1.87	50	56.63/c
RCTL28 (1 3/4 LONG)	23328	3/8 -16	1/2	1 3/4	5.71	50	96.93/c
RCT35	21701	3/8 -16	1/2	1 3/4	11.98	100	67.14/c
RCT29	21720	1/2 -13	5/8	1 1/4	1.46	25	70.52/c
RCTL29 (1 3/4 LONG)	23329	1/2 -13	5/8	1 3/4	2.95	25	308.85/c
RCT30	21725	5/8 -11	3/4	1 1/2	2.24	25	216.14/c
RCT31	21728	3/4 -10	7/8	1 1/4	7.19	25	591.20/c
RCT33	21730	7/8 -9	1 1/4	2 1/2	29.95	100	917.73/c
18-8 STAINLESS							
RCT26SS	10644	1/4 -20	3/8	7/8	1.02	50	610.54/c
RCT27SS	10645	5/16 -18	3/8	7/8	1.40	50	749.06/c
RCT28SS	21726	3/8 -16	1/2	1	1.87	50	980.44/c
RCT29SS	21727	1/2 -13	5/8	1 1/4	1.52	25	1210.77/c
RCT30SS	22830	5/8 -11	3/4	1 1/2	9.68	50	2433.99/c
316 STAINLESS							
RCT28SS316	94828	3/8 -16	1/2	1	1.89	50	1384.00/c
RCT29SS316	94829	1/2 -13	5/8	1 1/4	2.85	50	1908.95/c
RCT30SS316	94830	5/8 -11	3/4	1 1/2	4.48	50	1512.55/c
GALVANIZED							
RCT28G	21716	1/2 -13	5/8	1 3/4	3.15	50	201.60/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.




REDUCING HEX ROD COUPLING

STEEL ZINC

PART#	UPC#	SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
RCTR28	21706	3/8 -16 x 1/4 -20	2.02	50	90.94/c
RCTR27	21704	3/8 -16 x 5/16 -18	2.35	50	102.68/c
RCTR5812	21708	5/8 -11 x 1/2-13	2.62	25	470.40/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

Experience the Metallics difference!



**Metallics and
Avanti Screw, Inc.
Where Manufacturing
Quality is Job One!**



FIXTURE HANGING ACCESSORIES

THREADED ROD

STEEL ZINC • 304 STAINLESS • 316 STAINLESS • GALVANIZED

Threaded rod sold only in full bundle quantities where listed.



PART#	UPC#	SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	TUBE QTY.	SUGGESTED TRADE LIST PRICE PER
STEEL ZINC						
TRS4/6	90357	8-32 x 6'	.32	1	–	1.98 per foot
TRS6/3	21613	1/4 -20 x 3'	.37	1	–	.92 per foot
TRS6/113	21641	1/4 -20 x 4'	.49	1	–	1.97 per foot
TRS6/6B	21640	1/4 -20 x 6'	36.50	50	300 feet	.60 per foot
TRS610	21606	1/4 -20 x 10'	60.50	50	500 feet	.92 per foot
TRS7/3	21614	5/16 -18 x 3'	.59	1	–	1.27 per foot
TRS7/6	21610	5/16 -18 x 6'	42.00	35	210 feet	1.21 per foot
TRS710	21604	5/16 -18 x 10'	68.95	35	350 feet	1.33 per foot
TRS87	21647	3/8 -16 x 7"	.17	1	–	2.86 per foot
TRS8/3	21617	3/8 -16 x 3'	.85	1	–	1.45 per foot
TRS8/6B	21645	3/8 -16 x 6'	43.75	25	150 feet	.96 per foot
TRS810	21616	3/8 -16 x 10'	72.75	25	250 feet	1.41 per foot
TRS9/3	21618	1/2 -13 x 3'	1.58	1	–	2.63 per foot
TRS9/6B	21650	1/2 -13 x 6'	38.76	12	72 feet	1.72 per foot
TRS910	21621	1/2 -13 x 10'	65.04	12	120 feet	2.16 per foot
TRS912	21694	1/2 -13 x 12'	76.32	12	144 feet	2.73 per foot
TRS106	21607	5/8 -11 x 6'	30.00	8	48 feet	5.32 per foot
TRS1010	21685	5/8 -11 x 10'	67.04	8	80 feet	5.32 per foot
TRS11-6	21580	3/4 -10 x 6'	37.50	5	30 feet	7.97 per foot
TRS1110	21690	3/4 -10 x 10'	47.90	5	50 feet	8.26 per foot
TRS1210	21624	7/8 -9 x 10'	17.05	1	–	4.59 per foot
TRS1310	21634	1-8 x 10'	22.31	1	–	5.90 per foot
TRS1510	21636	1 1/2-6 x 10'	51.22	1	–	14.80 per foot
304 STAINLESS						
TRS6/3SS	90631	1/4 -20 x 3'	.59	1	–	1.35 per foot
TRS6/6SS	10619	1/4 -20 x 6'	.75	1	–	2.79 per foot
TRS612SS	21693	1/4 -20 x 12'	3.00	1	–	1.57 per foot
TRS7/3SS	21664	5/16 -18 x 3'	.59	1	–	1.30 per foot
TRS7/6SS	10618	5/16 -18 x 6'	1.20	1	–	4.58 per foot
TRS8/6SS	10616	3/8 -16 x 6'	1.80	1	–	5.28 per foot
TRS812SS	11550	3/8 -16 x 12'	3.60	1	–	4.56 per foot
TRS5/6SS	90538	7/16 -14 x 6'	.75	1	–	4.58 per foot
TRS9/6SS	10617	1/2 -13 x 6'	3.18	1	–	10.70 per foot
TRS912SS	21692	1/2 -13 x 12'	6.36	1	–	5.06 per foot
TRS106SS	21677	5/8 -11 x 6'	5.00	1	–	6.43 per foot
316 STAINLESS						
TRS8/6-316	21646	3/8 -16 x 6'	1.75	1	–	7.10 per foot
TRS9/6-316	10680	1/2 -13 x 6'	3.18	1	–	7.10 per foot
GALVANIZED						
TRS910G	21622	1/2 -13 x 10'	5.33	1	–	7.47 per foot
TRS106G	21676	5/8 -11 x 6'	3.60	1	–	89.66 per foot

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST. DOMESTIC ROD AVAILABLE BY REQUEST.

FIXTURE HANGING ACCESSORIES



KNOCK-ON SPRING STEEL BEAM CLAMP

Knock-On beam clamp for flanges $\frac{1}{8}$ - $\frac{1}{4}$ thick, such as I-beam flanges. Made of high quality spring steel.

Features:

- Hole will accommodate jack chain, ceiling wire or a $\frac{1}{4}$ bolt.
- Made of high quality spring steel.

PART#	UPC#	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
MHOK24C	81923	3.29	100	103.60/c
MHOK24M	81924	34.20	1000	924.00/m



KNOCK-ON SPRING STEEL BEAM CLAMP

Knock-On beam clamp for flanges $\frac{5}{16}$ - $\frac{1}{2}$ thick, such as I-beam flanges. Made of high quality spring steel.

Features:

- Hole will accommodate jack chain, ceiling wire or a $\frac{1}{4}$ bolt.
- Made of high quality spring steel.

PART#	UPC#	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
MHOK58C	81929	2.00	100	112.00/c
MHOK58M	81930	20.00	1000	1,008.00/m

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

SILVERHAWK™ TOP BEAM CLAMP

STEEL ZINC



SilverHawk Top Beam Clamps are our strongest, lightweight top beam clamps. Made from cold rolled steel with a zinc plated finish, they are rust and corrosion resistant. These super strong SilverHawk clamps exceed UL and FM testing requirements. Zinc finish aesthetically works with plated rods and plated swivel ring hangers.

Tested by industry professionals, SilverHawk installation is quick and easy. Their unique counter balance design makes it easy to spin them onto threaded rods so installation goes faster. The open back shape provides visual verification during installation.

- Supports $\frac{3}{8}$ rod
- 90° angle fits I-beam or T-bar up to $\frac{3}{4}$ thick.
- Extruded tap holes meet FM Approvals requirements.
- Accommodates retaining strap usage.
- Metric also available by request.



PART#	UPC#	SIZE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
SHUBC38	81532	$\frac{3}{8}$	1.88	10	233.00/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

FIXTURE HANGING ACCESSORIES



BEAM CLAMPS

STEEL ZINC • MALLEABLE IRON • STAINLESS

PART#	UPC#	SIZE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
STEEL ZINC					
BC14	81525	1/4 -20	1.16	10	155.60/c
BC38	81530	3/8 -16	2.86	10	303.00/c
MALLEABLE IRON					
MBC14	81535	1/4 -20	2.00	10	147.20/c
MBC38	81537	3/8 -16	6.81	10	648.80/c
MBC12	81539	1/2 -13	13.20	10	821.40/c
MBC58	81538	5/8 -11	14.19	25	446.88/c
STAINLESS					
BC14SS	19686	1/4 -20	1.00	10	754.20/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



SLIP-ON LOCK NUT KIT

STEEL ZINC

PART#	UPC#	SIZE	WT. PER PKG.	QTY	SUGGESTED TRADE LIST PRICE PER
SLNK1	22040	1/4 & 3/8	1.98	1	236.12/ea kit
SLNK2	22041	3/8	2.00	1	236.12/ea kit

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



SLIP-ON LOCK NUTS

STEEL ZINC

For Threaded Rod.

PART#	UPC#	SIZE	HEX SIZE	ACROSS CORNERS	HEIGHT	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
SLN14	22030	1/4 -20	.625	.715	.375	.11	5	479.80/c
SLN516	22032	5/16 -18	.750	.865	.375	.17	5	544.80/c
SLN38	22034	3/8 -16	.875	1.01	.490	.27	5	622.80/c
SLN38C	22120	3/8 -16	.875	1.01	.490	5.37	100	528.92/c
SLN12	22036	1/2 -13	1.068	1.23	.625	.48	5	734.80/c
SLN12C	22122	1/2 -13	1.068	1.23	.625	9.99	100	699.72/c
SLN58	22043	5/8 -11	1.31	1.52	.650	.75	5	1090.00/c
SLN58C	22125	5/8 -11	1.31	1.52	.650	14.99	100	1094.52/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



Square

Octagonal

SWIVEL FIXTURE HANGERS

STEEL ZINC

For 4" Square And Octagonal Boxes.

PART#	UPC#	BOX	PIPE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
MSC50	81541	Sq. box/pivot threaded	1/2 npt pipe	.71	1	35.68/ea
MSC75	81543	Sq. box/pivot threaded	3/4 npt pipe	.68	1	35.68/ea
MSC50R	81545	Oct. box/pivot threaded	1/2 npt pipe	.63	1	35.68/ea
MSC75R	81547	Oct. box/pivot threaded	3/4 npt pipe	.59	1	35.68/ea

PAINTED WHITE AVAILABLE BY SPECIAL QUOTE. OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

FIXTURE HANGING ACCESSORIES

SWIVEL FIXTURE HANGERS

STEEL ZINC



SQUARE




OCTAGONAL

- 20° swing from vertical
- Both load rated at 50 lbs.
- Rugged hinge construction
- **Hands-free fixture hanger**
- Single Electrician Installation
- Fits 4" square and round electrical boxes
- Fits 3/4" pipe and includes a reducing bushing for 1/2" pipe

PART#	UPC#	SHAPE	WT. EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
MSCU	81607	Square	.78	1	53.74/ea
MSCUR	81609	Round	.72	1	53.74/ea

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.




J-BOLTS

STEEL ZINC • GALVANIZED



PART#	UPC#	THREAD LENGTH	THREAD SIZE/ OVERALL LENGTH	INSIDE HOOK DIA.	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
STEEL ZINC							
BTJ1	81055	1 1/2	1/4 -20 x 2 5/16	7/16	.31	10	36.40/c
BTJ4	81061	1 1/2	1/4 -20 x 4	7/16	.52	10	88.30/c
BTJ2	81057	2	5/16 -18 x 3	1/2	.66	10	67.30/c
BTJ3	81059	2 1/4	3/8 -16 x 3 3/4	5/8	1.18	10	119.50/c
GALVANIZED							
BTJ6G	81656	2	1/2 -13 x 3 1/2	1/2	4.95	10	2492.00/c

HEXAGON NUTS AND WASHERS ORDERED SEPARATELY. OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



J-BOLT KIT

STEEL ZINC

PART#	UPC#	QTY.	SIZE	ITEM	WT. PER PKG.	SUGGESTED TRADE LIST PRICE PER
BTJK516	20325	25	5/16 x 3	J-Bolts	2.13	34.36/ea kit
		25	5/16 -18	Hex Lock Nuts Steel Zinc		

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



HOOK AND HOOK TURNBUCKLES

MALLEABLE IRON BODY • STEEL ZINC HOOKS



PART#	UPC#	THREAD DIAMETER	OVERALL LENGTH CLOSED	OVERALL LENGTH OPEN	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
TBH14	81577	1/4 - 20	5 1/2	7 5/8	.18	1	8.21/ea
TBH516	81579	5/16 - 18	6 3/4	9 1/4	.33	1	12.91/ea
TBH38	81581	3/8 - 16	7 1/2	10 1/2	.52	1	18.61/ea

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

FIXTURE HANGING ACCESSORIES



EYE BOLTS WITH HEX NUTS


STEEL ZINC • 18-8 STAINLESS

PART#	UPC#	THREAD LENGTH	THREAD SIZE	OVERALL LENGTH	INSIDE EYE SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
STEEL ZINC								
JEB6	80992	1 1/4	10-24	2	3/8	2.17	100	32.45/c
JEB1	80993	3/4	1/4 -20	2	1/2	4.34	100	34.36/c
JEB2	80994	1 1/4	1/4 -20	2 1/2	1/2	4.90	100	37.39/c
JEB3	80995	1 3/4	1/4 -20	3	1/2	5.36	100	42.48/c
JEB4	82220	2	1/4 -20	3 1/2	1/2	5.86	100	47.45/c
JEB5	82225	2 3/4	1/4 -20	4	1/2	6.22	100	48.30/c
JEB9	82229	3	1/4 -20	5	1/2	7.45	100	95.63/c
JEB15	82236	3	1/4 -20	6	1/2	8.41	100	176.22/c
JEB32	82253	2 3/4	5/16 -18	2 3/8	1/2	8.03	100	122.98/c
JEB33	82254	1/4	5/16 -18	3	1/2	2.43	25	296.76/c
EB12	22223	1 1/2	3/8 -16	2	1	14.60	100	206.94/c
EB13	22224	1 1/2	3/8 -16	3	1	14.80	100	238.81/c
JEB14	82235	2 1/2	3/8 -16	4	1	8.84	50	257.96/c
JEB8	81190	3	3/8 -16	5	1	5.13	25	600.16/c
JEB11	82231	3	3/8 -16	6	1	5.85	25	3068.18/c
EB17	22247	3 7/8	3/8 -16	8	1	7.50	25	210.04/c
JEB16	82237	3	7/16 -14	8	1	3.98	20	854.55/c
JEB124	77824	1 1/4	1/2 -13	4	1 1/8	3.57	10	592.30/c
EB18	22248	4	1/2 -13	12	1 1/8	3.70	20	2730.00/c
18-8 STAINLESS								
JEB1SS	94451	3/4	1/4 -20	2	1/2	4.25	100	681.09/c
JEB3SS	94453	1 3/4	1/4 -20	3	1/2	5.48	100	768.37/c
JEB3XXSS	99580	1 3/4	1/4 -20	3	1/2	1.10	20	768.37/c
JEB5SS	94455	2 3/4	1/4 -20	4	1/2	6.22	100	483.33/c
JEB13SS	94463	2 3/8	3/8 -16	3 7/8	1	4.01	25	833.75/c
EB14SS	22214	2	3/8 -16	4	1	18.07	100	1077.33/c
JEB124SS	98187	1 1/4	1/2 -13	4	1 1/8	10.55	25	4107.06/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



An American Made Alternative To the Blue Concrete Screw – See Page 138.



QUADRIVE CONCRETE SCREW ANCHORS

- Large fillet under head to fit 3/16" and 1/4" holes provides greater driving strength
- Fluted, interrupted threads aid tapping into masonry products
- Hilo threads for faster application
- Silver color to match conduit, strap and concrete

STOP THE SNAPPING

The QuaDrive

Square Drive + Hex + Slotted + Phillips = QuaDrive

America's Newest Drive – Designed, Developed and Manufactured Only By Metallics/Avanti Screw

MADE IN USA



Made by Avanti Screw, Inc., A Metallics Affiliate

We will be glad to send a sample bag of 10 pieces to our Distributors for their customer trials. **Please specify size!**

Metallics Inc. • 800-243-8272 • sales@metallics.us

FIXTURE HANGING ACCESSORIES



SCREW EYES

DOMESTIC • STEEL ZINC

With Lag Screw Thread




PART#	UPC#	OVERALL LENGTH	HOLE DIAMETER	THREAD DIAMETER	THREAD LENGTH	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
DOMESTIC STEEL ZINC								
JSE1	80996	1 ⁵ / ₁₆	1/2	#8	1/2	.83	100	12.54/c
JSE2	80997	1 ⁵ / ₁₆	5/8	1/4	3/4	1.58	100	28.22/c
JSE3	80998	2 ³ / ₁₆	1 ¹ / ₁₆	9/32	7/8	4.06	100	37.98/c
JSE4	81415	2 ⁵ / ₈	3/4	5/16	1	6.82	100	74.08/c
JSE13	81423	8	1 ¹ / ₈	9/16	2 ⁵ / ₈	4.71	10	2899.20/c
SE6	22416	8	7/16	7/16	2 ⁷ / ₈	11.50	25	815.36/c
STEEL ZINC								
JSE5	81416	3 ³ / ₄	1/2	1/4	3/4	6.65	100	176.62/c
JSE7	81414	5 ¹ / ₂	3/4	7/16	2 ¹ / ₈	8.27	25	376.32/c
SE8	22418	5 ¹ / ₄	1	1/2	2 ¹ / ₂	13.00	50	342.90/c
SE10	22420	8	1 ¹ / ₈	9/16	2 ⁵ / ₈	11.50	25	606.16/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

SCREW HOOKS


STEEL ZINC

With Lag Screw Thread



PART#	UPC#	LENGTH	WIRE DIAMETER	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JSH1	83500	2	.135	1.20	100	28.24/c
JSH2	83505	3 ³ / ₈	.192	3.92	100	54.58/c
SH3	22510	4 ¹ / ₈	.244	8.00	100	60.26/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



Steel Zinc

18-8 Stainless

S-HOOKS

STEEL ZINC • 18-8 STAINLESS

PART#	UPC#	LENGTH	WIRE DIAMETER	WT. PER PKG.	USE WITH	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
STEEL ZINC							
JSHK1A	81006	3/4	.071	.35	JC14	100	10.47/c
SHK6B	26262	1	.120	7.17	JC12/JC14	1000	84.42/m
JSHK1	81005	1 ¹ / ₄	.105	.74	JC12/JC14	100	10.85/c
SHK15M	73957	1 ¹ / ₄	.105	34.23	JC12/JC14	5000	81.20/m
JSHK2	81007	1 ¹ / ₂	.135	1.39	JC10/JC12	100	26.34/c
JSHK2A	81008	1 ³ / ₄	.186	3.12	JC10/JC12	100	39.42/c
JSHK3	81009	2	.243	5.63	JC10	100	119.01/c
SHK120	22303	2 ³ / ₄	.190	5.01	JC10/JC12	100	127.82/c
JSHK4	82256	3	.312	6.16	JC10	50	147.00/c
JSHK5	82260	3 ¹ / ₂	.375	5.56	JC10	25	282.66/c
18-8 STAINLESS							
JSHK0ASS	82301	3/4	.092	.38	JC14	100	92.58/c
JSHK1SS	82401	1 ¹ / ₄	.148	1.17	JC12/JC14	100	114.56/c
JSHK2SS	82306	1 ¹ / ₂	.184	2.30	JC12/JC14	100	168.36/c
JSHK2ASS	82265	1 ³ / ₄	.192	3.21	JC10/JC12	100	324.74/c
JSHK3SS	82270	2	.250	6.20	JC10	100	591.82/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



FIXTURE HANGING ACCESSORIES



TIE WIRE

LOW TENSILE STEEL • 18-8 STAINLESS • PVC COATED

PART#	UPC#	GAUGE	LENGTH	WT. PER PKG.	STD. PKG./ MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
LOW TENSILE STEEL						
MTW12	16120	12	165'	6.00	1	32.42/ea coil
MTW123M	16129	12	3000'	89.00	1	664.90/ea coil
MTW124M	16130	12	4000'	118.00	1	886.57/ea coil
MTW14	16127	14	203'	3.50	1	14.18/ea coil
MTW14M	16140	14	1000'	17.00	1	225.08/ea coil
MTW16	16125	16	350'	70.60	20 Coils (min. purchase)	13.81/ea coil
MTW17	22307	16/Galvanized	500'	66.00	12 Spools (min. purchase)	26.60/ea coil
MTW1725	22308	16/Galvanized	250'	71.60	20 Coils (min. purchase)	19.94/ea coil
MTW18	22313	18	350'	13.00	1	13.81/ea coil
18-8 STAINLESS						
MTW16SS1LB	22293	16	92'	1.00	1	77.69/ea coil
MTW16SSP	22292	16	1152'	2.40	1	290.95/ea coil
PVC COATED						
MTW9163	22324	16 Gauge PVC Coated Rebar			20 Coils/box	15.96/ea coil

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



TIE WIRE DISPENSER

MOUNTS ON TOOLBELT • METAL

A Very Handy Way To Store & Dispense Tie Wire

PART#	UPC#	WT. PER PKG.	STD. PKG./ MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
MWDM1	16120	2.00 lbs	1	73.00/ea



PRE-TIED CEILING WIRE

SINGLE LOOP • STRAIGHT NO LOOP • PIN & CLIP • CLIP ONLY

PART#	UPC#	LENGTH	TYPE	WT. PER PKG.	STD. BUNDLE.	SUGGESTED TRADE LIST PRICE PER
SWL612	16174	6'	single loop	20.00	100 pcs	137.98/c
SWL1212	16177	12'	single loop	39.00	100 pcs	235.20/c
SWL1612	16179	16'	single loop	52.00	100 pcs	319.87/c
SWLS126	16182	6'	straight no loop	19.00	100 pcs	81.25/c
SWLS1210	16176	10'	straight no loop	31.00	100 pcs	137.50/c
SWLS1212	16178	12'	straight no loop	36.00	100 pcs	162.50/c
SWP612	26612	6'	pin & clip	20.00	100 pcs	147.62/c
SWP812	26714	8'	pin & clip	27.00	100 pcs	251.72/c
SWP1212	26717	12'	pin & clip	39.00	100 pcs	237.90/c
SWP1612	26721	16'	pin & clip	57.00	100 pcs	208.90/c
SWPC1212	26712	12'	clip only	34.00	100 pcs	234.75/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

FIXTURE HANGING ACCESSORIES

JACK CHAIN

STEEL GALVANIZED • 18-8 STAINLESS



PART#	UPC#	TRADE SIZE	SIZE ACROSS LINK	WORK LOAD/LIMIT	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
STEEL GALVANIZED							
JC6	21528	#6	1¼	88	28.50	100' box	206.81/ea
JC8	21511	#8	1⅜	60	20.50	100' box	186.98/ea
JC10	21515	#10	½	43	7.35	50' box	34.59/ea
JC10T	21513	#10	½	43	26.00	250' box	172.95/ea
JC10F	21514	#10	½	43	77.00	500' pail	334.43/ea
JC12	21500	#12	⅜	29	4.12	50' box	23.54/ea
JC12C	21505	#12	⅜	29	8.30	100' reel	50.81/ea
JC12CB	21507	#12	⅜	29	8.23	100' box	47.11/ea
JC12CCL	21512	#12	⅜	29	21.25	250' reel	113.57/ea
JC12M	21510	#12	⅜	29	82.30	1000' bucket	462.65/ea
JC14	21518	#14	¼	16	5.50	100' box	45.37/ea
JC14M	21519	#14	¼	16	53.50	1000' reel	219.80/ea
JC16	21508	#16	⅝	11	3.00	100' box	94.06/ea
JC18CB	21535	#18	⅜	5	1.85	100' box	136.63/ea
18-8 STAINLESS							
JC10SS	21516	#10	½	43	7.66	50' box	251.25/ea
JC10CBSS	21517	#10	½	43	15.13	100' box	714.94/ea
JC12SS	21501	#12	⅜	29	4.36	50' box	305.47/ea
JC12CSS	21506	#12	⅜	29	8.72	100' box	620.39/ea
JC12MSS	21502	#12	⅜	29	89.20	1000' box	2242.50/ea
JC16SS	21523	#16	⅝	11	3.08	100' box	321.40/ea
JC18SS	21534	#18	⅜	5	1.79	100' box	261.52/ea

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

FIXTURE HANGING CHAIN

PLAIN STEEL FINISH WITH LACQUER



PART#	UPC#	LINK LENGTH	LINK WIDTH	LINK THICKNESS	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
FHC1	21410	2¼	¾	.148	44.15	(100) 3' Pieces	402.11/ea

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

DOUBLE LOOP CHAIN


STEEL GALVANIZED • 18-8 STAINLESS



PART#	UPC#	TRADE SIZE	WIRE DIA.	WORK LOAD LIMIT	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
STEEL GALVANIZED							
DLC1	21550	#1	.105	155	11.10	100' Box	70.48/ea
DLC1S	21555	#1	.105	155	27.75	250' Spool	174.04/ea
DLC2	21556	#2	.092	115	8.00	100' Box	50.37/ea
DLC3	21560	#3	.080	90	6.80	100' Box	55.35/ea
DLC3S	21565	#3	.080	90	16.00	250' Spool	138.36/ea
DLC4	21586	#4	.072	70	5.00	100' Box	51.07/ea
DLC2/0	21557	#2/0	.135	255	42.50	250' Box	208.62/ea
18-8 STAINLESS							
SDLC3	21570	#3	.080	90	6.34	100' Box	423.83/ea

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.


FIXTURE HANGING ACCESSORIES



FIXTURE HOOKS

STEEL ZINC

For Hanging Industrial Light Fixtures




PART#	UPC#	MOUNT	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
FHK1	21400	Top/End Mount	4.50	100	50.54/c
FHK2	21405	Side Mount	4.80	100	50.54/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

TIE WIRE ACOUSTICAL TOGGLE BOLTS

STEEL ZINC

Tie wire acoustical toggle bolts are primarily for overhead applications. The winged end is inserted through the drywall, ceiling, tile, etc., and expands behind that medium while the 1/4 x 1 1/4 fender washer and hex nut act to secure the anchor to the exterior of the hole.



Includes:

- (1) Tie wire 1/4 -20 toggle bolt
- (1) 1/4-20 nut
- (1) 1/4 washer
- (1) 1/4 toggle wing

PART#	UPC#	DIAMETER	LENGTH	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JTWA144	81402	1/4	4	2.47	25	190.68/c
JTWA145	81404	1/4	5	2.89	25	229.36/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



THREADED ROD TOGGLE

STEEL ZINC

Vertical Mount used for hanging threaded rod



SMDB2

SheetRock Toggle for 1/4 Rod (Vertical Mount) Use Nut Driver SMDB2

PART#	UPC#	SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JSRT14	81388	1/4	3.08	25	93.73/c
SMDB2	41330	1/4 & 3/8	.10	1	29.70/ea

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.



HANGER BOLTS

STEEL ZINC • PLAIN



PART#	UPC#	DESCRIPTION	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
STEEL ZINC					
JHAB14	82747	8-32 x 1 1/2	.63	100	45.14/c
JHAB9	81000	10-24 x 2	1.12	100	15.13/c
JHAB10	81001	1/4 -20 x 3	3.10	100	29.78/c
JHAB11	81002	3/8 -16 x 3	7.65	100	65.05/c
JHAB13	84111	3/8 -16 x 4	9.42	100	68.91/c
HAB15B	23289	3/8 -16 x 4 1/2	25.67	250	99.90/c
JHAB12	84110	3/8 -16 x 6	7.31	50	257.72/c
HAB12B	23281	3/8 -16 x 6	18.41	125	114.30/c
PLAIN					
HAB12PLB	23282	3/8 -16 x 6	18.00	125	91.80/c
HAB13PLB	20130	3/8 -16 x 4	24.14	250	52.68/c
HAB15PLB	23283	3/8 -16 x 4 1/2	21.60	250	69.90/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

FIXTURE HANGING ACCESSORIES

HANGER BOLT DRIVERS



With 1/4 Power Hex Shanks
Internal threads for driving hanger bolts and threaded rod

PART#	UPC#	DIAMETER	LENGTH	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
HABD10	23275	1/4 -20	2 ⁹ / ₁₆	.06	1	14.09/ea
HABD12	23280	3/8 -16	2 ⁹ / ₁₆	.08	1	17.91/ea

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

ACOUSTICAL DRILL SCREW

STEEL ZINC



Designed to penetrate 16-18 gauge steel stud for hanging acoustical ceilings

PART#	UPC#	THREAD SIZE	OVERALL LENGTH	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JATEK1	82020	1/4	2	1.05	50	108.56/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

ACOUSTICAL LAG SCREWS

STEEL ZINC



For use in tie wire and jack chain applications
For Wood Application

PART#	UPC#	THREAD SIZE	OVERALL LENGTH	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JALS14	81003	1/4	3	1.19	50	45.32/c
JALS15	77915	1/4	4	3.61	100	59.62/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

ACOUSTICAL LAG & ACOUSTICAL DRILL SCREW DRIVER



PART#	UPC#	SIZE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
ALSD	22050	7/16 X 2 ³ / ₁₆	.13	1	11.20/ea

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

TIE WIRE WEDGE ANCHORS

STEEL ZINC WITH STAINLESS STEEL CLIP



For various overhead suspension applications

PART#	UPC#	DIAMETER	OVERALL LENGTH	MIN. DEPTH IN LENGTH	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JTWA214	80906	1/4	2 ¹ / ₄	1 ³ / ₈	2.63	100	132.57/c
JTWA57	81409	5/16	1 ¹ / ₂	1	2.51	100	134.04/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

FIXTURE HANGING ACCESSORIES

EYE COUPLING

STEEL ZINC

For use in tie wire or jack chain applications



PART#	UPC#	DIAMETER	OVERALL LENGTH	WT. PER PKG.	STD. PKG./ MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JEC44	81004	1/4 -20	1 1/2	2.29	100	96.66/c
EC44M	81401	1/4 -20	1 1/2	23.10	1000	524.72/m
EC44B	90310	1/4 -20	1 1/2	57.75	2500	534.71/c

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST.

RIZE KWIK-LOC™ SYSTEM





A fast and easy way to hang signs, florescent fixtures, speakers, busbars, cable trays, and piping just to name a few.

No Tools Needed and KWIK-LOCS™ are reusable!

Kwik-Loc™ with 3/32 cable will safely suspend 150 lbs vertical.

NOTE: Suspension at angles does reduce safe working load.



WEIGHT CHART

SIZE	VERTICAL	15°	30°	45°	60°
3/32	150 lbs	144 lbs	129 lbs	105 lbs	75 lbs

RIZE Kwik-Loc™ System can be purchased in kits or individually

PART#	UPC#	DIAMETER LOOP CABLE	CABLE LENGTH	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
RLCK5	23055	3/32	5'	.15	1	15.99/ea
RLCK10	23060	3/32	10'	.23	1	18.75/ea
MKL100	23082	Kwik-Loc™ only for 1/16 & 3/32	-	.05	1	6.13/ea
RLC5	23065	3/32	5'	.10	1	10.04/ea
RLC10	23070	3/32	10'	.18	1	13.03/ea
RLC500	23066	3/32	550'	5.51	1	218.12/ea



LISTED
Luminaire Fitting
14HE

All Kwik-Locs have been tested to UL 1598 and are listed under File # E246601

Helpful Hints From Metallics:

Did You forget to ask...
GOT FASTENERS?

FIXTURE HANGING ACCESSORIES

VERTICAL MOUNT THREADED ROD ANCHOR SYSTEM

STEEL ZINC

Saves Time and Cost From Traditional Hanging Methods

Drill, Drive, Done!



PART#	JAR UPC#	ROD SIZE	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
WOOD						
JRWV25200	31859	1/4-20	1/4 x 2 Type 17 Point	2.00	25	184.50/c
JRWV37100	31861	3/8-16	1/4 x 1 Type 17 Point	2.00	25	186.75/c
JRWV37200	31862	3/8-16	1/4 x 2 Type 17 Point	2.00	25	189.00/c
JRWV37212	31863	3/8-16	5/16 x 2 1/2 Type 17 Point	2.00	25	191.25/c



METAL						
JRSV25100	31840	1/4-20	1/4 x 1 #3 Drill Point	2.00	25	236.25/c
JRSV37100N	31842	3/8-16	1/4 x 1 #3 Drill Point with Nut	2.00	25	247.50/c
JRSV37112	31843	3/8-16	1/4 x 1-1/2 #3 Drill Point	2.00	25	247.50/c
JRSV37112N	31844	3/8-16	1/4 x 1-1/2 #3 Drill Point with Nut	2.00	25	247.50/c
JRSV37112N5	31845	3/8-16	12-20 x 1-1/2 #5 Drill Point with Nut	2.00	25	261.00/c
JRSV37200	31847	3/8-16	1/4 x 2 #3 Drill Point	2.00	25	254.25/c



CONCRETE						
JTHD25112RH	31867	1/4-20	1/4 x 1-1/2 (Use 3/8 Socket)	1.00	25	258.75/c
JTHD37218RH	31870	3/8-16	3/8 x 2-1/8 (Use 1/2 Socket)	1.50	25	258.75/c
JTHD37212RH	31869	3/8-16	3/8 x 2-1/2 (Use 1/2 Socket)	2.50	25	351.00/c
JTHD50234RH	31873	1/2-13	1/2 x 2-3/4 (Use 11/16 Socket)	4.00	25	429.75/c



DRIVER						
RND62	31878	1/4 & 3/8	Driver (For Wood and Metal Only)	.10	1	24.75/ea



Metallics

An **AMERICAN** Source For Premier and Innovative Fasteners and Anchors

We believe Metallics has the largest ratio of American made to foreign produced product of any other American fastener company.



FIXTURE HANGING ACCESSORIES

HORIZONTAL MOUNT THREADED ROD ANCHOR SYSTEM

STEEL ZINC

Saves time and cost from traditional hanging methods

Drill, Drive, Done!



PART#	JAR UPC#	ROD SIZE	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
WOOD						
JRWH25100	31853	1/4-20	1/4 x 1 Type 17 Point	2.00	25	98.00/c
JRWH37200	31855	3/8-16	1/4 x 2 Type 17 Point	2.00	25	200.25/c
JRWH37212	31856	3/8-16	5/16 x 2 1/2 Type 17 Point	2.00	25	270.00/c



PART#	JAR UPC#	ROD SIZE	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
METAL						
JRSH25100N	31830	1/4-20	1/4 x 1 #3 Drill Point with Nut	2.00	25	265.50/c
JRSH251125	31831	1/4-20	12-20 x 1-1/2 #5 Drill Point	2.00	25	285.75/c
JRSH37100N	31833	3/8-16	1/4 x 1 #3 Drill Point with Nut	2.00	25	222.75/c
JRSH37112N5	31834	3/8-16	12-20 x 1-1/2 #5 Drill Point with Nut	2.00	25	285.75/c



PART#	JAR UPC#	ROD SIZE	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
DRIVER						
RND62	31878	1/4 & 3/8	Driver (For Wood and Metal Only)	.10	1	24.75/ea



MULTI-PURPOSE BAT WING SPRING STEEL CLIP

For Smooth/Threaded Rod & Ceiling Wire

Multi-purpose spring steel bat wing clip allows you to attach a variety of items such as J Hooks and conduit boxes to ceiling wire as thin as PIS 12 gauge and smooth/threaded rod up to 1/4".

- Threaded impressions accomodates 10-24 and 1/4-20 threads
- Highly versatile and adjustable
- Made of high quality spring steel
- Ideal fastener for J Hooks in above ceiling applications
- Attaches to 12 gauge ceiling wire up to 1/4" threaded rod
- Compare to Caddy® 4Z43, B-Line® BW2, and Minerallac® APS.

PART#	UPC#	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
MW34C	24632	.42	100	129.38/c


FIXTURE HANGING ACCESSORIES

STEEL DECKING THREADED ROD ANCHOR SYSTEM

STEEL ZINC


Saves time and cost from traditional hanging methods

Drill, Drive, Done!



Expands to provide direct Vertical attachment in:

- Metal Deck (16-22 gauge)
- Z Purlin (16-18 gauge)
- Install in seconds
- Retaining nut is not required



PART#	UPC#	MOUNT	ROD SIZE	WT. PER PKG.	STD. PKG./MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JSMX1	41435	Vertical	1/4 - 20	.44	5	1262.00/c
JSMX125	41570	Vertical	1/4 - 20	2.02	25	709.00/c
JSMX2	41440	Vertical	3/8 - 16	.45	5	1262.00/c
JSMXP35	41580	Vertical Swivel	3/8 - 16	.48	5	1546.60/c
JSMXP3525	41625	Vertical Swivel	3/8 - 16	2.40	25	1511.12/c
SMXX1	41445		*Installation tool	1.01	1	440.40/ea
SMXB1	41450		*25/64 Custom Drill Bit for Tool	.09	1	44.63/ea


Installation Kit Includes: Sleeve, bit receiver, hex wrench, and 25/64 drill bit

PLEASE CALL FOR TECHNICAL INFORMATION



An American Made Alternative To the Blue Concrete Screw – See Page 138.

QUADRIVE CONCRETE SCREW ANCHORS



- Large fillet under head to fit 3/16" and 1/4" holes provides greater driving strength
- Fluted, interrupted threads aid tapping into masonry products
- Hilo threads for faster application
- Silver color to match conduit, strap and concrete

STOP THE SNAPPING

The QuaDrive

Square Drive + Hex + Slotted + Phillips = QuaDrive

America's Newest Drive – Designed, Developed and Manufactured Only By Metalics/Avanti Screw



Made by Avanti Screw, Inc., A Metalics Affiliate

We will be glad to send a sample bag of 10 pieces to our Distributors for their customer trials. Please specify size!

Metalics Inc. • 800-243-8272 • sales@metalics.us

www.metalics.us