

# HALOHOME™

Smart Lighting System



## HALO Home RL LED Recessed Downlight

### HALO

The HALO Home RL series integrated LED modules with Bluetooth mesh connectivity is designed for 4-inch and 5/6-inch aperture recessed downlights. Pair the modules with the HALO Home mobile app for wireless control and customization including ON/OFF, grouping, color tuning, dimming, scheduling, scenes and more. Users can add HALO Home wall controllers for expanded “smart” functionality. Suitable for new construction, remodel and retrofit installation, the RL series is designed to connect to the HALO Home Bluetooth network with no hub or internet connection required.



RL4069BLE40AWH



RL56069BLE40AWH



Catalog Number	Product Description	Replaces Up To	Selectable CCT	Voltage	CRI	Finish	Lumens (up to)	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
RL4069BLE40AWH	4" LED Module, Bluetooth	60W INC	2700K-5000K	120V	90	White	600	8	588	080083809257	2308008
RL56069BLE40AWH	5/6" LED Module, Bluetooth	65W INC	2700K-5000K	120V	90	White	600	10	300	080083809233	2308006

# HALO Home FTS and MST LED Outdoor Flood and Motion Lighting

## HALO

The HALO Home FTS outdoor security smart LED floodlight and MST motion-activated floodlight enhances security around the home and can be controlled via Bluetooth mesh connectivity through the free HALO Home mobile app. Customers can control one or multiple lights with grouping, scheduling, dimming and color tuning capabilities.



FTS20CB

MST20C18B



Catalog Number	Product Description	Replaces Up To	Selectable CCT	Voltage	Finish	Lumens (up to)	Watts	Pallet Quantity	UPC
MST20C18B	Twin LED Flood, Bluetooth, Motion	2 - Head PAR 38, 90W INC.	3000K-5000K	120-277V	Bronze	2,034	23	240	080083810512
MST20C18W	Twin LED Flood, Bluetooth, Motion	2 - Head PAR 38, 90W INC.	3000K-5000K	120-277V	White	2,034	23	240	080083810499
FTS20CB	Twin LED Flood, Bluetooth	2 - Head PAR 38, 90W INC.	3000K-5000K	120-277V	Bronze	2,034	23	180	080083810475
FTS20CW	Twin LED Flood, Bluetooth	2 - Head PAR 38, 90W INC.	3000K-5000K	120-277V	White	2,034	23	180	080083810451

# HALO Home Smart Controls and Accessories

## HALO

The HALO Home smart dimmers and accessories allow for maximum control of HALO Home smart lighting devices. The dimmer and accessories all connect to the HALO Home Bluetooth Mesh network with no hub or internet connection required. The In-Wall Smart Dimmer turns standard lights into smart lights. The In-Wall Accessory Dimmer controls a HALO Home lighting devices from a central location. The Anyplace Dimmer lets customers control HALO Home smart lights and accessories from anywhere in the home without rewiring. The Plug-In Lamp Dimmer works with residential lighting LED luminaires. The Internet Access Bridge enables customers to control HALO Home lighting devices from anywhere in the world and allows for Amazon Alexa and Google Assistant voice control.



HIWAC1BLE40AWH

HIWMA1BLE40AWH



HWAS1BLE40AWH



HWB1BLE40AWH



HWP1BLE40AWH



Catalog Number	Product Description	Voltage	Finish	Watts	Pallet Quantity	UPC
HIWAC1BLE40AWH	In Wall Accessory Dimmer, Bluetooth	120V	White	5	1,792	080083826544
HIWMA1BLE40AWH	In Wall Dimmer, Bluetooth	120V	White	5	1,536	080083826520
HWB1BLE40AWH	Internet Access Bridge, Bluetooth	110/120V	White		576	080083811168
HWAS1BLE40AWH	Anyplace Dimmer, Bluetooth		White		1,120	080083811182
HWP1BLE40AWH	Plug-In Lamp Dimmer, Bluetooth	110/120V	White		2,304	080083826506

# Recessed

HALO

Commercial & Residential  
Downlighting



# HLB LED Direct Mount Downlight

## HALO

The HLB ultra-thin LED lens downlight series (4-inch and 6-inch sizes) features a remote driver/junction box suitable for new construction and remodel applications. The products simply install in drywall or a suspended ceiling, eliminating the need for a recessed can. The products install from below the ceiling in as little as 3-1/2-inch plenum height and can be used in direct contact with insulation. The modules are available in a choice of 3000K or 4000K, or choose a model with CCT selectable technology, allowing the user to choose from a range of five color temperatures from 2700K to 5000K via a switch.



Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens (up to)	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
HLB4069301EMWR	4" Module, Round Remote Driver J-Box	White	65W INC	3000K	120V	697	12	720	080083863242	Energy Star pending
HLB4069401EMWR	4" Module, Round Remote Driver J-Box	White	65W INC	4000K	120V	773	12	720	080083863266	Energy Star pending
HLB4069FS1EMWR	4" Module, Round Remote Driver J-Box	White	65W INC	Selectable 2700K-5000K	120V	752	12	864	080083848140	2322243
HLB4S069301EMWR	4" Module, Square Remote Driver J-Box	White	65W INC	3000K	120V	734	12	720	080083863280	Energy Star pending
HLB4S069401EMWR	4" Module, Square Remote Driver J-Box	White	65W INC	4000K	120V	721	12	720	080083873463	Energy Star pending
HLB4S069FS1EMWR	4" Module, Square Remote Driver J-Box	White	65W INC	Selectable 2700K-5000K	120V	752	12	720	080083863303	Energy Star pending
HLB6099301EMWR	6" Module, Round Remote Driver J-Box	White	65W INC	3000K	120V	992	12	432	080083863327	Energy Star pending
HLB6099401EMWR	6" Module, Round Remote Driver J-Box	White	65W INC	4000K	120V	1,057	12	432	080083863341	Energy Star pending
HLB6099FS1EMWR	6" Module, Square Remote Driver J-Box	White	65W INC	Selectable 2700K-5000K	120V	1,103	16	450	080083848164	Energy Star pending
HLB6S099301EMWR	6" Module, Square Remote Driver J-Box	White	65W INC	3000K	120V	949	12	432	080083863365	Energy Star pending
HLB6S099401EMWR	6" Module, Square Remote Driver J-Box	White	65W INC	4000K	120V	987	12	432	080083873487	Energy Star pending
HLB6S099FS1EMWR	6" Module, Round Remote Driver J-Box	White	65W INC	Selectable 2700K-5000K	120V	1,103	12	432	080083863389	Energy Star pending

# RL LED Baffle Trim Direct Mount

## HALO

The RL-DM is a 4-inch or 6-inch regressed LED lens downlight with remote driver/junction box suitable for new construction and remodel applications. Field selectable color temperature and high color rendering provide excellent color performance. Simplified installation in drywall or suspended ceilings eliminates recessed cans saving time and money. Installs from below the ceiling in shallow plenum height, can be used in direct contact with insulation and is airtight.



Catalog Number	Product Description	Finish	Replaces Up To	Selectable CCT	Voltage	Lumens (up to)	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
RL4069S1EWHDM	4" Retrofit Baffle-Trim, Remote Driver J-Box	White	65W INC	2700K-5000K	120V	652	9	300	080083858101	2325604
RL6069S1EWHDM	6" Retrofit Baffle-Trim, Remote Driver J-Box	White	65W INC	2700K-5000K	120V	719	9	240	080083858125	2325603

# SMD LED Direct Mount Module

## HALO

The HALO Surface Mount LED Downlight (SMD-DM) is a low profile surface luminaire with a larger look and high performance. SMD-DM (Direct Mount with spring clips) is designed for new installation into drywall, without any additional housing or junction box needed. Suitable for residential or commercial installations. Ideal for general areas, closets, storage areas, attics and basements.



SMD4R6930WHDM



SMD6R6930WHDM



Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
SMD4R6930WHDM	4" RD Surface	White	65W INC	3000K	120V	700	10	240	080083766390	2281593
SMD6R6930WHDM	6" RD Surface	White	65W INC	3000K	120V	750	10	240	080083767090	2281592

# RL LED Baffle Trim Downlight

## HALO

The HALO RL Series is a complete LED baffle-trim module for 4-inch or 5/6-inch aperture recessed downlights. Ideal for new construction, remodel and retrofit installation, the integral LED driver offers 120V dimming capability and the lens provides uniform illumination and a wet location listing. The modules are available in a choice of 2700K or 3000K or choose the baffle-trim modules with CCT selectable technology that allows the user to choose from a range of five color temperatures from 2700K to 5000K via a switch.



RL460WH927PK



RL560WH6927



Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
RL4069S1EWH	4" Retrofit Baffle-Trim	White	65W INC	Selectable 2700K-5000K	120V	621	9	300	080083816712	2326218
RL4099S1EWH	4" Retrofit Baffle-Trim	White	65W INC	Selectable 2700K-5000K	120V	1006	12	504	080083816736	2321466
RL56069S1EWH	5/6" Retrofit Baffle-Trim	White	65W INC	Selectable 2700K-5000K	120V	712	8	240	080083816750	2326217
RL56099S1EWH	5/6" Retrofit Baffle-Trim	White	65W INC	Selectable 2700K-5000K	120V	1,006	12	240	080083818679	2326219
RL56129S1EWH	5/6" Retrofit Baffle-Trim	White	65W INC	Selectable 2700K-5000K	120V	1,272	14	240	080083818693	2321465
RL460WH927PK	4" Retrofit Baffle-Trim	White	60W INC	2700K	120V	530	8	630	080083699445	2286441, 2286440
RL460WH930PK	4" Retrofit Baffle-Trim	White	60W INC	3000K	120V	570	8	1,008	080083690770	2286445, 2286444
RL560WH6927	5/6" Retrofit Baffle-Trim	White	65W INC	2700K	120V	633	10	288	080083699384	2269156, 2286436, 2286422
RL560WH6930	5/6" Retrofit Baffle-Trim	White	65W INC	3000K	120V	610	8	288	080083690602	2269160, 2286425, 2286424

# RLD LED Deep Baffle Downlight

## HALO

The RLD Deep Baffle series is a complete LED baffle-trim module for 4-inch (RLD4) or 6-inch (RLD6) aperture recessed downlights suitable for new construction, remodel and retrofit installation. The regressed lens provides uniform illumination and 50° optical cutoff. The Deep Baffle comes standard with both white and black Coilex baffle included and is wet location. Precision construction makes any housing airtight for added savings and code compliance.



Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
RLD4069301EWH	4" Retrofit Deep Baffle-Trim	White	40W INC	3000K	120V	681	9	420	080083823604	2320421
RLD6069301EWH	6" Retrofit Deep Baffle-Trim	White	40W INC	3000K	120V	668	9	120	080083823642	2320420

# LT LED Retrofit Baffle Trim Downlight

## HALO

The LT Series combines the energy savings, long life and sustainability of LED in an easy-to-install retrofit baffle trim kit. The modules are available in 4-inch and 5/6-inch sizes and supplied with torsion springs or friction blades to secure the trim tight to ceiling. The diffuse lens provides shielding to the source and a wet location listing; suitable for use in showers or in outdoor covered ceiling applications. The series is ideal for new construction or remodel applications.




Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
LT460WH6927	4" Retrofit Baffle-Trim	White	60W INC	2700K	120V	544	8	420	080083762033	2277226
LT460WH6930	4" Retrofit Baffle-Trim	White	60W INC	3000K	120V	554	8	504	080083742394	2257770, 2277227
LT560WH6927	5/6" Retrofit Baffle-Trim	White	60W INC	2700K	120V	700	10	288	080083762897	2277231
LT560WH6930	5/6" Retrofit Baffle-Trim	White	60W INC	3000K	120V	683	10	240	080083742417	2252183, 2277232
LT560WH6935	5/6" Retrofit Baffle-Trim	White	60W INC	3500K	120V	697	10	288	080083762910	2277233
LT560WH6940	5/6" Retrofit Baffle-Trim	White	60W INC	4000K	120V	737	10	288	080083762934	2277234

Recessed

# RSQ All-Purpose Square LED Downlights

## HALO

The RSQ all-purpose square lens LED modules are available in three sizes for use in HALO or compatible 4, 5 or 6-inch recessed housings. Designed for both new construction or to update an existing installation, the wide distribution patterns work well in low to high ceilings, providing general area illumination. The regressed flat lens with step baffle provides visual comfort and glare control.



RSQ4089301EMWWB

RSQ5089301EMWWB



RSQ6089301EMWWB



Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
RSQ4089271EMWWB	4" Retrofit Square Baffle-trim	White	60W INC	2700K	120V	807	9	672	080083824410	2323426
RSQ4089301EMWWB	4" Retrofit Square Baffle-trim	White	60W INC	3000K	120V	814	9	672	080083824434	2323427
RSQ4089351EMWWB	4" Retrofit Square Baffle-trim	White	60W INC	3500K	120V	825	9	672	080083824458	2323428
RSQ4089401EMWWB	4" Retrofit Square Baffle-trim	White	60W INC	4000K	120V	835	9	672	080083824472	2323429
RSQ5089271EMWWB	5" Retrofit Square Baffle-trim	White	60W INC	2700K	120V	813	9	360	080083824519	2323485
RSQ5089301EMWWB	5" Retrofit Square Baffle-trim	White	60W INC	3000K	120V	837	9	360	080083824533	2323486
RSQ5089351EMWWB	5" Retrofit Square Baffle-trim	White	60W INC	3500K	120V	828	9	360	080083824557	2323487
RSQ5089401EMWWB	5" Retrofit Square Baffle-trim	White	60W INC	4000K	120V	840	9	360	080083824571	2323488
RSQ6089271EMWWB	6" Retrofit Square Baffle-trim	White	60W INC	2700K	120V	835	9	240	080083824618	2323481
RSQ6089301EMWWB	6" Retrofit Square Baffle-trim	White	60W INC	3000K	120V	844	9	240	080083824632	2323482
RSQ6089351EMWWB	6" Retrofit Square Baffle-trim	White	60W INC	3500K	120V	835	9	240	080083824656	2323483
RSQ6089401EMWWB	6" Retrofit Square Baffle-trim	White	60W INC	4000K	120V	845	9	240	080083824670	2323484
RSQ4TRMMW	4" Splay trim	Paintable						3780	080083840984	
RSQ4TRMSNB	4" Baffle MW, trim	Satin Nickel						3780	080083841004	
RSQ4TRMTBZB	4" Baffle trim	Tuscan Bronze						3780	080083841028	
RSQ5TRMMW	5" Splay trim	Paintable						2520	080083841042	
RSQ5TRMSNB	5" Baffle MW, trim	Satin Nickel						2520	080083841066	
RSQ5TRMTBZB	5" Baffle trim	Tuscan Bronze						2520	080083841080	
RSQ6TRMMW	6" Splay trim	Paintable						1800	080083841103	
RSQ6TRMSNB	6" Baffle MW, trim	Satin Nickel						1800	080083841127	
RSQ6TRMTBZB	6" Baffle trim	Tuscan Bronze						1800	080083841141	

# SLD LED Surface Mount Module

## HALO

The HALO Surface LED Downlight (SLD) incorporates WaveStream™ technology to create an ultra-low profile surface-mounting luminaire with the performance and look of a traditional downlight. Available in 4-inch and 6-inch sizes, the SLD is designed for installation in many standard and fire-rated junction boxes. A supply wire adapter with LED quick wiring connector is included. Suitable for residential or commercial installations, the SLD is ideal for closets, storage areas, attics and basements.



SLD405830WH



SLD606830WH

Recessed

Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
SLD405830WH*	4" Surface Downlight	White	60W INC	3000K	120V	750	12	540	080083697564	2275534
SLD405830WHJB	4" Surface Downlight, J-Box	White	60W INC	3000K	120V	750	12	540	080083705979	2275534
SLD606830WH*	6" Surface Downlight	White	65W INC	3000K	120V	760	12	300	080083697588	2271848
SLD606830WHJB	6" Surface Downlight, J-Box	White	65W INC	3000K	120V	760	12	300	080083705993	2271848
SLD606930WH*	6" Surface Downlight	White	65W INC	3000K	120V	735	13	300	080083697625	2271068
SLD606930WHJB	6" Surface Downlight, J-Box	White	65W INC	3000K	120V	735	13	300	080083706037	2271068

\*Not for sale in California. For California, apply "CA" to the model number (i.e. SLD405830WH-CA)

# BLD LED Surface Mount Module

## HALO

The Backlit downlight is a low-profile, high-performance surface mount luminaire that offers the added flexibility of seleCCTable color temperatures at time of installation. BLD4 (4-inch) and BLD6 (6-inch) are designed for installation in many 3-1/2-inch and 4-inch square, octagon, or round junction boxes. The BLD4/BLD6 may also retrofit in 4-inch, 5-inch and 6-inch aperture IC and Non-IC recessed housings. The user can choose from a range of five color temperatures from 2700K to 5000K via a switch.



BLD406930WH



BLD606930WH

Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
BLD406930WH	4" RD Surface, Direct Mount	White	65W INC	3000K	120V	690	8	648	080083826667	2319363
BLD4089SWH	4" RD Surface, Direct Mount	White	65W INC	Selectable 2700K-5000K	120V	802	10	432	080083826681	2319361
BLD606930WH	6" RD Surface, Direct Mount	White	65W INC	3000K	120V	700	8	450	080083826704	2319362
BLD6089SWH	6" RD Surface, Direct Mount	White	65W INC	Selectable 2700K-5000K	120V	812	10	300	080083826728	2319364



# SMD LED Surface Mount Module

## HALO

The Surface Mount LED Downlight (SMD) is an low-profile, surface-mounting luminaire with a modern look that provides high performance. The SMD is designed for installation with many square, octagon, or round junction boxes and a supply wire adapter with LED quick wiring connector is included. The SMD-DM model is designed for new installation into drywall, without the need for a housing or junction box.



SMD4R6930WH



SMD6R12927WH



SMD6S12927WH



Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
SMD4R6930WH	4" RD Surface Mount	White	60W INC	3000K	120V	700	10	504	080083766352	2281593
SMD6R6930WH	6" RD Surface Mount	White	65W INC	3000K	120V	758	10	300	080083767052	2281592
SMD6R12927WH	6" RD Surface Mount	White	80W INC	2700K	120V	1,244	16	360	080083825400	2308976
SMD6R12927WHE	6" RD Surface Mount	White	80W INC	2700K	120-277V	1,210	15	450	080083817603	2322244
SMD6R12930WH	6" RD Surface Mount	White	80W INC	3000K	120V	1,242	15	360	080083825424	2308976
SMD6R12930WHE	6" RD Surface Mount	White	80W INC	3000K	120-277V	1,203	15	450	080083817627	2322245
SMD6R12935WH	6" RD Surface Mount	White	80W INC	3500K	120V	1,264	15	360	080083825448	2308976
SMD6R12935WHE	6" RD Surface Mount	White	80W INC	3500K	120-277V	1,200	15	450	080083817641	2322246
SMD6R12940WH	6" RD Surface Mount	White	80W INC	4000K	120V	1,223	15	360	080083825462	2308976
SMD6R12940WHE	6" RD Surface Mount	White	80W INC	4000K	120-277V	1,260	15	450	080083817665	2322247
SMD6R12950WH	6" RD Surface Mount	White	80W INC	5000K	120V	1,252	15	360	080083825486	2308976
SMD6R12950WHE	6" RD Surface Mount	White	80W INC	5000K	120-277V	1,200	15	450	080083817689	2322248
SMD6S12927WH	6" RD Surface Mount	White	76W INC	2700K	120V	1,190	16	360	080083825509	2308976
SMD6S12927WHE	6" RD Surface Mount	White	76W INC	2700K	120-277V	1,167	16	450	080083817702	2322250
SMD6S12930WH	6" RD Surface Mount	White	76W INC	3000K	120V	1,180	16	360	080083825523	2308976
SMD6S12930WHE	6" RD Surface Mount	White	76W INC	3000K	120-277V	1,135	16	450	080083817726	2322251
SMD6S12935WH	6" RD Surface Mount	White	80W INC	3500K	120V	1,237	16	360	080083825547	2308976
SMD6S12935WHE	6" RD Surface Mount	White	76W INC	3500K	120-277V	1,140	16	450	080083817740	2322252
SMD6S12940WH	6" RD Surface Mount	White	80W INC	4000K	120V	1,215	16	360	080083825561	2308976
SMD6S12940WHE	6" RD Surface Mount	White	76W INC	4000K	120-277V	1,155	16	450	080083817764	2322253
SMD6S12950WH	6" RD Surface Mount	White	80W INC	5000K	120V	1,235	16	360	080083825585	2308976
SMD6S12950WHE	6" RD Surface Mount	White	76W INC	5000K	120-277V	1,180	16	450	080083817788	2322254

# RA LED Adjustable Gimbal

## HALO

The RA LED is a complete adjustable gimbal LED module for 4-inch and 5/6-inch aperture recessed downlights; suitable for new construction, remodel and retrofit installation. The RA adjustable gimbal offers 35° tilt and up to 360° rotation and is compatible with Leading Edge and Trailing Edge phase control dimmers. The modules are offered in Very Wide Flood (VWFL) and Narrow Flood (NFL) models. The modules are available in a choice of 2700K or 3000K or choose the gimbal with CCT selectable technology that allows the user to choose from a range of five color temperatures from 2700K to 5000K via a switch.



RA406927WH



RA5606927WH



Recessed

Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
RA4069S1EWH	4" Retrofit Adjustable, Wide	White	65W INC	2700K-5000K	120V	615	7	504	080083817887	2319905
RA406927WH	4" Retrofit Adjustable, Wide	White	65W INC	2700K	120V	600	10	384	080083693184	2284607, 2319592
RA406930WH	4" Retrofit Adjustable, Wide	White	65W INC	3000K	120V	615	10	288	080083693207	2281535, 2319593
RA406930NFLWH	4" Retrofit Adjustable, Narrow	White	65W INC	3000K	120V	640	10	384	080083693283	2319591
RA56069S1EWH	5/6" Retrofit Adjustable, Wide	White	65W INC	Selectable 2700K-5000K	120V	630	7	270	080083817900	2319904
RA5606927WH	5/6" Retrofit Adjustable, Wide	White	65W INC	2700K	120V	645	10	240	080083693221	2272165, 2319596
RA5606930WH	5/6" Retrofit Adjustable, Wide	White	65W INC	3000K	120V	670	10	240	080083693245	2271987, 2319597
RA5606930NFLWH	5/6" Retrofit Adjustable, Wide	White	65W INC	2700K	120V	645	10	192	080083693320	2272166, 2319595

# LA LED Adjustable Gimbal

## HALO

The HALO LA LED Adjustable Downlight series is and adjustable LED modules for 4-inch and 5/6-inch aperture recessed downlights. The LA gimbals feature adjustment of 35° tilt and up to 360° rotation. The lens provides uniform illumination and wet location listing and precision construction makes any housing AIR-TITE for added savings and code compliance. The series is offered in five color temperatures and 90 CRI.



LA56069271EWH



LA56069271EWH



Catalog Number	Product Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
LA4069271EWH	4" Retrofit Adjustable, Plastic, Wide	White	40W INC	2700K	120V	611	9	576	080083818129	2325615
LA4069301EWH	4" Retrofit Adjustable, Plastic, Wide	White	40W INC	3000K	120V	613	9	576	080083818143	2325616
LA4069351EWH	4" Retrofit Adjustable, Plastic, Wide	White	40W INC	3500K	120V	630	9	576	080083818167	2325617
LA4069401EWH	4" Retrofit Adjustable, Plastic, Wide	White	40W INC	4000K	120V	640	9	576	080083818181	2325618
LA4069501EWH	4" Retrofit Adjustable, Plastic, Wide	White	40W INC	5000K	120V	630	9	576	080083818204	2325619
LA56069271EWH	5/6" Retrofit Adjustable, Plastic, Wide	White	40W INC	2700K	120V	614	9	270	080083818228	2325605
LA56069301EWH	5/6" Retrofit Adjustable, Plastic, Wide	White	40W INC	3000K	120V	637	9	270	080083818242	2325606
LA56069351EWH	5/6" Retrofit Adjustable, Plastic, Wide	White	40W INC	3500K	120V	640	9	270	080083818266	2325607
LA56069401EWH	5/6" Retrofit Adjustable, Plastic, Wide	White	40W INC	4000K	120V	640	9	270	080083818280	2325608
LA56069501EWH	5/6" Retrofit Adjustable, Plastic, Wide	White	40W INC	5000K	120V	630	9	270	080083818303	2325609

# HU10 LED Undercabinet

## HALO

The HU10 undercabinet low-profile design delivers maximum energy savings and life with easy installation. The integrated driver allowing 120V direct to the fixture for easy installation. Available in multiple lengths, the HALO system can be configured to fit almost anywhere. Smooth dimming down to 5% using a standard dimmer and connector cables in a variety of different lengths make it easy to link one unit to another. Each unit has an integrated on-off switch.



HU1018D930PR



HU1018D930MBR



Catalog Number	Product Description	Finish	Length	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
HU1009D930MBR	Dimming, Cord/Plug or Direct Wire	Black	9"	17W INC	3000K	120V	248	4	576	080083748310	2271988
HU1009D930PR	Dimming, Cord/Plug or Direct Wire	White	9"	17W INC	3000K	120V	248	4	576	080083747436	2271988
HU1018D930PR	Dimming, Cord/Plug or Direct Wire	White	18"	33W INC	3000K	120V	495	7	336	080083747450	2272162
HU1018D930MBR	Dimming, Cord/Plug or Direct Wire	Black	18"	33W INC	3000K	120V	495	7	336	080083748334	2272162
HU1024D930MBR	Dimming, Cord/Plug or Direct Wire	Black	24"	44W INC	3000K	120V	660	7	224	080083748358	2289580
HU1024D930PR	Dimming, Cord/Plug or Direct Wire	White	24"	44W INC	3000K	120V	660	7	224	080083748280	2289580

# HU30 LED Undercabinet

## HALO

The HU30 undercabinet maintains HALO's signature low-profile design and offers users selectable color temperature options (2700K, 3000K, 3500K and 4000K) via a switch. The integrated driver allows operation at 120V and 277V with various back and side wiring options. Available in multiple lengths, the HALO system can be configured to fit almost any space. With a motion sensor or USB port as standard options, customers can maximize utility and efficiency from their undercabinet fixture.



HU30BSC18P



HU30ADV18MB




Recessed

Catalog Number	Product Description	Finish	Length	Replaces Up To	Selectable CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
HU30SCT09P	Low Profile, Dimming	White	9"	15W INC	2700K-4000K	120-277V	222	4	1008	080083797868	2308975
HU30SCT09MB	Low Profile, Dimming	Black	9"	15W INC	2700K-4000K	120-277V	222	4	1008	080083797882	2308975
HU30BSC18P	Low Profile, Dimming, USB Port	White	18"	29W INC	2700K-4000K	120-277V	440	8	648	080083797905	
HU30BSC18MB	Low Profile, Dimming, USB Port	Black	18"	29W INC	2700K-4000K	120-277V	440	8	648	080083797943	
HU30ADV18P	Low Profile, Dimming, Motion Sensor	White	18"	29W INC	2700K-4000K	120-277V	440	8	648	080083797929	2310291
HU30ADV18MB	Low Profile, Dimming, Motion Sensor	Black	18"	29W INC	2700K-4000K	120-277V	440	8	648	080083797967	2310291
HU30ADV24P	Low Profile, Dimming, USB Port	White	24"	42W INC	2700K-4000K	120-277V	627	11	648	080083798001	2310169
HU30ADV24MB	Low Profile, Dimming, USB Port	Black	24"	42W INC	2700K-4000K	120-277V	627	11	648	080083798049	2310169
HU30BSC24P	Low Profile, Dimming, Motion Sensor	White	24"	42W INC	2700K-4000K	120-277V	627	11	648	080083797981	
HU30BSC24MB	Low Profile, Dimming, Motion Sensor	Black	24"	42W INC	2700K-4000K	120-277V	627	11	648	080083798025	
HU30BSC36P	Low Profile, Dimming, USB Port	White	36"	56W INC	2700K-4000K	120-277V	844	14	272	080083798063	
HU30BSC36MB	Low Profile, Dimming, USB Port	Black	36"	56W INC	2700K-4000K	120-277V	844	14	272	080083798100	
HU30ADV36P	Low Profile, Dimming, Motion Sensor	White	36"	56W INC	2700K-4000K	120-277V	844	14	272	080083798087	2310168
HU30ADV36MB	Low Profile, Dimming, Motion Sensor	Black	36"	56W INC	2700K-4000K	120-277V	844	14	272	080083798124	2310168
HU30BSC48P	Low Profile, Dimming, USB Port	White	48"	84W INC	2700K-4000K	120-277V	1,253	21	272	080083798148	
HU30BSC48MB	Low Profile, Dimming, USB Port	Black	48"	84W INC	2700K-4000K	120-277V	1,253	21	272	080083798186	
HU30ADV48P	Low Profile, Dimming, Motion Sensor	White	48"	84W INC	2700K-4000K	120-277V	1,253	21	272	080083798162	2310292
HU30ADV48MB	Low Profile, Dimming, Motion Sensor	Black	48"	84W INC	2700K-4000K	120-277V	1,253	21	272	080083798209	2310292

# E Series Housings

## HALO

The E Series is a compact and efficient recessed housing family optimized and listed for EISA compliant tungsten-HALoGen lamps, as well as INC, CFL and LED lamps. The housings are suitable for new or retrofit residential or light commercial construction. The housings are designed for installation in insulated ceilings or non-insulated ceilings with airtight code compliant construction and can be used with a variety of trims and finishes to create different lighting effects or to match any decor. The family includes ultra-shallow housings for application with limited plenum space.



E27ICAT

E27RICAT



Catalog Number	Product Description	Socket	Lamp Source*	Voltage	Pallet Quantity	UPC
E27ICAT	6" IC, Shallow, New Construction	E26	HAL., INC., LED, CFL	120V	192	080083737604
E27RICAT	6" IC, Shallow, Remodel	E26	HAL., INC., LED, CFL	120V	192	080083737482
E4ICATSB	4" IC, Shallow, New Construction	E26	HAL., INC., LED, CFL	120V	108	080083751525
E4RTATSB	4" NON-IC Air-Tite, Remodel, w/Socket Bracket	E26	HAL., INC., LED, CFL	120V	168	080083751501
E4TATSB	4" NON-IC, Air-Tite, New Construction w/Socket Bracket	E26	HAL., INC., LED, CFL	120V	168	080083751488
E5ICAT	5" IC, Air-Tite, New Construction	E26	HAL., INC., LED, CFL	120V	144	080083737420
E5ICATNB	5" IC, Air-Tite, New Construction, No Socket Bracket	E26	HAL., INC., LED, CFL	120V	144	080083737390
E5RICAT	5" IC, Air-Tite, Remodel	E26	HAL., INC., LED, CFL	120V	180	080083737307
E750ICAT	6" IC, Air-Tite, LED New Construction	Quick Connect (No Socket)	LED Modules	120-277V	144	080083775040
E750RICAT	6" IC, Air-Tite, LED Remodel	Quick Connect (No Socket)	LED Modules	120-277V	144	080083778584
E7ICAT	6" IC, Air-Tite, New Construction Housing	E26	HAL., INC., LED, CFL	120V	144	080083737727
E7ICATNB	6" IC, AIRTITE, New Construction, No Socket Bracket	E26	HAL., INC., LED, CFL	120V	144	080083737697
E7RICAT	6" IC, Air-Tite, Remodel	E26	HAL., INC., LED, CFL	120V	144	080083737543

Note: Lamps not included.

## 4", 5" and 6" Trims

### HALO

Baffle, Gimbal, Coilex, Splay, Cone, Slope and Open Socket baffle trims are an ideal solution to shape light to minimize aperture glare and reduce ceiling brightness. Open trims focus the downlighting beam to provide uniform distribution. The trims can be used in new construction and remodel housings. The lensed shower trims are wet location listed.




Catalog Number	Product Description	Finish	Lamp Source*	Pallet Quantity	UPC
4001WB	4" Step Baffle - Plastic	White	HALOgen, INC, LED, CFL	960	080083745869
993W	4" Coilex Baffle	White	HALOgen, INC, LED, CFL	840	080083628483
5001P	5" Metal Splay Baffle	White	HALOgen, INC, LED, CFL	360	662400602729
5125WB	5" Full Cone Baffle	White	HALOgen, INC, LED, CFL	288	080083743162
300P	6" Open - Socket Supporting	White	HALOgen, INC, LED, CFL	450	662400302421
30WAT	6" Air-Tite Baffle	White	HALOgen, INC, LED, CFL	540	662400603320
310W	6" Coilex Baffle	White	HALOgen, INC, LED, CFL	540	080083515882
456W	6" Baffle for Slope Ceiling	White	HALOgen, INC, LED, CFL	360	662400676287
6100WB	6" Tapered Metal Baffle, 2-Rings Narrow & Wide	White	HALOgen, INC, LED, CFL	1,080	080083743452
6125WB	6" Full Cone Baffle	White	HALOgen, INC, LED, CFL	432	080083742912

Note: Lamps not included.

# H Series Housings

## HALO

The H Series is the standard in the industry for both commercial and residential applications. Optimized and listed for EISA compliant tungsten-HALOgen lamps, as well as Incandescent, CFL and LED lamps. For installation in insulated ceilings and non-insulated ceilings with airtight code compliant construction. Use with a variety of trims and finishes to create different lighting effects or to match any decor. The wide variety of trims available allows a number of different lighting effects to be created.



H271CAT



H27RICAT

Recessed


Catalog Number	Product Description	Socket	Lamp Source*	Voltage	Pallet Quantity	UPC
H1499ICAT	4" IC Air-Tite, 12V Low Voltage	GU5.3	HAL., INC., LED, CFL	120V	40	080083584079
H245ICAT	4" New Construction Ultra Shallow	Quick Connect (No Socket)	LED Modules	120/277V	180	080083770717
H245RICAT	4" Remodel Ultra Shallow	Quick Connect (No Socket)	LED Modules	120-277V	540	080083756520
H2750ICAT	6" New Construction, Shallow, IC Air-Tite	Quick Connect (No Socket)	LED Modules	120/277V	144	080083618163
H271CAT	6" New Construction, Shallow Ceiling, IC Air-Tite	E26	HAL., INC., LED, CFL	120V	144	662400605898
H27RICAT	6" Remodel, Shallow Ceiling, IC Air-Tite	E26	HAL., INC., LED, CFL	120V	180	080083609253
H550ICAT	5" New Construction, IC Air-Tite	Quick Connect (No Socket)	LED Modules	120/277V	120	080083626533
H550RICAT	5" Remodel, IC Air-Tite	Quick Connect (No Socket)	LED Modules	120/277V	144	080083626557
H51CAT	5" New Construction, IC Air-Tite	E26	HAL., INC., LED, CFL	120V	120	080083609413
H51CATNB	5" New Construction, IC Air-Tite, No Socket Bracket	E26	HAL., INC., LED, CFL	120V	120	080083756063
H51RICAT	5" Remodel, IC Air-Tite	E26	HAL., INC., LED, CFL	120V	144	080083609444
H750ICAT	6" New Construction, IC Air-Tite	Quick Connect (No Socket)	LED Modules	120/277V	120	623961872655
H750RICAT	6" Remodel, IC Air-Tite	Quick Connect (No Socket)	LED Modules	120/277V	144	623961052248
H71CAT	6" New Construction, IC Air-Tite	E26	HAL., INC., LED, CFL	120V	120	080083609628
H71CATNB	6" New Construction, IC Air-Tite, No Socket Bracket	E26	HAL., INC., LED, CFL	120V	120	662400612032
H71ICT	6" New Construction, IC	E26	HAL., INC., LED, CFL	120V	120	080083609680
H71ICTNB	6" New Construction, IC, No Socket Bracket	E26	HAL., INC., LED, CFL	120V	120	662400608523
H71RICAT	6" Remodel, IC Air-Tite	E26	HAL., INC., LED, CFL	120V	144	662400610588
H71RICT	6" Remodel, IC	E26	HAL., INC., LED, CFL	120V	144	662400600718
H995ICAT	4" New Construction, IC Air-Tite, Shallow	Quick Connect (No Socket)	LED Modules	120/277V	144	080083616930
H995RICAT	4" Remodel, IC Air-Tite, Shallow	Quick Connect (No Socket)	LED Modules	120/277V	162	080083616947
H991CAT	4" New Construction, IC Air-Tite, Shallow	E26	HAL., INC., LED, CFL	120V	144	080083582259
H99RTAT	4" Remodel, Non-IC, Air-Tite, Shallow	E26	HAL., INC., LED, CFL	120V	252	080083584369
H99TAT	4" New Construction, Non-IC, Air-Tite, Shallow	E26	HAL., INC., LED, CFL	120V	168	080083584260

Note: Lamps not included.

## E44 Housings

### HALO

The E44 Series is a compact and efficient recessed housing family optimized for use with LED, MR16 and PAR16 lamps (not included). The housings are suitable for new or retrofit residential or light commercial construction. The housings are designed for installation in insulated ceilings or non-insulated ceilings with airtight code compliant construction and can be used with a variety of trims and finishes to create different lighting effects or to match any decor.



E44MR16ICAT

E44MR16RICAT

Catalog Number	Product Description	Socket	Lamp Source*	Pallet Quantity	UPC
E44MR16ICAT	4" Ultra Shal, ICAT	Gx5.3/bi-pin 12V LED MR16	LED	192	080083818327
E44MR16RICAT	4" Ultra Shal Remodel, ICAT	Gx5.3/bi-pin 12V LED MR16	LED	630	080083818341
E44PAR16ICAT	4" Ultra Shal, ICAT	GU10/120V LED PAR16	LED, HAL	192	080083818785
E44PAR16RICAT	4" Ultra Shal Remodel, ICAT	GU10/120V LED PAR16	LED, HAL	630	080083818822

Note: Lamps not included.

## 4" Trims for MR/PAR16 Lamps

### HALO

The E44 series of round and square aperture trims are designed for use with HALO E44 series housings and optimized for use with LED, MR16 and PAR16 lamps (not included). An ideal solution to shape light to minimize aperture glare and reduce ceiling brightness, the family includes many trim types and finishes including Open, Lens and Lens Wall Wash available in White, Black with some models offered in Brushed Nickel and German Bronze. The lensed trims are wet location listed.



1440H



1441WBWF



1442H



1444MW

Catalog Number	Product Description	Finish	Lamp Source	Pallet Quantity	UPC
1440H	4" Conical Ref, Open	Haze	LED; HALOgen PAR16	168	080083820726
1440HWF	4" Conical Ref, Open	Haze, White Flange	LED; HALOgen PAR16	168	080083820740
1440MWWF	4" Conical Ref, Open	Matte White, White Flange	LED; HALOgen PAR16	168	080083820702
1441WBWF	4" Conical Baf, Open	White Baffle, White Flange	LED; HALOgen PAR16	168	080083820900
1442H	4" Conical Lens Wall Wash	Haze	LED; HALOgen PAR16	168	080083821006
1442HWF	4" Conical Lens Wall Wash	Haze, White Flange	LED; HALOgen PAR16	168	080083821020
1442MWWF	4" Conical Lens Wall Wash	Matte White, White Flange	LED; HALOgen PAR16	168	080083820986
1443H	4" Conical Ref, Diffuse Lens	Haze	LED; HALOgen PAR16	168	080083821068
1443HWF	4" Conical Ref, Diffuse Lens	Haze, White Flange	LED; HALOgen PAR16	168	080083821082
1443MWWF	4" Conical Ref, Diffuse Lens	Matte White, White Flange	LED; HALOgen PAR16	168	080083821044
1444MW	4" Rnd Pinhole, Open	Matte White	LED; HALOgen PAR16	168	080083821143
1445MWWB	4" Rnd Pinhole w/Oculus	White Baffle, White Flange	LED; HALOgen PAR16	168	080083821228
1446MWWB	4" Rnd Pinhole, Lens Wall Wash	White Baffle, White Flange	LED; HALOgen PAR16	168	080083821303
1447MWWB	4" Rnd Pinhole, Diffuse Lens	White Baffle, White Flange	LED; HALOgen PAR16	168	080083821341
1449AAG	4" Rnd All Acrylic Glass, Diffuse Lens	Acrylic Glass	LED; HALOgen PAR16	360	080083821426
1484MW	4" Sq Pinhole, Open	Matte White	LED; HALOgen PAR16	168	080083821440
1485MWWB	4" Sq Pinhole w/Oculus	Matte White, White Baffle	LED; HALOgen PAR16	168	080083821525
1486MWWB	4" Sq Pinhole, Lens Wall Wash	Matte White, White Baffle	LED; HALOgen PAR16	168	080083821600
1487MWWB	4" Sq Pinhole, Diffuse Lens	Matte White, White Baffle	LED; HALOgen PAR16	168	080083821648
1489AAG	4" Sq All Acrylic Glass, Diffuse Lens	Acrylic Glass	LED; HALOgen PAR16	360	080083821723

Note: Lamps not included.

