







58351-1/2

58351-B-1/4  
"B" bracket  
recessed 1/4"


58361-1/2





58361-3/4

58361-V-1/2  
"CV" bracket  
recessed 1/2"


58371-1/2



58371-3/4

58371-T-1/2  
"T" bracket  
recessed 3/8"58371-V-1/2  
"CV" bracket  
recessed 1/2"

59361-1/2



59361-3/4

## 4" x 2 1/8" Utility Boxes

Cat. No.	Brkts.	Knockouts			Std. Ctn.
		Ea. Side Conduit	Ea. End Conduit	Bottom Conduit	
<b>1 1/2" deep—with conduit KOs—10.3 cubic inch capacity</b>					
58351-1/2*	—	3-1/2"	1-1/2"	2-1/2"	50
58351-B-1/4	B	3-1/2"	1-1/2"	2-1/2"	25
<b>1 7/8" deep—with conduit KOs—13.0 cubic inch capacity</b>					
58361-1/2*	—	3-1/2"	1-1/2"	2-1/2"	50
58361-3/4	—	2-3/4"	1-3/4"	2-3/4"	50
58361-V-1/2*	CV	3-1/2"	1-1/2"	2-1/2"	50
<b>2 1/8" deep—with conduit KOs—14.5 cubic inch capacity</b>					
58371-1/2*	—	3-1/2"	1-1/2"	2-1/2"	50
58371-3/4	—	2-3/4"	1-3/4"	2-3/4"	50
58371-T-1/2*	T	3-1/2"	1-1/2"	2-1/2"	25
58371-V-1/2-25*	CV	3-1/2"	1-1/2"	2-1/2"	25

\* Factory provided raised ground screw location.

## 4" x 2 1/8" Utility Box Extension Rings

Cat. No.	Knockouts		Std. Ctn.
	Ea. Side Conduit	Ea. End Conduit	
<b>1 7/8" deep—with conduit KOs—13.0 cubic inch capacity</b>			
59361-1/2	3-1/2"	1-1/2"	50
59361-3/4	2-3/4"	1-3/4"	25