


LED Outdoor



WAC LIGHTING
Responsible Lighting[®]

Endurance WAC LIGHTING



LED technology offers superior alternatives to conventional Halogen and HID sources. With diecast aluminum factory sealed housings Endurance provides durable performance for years. Patent pending design for a water and dust proof, IP66 rated luminaire.

Thermal engineering for 100,000 hours of rated life, eliminating the need for maintenance once installed. Thoughtful details include a built-in level and factory sealed light engine.



Dark Sky Friendly



Factory-Sealed Fixture Housing
Protects LEDs From Environmental Factors



LED Performs Efficiently
In Cold Weather With Added Lifespan



Aluminum

Durable Die-Cast Aluminum



Motion and Photocell Sensor Ready



IP66, WET

IP 66 Rated
Dust Tight, Waterproof





ENERGY STAR® Rated



ETL Listed



DLC Certified


	Motion Sensor (120V)	MS-120	BZ Bronze GY Gray WT White
	Photocell Sensor (120V)	PC-120	

Example: **MS-120-WT**



5 Year WAC Product Warranty

- 3 Outputs
- 2 Color Temperatures
- 1 Size




Endurance Fin

CRI: 85
Rated Life: 100,000 hours




- Factory-Sealed LED Light Engine
- IP66 and ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- 20° Forward Throw Illumination
- Photocell/Motion Sensor Sold Separately
- Built-in Level For Easy Adjustment
- Universal Voltage (120V - 277V)
- Dimming: ELV (120V) or 0-10V

	Power	Comparable	Max Lumen	Color Temp	Finish
	WP-LED119 19W	39W HID	1460	30 3000K 50 5000K	BZ Bronze GH Graphite WT White
	WP-LED127 27W	70W HID	2135		
	WP-LED135 35W	100W HID	2825		

Example: **WP-LED119-30-WT**




For Direct and Indirect Illumination
Mounts In Any Orientation




Endurance Hawk

CRI: 85
Rated Life: 100,000 hours



- Factory-Sealed LED Light Engine
- IP66 and ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- 20° Forward Throw Illumination
- Photocell/Motion Sensor Sold Separately
- Built-in Level For Easy Adjustment
- Universal Voltage (120V - 277V)
- Dimming: ELV (120V) or 0-10V

	Power	Comparable	Max Lumen	Color Temp	Finish
	WP-LED219 19W	39W HID	1435	30 3000K	BZ Bronze
	WP-LED227 27W	70W HID	2095	50 5000K	GH Graphite
					WT White

Example: **WP-LED219-30-WT**



360° Horizontal Rotation
90° Vertical Aiming






Endurance Flood

CRI: 85
Rated Life: 60,000 hours

Includes Two Canopy Accessories for Surface Mount or Recessed Junction Boxes


- Factory-Sealed LED Light Engine
- IP66 and ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- Photocell/Motion Sensor Sold Separately
- Smooth and Continuous ELV Dimming



	Power	Comparable	Max Lumen	Color Temp	Finish
	WP-LED335 35W	100W HID	2070	30 3000K	BZ Bronze
				50 5000K	WT White

Example: **WP-LED335-30-WT**








Tube

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- Dimming: ELV (120V) or 0-10V



Distribution	Beam	Voltage	Watt	Lumens	Finish
 Wall Mount Single Light (Dark sky, ADA)	78°	120V - 277V	16W	824	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White
 Wall Mount Double Light (ADA)	78°	120V - 277V	30W	1526	


Example: **WS-W2609-WT**





Tube

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours


- IP65 Rated, ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- Dimming: ELV (120V) or 0-10V



Distribution	Beam	Voltage	Watt	Lumens	Finish
 Wall Mount Single Light (Dark sky)	35°	120V	16W	803	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White
 Wall Mount Double Light	35°	120V - 277V	30W	1748	

Example: **WS-W2604-BZ**






Tube

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours



- IP65 Rated, ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- Dimming: ELV (120V) or 0-10V



FM-W2612



FM-W2605

Distribution	Beam	Voltage	Watt	Lumens	Finish	
 Ceiling Mount Down	FM-W2612	31°	120V - 277V	30W	1741	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White
 Ceiling Mount Down	FM-W2605	35°	120V	16W	803	


Example: **FM-W2612-GH**




Tube

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- Dimming: ELV (120V) or 0-10V





PD-W2605

Distribution	Beam	Voltage	Watt	Lumens	Finish	
 Pendant Down	PD-W2605	35°	120V	16W	803	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White

Example: **PD-W2605-BK**








Scoop

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- Universal Voltage (120V - 277V)
- Dimming: ELV (120V) or 0-10V



Distribution Beam Voltage Watt Lumens Finish

	Wall Mount (ADA)	WS-W20506	86°	120V - 277V	16W	807	AL Brushed Aluminum	
							BK Black	
							BZ Bronze	
							GH Graphite	
							WT White	

Example: **WS-W20506-BZ**






Rubix

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- Universal Voltage (120V - 277V)
- Dimming: ELV (120V) or 0-10V





Distribution Beam Voltage Watt Lumens Finish

	Wall Mount Down (Dark sky, ADA)	WS-W2509	86°	120V - 277V	16W	807	AL Brushed Aluminum	
							BK Black	
	Wall Mount Up & Down (ADA)	WS-W2510	86°	120V - 277V	30W	1384	BZ Bronze	
							GH Graphite	
							WT White	

Example: **WS-W2510-GH**







Rubix

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- Universal Voltage (120V - 277V)
- Dimming: ELV (120V) or 0-10V



Distribution	Beam	Voltage	Watt	Lumens	Finish
 Wall Mount Single Light (Dark sky)	WS-W2504	88°	120V - 277V	16W	752
 Wall Mount Double Light	WS-W2505	88°	120V - 277V	30W	1401
					AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White


Example: **WS-W2504-GH**





Rubix

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- Die-Cast Aluminum Construction
- Universal Voltage (120V - 277V)
- Dimming: ELV (120V) or 0-10V



Distribution	Beam	Voltage	Watt	Lumens	Finish
 Ceiling Mount Down	FM-W2505	88°	120V - 277V	16W	701
 Ceiling Mount Down	FM-W2510	97°	120V - 277V	30W	1876
					AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White


Example: **WS-W2510-WT**







Janus

Color Temp: 3000K
 CRI: 90
 Dimming: 100% – 10%
 Rated Life: 80,000 hours




- IP65 Rated, ETL & cETL Wet Location Listed
- Indirect Light for Architectural Illumination
- 120V Direct Wire - No Driver Needed
- Aluminum Construction
- Weatherproof Polyester Powder Coat Finishes
- Smooth and Continuous ELV Dimming



	Length	Watt	Lumens	Finish
	12"	WS-W5812	15W 340	BZ Bronze GH Graphite WT White 
	17"	WS-W5817	19W 605	
	22"	WS-W5822	30W 960	


Example: **WS-W5822-GH**
 For 277V, add an "F" before the finish: **WS-W5822F-GH**

Rectangular Step and Wall Lights LEDme®



- Power:** 3.9W
Lumens: Up to 68
CRI: 85
Rated Life: 40,000 hours
- Die-cast aluminum with Weatherproof Polyester Power Coat
 - 316 marine grade stainless steel (SS finish)
 - 120V or 277V Direct Wire - No Driver Needed
 - Fits into 2" X 4" J-Box with minimum inside dimensions of 3"x2"x2"
 - IP66, wet location rated for indoor and outdoor installations*
 - Smooth and continuous ELV dimming

*Finishes are not recommended for contact with chemicals or sustained contact with water. Use Stainless Steel for harsh environments.

System	Color	Finish
WL-LED100 WL-LED100F	<i>Horizontal Scoop, 120V</i> <i>Horizontal Scoop, 277V</i>	SS Stainless Steel BK Black WT White BN Brushed Nickel BZ Bronze 
WL-LED200 WL-LED200F	<i>Vertical Scoop, 120V</i> <i>Vertical Scoop, 277V</i>	
C White 3000K AM Amber RD Red BL Blue		

Example: **WL-LED100F-C-SS**

For Our Complete Line of LED Outdoor
Please Visit www.waclighting.com/outdoor

WAC LIGHTING
Responsible Lighting®