

Part # Reference List

Part Number	Model Number	General Characteristics					Mechanical Package	Features
		Base Model	Operating Mode	Output Voltage	Output Current	Output Power		
20-4388	M9-A12-0500	M9-A	CC	11-12V	500mA	10-Watts	Small Rectangle	AC Dimm +®
20-4385	M9-A12-0600	M9-A	CC	10-12V	600mA	10-Watts	Small Rectangle	AC Dimm +®
20-4315	M9-A12-0700	M9-A	CC	8-12V	700mA	10-Watts	Small Rectangle	AC Dimm +®
20-4332	M9-A12-0750	M9-A	CC	8-12V	750mA	10-Watts	Small Rectangle	AC Dimm +®
20-4333	M9-A18-0500	M9-A	CC	11-18V	500mA	10-Watts	Small Rectangle	AC Dimm +®
20-4302	M9-A24-0350	M9-A	CC	15-24V	350mA	10-Watts	Small Rectangle	AC Dimm +®
20-4303	M9-A24-0375	M9-A	CC	15-24v	375mA	10-Watts	Small Rectangle	AC Dimm +®
20-4334	M9-A30-0300	M9-A	CC	18-30V	300mA	10-Watts	Small Rectangle	AC Dimm +®
20-4335	M9-A36-0250	M9-A	CC	22-36V	250mA	10-Watts	Small Rectangle	AC Dimm +®
20-4336	M9-A42-0220	M9-A	CC	25-42v	220mA	10-Watts	Small Rectangle	AC Dimm +®
20-4337	M9-A48-0190	M9-A	CC	29-48V	190mA	10-Watts	Small Rectangle	AC Dimm +®
20-4373	M9-U12-0350	M9-U	CC	9-12V	350mA	10-Watts	Small Rectangle	AC Dimm®
20-4555	M9-U12-0500	M9-U	CC	9-12V	500mA	10-Watts	Small Rectangle	AC Dimm®
20-4352	M9-U12-0700	M9-U	CC	8-12V	700mA	10-Watts	Small Rectangle	AC Dimm®
20-4321	M9-U12-0750	M9-U	CC	8-12V	750mA	10-Watts	Small Rectangle	AC Dimm®
20-4540	M9-U18-0350	M9-U	CC	12-18V	350mA	10-Watts	Small Rectangle	AC Dimm®
20-4355	M9-U18-0500	M9-U	CC	11-18V	500mA	10-Watts	Small Rectangle	AC Dimm®
20-4372	M9-U22-0415	M9-U	CC	14-22V	415mA	10-Watts	Small Rectangle	AC Dimm®
20-4532	M9-U24-0120	M9-U	CC	16-24V	120mA	10-Watts	Small Rectangle	AC Dimm®
20-4533	M9-U24-0220	M9-U	CC	16-24V	220mA	10-Watts	Small Rectangle	AC Dimm®
20-4356	M9-U24-0350	M9-U	CC	17-42V	350mA	10-Watts	Small Rectangle	AC Dimm®
20-4323	M9-U24-0375	M9-U	CC	15-24V	375mA	10-Watts	Small Rectangle	AC Dimm®
20-4564	M9-U24-0375-XP	M9-U	CC	16-24V	375mA	10-Watts	Small Rectangle	AC Dimm®
20-4517	M9-U24-0420-XP	M9-U	CC	16-24V	420mA	10-Watts	Small Rectangle	AC Dimm®
20-4535	M9-U28-0350-XP	M9-U	CC	17-28V	350mA	10-Watts	Small Rectangle	AC Dimm®
20-4544	M9-U30-0175	M9-U	CC	23-30V	175mA	10-Watts	Small Rectangle	AC Dimm®
20-4324	M9-U30-0300	M9-U	CC	18-30V	300mA	10-Watts	Small Rectangle	AC Dimm®
20-4545	M9-U36-0175-XP	M9-U	CC	26-36V	175mA	10-Watts	Small Rectangle	AC Dimm®
20-4552	M9-U36-0250-XP	M9-U	CC	22-36V	250mA	10-Watts	Small Rectangle	AC Dimm®
20-4565	M9-U42-0150	M9-U	CC	33-42V	150mA	10-Watts	Small Rectangle	AC Dimm®
20-4549	M9-U42-0200-XP	M9-U	CC	33-42V	200mA	10-Watts	Small Rectangle	AC Dimm®
20-4326	M9-U42-0220	M9-U	CC	25-42V	220mA	10-Watts	Small Rectangle	AC Dimm®
20-4327	M9-U48-0190	M9-U	CC	29-48V	190mA	10-Watts	Small Rectangle	AC Dimm®

Model Number Structure:

M 9 - U 24 - 0375 - XP

1. 2. - 3. 4. - 5. - 6.

- | | |
|-------------------------------|--|
| 1. Product Family: | M = Multi-Purpose Family |
| 2. Output Power: | 9 = 10-Watts Max |
| 3. Input Voltage: | A = 120VAC Only
E = 240VAC Only
U = 100-277VAC |
| 4. Output Voltage: | 12, 18, 24, 30, 36, 42, & 48VDC |
| 5. Output Current: | 0375 = 375mA |
| 6. Mechanical Package: | Blank = Plastic, 5VA Flamability Rating, XP = Plastic, V0 Flamability Rating |

Important Notes:

- A This list intended as a Part Number Reference List as such is for reference use only. New part numbers are added on a continuous basis.
- B In the event the model # or characteristics you are looking are not found on this part# list please contact your Magtech Sales Application
- C **Output Power:** Is the maximum driver Output Power Rating as defined per our UL certification.
- D **Mechanical Package:** Please refer to the Case Drawings located in the Product Documentation section of the Technical Library.

E Standard Features:

AC Dimm +®

A & E versions come standard with both AC Leading Edge Dimming (for TRIAC Dimming Controls) & AC Trailing Edge Dimming (for ELV Dimming Controls)

AC Dimm®

U versions come standard with AC Trailing Edge Dimming (for ELV Dimming Controls)