

A23 25W 277V E26 TITANIUM LED SERIES



PRO



Optional Lamp Extender

25W REPLACES



200W Inc.

80% Energy Savings

- Direct line voltage 120-277V - Not compatible with ballasts
- Omnidirectional: 290° beam angle
- Exceptional efficacy 132 LPW in Cool White
- Frosted diffuser maintains low glare
- Optional lamp extender available for use in larger fixtures
- Suitable for use in totally enclosed fixtures



A23 PRODUCT FEATURES


Suitable for Enclosed Fixtures



This A23 lamp replaces a 200W Inc. and is suitable for use in enclosed fixtures. Its high lumen output and exceptional efficacy make it an ideal choice for bollard, post top, low bay and other outdoor applications. An optional lamp extender is also available for use in larger fixtures.

Omnidirectional Lighting

This A23 emits 290° of uniform light and meets ENERGY STAR requirements. Its compact form factor and omnidirectional output provides a fuller distribution than other LED lamps.



A23 25W 277V E26 TITANIUM LED SERIES




APPLICATIONS

Bollard Lighting



Post Top Lighting



Low Bay Lighting



SPECIFICATIONS

| Product | 97972 | 97973 | 97974 |
|------------------------------------|------------------------|------------------------|------------------------|
| Model | 25HID/830/277V/E26 | 25HID/840/277V/E26 | 25HID/850/277V/E26 |
| Type | A23 | A23 | A23 |
| Base | E26 | E26 | E26 |
| Power (W) | 25 | 25 | 25 |
| Voltage - Frequency | 120-277V 50/60Hz | 120-277V 50/60Hz | 120-277V 50/60Hz |
| Color Temp. (ANSI) | Warm White 3000K | Cool White 4000K | Daylight 5000K |
| CRI (Ra) (typ.) | 82 | 82 | 82 |
| Typical lumens (lm) | 3200 | 3300 | 3400 |
| Efficacy (LPW) | 128 | 132 | 136 |
| Beam Angle | 290° | 290° | 290° |
| Dimmable | No | No | No |
| Power Factor | 0.9 | 0.9 | 0.9 |
| Rated Lifetime - L70 (hrs.) | 50,000 | 50,000 | 50,000 |
| Temperature Rating | -4°F/-20°C - 95°F/35°C | -4°F/-20°C - 95°F/35°C | -4°F/-20°C - 95°F/35°C |
| Dia. x MOL | 3.23"x6.34" (82x161mm) | 3.23"x6.34" (82x161mm) | 3.23"x6.34" (82x161mm) |
| Weight (lb. / g) | 1.04lb. / 470g | 1.04lb. / 470g | 1.04lb. / 470g |

* Suitable for use in totally enclosed fixtures

** Suitable for damp locations. Not for use where directly exposed to weather or water

Ref.#: DS2-46-A23-LED-25W-277V-E26-020818