

Halogen Lamps

Single Ended Halogen Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
Q250CL/DC-130V	15264	250	130	T-4	DC Bayonet (BA15d)	CC-8	3.00/76.2	0.52/13.0	2000
Q250CL/MC-120V	49609	250	120	T-4	Miniature Candelabra Screw (E11)	CC-8	3.15/80.0	0.52/13.0	2000
Q250CL/MC-130V	15268	250	130	T-4	Miniature Candelabra Screw (E11)	CC-8	3.15/80.0	0.52/13.0	2000
Q250DC-120V	49607	250	120	T-4 1/4	DC Bayonet (BA15d)	CC-8	3.15/80.0	0.55/14.0	2000
Q250DC-130V	15266	250	130	T-4	DC Bayonet (BA15d)	CC-8	3.00/76.2	0.52/13.0	2000
Q250MC-120V	49608	250	120	T-4	Miniature Candelabra Screw (E11)	CC-8	3.19/81.0	0.52/13.0	2000
Q250MC-130V	15270	250	130	T-4	Miniature Candelabra Screw (E11)	CC-8	3.19/81.0	0.52/13.0	2000
Q500/MC-120V	49612	500	120	T-4	Miniature Candelabra Screw (E11)	CC-8	3.75/95.3	0.52/13.0	1700
Q500/MC-130V	49614	500	130	T-4	Miniature Candelabra Screw (E11)	CC-8	3.75/95.3	0.52/13.0	1700
Q500CL/DC-120V	15282	500	120	T-4	DC Bayonet (BA15d)	CC-8	3.75/95.3	0.59/15.0	1700
Q500CL/DC-120V	49613	500	120	T-4	Miniature Candelabra Screw (E11)	CC-8	3.75/95.3	0.55/14.0	1700
Q500CL/MC-130V	49615	500	130	T-4	Miniature Candelabra Screw (E11)	CC-8	3.75/95.3	0.52/13.0	1700
Q500DC-120V	15284	500	120	T-4	DC Bayonet (BA15d)	CC-8	3.75/95.3	0.59/15.0	1700

Double Ended Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
Q100T3/CL/120V	15159	100	120	T-3	Recessed Single Contact (R7s)	CC-8	4.69/119.1	0.40/10.0	2000
Q150T3/CL/120V	15161	150	120	T-3	Recessed Single Contact (R7s)	CC-8	4.69/119.1	0.40/10.0	2000
Q250T3/CL/120V	15162	250	120	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q300T3/CL/120V	15164	300	120	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q300T3/CL/130V	15166	300	130	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q300T3/CL/220V	15168	300	220	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q300T3/CL/240V	00196	300	240	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q500T3/CL/120V	15170	500	120	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q500T3/CL/130V	15172	500	130	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q500T3/CL/220V	15174	500	220	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q500T3/CL/240V	15176	500	240	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q750T3/CL/120V	49568	750	120	T-3	Recessed Single Contact (R7s)	C-8	7.50/190.5	0.40/10.0	2000
Q750T3/CL/240V	15180	750	240	T-3	Recessed Single Contact (R7s)	C-8	7.50/190.5	0.40/10.0	2000
Q1000T3/CL/120V	49569	1000	120	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1000T3/CL/220V	15182	1000	220	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1000T3/CL/240V	15184	1000	240	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1000T3/CL/277V	15186	1000	277	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/120V	49570	1500	120	T-3	Recessed Single Contact (R7s)	CC-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/208V	15188	1500	208	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/220V	15190	1500	220	T-3	Recessed Single Contact (R7s)	CC-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/240V	15192	1500	240	T-3	Recessed Single Contact (R7s)	CC-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/277V	15194	1500	277	T-3	Recessed Single Contact (R7s)	CC-8	10.06/255.6	0.40/10.0	2000

Double Ended Short Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
Q100W/S120V	15200	100	120	T-2 1/2	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.315/8.0	2000
Q100W/S130V	15202	100	130	T-2 1/2	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.315/8.0	2000
Q150W/S120V	15206	150	120	T-2 3/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.344/8.74	2000
Q150W/S130V	15208	150	130	T-2 3/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.344/8.74	2000
Q200W/S120V	15211	200	120	T-2 3/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.344/8.74	2000
Q200W/S130V	15213	200	130	T-2 3/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.344/8.74	2000
Q200W/S220V	15209	200	220	T-2 3/4	Recessed Single Contact (R7s)	CC-8	3.15/80.0	0.344/8.74	2000
Q250W/S120V	49571	250	120	T-2 7/8	Recessed Single Contact (R7s)	CC-8	3.15/80.0	0.360/9.13	2000
Q300W/S120V	00019	300	120	T-2 7/8	Recessed Single Contact (R7s)	CC-8	3.15/80.0	0.360/9.13	2000
Q300W/S130V	15216	300	130	T-2 7/8	Recessed Single Contact (R7s)	CC-8	3.15/80.0	0.360/9.13	2000
Q400W/S130V	15221	400	130	T-3 1/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.406/10.32	2000

G4 Base 2-pin Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
JC12V5W-FR	81120	5	12	T-3	G4 (Sub-Miniature 2-Pin)	C-6	1.38/35.0	0.36/9.0	2000
JC12V20W	03510	20	12	T-3	G4 (Sub-Miniature 2-Pin)	C-6	1.38/35.0	0.36/9.0	50
JC12V30W	03520	30	12	T-3	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	50
JCD6V10WH20	15001	10	6	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	2000
JCD6V20WH20	15003	20	6	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	2000
JCD12V5WH20	15005	5	12	T-2 1/2	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.32/8.2	2000
JCD12V10WH20	15007	10	12	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	2000
JCD12V20WH20	15009	20	12	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	2000
JCD12V35WH20	49561	35	12	T-3 1/2	G4 (Sub-Miniature 2-Pin)	CC-6	1.22/31.0	0.36/9.0	2000
JCD24V20WH20	15011	20	24	T-3 1/4	G4 (Sub-Miniature 2-Pin)	CC-6	1.22/31.0	0.44/11.0	2000