

# New Products. Advanced Technology.




## 2018 New Product Stock Catalog & Promotion



**Metalux**



**Halo**



**Lumark**



**Sure-Lites**



**Greengate**



**Lighting solutions**

Q4 2018  
[eaton.com/npistock](http://eaton.com/npistock)

[www.eaton.com/npistock](http://www.eaton.com/npistock)



# We power what matters.\*



We make endless possibilities work by providing you with an innovative portfolio of lighting solutions for buildings, homes and communities including indoor and outdoor smart lighting solutions. Our products are designed to help create safer communities, simplify and personalize lighting for consumers' unique needs and help solve complex business challenges by applying data insights to make smarter business decisions. Whether you're planning for a new manufacturing facility, park or a new home community, Eaton has you covered.

To learn more visit [www.eaton.com/npistock](http://www.eaton.com/npistock)

## Table of Contents

|           |                           |           |                                                    |
|-----------|---------------------------|-----------|----------------------------------------------------|
| <b>4</b>  | <b>Halo Home</b>          | <b>16</b> | <b>Exit &amp; Emergency</b><br>Sure-Lites, ALL PRO |
| <b>6</b>  | <b>Recessed</b><br>Halo   | <b>18</b> | <b>Outdoor</b><br>Lumark, HALO                     |
| <b>14</b> | <b>Ambient</b><br>Metalux | <b>26</b> | <b>Controls</b><br>Greengate                       |



# HALOHOME™

Smart Lighting System



## HALO Home RL LED Bluetooth Recessed Downlight Module

### HALO

The HALO Home RL series integrated LED modules with Bluetooth mesh connectivity for 5/6-inch and 4-inch aperture recessed downlights. Pair with the HALO Home mobile app for wireless control and customization - ON/OFF, grouping, color tuning, dimming, scheduling, scenes and more. Add HALO Home wall controllers for expanded "smart" functionality. Suitable for new construction, remodel and retrofit installation, the RL series is designed to connect to the HALO Home Bluetooth network with no hub or internet connection required.



RL4069BLE40AWH



RL56069BLE40AWH

| Catalog Number  | Product Description         | Replaces Up To | CCT                    | Voltage | CRI | Lumens | Watts | Pallet Quantity | UPC          |
|-----------------|-----------------------------|----------------|------------------------|---------|-----|--------|-------|-----------------|--------------|
| RL4069BLE40AWH  | 4" LED Module, Bluetooth    | 60W INC        | Adjustable 2700K-5000K | 120V    | 90  | 600    | 8     | 588             | 080083809257 |
| RL56069BLE40AWH | 5"/6" LED Module, Bluetooth | 65W INC        | Adjustable 2700K-5000K | 120V    | 90  | 600    | 10    | 300             | 080083809233 |



# HALO Home FTS and MST LED Bluetooth Outdoor Flood and Motion Lighting

## HALO

The HALO Home FTS outdoor security smart LED floodlight and MST motion-activated floodlight enhances security around the home and can be controlled via Bluetooth mesh connectivity through the free HALO Home mobile app. Customers can control one or multiple lights with grouping, scheduling, dimming and color tuning capabilities.



FTS20CB



MST20C18B

| Catalog Number | Product Description               | Replaces Up To            | CCT                        | Voltage  | Lumens        | Watts | Pallet Quantity | UPC          |
|----------------|-----------------------------------|---------------------------|----------------------------|----------|---------------|-------|-----------------|--------------|
| MST20C18B      | Twin LED Flood, Bluetooth, Bronze | 2 - Head PAR 38, 90W INC. | Adjustable CCT 3000K-5000K | 120-277V | 2034 at 4000K | 23    | 240             | 080083810512 |
| MST20C18W      | Twin LED Flood, Bluetooth, White  | 2 - Head PAR 38, 90W INC. | Adjustable CCT 3000K-5000K | 120-277V | 2034 at 4000K | 23    | 240             | 080083810499 |
| FTS20CB        | Twin LED Flood, Bluetooth, Bronze | 2 - Head PAR 38, 90W INC. | Adjustable CCT 3000K-5000K | 120-277V | 2034 at 4000K | 23    | 180             | 080083810475 |
| FTS20CW        | Twin LED Flood, Bluetooth, White  | 2 - Head PAR 38, 90W INC. | Adjustable CCT 3000K-5000K | 120-277V | 2034 at 4000K | 23    | 180             | 080083810451 |

## HALO Home Smart Controls and Accessories

### HALO

The HALO Home dimmers and accessories allow for maximum control of a HALO Home smart lighting devices. The dimmer and accessories all connect to the HALO Home Bluetooth Mesh network with no hub or internet connection required. The In-Wall Smart Dimmer turns standard lights into smart lights. The In-Wall Accessory Dimmer controls a

HALO Home lighting devices from a central location. The Anyplace Dimmer lets customers control HALO Home smart lights and accessories from anywhere in the home without rewiring. The Internet Access Bridge enables customers to control HALO Home lighting devices from anywhere in the world and allows for Amazon Alexa and Google Assistant voice control.



HIWAC1BLE40AWH



HIWMA1BLE40AWH



HWAS1BLE40AWH



HWB1BLE40AWH

| Catalog Number | Product Description                        | Voltage  | Watts | Pallet Quantity | UPC          |
|----------------|--------------------------------------------|----------|-------|-----------------|--------------|
| HIWAC1BLE40AWH | In Wall Accessory Dimmer, White, Bluetooth | 120V     | 5     | 1792            | 080083826544 |
| HIWMA1BLE40AWH | In Wall Dimmer, White, Bluetooth           | 120V     | 5     | 1536            | 080083826520 |
| HWB1BLE40AWH   | Internet Access Bridge, White, Bluetooth   | 110/220V | N/A   | 576             | 080083811168 |
| HWAS1BLE40AWH  | Anyplace Dimmer, White, Bluetooth          | N/A      | N/A   | 1120            | 080083811182 |

# SeleCCTable Technology

SeleCCTable™ technology allows homeowners or contractors to easily switch between color temperatures all in the same fixture. Featuring five color temperatures in each fixture, the SeleCCTable fixtures allow distributors and contractors to stock one product instead of several, streamlining inventory and saving on space and cost. Easy color tuning also reduces callbacks for contractors, as customers can easily adjust the color if they change their mind.



seleCCTable™  
colors



Using the switch located on the back of the fixture, choose from a range of five color temperatures 2700K - 5000K.



warm

adjust  
temperature

cool



# RL LED SeleCCTable Baffle-Trim Modules

## HALO

- All-in-one 5 field seleCCTable CCTs with a simple switch
- Available in 4" and 5"/6"
- 600, 900 and 1200-lumen packages



RL4069S1EWH



RL56069S1EWH



| Catalog Number | Product Description                                               | Replaces Up To   | CCT                        | Voltage | Lumens        | Watts | Pallet Quantity | UPC          |
|----------------|-------------------------------------------------------------------|------------------|----------------------------|---------|---------------|-------|-----------------|--------------|
| RL4069S1EWH    | 4" SeleCCTable Retrofit Baffle-Trim, 600 Lumen, White, 90 CRI     | 65W INC at 3000K | Selectable CCT 2700K-5000K | 120V    | 575 at 3000K  | 8     | 504             | 080083816712 |
| RL4099S1EWH    | 4" SeleCCTable Retrofit Baffle-Trim, 900 Lumen, White, 90 CRI     | 65W INC at 3000K | Selectable CCT 2700K-5000K | 120V    | 915 at 3000K  | 12    | 504             | 080083816736 |
| RL56069S1EWH   | 5"/6" SeleCCTable Retrofit Baffle-Trim, 600 Lumen, White, 90 CRI  | 44W INC at 3000K | Selectable CCT 2700K-5000K | 120V    | 665 at 3000K  | 8     | 240             | 080083816750 |
| RL56099S1EWH   | 5"/6" SeleCCTable Retrofit Baffle-Trim, 900 Lumen, White, 90 CRI  | 63W INC at 3000K | Selectable CCT 2700K-5000K | 120V    | 940 at 3000K  | 12    | 240             | 080083818679 |
| RL56129S1EWH   | 5"/6" SeleCCTable Retrofit Baffle-Trim, 1200 Lumen, White, 90 CRI | 80W INC at 3000K | Selectable CCT 2700K-5000K | 120V    | 1221 at 3000K | 14    | 240             | 080083818693 |

# RA LED SeleCCTable Adjustable Gimbal Modules

## HALO

- Adjustable downlight
- Available in 4" and 5"/6"
- Field SeleCCTable with 5 CCT options



RA4069S1EWH



RA56069S1EWH



| Catalog Number | Product Description                                | Replaces Up To   | CCT                        | Voltage | Lumens       | Watts | Pallet Quantity | UPC          |
|----------------|----------------------------------------------------|------------------|----------------------------|---------|--------------|-------|-----------------|--------------|
| RA4069S1EWH    | 4" SeleCCTable Adjustable Gimbal, White, 90 CRI    | 41W INC at 3000K | Selectable CCT 2700K-5000K | 120V    | 615 at 3000K | 7     | 504             | 080083817887 |
| RA56069S1EWH   | 5"/6" SeleCCTable Adjustable Gimbal, White, 90 CRI | 41W INC at 3000K | Selectable CCT 2700K-5000K | 120V    | 630 at 3000K | 7     | 270             | 080083817900 |


# HLB Direct Mount LED Downlights

## HALO

- Available in 4" and 6" round
- Fixed 3000 and 4000K CCT
- All-in-one 5 field seleCCTable CCTs with a simple switch
- Remote driver junction box included
- No housing or J-Box needed



HLB4069FS1EMWR



HLB6099FS1EMWR



| Catalog Number | Product Description                                 | Replaces Up To | CCT                        | Voltage | Lumens        | Watts | Pallet Quantity | UPC          |
|----------------|-----------------------------------------------------|----------------|----------------------------|---------|---------------|-------|-----------------|--------------|
| HLB4069FS1EMWR | 4" Direct Mount Round Lens Downlight, White, 90 CRI | 48W at 3000K   | Selectable CCT 2700K-5000K | 120V    | 723 at 3000K  | 12    | 864             | 080083848140 |
| HLB6099FS1EMWR | 6" Direct Mount Round Lens Downlight, White, 90 CRI | 71W at 3000K   | Selectable CCT 2700K-5000K | 120V    | 1061 at 3000K | 16    | 450             | 080083848164 |

# BLD Surface LED Downlight

## HALO

- Available in 4" and 6"
- Dedicated 3000K CCT and field SeleCCTable with 5 CCT options.
- Low profile surface luminaire with wide distribution
- Fits most j-boxes and recessed housings



BLD406930WH



BLD606930WH



| Catalog Number | Product Description                                   | Replaces Up To | CCT                        | Voltage | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|-------------------------------------------------------|----------------|----------------------------|---------|--------|-------|-----------------|--------------|
| BLD406930WH    | 4" Surface Mount Downlight, White, 90 CRI             | 40W INC        | 3000K                      | 120V    | 690    | 8     | 648             | 080083826667 |
| BLD4089SWH     | 4" SeleCCTable Surface Mount Downlight, White, 90 CRI | 60W INC        | Selectable CCT 2700K-5000K | 120V    | 802    | 10    | 432             | 080083826681 |
| BLD606930WH    | 6" Surface Mount Downlight, White, 90 CRI             | 47W INC        | 300K                       | 120V    | 700    | 8     | 450             | 080083826704 |
| BLD6089SWH     | 6" SeleCCTable Surface Mount Downlight, White, 90 CRI | 60W INC        | Selectable CCT 2700K-5000K | 120V    | 812    | 10    | 300             | 080083826728 |



# HU10 & HU30 LED Undercabinets

## HALO

### HU10

- Fixed 2700, 3000 or 4000K CCT
- Cord and plug or direct wire

### HU30

- 4 SeleCCTable CCT settings
- Motion sensor or USB charging
- Universal voltage – commercial or residential



HU30BSC18P



HU30ADV18MB



Recessed

| Catalog Number | Product Description                          | Replaces Up To | CCT                        | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|----------------------------------------------|----------------|----------------------------|----------|--------|-------|-----------------|--------------|
| HU1009D930MBR  | HU10, 9", Dimmable, Black, 90 CRI            | 17W INC        | 3000K                      | 120V     | 248    | 4     | 576             | 080083748310 |
| HU1009D930PR   | HU10, 9", Dimmable, White, 90 CRI            | 17W INC        | 3000K                      | 120V     | 248    | 4     | 576             | 080083747436 |
| HU30SCT09MB    | HU30, 9", SeleCCTable, Black                 | 15W INC        | Selectable CCT 2700K-4000K | 120-277V | 222    | 4     | 1008            | 080083797882 |
| HU30SCT09P     | HU30, 9", SeleCCTable, White                 | 15W INC        | Selectable CCT 2700K-4000K | 120-277V | 222    | 4     | 1008            | 080083797868 |
| HU1018D930MBR  | HU10, 18", Dimmable, Black, 90 CRI           | 33W INC        | 3000K                      | 120V     | 495    | 7     | 336             | 080083748334 |
| HU1018D930PR   | HU10, 18", Dimmable, White, 90 CRI           | 33W INC        | 3000K                      | 120V     | 495    | 7     | 336             | 080083747450 |
| HU30ADV18MB    | HU30, 18", SeleCCTable, Motion Sensor, Black | 29W INC        | Selectable CCT 2700K-4000K | 120-277V | 440    | 8     | 648             | 080083797967 |
| HU30ADV18P     | HU30, 18", SeleCCTable, Motion Sensor, White | 29W INC        | Selectable CCT 2700K-4000K | 120-277V | 440    | 8     | 648             | 080083797929 |
| HU30BSC18MB    | HU30, 18", SeleCCTable, USB, Black           | 29W INC        | Selectable CCT 2700K-4000K | 120-277V | 440    | 8     | 648             | 080083797943 |
| HU30BSC18P     | HU30, 18", SeleCCTable, USB, White           | 29W INC        | Selectable CCT 2700K-4000K | 120-277V | 440    | 8     | 648             | 080083797905 |
| HU1024D930MBR  | HU10, 24", Dimmable, Black, 90 CRI           | 44W INC        | 3000K                      | 120V     | 660    | 7     | 224             | 080083748358 |
| HU1024D930PR   | HU10, 24", Dimmable, White, 90 CRI           | 44W INC        | 3000K                      | 120V     | 660    | 7     | 224             | 080083748280 |
| HU30BSC24MB    | HU30, 24", SeleCCTable, Motion Sensor, Black | 42W INC        | Selectable CCT 2700K-4000K | 120-277V | 627    | 11    | 648             | 080083798025 |
| HU30BSC24P     | HU30, 24", SeleCCTable, Motion Sensor, White | 42W INC        | Selectable CCT 2700K-4000K | 120-277V | 627    | 11    | 648             | 080083797981 |
| HU30ADV24MB    | HU30, 24", SeleCCTable, USB, Black           | 42W INC        | Selectable CCT 2700K-4000K | 120-277V | 627    | 11    | 648             | 080083798049 |
| HU30ADV24P     | HU30, 24", SeleCCTable, USB, White           | 42W INC        | Selectable CCT 2700K-4000K | 120-277V | 627    | 11    | 648             | 080083798001 |
| HU30ADV36MB    | HU30, 36", SeleCCTable, Motion Sensor, Black | 56W INC        | Selectable CCT 2700K-4000K | 120-277V | 844    | 14    | 272             | 080083798124 |
| HU30ADV36P     | HU30, 36", SeleCCTable, Motion Sensor, White | 56W INC        | Selectable CCT 2700K-4000K | 120-277V | 844    | 14    | 272             | 080083798087 |
| HU30BSC36MB    | HU30, 36", SeleCCTable, USB, Black           | 56W INC        | Selectable CCT 2700K-4000K | 120-277V | 844    | 14    | 272             | 080083798100 |
| HU30BSC36P     | HU30, 36", SeleCCTable, USB, White           | 56W INC        | Selectable CCT 2700K-4000K | 120-277V | 844    | 14    | 272             | 080083798063 |
| HU30ADV48MB    | HU30, 48", SeleCCTable, Motion Sensor, Black | 84W INC        | Selectable CCT 2700K-4000K | 120-277V | 1253   | 14    | 272             | 080083798209 |
| HU30ADV48P     | HU30, 48", SeleCCTable, Motion Sensor, White | 84W INC        | Selectable CCT 2700K-4000K | 120-277V | 1253   | 21    | 272             | 080083798162 |
| HU30BSC48MB    | HU30, 48", SeleCCTable, USB, Black           | 84W INC        | Selectable CCT 2700K-4000K | 120-277V | 1253   | 21    | 272             | 080083798186 |
| HU30BSC48P     | HU30, 48", SeleCCTable, USB, White           | 84W INC        | Selectable CCT 2700K-4000K | 120-277V | 1253   | 21    | 272             | 080083798148 |

# RLD LED Deep Baffle Downlight

## HALO

- Available in 4" and 6"
- White and black baffle included
- Dedicated CCT
- Regressed light source and increased optical cutoff



RLD4069301EWH



RLD6069301EWH



| Catalog Number | Product Description                | Replaces Up To | CCT   | Voltage | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|------------------------------------|----------------|-------|---------|--------|-------|-----------------|--------------|
| RLD4069301EWH  | 4" Deep Baffle-Trim, White, 90 CRI | 40W INC        | 3000K | 120V    | 681    | 9     | 420             | 080083823604 |
| RLD6069301EWH  | 6" Deep Baffle-Trim, White, 90 CRI | 40W INC        | 3000K | 120V    | 668    | 9     | 120             | 080083823642 |

# LA All-Purpose LED Adjustable Gimbal LED Modules

## HALO

- Easy to install retrofit kit
- Available in 4" and 5"/6"
- Supplied with torsion springs or friction blades to secure the trim tight to ceiling
- Diffuse lens provides shielding to the source
- Wet and Damp location listed
- Ideal for new construction or remodel applications



LA4069271EWH



LA56069271EWH

| Catalog Number | Product Description                    | Replaces Up To | CCT   | Voltage | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|----------------------------------------|----------------|-------|---------|--------|-------|-----------------|--------------|
| LA4069271EWH   | 4" Adjustable Gimbal, White, 90 CRI    | 40W INC        | 2700K | 120V    | 611    | 9     | 576             | 080083818129 |
| LA4069301EWH   | 4" Adjustable Gimbal, White, 90 CRI    | 40W INC        | 3000K | 120V    | 613    | 9     | 576             | 080083818143 |
| LA4069351EWH   | 4" Adjustable Gimbal, White, 90 CRI    | 40W INC        | 3500K | 120V    | 630    | 9     | 576             | 080083818167 |
| LA4069401EWH   | 4" Adjustable Gimbal, White, 90 CRI    | 40W INC        | 4000K | 120V    | 640    | 9     | 576             | 080083818181 |
| LA4069501EWH   | 4" Adjustable Gimbal, White, 90 CRI    | 40W INC        | 5000K | 120V    | 630    | 9     | 576             | 080083818204 |
| LA56069271EWH  | 5"/6" Adjustable Gimbal, White, 90 CRI | 40W INC        | 2700K | 120V    | 614    | 9     | 270             | 080083818228 |
| LA56069301EWH  | 5"/6" Adjustable Gimbal, White, 90 CRI | 40W INC        | 3000K | 120V    | 637    | 9     | 270             | 080083818242 |
| LA56069351EWH  | 5"/6" Adjustable Gimbal, White, 90 CRI | 40W INC        | 3500K | 120V    | 640    | 9     | 270             | 080083818266 |
| LA56069401EWH  | 5"/6" Adjustable Gimbal, White, 90 CRI | 40W INC        | 4000K | 120V    | 640    | 9     | 270             | 080083818280 |
| LA56069501EWH  | 5"/6" Adjustable Gimbal, White, 90 CRI | 40W INC        | 5000K | 120V    | 630    | 9     | 270             | 080083818303 |


# RSQ All-Purpose Square LED Downlights

## HALO

- Available in 4", 5" and 6"
- Dedicated CCT
- Square lens module provides a wide distribution pattern that works well in low to medium ceiling heights
- Use in Halo or compatible 4, 5, 6-inch housings
- Supplied with torsion springs or friction blades to secure the trim tight to ceiling



RSQ4089301EMWWB



RSQ5089271EMWWB



RSQ6TRMMW

Recessed

| Catalog Number  | Product Description                              | Replaces Up To | CCT   | Voltage | Lumens | Watts | Pallet Quantity | UPC          |
|-----------------|--------------------------------------------------|----------------|-------|---------|--------|-------|-----------------|--------------|
| RSQ4089271EMWWB | 4" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 2700K | 120V    | 807    | 9     | 672             | 080083824410 |
| RSQ4089301EMWWB | 4" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 3000K | 120V    | 814    | 9     | 672             | 080083824434 |
| RSQ4089351EMWWB | 4" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 3500K | 120V    | 825    | 9     | 672             | 080083824458 |
| RSQ4089401EMWWB | 4" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 4000K | 120V    | 835    | 9     | 672             | 080083824472 |
| RSQ5089271EMWWB | 5" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 2700K | 120V    | 813    | 9     | 360             | 080083824519 |
| RSQ5089301EMWWB | 5" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 3000K | 120V    | 837    | 9     | 360             | 080083824533 |
| RSQ5089351EMWWB | 5" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 3500K | 120V    | 828    | 9     | 360             | 080083824557 |
| RSQ5089401EMWWB | 5" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 4000K | 120V    | 840    | 9     | 360             | 080083824571 |
| RSQ6089271EMWWB | 6" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 2700K | 120V    | 835    | 9     | 240             | 080083824618 |
| RSQ6089301EMWWB | 6" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 3000K | 120V    | 844    | 9     | 240             | 080083824632 |
| RSQ6089351EMWWB | 6" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 3500K | 120V    | 835    | 9     | 240             | 080083824656 |
| RSQ6089401EMWWB | 6" Square LED Module, Baffle trim, White, 90 CRI | 60W INC        | 4000K | 120V    | 845    | 9     | 240             | 080083824670 |
| RSQ4TRMMW       | 4" White Paintable Splay trim                    | N/A            | N/A   | N/A     | N/A    | N/A   | 3780            | 080083840984 |
| RSQ4TRMSNB      | 4" Satin Nickel Baffle trim                      | N/A            | N/A   | N/A     | N/A    | N/A   | 3780            | 080083841004 |
| RSQ4TRMTBZB     | 4" Tuscan Bronze Baffle trim                     | N/A            | N/A   | N/A     | N/A    | N/A   | 3780            | 080083841028 |
| RSQ5TRMMW       | 5" White Paintable Splay trim                    | N/A            | N/A   | N/A     | N/A    | N/A   | 2520            | 080083841042 |
| RSQ5TRMSNB      | 5" Satin Nickel Baffle trim                      | N/A            | N/A   | N/A     | N/A    | N/A   | 2520            | 080083841066 |
| RSQ5TRMTBZB     | 5" Tuscan Bronze Baffle trim                     | N/A            | N/A   | N/A     | N/A    | N/A   | 2520            | 080083841080 |
| RSQ6TRMMW       | 6" White Paintable Splay trim                    | N/A            | N/A   | N/A     | N/A    | N/A   | 1800            | 080083841103 |
| RSQ6TRMSNB      | 6" Satin Nickel Baffle trim                      | N/A            | N/A   | N/A     | N/A    | N/A   | 1800            | 080083841127 |
| RSQ6TRMTBZB     | 6" Tuscan Bronze Baffle trim                     | N/A            | N/A   | N/A     | N/A    | N/A   | 1800            | 080083841141 |



# SMD 1200 LED Downlight Series

## HALO

- 6" round & square apertures
- 120-277V universal voltage - commercial or residential
- Versatile recessed housing mount options
- 0-10V dimming
- Available in 2700, 3000, 3500, 4000 or 5000K CCT



SMD6R12927WH



SMD6S12927WH

| Catalog Number | Product Description                         | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|---------------------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| SMD6R12927WH   | 6" Round Surface Mount, White, 90 CRI       | 80W INC        | 2700K | 120V     | 1244   | 16    | 360             | 080083825400 |
| SMD6R12927WHE  | 6" Round Surface Mount, White, 90 CRI, UNV  | 80W INC        | 2700K | 120-277V | 1210   | 15    | 450             | 080083817603 |
| SMD6R12930WH   | 6" Round Surface Mount, White, 90 CRI       | 80W INC        | 3000K | 120V     | 1242   | 15    | 360             | 080083825424 |
| SMD6R12930WHE  | 6" Round Surface Mount, White, 90 CRI, UNV  | 80W INC        | 3000K | 120-277V | 1203   | 15    | 450             | 080083817627 |
| SMD6R12935WH   | 6" Round Surface Mount, White, 90 CRI       | 80W INC        | 3500K | 120V     | 1264   | 15    | 360             | 080083825448 |
| SMD6R12935WHE  | 6" Round Surface Mount, White, 90 CRI, UNV  | 80W INC        | 3500K | 120-277V | 1200   | 15    | 450             | 080083817641 |
| SMD6R12940WH   | 6" Round Surface Mount, White, 90 CRI       | 80W INC        | 4000K | 120V     | 1223   | 15    | 360             | 080083825462 |
| SMD6R12940WHE  | 6" Round Surface Mount, White, 90 CRI, UNV  | 80W INC        | 4000K | 120-277V | 1260   | 15    | 450             | 080083817665 |
| SMD6R12950WH   | 6" Round Surface Mount, White, 90 CRI       | 80W INC        | 5000K | 120V     | 1252   | 15    | 360             | 080083825486 |
| SMD6R12950WHE  | 6" Round Surface Mount, White, 90 CRI, UNV  | 80W INC        | 5000K | 120-277V | 1200   | 15    | 450             | 080083817689 |
| SMD6S12927WH   | 6" Square Surface Mount, White, 90 CRI      | 76W INC        | 2700K | 120V     | 1190   | 16    | 360             | 080083825509 |
| SMD6S12927WHE  | 6" Square Surface Mount, White, 90 CRI, UNV | 76W INC        | 2700K | 120-277V | 1167   | 16    | 450             | 080083817702 |
| SMD6S12930WH   | 6" Square Surface Mount, White, 90 CRI      | 76W INC        | 3000K | 120V     | 1180   | 16    | 360             | 080083825523 |
| SMD6S12930WHE  | 6" Square Surface Mount, White, 90 CRI, UNV | 76W INC        | 3000K | 120-277V | 1135   | 16    | 450             | 080083817726 |
| SMD6S12935WH   | 6" Square Surface Mount, White, 90 CRI      | 80W INC        | 3500K | 120V     | 1237   | 16    | 360             | 080083825547 |
| SMD6S12935WHE  | 6" Square Surface Mount, White, 90 CRI, UNV | 76W INC        | 3500K | 120-277V | 1140   | 16    | 450             | 080083817740 |
| SMD6S12940WH   | 6" Square Surface Mount, White, 90 CRI      | 80W INC        | 4000K | 120V     | 1215   | 16    | 360             | 080083825561 |
| SMD6S12940WHE  | 6" Square Surface Mount, White, 90 CRI, UNV | 76W INC        | 4000K | 120-277V | 1155   | 16    | 450             | 080083817764 |
| SMD6S12950WH   | 6" Square Surface Mount, White, 90 CRI      | 80W INC        | 5000K | 120V     | 1235   | 16    | 360             | 080083825585 |
| SMD6S12950WHE  | 6" Square Surface Mount, White, 90 CRI, UNV | 76W INC        | 5000K | 120-277V | 1180   | 16    | 450             | 080083817788 |







# Ambient

## Metalux

Commercial, Residential  
& Industrial



## 8SL 8ft. LED Striplight

### Metalux

- 8ft. commercial LED strip with lens
- Single or continuous row mount capable
- Surface or suspended mount with supplied end caps
- UNV 120-277V, 0 to 10V or dimming
- J-box cover and hardware kit included



| Catalog Number | Product Description                    | Replaces Up To      | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|----------------------------------------|---------------------|-------|----------|--------|-------|-----------------|--------------|
| 8SL8040        | LED 8' Strip, 0-10V continuous dimming | 4-T8 32W, 2-T12 75W | 4000K | 120/277V | 8176   | 71    | 80              | 080083807925 |

## WPLD LED Wraparound Series

### Metalux

- 4ft. low profile LED wrap
- 0-10V dimming UNV and phase cut dimming
- Suitable for ceiling, wall, or suspension mounting
- Smooth white lens for soft, uniform, glare-free light



| Catalog Number | Product Description                         | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|---------------------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| 4WPLD4035C     | LED 4' Wrap Light, 0-10V continuous dimming | 2-T8 32W       | 3500K | 120/277V | 4460   | 39    | 84              | 080083750603 |
| 4WPLD4040C     | LED 4' Wrap Light, 0-10V continuous dimming | 2-T8 32W       | 4000K | 120V     | 4603   | 42    | 84              | 080083749676 |



# ST1 and ST2 Striplights

## Metalux

- Light duty commercial LED strip
- Designed to replace and look like a fluorescent fixture
- 2 ft., 4 ft. and 8 ft. lengths
- 1000 to 8000 lumen output at 105 lpw
- Single or dual lens exterior design
- Easy, flexible installation
- Single or continuous row mount with surface, chain or stem mounting options



| Catalog Number | Product Description                   | Replaces Up To       | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|---------------------------------------|----------------------|-------|----------|--------|-------|-----------------|--------------|
| 2ST1L1040R     | LED 2' Strip, Single Lens, UNV NO-DIM | 1-T8 17W             | 4000K | 120/277V | 1165   | 10    | 288             | 080083838165 |
| 2ST2L2040R     | LED 2' Strip, Dual Lens, UNV NO-DIM   | 2-T8 17W             | 4000K | 120/277V | 2298   | 19    | 180             | 080083838172 |
| 4ST1L2040R     | LED 4' Strip, Single Lens, UNV NO-DIM | 1-T8 32W             | 4000K | 120/277V | 2153   | 20    | 252             | 080083838189 |
| 4ST2L4040R     | LED 4' Strip, Dual Lens, UNV NO-DIM   | 2-T8 32W, 1-T5H0 54W | 4000K | 120/277V | 4433   | 39    | 150             | 080083838196 |
| 8ST2L8040R     | LED 8' Strip, Dual Lens, UNV NO-DIM   | 4-T8 32W, 2-T12 75W  | 4000K | 120/277V | 8867   | 78    | 150             | 080083838202 |

# RHB LED High/Low Bay

## Metalux

- Designed for a wide variety of applications and mounting heights
- Available in multiple lumen packages
- Energy-efficient one-for-one replacement for HID fixtures
- Ideal for industrial, manufacturing, warehouse, grocery, and retail applications



Shown with RHB Lens

| Catalog Number       | Product Description           | Replaces Up To            | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|----------------------|-------------------------------|---------------------------|-------|----------|--------|-------|-----------------|--------------|
| RHB-18-UNV-L840-CD-U | Round High Bay, 0-10V dimming | (6) T8, (4) T5H0, 320W MH | 4000K | 120-277V | 18000  | 154W  | 36              | 080083808120 |
| RHB-18-UNV-L850-CD-U | Round High Bay, 0-10V dimming | (6) T8, (4) T5H0, 320W MH | 5000K | 120-277V | 18000  | 154W  | 36              | 080083808144 |
| RHB-24-UNV-L840-CD-U | Round High Bay, 0-10V dimming | (6) T5H0, 400W MH         | 4000K | 120-277V | 24000  | 194W  | 36              | 080083808182 |
| RHB-24-UNV-L850-CD-U | Round High Bay, 0-10V dimming | (6) T5H0, 400W MH         | 5000K | 120-277V | 24000  | 194W  | 36              | 080083808205 |
| RHB-CLR              | 16" Clear Refractor           | N/A                       | N/A   | N/A      | N/A    | N/A   | 90              | 080083808243 |
| RHB-FRR              | 16" Frosted Refractor         | N/A                       | N/A   | N/A      | N/A    | N/A   | 12              | 080083808229 |
| RHB-CGL              | 16" Clear Glass Lens          | N/A                       | N/A   | N/A      | N/A    | N/A   | N/A             | N/A          |

# Exit & Emergency

## Sure-Lites

### Commercial & Industrial

\*Sure-Lites products not available in Canada



## AP2SQLED Emergency Light

### Sure-Lites

- Operates for a minimum of 90 minutes during an emergency power outage
- UL 924 code compliant
- Maintenance free nickel cadmium battery
- Fully adjustable square LED heads



| Catalog Number | Product Description                  | Replaces Up To  | Coverage | Voltage  | Lumens    | Watts     | Pallet Quantity | UPC          |
|----------------|--------------------------------------|-----------------|----------|----------|-----------|-----------|-----------------|--------------|
| AP2SQLED       | LED Emergency, plastic, Square Heads | 2 5W Inc. Heads | 12 FT    | 120/277V | 80lm/head | 2 at 277V | 288             | 080083824922 |

# APEL LED Emergency Series

## ALL-PRO

- UL 924 listed emergency light
- 90 minutes of run time
- LED heads and no maintenance
- Nickel cadmium battery
- Fully adjustable LED heads to maximize design flexibility
- Universal j-box mounting pattern
- Snap fit housing construction reduces installation time



| Catalog Number | Product Description  | Replaces Up To  | Coverage | Voltage  | Lumens   | Watts     | Pallet Quantity | UPC          |
|----------------|----------------------|-----------------|----------|----------|----------|-----------|-----------------|--------------|
| APEL           | 2 Head, NiCad, White | 2.5W Inc. Heads | 17 FT    | 120/277V | 100/head | 1 at 277V | 512             | 080083566501 |

# APC Emergency Light

## Sure-Lites

- UL924 code compliant solution for indoor exit and emergency requirements
- Operates for a minimum of 90 minutes during a power outage



| Catalog Number | Product Description                  | Replaces Up To    | Coverage | Voltage  | Lumens     | Watts     | Pallet Quantity | UPC          |
|----------------|--------------------------------------|-------------------|----------|----------|------------|-----------|-----------------|--------------|
| APC7R          | Combo Unit, White, 2 Heads, Unv. Red | 2-5.4W Inc. Heads | 17 FT    | 120/277V | 100lm/head | 2 at 277V | 288             | 080083566556 |

# APX LED Exit Series

## Sure-Lites

- Durable, injection molded, thermoplastic material resists discoloration due to UV radiation
- Energy-efficient, low-maintenance LEDs
- Universal configurations (single and double face)
- Universal mounting capability (ceiling, wall and end)



| Catalog Number | Product Description           | Replaces Up To | Voltage  | Watts     | Pallet Quantity | UPC          |
|----------------|-------------------------------|----------------|----------|-----------|-----------------|--------------|
| APX7R          | Self Powered, White, Unv. Red | N/A            | 120/277V | 1 at 277V | 270             | 080083566532 |



# Outdoor

## Lumark and HALO Commercial & Residential



## PRV Prevail LED Area/Site Luminaire

### Lumark

- Low profile, die-cast aluminum housing
- Type III, IV, distributions
- Up to 18,900 lumens
- Replaces up to 450W equivalent metal halide
- 120-277V 50/60Hz, 347V 60Hz or 480V 60Hz
- 0-10V dimming standard
- Versatile Mount Arm - multiple drill patterns, round and square poles



| Catalog Number  | Product Description                 | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|-----------------|-------------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| PRVS-A15-UNV-T3 | T3 Distr., STD Mounting Arm, Bronze | 150W HID       | 4000K | 120-277V | 6192   | 57    | 16              | 080083746217 |
| PRVS-A15-UNV-T4 | T4 Distr., STD Mounting Arm, Bronze | 150W HID       | 4000K | 120-277V | 6173   | 57    | 16              | 080083753499 |
| PRVS-A25-UNV-T3 | T3 Distr., STD Mounting Arm, Bronze | 250W HID       | 4000K | 120-277V | 10,292 | 87    | 16              | 080083746224 |
| PRVS-A25-UNV-T4 | T4 Distr., STD Mounting Arm, Bronze | 250W HID       | 4000K | 120-277V | 10,261 | 87    | 16              | 080083753482 |
| PRVS-A40-UNV-T3 | T3 Distr., STD Mounting Arm, Bronze | 400W HID       | 4000K | 120-277V | 15,203 | 143   | 30              | 080083746231 |
| PRVS-A40-UNV-T4 | T4 Distr., STD Mounting Arm, Bronze | 400W HID       | 4000K | 120-277V | 15,157 | 143   | 16              | 080083753475 |
| PRVS-A60-UNV-T3 | T3 Distr., STD Mounting Arm, Bronze | 450W HID       | 4000K | 120-277V | 18,992 | 163   | 16              | 080083773695 |
| PRVS-A60-UNV-T4 | T4 Distr., STD Mounting Arm, Bronze | 450W HID       | 4000K | 120-277V | 18,935 | 163   | 16              | 080083773701 |

# AL3050 Series

## HALO Outdoor

- Provides up to 3000 lumens with
- Maintenance-free LEDs with 50,000 hours of life
- Exceptional large light coverage that is equivalent to 300W incandescent or 100W metal halide or 85W CFL
- NEMA photocontrol provides nighttime ON / daytime OFF functionality
- Perfect for barns, side roads or security lighting



| Catalog Number | Product Description                           | Replaces Up To    | CCT   | Voltage | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|-----------------------------------------------|-------------------|-------|---------|--------|-------|-----------------|--------------|
| AL3050LPCGY    | LED Area Light, Integrated Photocontrol, Gray | 100W HID; 65W CFL | 5000K | 120V    | 3300   | 34    | 48              | 080083709977 |

# CLCSLED Canopy

## Lumark

- Slim, low-profile, traditional design
- High performing, energy-efficient illumination
- Seamlessly integrates into new or existing spaces
- Ideal for bank and retail drive-thrus, covered side walks, and hospitality entryways



| Catalog Number          | Product Description               | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|-------------------------|-----------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| CLCSLED-40-SM-UNV       | Canopy LED, Surface Mount, Bronze | 400W HID       | 4000K | 120-277V | 4839   | 36    | 144             | 080083776061 |
| CLCSLED-40-SM-UNV-7050  | Canopy LED, Surface Mount, Bronze | 400W HID       | 5000K | 120-277V | 4739   | 36    | 144             | 080083776184 |
| CLCSLED-55-SM-UNV       | Canopy LED, Surface Mount, Bronze | 400W HID       | 4000K | 120-277V | 7230   | 56    | 144             | 080083776085 |
| CLCSLED-55-SM-UNV-7050  | Canopy LED, Surface Mount, Bronze | 400W HID       | 5000K | 120-277V | 6878   | 56    | 144             | 080083776207 |
| CLCSLED-86-SM-UNV       | Canopy LED, Surface Mount, Bronze | 400W HID       | 4000K | 120-277V | 11,494 | 92    | 44              | 080083776108 |
| CLCSLED-86-SM-UNV-7050  | Canopy LED, Surface Mount, Bronze | 400W HID       | 5000K | 120-277V | 11,279 | 90    | 44              | 080083776221 |
| CLCSLED-117-SM-UNV      | Canopy LED, Surface Mount, Bronze | 400W HID       | 4000K | 120-277V | 13,828 | 121   | 44              | 080083776160 |
| CLCSLED-117-SM-UNV-7050 | Canopy LED, Surface Mount, Bronze | 400W HID       | 5000K | 120-277V | 13,882 | 120   | 44              | 080083776245 |

# FHS LED Floodlight with Selectable CCT

## HALO Outdoor

- Durable die-cast aluminum housing with UV resistant polycarbonate lens
- Field-selectable color temperature options of 3000K, 4000K and 5000K
- Maintenance-free LEDs rated for 70,000 hours
- Two-stage optics for consistent distribution across all CCT options
- Wattage equivalents ranging from 280W halogen
- Wall and eave mountable to recessed and surface mount junction boxes



| Catalog Number | Product Description                     | Replaces Up To | CCT                           | Voltage  | Lumens        | Watts | Pallet Quantity | UPC          |
|----------------|-----------------------------------------|----------------|-------------------------------|----------|---------------|-------|-----------------|--------------|
| FHS303TW       | Triple LED Flood, Selectable CCT, White | 280W INC       | Selectable CCT: (3000K-5000K) | 120-277V | 2853 at 4000K | 32    | 150             | 080083810413 |

# FSL Series LED Floodlight with Selectable CCT

## HALO Outdoor

- Durable die-cast aluminum housing with UV resistant polycarbonate lens
- Field-selectable color temperature options of 3000K, 4000K and 5000K
- Maintenance-free LEDs rated for 70,000 hours
- Two-stage optics for consistent distribution across all CCT options
- Wattage equivalents ranging from 180W to 280W halogen
- Available with or without integrated photocontrol
- Wall and eave mountable to recessed and surface mount junction boxes



| Catalog Number | Product Description                                                      | Replaces Up To | CCT                           | Voltage  | Lumens        | Watts | Pallet Quantity | UPC          |
|----------------|--------------------------------------------------------------------------|----------------|-------------------------------|----------|---------------|-------|-----------------|--------------|
| FSL203TB       | Large Single LED Flood, Selectable CCT, Bronze                           | 180W INC       | Selectable CCT: (3000K-5000K) | 120-277V | 1916 at 4000K | 23    | 180             | 080083809677 |
| FSL203TIB      | Large Single LED Flood, Selectable CCT, Photocontrol, Bronze             | 180W INC       | Selectable CCT: (3000K-5000K) | 120V     | 1916 at 4000K | 23    | 288             | 080083809691 |
| FSL203TW       | Large Single LED Flood, Selectable CCT, White                            | 180W INC       | Selectable CCT: (3000K-5000K) | 120-277V | 1916 at 4000K | 23    | 180             | 080083809738 |
| FSL303TB       | Large Single High Output LED Flood, Selectable CCT, Bronze               | 280W INC       | Selectable CCT: (3000K-5000K) | 120-277V | 2900 at 4000K | 32    | 180             | 080083809752 |
| FSL303TIB      | Large Single High Output LED Flood, Selectable CCT, Photocontrol, Bronze | 280W INC       | Selectable CCT: (3000K-5000K) | 120V     | 2900 at 4000K | 32    | 150             | 080083809776 |
| FSL303TW       | Large Single High Output LED Flood, Selectable CCT, White                | 280W INC       | Selectable CCT: (3000K-5000K) | 120-277V | 2900 at 4000K | 32    | 150             | 080083809813 |



# FSS Series LED Floodlight with Selectable CCT

## HALO Outdoor

- Durable die-cast aluminum housing with UV resistant polycarbonate lens
- Field-selectable color temperature options of 3000K, 4000K and 5000K
- Maintenance-free LEDs rated for 70,000 hours
- Two-stage optics for consistent distribution across all CCT options
- Supplied with integrated photocontrol
- Wall and eave mount to recessed and surface junction boxes



| Catalog Number | Product Description                                          | Replaces Up To | CCT                           | Voltage | Lumens        | Watts | Pallet Quantity | UPC          |
|----------------|--------------------------------------------------------------|----------------|-------------------------------|---------|---------------|-------|-----------------|--------------|
| FSS153TIB      | Small Single LED Flood, Selectable CCT, Photocontrol, Bronze | 150W INC       | Selectable CCT: (3000K-5000K) | 120V    | 1503 at 4000K | 17    | 288             | 080083809851 |
| FSS153TIW      | Small Single LED Flood, Selectable CCT, Photocontrol, White  | 150W INC       | Selectable CCT: (3000K-5000K) | 120V    | 1503 at 4000K | 17    | 288             | 080083809974 |

# MST Series LED Motion Floodlight with Selectable CCT

## HALO Outdoor

- Durable die-cast aluminum housing with UV resistant polycarbonate lens
- Field-selectable color temperature options of 3000K, 4000K and 5000K
- Motion sensor available with 180° or 270° detection and 50' range
- Maintenance-free LEDs rated for 70,000 hours
- Two-stage optics for consistent distribution across all CCT options
- Wattage equivalents ranging from 150W to 280W halogen
- Wall and eave mountable to recessed and surface mount junction boxes



| Catalog Number | Product Description                                     | Replaces Up To | CCT                           | Voltage | Lumens        | Watts | Pallet Quantity | UPC          |
|----------------|---------------------------------------------------------|----------------|-------------------------------|---------|---------------|-------|-----------------|--------------|
| MST203T18B     | Twin LED Motion Flood, 180° PIR, Selectable CCT, Bronze | 180W INC       | Selectable CCT: (3000K-5000K) | 120V    | 2034 at 4000K | 23    | 180             | 080083810161 |
| MST203T18W     | Twin LED Motion Flood, 180° PIR, Selectable CCT, White  | 180W INC       | Selectable CCT: (3000K-5000K) | 120V    | 2034 at 4000K | 23    | 180             | 080083810185 |
| MST203T27B     | Twin LED Motion Flood, 270° PIR, Selectable CCT, Bronze | 180W INC       | Selectable CCT: (3000K-5000K) | 120V    | 2034 at 4000K | 23    | 180             | 080083810246 |

# MSS Series LED Motion Floodlight with Selectable CCT

## HALO Outdoor

- Durable die-cast aluminum housing with UV resistant polycarbonate lens
- Field-selectable color temperature options of 3000K, 4000K and 5000K
- Motion sensor available with 180° detection and 50' range
- Maintenance-free LEDs rated for 70,000 hours
- Two-stage optics for consistent distribution across all CCT options
- Wattage equivalents ranging from 150W halogen
- Wall and eave mountable to recessed and surface mount junction boxes



| Catalog Number | Product Description                                       | Replaces Up To | CCT                           | Voltage | Lumens        | Watts | Pallet Quantity | UPC          |
|----------------|-----------------------------------------------------------|----------------|-------------------------------|---------|---------------|-------|-----------------|--------------|
| MSS153T18B     | Single LED Motion Flood, 180° PIR, Selectable CCT, Bronze | 150W INC       | Selectable CCT: (3000K-5000K) | 120V    | 1503 at 4000K | 17    | 180             | 080083808908 |

# FT Series LED Floodlight

## HALO Outdoor

- Delivers 1000-2000 lumens in 5000K CCT
- Maintenance-free LEDs with 35,000 hours of life
- Wall or eave mount installation
- Durable polycarbonate housing available in white or bronze finish
- Area coverage replaces up to 90W-180W incandescent flood
- Available with integrated photocontrol



| Catalog Number | Product Description                  | Replaces Up To | CCT   | Voltage | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|--------------------------------------|----------------|-------|---------|--------|-------|-----------------|--------------|
| FT1850L        | Twin LED Flood, Bronze               | 90W INC        | 5000K | 120V    | 1050   | 13    | 180             | 080083742295 |
| FT1850LPC      | Twin LED Flood, Photocontrol, Bronze | 90W INC        | 5000K | 120V    | 1050   | 13    | 180             | 080083742318 |
| FT1850LPCW     | Twin LED Flood, Photocontrol, White  | 90W INC        | 5000K | 120V    | 1050   | 13    | 180             | 080083742301 |
| FT1850LW       | Twin LED Flood, White                | 90W INC        | 5000K | 120V    | 1050   | 13    | 180             | 080083742288 |
| FT2850L        | Twin LED Flood, Bronze               | 180W INC       | 5000K | 120V    | 2000   | 25    | 144             | 080083757848 |
| FT2850LW       | Twin LED Flood, White                | 180W INC       | 5000K | 120V    | 2220   | 25    | 168             | 080083757855 |

# MST Series LED Motion Floodlight

## HALO Outdoor

- Produces 1000-2000 lumens in 5000K CCT
- Maintenance-free LEDs with 35,000 hours of life
- Wall or eave mount installation
- Durable polycarbonate housing available in white or bronze finish
- Area coverage replaces up to 90W-180W incandescent flood
- Duration and sensitivity adjustments




| Catalog Number | Product Description                     | Replaces Up To | CCT   | Voltage | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|-----------------------------------------|----------------|-------|---------|--------|-------|-----------------|--------------|
| MST1850L       | Twin LED Motion Flood, 180° PIR, Bronze | 90W INC        | 5000K | 120V    | 1050   | 13    | 180             | 080083727599 |
| MST1850LW      | Twin LED Motion Flood, 180° PIR, White  | 90W INC        | 5000K | 120V    | 1050   | 13    | 180             | 080083727582 |
| MST2850L       | Twin LED Motion Flood, 180° PIR, Bronze | 180W INC       | 5000K | 120V    | 2000   | 25    | 144             | 080083758081 |
| MST2850LW      | Twin LED Motion Flood, 180° PIR, White  | 180W INC       | 5000K | 120V    | 2220   | 25    | 168             | 080083758098 |

# Axcent Large LED Wall Pack

## Lumark

- Flush-mounted, architectural design
- High performing, energy efficient illumination
- 88 percent energy savings



| Catalog Number | Product Description                          | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|----------------|----------------------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| AXCL6A         | Axcent Large LED, Full Cutoff Lens           | 320W HID       | 4000K | 120-277V | 7594   | 56    | 45              | 080083811564 |
| AXCL6ARL       | Axcent Large LED, Refractive Lens            | 320W HID       | 4000K | 120-277V | 7809   | 56    | 45              | 080083811649 |
| AXCL8A         | Axcent Large LED, Full Cutoff Lens           | 400W HID       | 4000K | 120-277V | 9696   | 72    | 45              | 080083811588 |
| AXCL8ARL       | Axcent Large LED, Refractive Lens            | 400W HID       | 4000K | 120-277V | 9970   | 72    | 45              | 080083811663 |
| AXCL10A        | Axcent Large LED, Full Cutoff Lens           | 425W HID       | 4000K | 120-277V | 13,283 | 102   | 45              | 080083811601 |
| AXCL10ARL      | Axcent Large LED, Refractive Lens, 120-277V  | 425W HID       | 4000K | 120-277V | 13,641 | 102   | 45              | 080083811687 |
| AXCL12A        | Axcent Large LED, Full Cutoff Lens, 120-277V | 450W HID       | 4000K | 120-277V | 16,823 | 123   | 45              | 080083811625 |
| AXCL12ARL      | Axcent Large LED, Refractive Lens, 120-277V  | 450W HID       | 4000K | 120-277V | 17,346 | 123   | 45              | 080083811700 |



# WPMLED Series LED Glass Wall Packs

## Lumark

- Rugged, die-cast aluminum housing
- Replaces up to 320W Metal Halide HID
- Borosilicate Glass Door
- Lumens ranging to 8,818 lumens
- Available in 4000K CCT or 5000K CCT models
- IP66 rated, UL/cUL listed
- 120-277V 50/60Hz
- Available with integrated photocontrol



| Catalog Number        | Product Description                              | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|-----------------------|--------------------------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| WPMLED-75-GL-UNV      | Glass LED Medium Wall Pack, Bronze               | 320W HID       | 4000K | 120-277V | 8683   | 76    | 72              | 080083776382 |
| WPMLED-75-GL-UNV-7050 | Glass LED Medium Wall Pack, Bronze               | 320W HID       | 5000K | 120-277V | 8818   | 76    | 72              | 080083776467 |
| WPMLED-75-GL-UNV-PC   | Glass LED Medium Wall Pack, Photocontrol, Bronze | 320W HID       | 4000K | 120-277V | 8683   | 76    | 72              | 080083776542 |

# WPSLED Series LED Glass Wall Packs

## Lumark

- Rugged, die-cast aluminum housing
- Replaces up to 150W Metal Halide HID
- Borosilicate Glass Door
- Lumens ranging to 3,435 lumens
- Available in 4000K CCT or 5000K CCT models
- IP66 rated, UL/cUL listed
- 120-277V 50/60Hz
- Available with integrated photocontrol



| Catalog Number        | Product Description                             | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|-----------------------|-------------------------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| WPSLED-30-GL-UNV      | Glass LED Small Wall Pack, Bronze               | 150W HID       | 4000K | 120-277V | 3382   | 27    | 26              | 080083776368 |
| WPSLED-30-GL-UNV-7050 | Glass LED Small Wall Pack, Bronze               | 150W HID       | 5000K | 120-277V | 3435   | 27    | 26              | 080083776443 |
| WPSLED-30-GL-UNV-PC   | Glass LED Small Wall Pack, Photocontrol, Bronze | 150W HID       | 4000K | 120-277V | 3382   | 27    | 26              | 080083776528 |

# WPLLED Series LED Glass Wall Packs

## Lumark

- Rugged, die-cast aluminum housing
- Replaces up to 450W Metal Halide
- Borosilicate Glass Door
- Lumens ranging from 10,264 to 15,143 lumens
- Standard 4000K CCT, minimum 70 CRI, Optional 5000K CCT
- IP66 rated, UL/cUL listed
- 120-277V 50/60Hz, 347V 60Hz
- Button photocontrol models available



| Catalog Number         | Product Description                             | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|------------------------|-------------------------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| WPLLED-100-GL-UNV      | Glass LED Large Wall Pack, Bronze               | 400W HID       | 4000K | 120-277V | 10,264 | 82    | 48              | 080083776405 |
| WPLLED-100-GL-UNV-7050 | Glass LED Large Wall Pack, Bronze               | 400W HID       | 5000K | 120-277V | 10,424 | 82    | 48              | 080083776481 |
| WPLLED-100-GL-UNV-PC   | Glass LED Large Wall Pack, Photocontrol, Bronze | 400W HID       | 4000K | 120-277V | 10,264 | 82    | 48              | 080083776566 |
| WPLLED-125-GL-UNV      | Glass LED Large Wall Pack, Bronze               | 450W HID       | 4000K | 120-277V | 15,143 | 122   | 40              | 080083776429 |
| WPLLED-125-GL-UNV-7050 | Glass LED Large Wall Pack, Bronze               | 450W HID       | 5000K | 120-277V | 15,379 | 122   | 40              | 080083776504 |
| WPLLED-125-GL-UNV-PC   | Glass LED Large Wall Pack, Photocontrol, Bronze | 450W HID       | 4000K | 120-277V | 15,143 | 122   | 40              | 080083776580 |

# WPSQLED Series LED Glass Wall Packs

## Lumark

- Rugged die-cast aluminum housing for enhanced durability
- Removable door offers ease of maintenance
- IP66 rated and UL/cUL wet location listed
- Borosilicate refractive glass lens
- Optional button photocontrol to enable dusk-to-dawn control
- Replaces up to 450W equivalent metal halide luminaires
- Lumen packages ranging from 7,108 to 11,322 lumens
- 120-277V 50/60Hz



| Catalog Number       | Product Description                              | Replaces Up To | CCT   | Voltage  | Lumens | Watts | Pallet Quantity | UPC          |
|----------------------|--------------------------------------------------|----------------|-------|----------|--------|-------|-----------------|--------------|
| WPSQLED-65-UNV       | Square Glass LED Wall Pack, Bronze               | 175W HID       | 4000K | 120-277V | 7108   | 64    | 16              | 080083805662 |
| WPSQLED-65-UNV-7050  | Square Glass LED Wall Pack, Bronze               | 175W HID       | 5000K | 120-277V | 7446   | 64    | 16              | 080083805723 |
| WPSQLED-65-UNV-PC    | Square Glass LED Wall Pack, Photocontrol, Bronze | 175W HID       | 4000K | 120-277V | 7108   | 64    | 16              | 080083805907 |
| WPSQLED-75-UNV       | Square Glass LED Wall Pack, Bronze               | 320W HID       | 4000K | 120-277V | 7706   | 75    | 16              | 080083805686 |
| WPSQLED-75-UNV-7050  | Square Glass LED Wall Pack, Bronze               | 320W HID       | 5000K | 120-277V | 7918   | 75    | 16              | 080083805747 |
| WPSQLED-75-UNV-PC    | Square Glass LED Wall Pack, Photocontrol, Bronze | 320W HID       | 4000K | 120-277V | 7706   | 75    | 16              | 080083805921 |
| WPSQLED-100-UNV      | Square Glass LED Wall Pack, Bronze               | 400W HID       | 4000K | 120-277V | 11,043 | 101   | 16              | 080083805709 |
| WPSQLED-100-UNV-7050 | Square Glass LED Wall Pack, Bronze               | 400W HID       | 5000K | 120-277V | 11,322 | 101   | 16              | 080083805761 |
| WPSQLED-100-UNV-PC   | Square Glass LED Wall Pack, Photocontrol, Bronze | 400W HID       | 4000K | 120-277V | 11,043 | 101   | 16              | 080083805945 |

# Controls

Greengate  
Commercial, Residential  
& Industrial



## SP20 Switch Pack

Greengate

- LED ready
- Auto On or Manual ON
- Fail-Safe circuitry-in the event of failure, return to close (ON)
- Zero-Cross circuitry
- Photocell switching ready
- 24VDC regulated output to sensors
- Suitable for general purpose plug load control



| Catalog Number | Product Description            | Watts       | Voltage        | Detection Type | Coverage | Pallet Quantity | UPC          |
|----------------|--------------------------------|-------------|----------------|----------------|----------|-----------------|--------------|
| SP20-MV        | Standard Heavy Duty Switchpack | 2400W-5400W | 120/277V       | N/A            | N/A      | 1800            | 080083503223 |
| SP20-RD4       | Advanced Heavy Duty Switchpack | 2400W-5400W | 120-230-277VAC | N/A            | N/A      | 156             | 080083815869 |



# Emergency Power Control

## Greengate

- Eliminates energy waste by allowing emergency lighting to be switched and dimmed
- Fail safe operation
- Visible emergency power LED
- Visible regular power LED
- Integral test switch
- Senses local circuit power loss
- UL 924 listed, meets NEC, OSHA and NFPA safety codes



| Catalog Number | Product Description                | Watts | Voltage      | Detection Type | Coverage | Pallet Quantity | UPC          |
|----------------|------------------------------------|-------|--------------|----------------|----------|-----------------|--------------|
| CEPC-2-D       | 0-10V Load Emergency Power Control | 20A   | 120V or 277V | N/A            | N/A      | 920             | 080083832088 |

# RRU – UL 924 Remote Relay Unit

## Greengate

- UL 924 Listed
- Supports 120 VAC and 277 VAC input voltage configurations
- The Remote Relay Unit (RRU) supports 120/277VAC
- Accessory Detects loss of normal power and automatically sends signal to lighting control panel
- Allows Eaton lighting panels to be listed as UL 924 when RRU is connected



| Catalog Number | Product Description                             | Watts | Voltage  | Detection Type | Coverage | Pallet Quantity | UPC          |
|----------------|-------------------------------------------------|-------|----------|----------------|----------|-----------------|--------------|
| RRU-X-UNV      | Emergency Power Control, 0-10V and Line Voltage | N/A   | 120-277V | N/A            | N/A      | 920             | 080083807567 |

# Room Controller

## Greengate

- Click & Go ready, RJ45 connections
- Preconfigured for automatic functionality upon power-up
- Manual or Automatic On, bi-level, tri-level and dimming control strategies
- Integral Demand Response input with four levels of preconfigured energy reduction
- Integral Solatube® connection for classrooms
- Guaranteed compatibility with Eaton LED and 0-10V fluorescent fixtures
- Ladderless UL 924 Emergency Mode testing (RC3DE)



| Catalog Number | Product Description      | Watts | Voltage   | Detection Type | Coverage | Pallet Quantity | UPC          |
|----------------|--------------------------|-------|-----------|----------------|----------|-----------------|--------------|
| RC3DE-PL       | 3 Zone with emergency    | N/A   | 120V/277V | N/A            | N/A      | 1120            | 080083713585 |
| RC3D-PL        | 3 Zone without emergency | N/A   | 120V/277V | N/A            | N/A      | 80              | 080083713578 |

# QuickConnect Pre-terminated Cables

## Greengate

- Available in plenum and non-plenum rated
- Automatically included as part of the Room Controller Quick Kit



| Catalog Number | Product Description               | Watts | Voltage | Detection Type | Coverage | Pallet Quantity | UPC          |
|----------------|-----------------------------------|-------|---------|----------------|----------|-----------------|--------------|
| GGRJ45-006-G   | QuickConnect RJ45 cable, 6 inches | N/A   | 24VDC   | N/A            | N/A      | 1120            | 080083714933 |
| GGRJ45-10-G    | QuickConnect RJ45 cable, 10 feet  | N/A   | 24VDC   | N/A            | N/A      | 4500            | 080083657025 |
| GGRJ45-25-G    | QuickConnect RJ45 cable, 25 feet  | N/A   | 24VDC   | N/A            | N/A      | 1920            | 080083657032 |
| GGRJ45-50-G    | QuickConnect RJ45 cable, 50 feet  | N/A   | 24VDC   | N/A            | N/A      | 960             | 080083657049 |

\*Works with Room Controller

# Input/Output Device

## Greengate

- Input/Output integration
- Provides connection of any Greengate low voltage occupancy sensor, or other low voltage maintain closure
- Automatically provide Egress or HVAC integration based on room occupancy junction box
- Allows connection of standard switchpacks



| Catalog Number | Product Description | Watts | Voltage | Detection Type | Coverage | Pallet Quantity | UPC          |
|----------------|---------------------|-------|---------|----------------|----------|-----------------|--------------|
| OCC-RJ45       | Input/output device | N/A   | 24VDC   | N/A            | N/A      | 3000            | 080083657124 |

\*Works with Room Controller

# Open Loop Daylight Sensor/ IR Receiver

## Greengate

- RJ45 connection
- Easily installed in suspended fixture or drop ceiling
- Three light sensor ranges (3-300 lux, 30-3000 lux, 300-30000 lux)
- Feedback LED
- Mounting bracket for installation in light well or hard ceiling
- IR receiver for handheld remotes



| Catalog Number | Product Description       | Watts | Voltage | Detection Type      | Coverage | Pallet Quantity | UPC          |
|----------------|---------------------------|-------|---------|---------------------|----------|-----------------|--------------|
| DSRC-FM0IR     | Open Loop Daylight Sensor | N/A   | 24VDC   | Open Loop Photocell | N/A      | 2100            | 080083656653 |


\*Works with Room Controller




# Room Controller Wallstation Series

## Greengate

- Low voltage control for ON/OFF and dimming loads
- Click & Go ready with RJ45 QuickConnect ports eliminate wiring errors
- Available in 2, 3, 4, 5, 6 button models designed to fit in decorator wallplates (included)
- Wallstations can be used for multi-way control
- Custom engraving options may be replaced in the field



RC-6TSB-OS3-W



RC-3TLB-Z3D-W

| Catalog Number | Product Description                                                                      | Watts | Voltage | Detection Type | Coverage | Pallet Quantity | UPC          |
|----------------|------------------------------------------------------------------------------------------|-------|---------|----------------|----------|-----------------|--------------|
| RC-3TLB-OS1-W  | Office station, Buttons (Half Lights, Full Lights, All OFF)                              | N/A   | 24VDC   | N/A            | N/A      | 1120            | 080083657315 |
| RC-3TLB-Z1D-W  | 1 Zone wall station                                                                      | N/A   | 24VDC   | N/A            | N/A      | 1120            | 080083695126 |
| RC-3TLB-Z2D-W  | 2 Zone wall station                                                                      | N/A   | 24VDC   | N/A            | N/A      | 1120            | 080083695133 |
| RC-3TLB-Z3D-W  | 3 Zone wall station                                                                      | N/A   | 24VDC   | N/A            | N/A      | 1120            | 080083695140 |
| RC-5TSB-OS2-W  | Office station, Buttons (Half Lights, Full Lights, Raise, Lower, All OFF)                | N/A   | 24VDC   | N/A            | N/A      | 1120            | 080083657322 |
| RC-6TSB-OS3-W  | Office station, Buttons (Half Lights, Full Lights, Under cabinet, Raise, Lower, All OFF) | N/A   | 24VDC   | N/A            | N/A      | 1120            | 080083657339 |
| RC-6TSB-ZAD-W  | Office station, 3 Zone (UP and DN)                                                       | N/A   | 24VDC   | N/A            | N/A      | 1120            | 080083697168 |

\*Works with Room Controller

## Dual Technology Wall/Corner Sensor

## Greengate

- MicroSet self-adjusting time delay and sensitivity
- Optional built-in light level sensor
- Optional BAS/HVAC isolated relay
- NEMA WD7 Guide robotic method utilized to verify coverage patterns
- Manual On feature for use with 1 or 2 momentary switches controlling 1 or more Switchpacks
- Selectable Walk-Through Mode



OAWC-DT-120W



OAWC-P-120W

| Catalog Number | Product Description | Watts | Voltage | Detection Type     | Coverage   | Pallet Quantity | UPC          |
|----------------|---------------------|-------|---------|--------------------|------------|-----------------|--------------|
| OAWC-DT-120W   | Wall/Corner Sensor  | N/A   | 0-30VDC | PIR and Ultrasonic | 1200 sq ft | 540             | 080083579563 |
| OAWC-P-120W    | Wall/Corner Sensor  | N/A   | 0-30VDC | PIR                | 1200 sq ft | 360             | 080083577668 |

\*Low Voltage sensors requires SP20 Switchpack

# MicroSet Dual Tech Low and Line Voltage Ceiling Sensor

## Greengate

- MicroSet self-adjusting time delay and sensitivity
- Built-in light level sensor
- Units available for control of single or two separate loads
- Products tested to NEMA WD 7 - 2011 Occupancy
- Motion Sensors Standard LED Rated



| Catalog Number  | Product Description                       | Watts     | Voltage  | Detection Type     | Coverage   | Pallet Quantity | UPC          |
|-----------------|-------------------------------------------|-----------|----------|--------------------|------------|-----------------|--------------|
| OAC-DT-0501     | Ceiling Mount Sensor                      | N/A       | 10-30VDC | PIR and Ultrasonic | 500 sq ft  | 770             | 080083579228 |
| OAC-DT-1000     | Ceiling Mount Sensor                      | N/A       | 10-30VDC | PIR and Ultrasonic | 1000 sq ft | 540             | 080083579242 |
| OAC-DT-2000     | Ceiling Mount Sensor                      | N/A       | 10-30VDC | PIR and Ultrasonic | 2000 sq ft | 770             | 080083579266 |
| OAC-DT-2000-DMV | Line Voltage Ceiling Mount Sensor 2 relay | 1200-2700 | 120-347V | PIR and Ultrasonic | 2000 sq ft | 24              | 080083579433 |
| OAC-DT-2000-MV  | Line Voltage Ceiling Mount Sensor         | 1200-2700 | 120-347V | PIR and Ultrasonic | 2000 sq ft | 840             | 080083579426 |
| OAC-P-0500      | Ceiling Mount Sensor                      | N/A       | 10-30VDC | PIR                | 500 sq ft  | 770             | 080083579129 |
| OAC-P-1500      | Ceiling Mount Sensor                      | N/A       | 10-30VDC | PIR                | 1500 sq ft | 1600            | 080083579143 |
| OAC-P-1500-DMV  | Line Voltage Ceiling Mount Sensor 2 relay | 1200-2700 | 120-347V | PIR                | 1500 sq ft | 770             | 080083608607 |
| OAC-P-1500-MV   | Line Voltage Ceiling Mount Sensor 2 relay | 1200-2700 | 120-347V | PIR                | 1500 sq ft | 630             | 080083579402 |

\*Low Voltage sensors requires SP20 Switchpack

# Fixture Mount PIR High Bay/Low Bay Dimming Occupancy Sensor

## Greengate

- 1-100% continuous dimming for LED fixture control
- Suitable for use in standard and cold storage applications
- RGB LED indicators for device status and easy troubleshooting
- Alternating relay software for increased lamp life
- Interchangeable 360° high bay and low bay lenses included
- Adjustable time delay (no power required)
- Pre-stripped color-coded wire leads
- Quicksnap feature for easy installation, Zero crossing circuitry, Robust mechanical latching relay
- Relay always returns to close after power loss event
- UL listed for electronic ballast loads 120/277V



| Catalog Number | Product Description  | Watts | Voltage  | Detection Type | Coverage   | Pallet Quantity | UPC          |
|----------------|----------------------|-------|----------|----------------|------------|-----------------|--------------|
| OEF-P-010V-MV  | Fixture Mount Sensor | 1200  | 120/277V | PIR            | 1500 sq ft | 750             | 080083758104 |

## NeoSwitch Wall Switch Occupancy Sensor

### Greengate

- Selectable built-in light level sensor
- NEMA WD7 Guide robotic method utilized to verify coverage patterns
- Tracking/HVAC Mode
- LED Load rating



ONW-D-1001-DMV-W



ONW-P-1001-DMV-W

| Catalog Number    | Product Description                         | Watts  | Voltage  | Detection Type     | Coverage   | Pallet Quantity | UPC          |
|-------------------|---------------------------------------------|--------|----------|--------------------|------------|-----------------|--------------|
| ONW-D-1001-DMV-W  | Wall Switch Sensor, Ground Required, White  | 0/2700 | 120/277V | PIR and Ultrasonic | 1000 sq ft | 1500            | 080083524754 |
| ONW-D-1001-MV-N-W | Wall Switch Sensor, Neutral Required, White | 0/2700 | 120/277V | PIR and Ultrasonic | 1000 sq ft | 900             | 080083524594 |
| ONW-D-1001-MV-W   | Wall Switch Sensor, Ground Required, White  | 0/2700 | 120/277V | PIR and Ultrasonic | 1000 sq ft | 150             | 080083524709 |
| ONW-P-1001-DMV-W  | Wall Switch Sensor, Ground Required, White  | 0/2700 | 120/277V | PIR                | 1000 sq ft | 1050            | 080083524013 |
| ONW-P-1001-MV-W   | Wall Switch Sensor, Ground Required, White  | 0/2700 | 120/277V | PIR                | 1000 sq ft | 1200            | 080083523863 |
| ONW-P-1001-SP-W   | Wall Switch Sensor, Low Voltage, White      | 0/2700 | 10-30VDC | PIR                | 1000 sq ft | 1200            | 080083524150 |

## NeoSwitch Wall Switch Vacancy Sensor

### Greengate

- Air-gap switch ensures no leakage current to load
- Selectable built-in light level sensor
- Products tested to NEMA WD 7 - 2011 Occupancy Motion Sensors Standard
- Requires Manual On for activation
- LED Rated



| Catalog Number   | Product Description                                         | Watts  | Voltage  | Detection Type     | Coverage   | Pallet Quantity | UPC          |
|------------------|-------------------------------------------------------------|--------|----------|--------------------|------------|-----------------|--------------|
| VNW-D-1001-DMV-W | Vacancy wall box sensor, Dual Relay, Ground Required, White | 0/2700 | 120/277V | PIR and Ultrasonic | 1000 sq ft | 1350            | 080083652068 |
| VNW-D-1001-MV-W  | Vacancy wall box sensor, Ground Required, White             | 0/2700 | 120/277V | PIR and Ultrasonic | 1000 sq ft | 1350            | 080083644438 |

# Single Level Wall Switch Vacancy Sensor

## Greengate

- 0-10V three in one control, occupancy, daylight and manual
- Adjustable Time Delay Integral daylight sensor
- Manual On operation only
- Works with incandescent, LED, fluorescent, CFL, MLV, ELV or 1/6 hp motor load
- LED rated



| Catalog Number   | Product Description                                | Watts     | Voltage  | Detection Type | Coverage   | Pallet Quantity | UPC          |
|------------------|----------------------------------------------------|-----------|----------|----------------|------------|-----------------|--------------|
| VSW-P-010        | 0-10V Vacancy wall box sensor/dimmer, White        | 1200-2200 | 120-277V | PIR            | 1000 sq ft | 576             | 080083758975 |
| VSW-P-010-G      | 0-10V Vacancy wall box sensor/dimmer, Gray         | 1200-2200 | 120-277V | PIR            | 1000 sq ft | 576             | 080083758913 |
| VSW-P-010-LA     | 0-10V Vacancy wall box sensor/dimmer, Light Almond | 1200-2200 | 120-277V | PIR            | 1000 sq ft | 576             | 080083758937 |
| VSW-P-010-V      | 0-10V Vacancy wall box sensor/dimmer, Ivory        | 1200-2200 | 120-277V | PIR            | 1000 sq ft | 576             | 080083758951 |
| VSW-P-0801-120-W | 120V Vacancy wall box sensor                       | 0-600     | 120V     | PIR            | 800 sq ft  | 864             | 032664729874 |

# 0-10V Decorator Dimmer Wallstation

## Greengate

- Preset feature allows user to return to previous light level when turning lights ON
- Integrated full-slide control for easy, precise operation
- Neutral is not required for installation of device
- Adjustable high-level trim setting for optimal lamp compatibility
- Some packages include faceplate kit with 3 colors



| Catalog Number | Product Description                                                  | Voltage   | Pallet Quantity | UPC          |
|----------------|----------------------------------------------------------------------|-----------|-----------------|--------------|
| WBSD-010DEC-C1 | 0-10V Decorator Dimmer, White, Ivory, Almond Color Kit               | 120V/277V | 1050            | 080083735266 |
| WBSD-010DEC-C2 | 0-10V Decorator Dimmer, White, Ivory, Light Almond Color Kit         | 120V/277V | 1050            | 080083735273 |
| WBSD-010DEC-C5 | 0-10V Decorator Dimmer, White, Black, Gray Color kit                 | 120V/277V | 1050            | 080083734719 |
| WBSD-010SLD-BK | 0-10V Decorator Dimmer, Black                                        | 120V/277V | 1050            | 080083735334 |
| WBSD-010SLD-GY | 0-10V Decorator Dimmer, Gray                                         | 120V/277V | 1050            | 080083735327 |
| WBSD-010SLD-LA | 0-10V Decorator Dimmer, Light Almond                                 | 120V/277V | 1050            | 080083735310 |
| WBSD-010SLD-V  | 0-10V Decorator Dimmer, Ivory                                        | 120V/277V | 1050            | 080083735303 |
| WBSD-010SLD-W  | 0-10V Decorator Dimmer, White                                        | 120V/277V | 1050            | 080083735280 |
| WBSD-DEC-C1    | Multi Load Decorator Line Voltage Dimmer, White, Almond, Ivory       | 120V/277V | 1050            | 080083735402 |
| WBSD-DEC-C2    | Multi Load Decorator Line Voltage Dimmer, Light Almond, White, Ivory | 120V/277V | 1050            | 080083735419 |
| WBSD-DEC-C5    | Multi Load Decorator Line Voltage Dimmer, Black, Gray, White         | 120V/277V | 1050            | 080083735426 |



# Single Level Wall Switch Sensor

## Greengate

- 0-10V three in one control, occupancy, daylight and manual
- Integral Daylight Sensor (some models)
- Choice of Manual On or Auto On operation
- Works with Incandescent, LED, Fluorescent, CFL, MLV, ELV or 1/2 HP motor load
- NEMA WD7 Standard robotic method utilized to verify coverage patterns
- LED rated



| Catalog Number    | Product Description                                | Watts     | Voltage  | Detection Type | Coverage   | Pallet Quantity | UPC          |
|-------------------|----------------------------------------------------|-----------|----------|----------------|------------|-----------------|--------------|
| OSW-P-010         | Occ wall box sensor/dimmer, White                  | 1200/2200 | 120/277V | PIR            | 1000 sq ft | 1188            | 080083758661 |
| OSW-P-010-BK      | Occ wall box sensor/dimmer, Black                  | 1200/2200 | 120/277V | PIR            | 1000 sq ft | 576             | 080083758289 |
| OSW-P-010-G       | Occ wall box sensor/dimmer, Gray                   | 1200/2200 | 120/277V | PIR            | 1000 sq ft | 576             | 080083758302 |
| OSW-P-010-LA      | Occ wall box sensor/dimmer, Light Almond           | 1200/2200 | 120/277V | PIR            | 1000 sq ft | 576             | 080083758326 |
| OSW-P-010-V       | Occ wall box sensor/dimmer, Ivory                  | 1200/2200 | 120/277V | PIR            | 1000 sq ft | 576             | 080083758340 |
| OSW-P-0451-DMV-W  | Occ wall box sensor, Two Circuit/Dual-Level, White | 0/1200    | 120/277V | PIR            | 450 sq ft  | 2400            | 080083503490 |
| OSW-P-0451-MV-N-W | Occ wall box sensor, Neutral Required, White       | 0/1200    | 120/277V | PIR            | 450 sq ft  | 1920            | 080083503407 |
| OSW-P-0801-120-W  | 120V Wall switch sensor                            | 600       | 120V     | PIR            | 800 sq ft  | 990             | 032664729829 |
| OSW-P-1001-MV-W   | Wall Switch Sensor, Ground Required, White         | 0/2200    | 120/277V | PIR            | 1000 sq ft | 1680            | 032664729775 |
| OSW-U-0721-MV-W   | Ultrasonic wall box sensor, White                  | 0/1200W   | 120/277V | Ultrasonic     | 500 sq ft  | 2250            | 080083503315 |



### **Lighting Product Lines**

Halo  
Halo Commercial  
Portfolio  
Iris  
RSA  
Metalux  
Corelite  
Neo-Ray  
Fail-Safe  
MWS  
Ametrix  
Shaper  
io  
Lumark  
McGraw-Edison  
Invue  
Ephesus  
Lumière  
Streetworks  
AtLite  
Sure-Lites

### **Controls Product Lines**

Greengate  
iLumin  
Zero 88  
Fifth Light Technology  
iLight (International Only)

### **Connected Lighting Systems**

LumaWatt Pro  
WaveLinx  
Distributed Low-Voltage Power  
ConnectWorks



**Eaton**  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
[www.eaton.com/lighting](http://www.eaton.com/lighting)

**Canada Sales**  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2018 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. CA525034EN  
October 2018

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.