

DISTRIBUTION

- Full LED product line with nickel cadmium batteries
- All products stocked and priced to sell
- EBPLED & SELW are market leading products – perfect entry at distribution

COMMERCIAL

- Market leading LED emergency coverage creates lowest total cost solution
- Intuitive catalog logic and bundled features simplify the design process
- Superior options for design build applications

INDUSTRIAL

- Market leading LED emergency coverage creates lowest total cost solution
- Intuitive catalog logic and bundled features simplify the design process
- Ideal for wet locations, extreme temperatures and harsh environments

SPECIFICATION

- Full LED portfolio
- Market leading, products with superior aesthetics
- Customizable, specification locking and patent pending features
- Superior aesthetics



Powering Business Worldwide

Emergency Products



	APEL	SELWT29SD SELW29SD SELW25	SEL50 SEL25 SEL17	SEL50R7SD/ SEL25R10SD/ SEL60R4SD	SEL60R10SD/ SEL50R14SD/ SEL25R16SD	SEL60R4SD	SELM60R10SD/ SELM50R14SD/ SELM25R16SD	SELM-REC	SELA	SELDWA	SELMTG	AEL2SD AEL2	SELIN	SELSD
Series	<u>APEL</u>	<u>SELW</u>	<u>SEL</u>	<u>SEL</u>	<u>SEL</u>	<u>SELM</u>	<u>SELMREC</u>	<u>SELA</u>	<u>SELDWA</u>	<u>SELMTG</u>	<u>AEL2</u>	<u>SELIN60SD</u>	<u>SELD</u>	
Material	Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate	Sheet Metal	Sheet Metal	Polycarbonate	Die cast AL	Sheet metal	Die Cast AL	Fiberglass	Die Cast AL	
Source	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	
Coverage	15 feet	25 or 29 feet	17/25/50 feet	25/50/60 feet	25/50/60 feet	25 feet or 60 feet	25, 50 or 60 feet	29 feet	29 or 50 feet	60 feet	25 feet	25, 50 or 60 feet	60 feet	
Battery	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	
Remote Capability	N/A	N/A	N/A	4 to 10 watts	10 to 16 watts	4 to 16 watts	4 to 10 watts	N/A	N/A	5 watts	N/A	Yes	N/A	
Color	White	Ag/BK/WH/BZ	White or Black	White or Black	White or Black	White	White or Black	White or Black	Ag/BK/WH/BZ	White or Black	Ag/BK/WH/BZ	Grey	Ag/BK/Wh	
Temp Range	10° C to 40° C	0° C to 40° C / -20° C to 55° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0C to 40C / -20C to 55C	0C to 40C	-30° C to 55° C	0° C to 40° C	-30° C to 50° C	
Self Diagnostics	No	Option	Option	Option	Standard	Standard	Standard	Standard	Standard	Standard	Option	Standard	Standard	
UL Rating	Damp location	Wet Location	Damp location	Damp location	Damp location	Damp location	Damp location	Damp location	Wet location	Damp location	Wet Location	NEMA4x	NEMA 4X / HAZ option	
Always On	No	No	No	No	No	No	No	No	No	No	Yes	No	No	
Availability	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Q2 2019	Stock	Stock	

\$

\$\$

\$\$\$












\$\$\$\$



Powering Business Worldwide

Exit Products



	APX	APC	LPX LPXSD	CXSD	LPXC	EUS EUR	LPXW Outdoor	EUX EUXSD	ACE	ELX/ES	UX UX HAZ
											
Series	APX	APC/APCH	LPX	CX	LPXC	EU	LPXW	EUX	ACE	ES / ELX	UX
Type	Box	Combo	Box	Box	Combo	Edge Lit	Box	Edge Lit	Circular	Edge Lit	Box
Material	Polycarbonate	Polycarbonate	Polycarbonate	Die Cast	Polycarbonate	Aluminum	Polycarbonate	Aluminum	Aluminum	Aluminum	Die Cast AL
Mounting	Universal		Universal	Universal	Universal	Sur / Rec	Universal	Universal	Universal	Sur / Rec	Universal
Faces	Universal	Universal	Universal	Universal	Universal	Universal	One or Two	Universal	Universal	One or Two	One or Two
Letter Color	Red or Green	Red or Green	Red & Green	Red & Green	Red & Green	Red or Green	Red or Green	Red or Green	Red & Green	Red or Green	Red & Green
Housing Color	White, Black	White, Black	White, Black	Silver, Black, White	White, Black	Silver	Silver, Black, White	Silver, Black, White	Silver, Black, White	Wh,BK,B-Z,BR,AL	Silver, Black, White
Self Diagnostics	N/A	N/A	Option	Option	Option	N/A	Standard	Option	Standard	Option ELX	Standard
Remote Capacity	Option	Yes	Option	No	Option	No	No	No	No	No	No
UL Rating	Damp location	Damp location	Damp location	Damp location	Damp location	Damp location	Wet location	Damp location	Damp location	Damp location	NEMA4X/HAZ
Availability	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	MTO	Stock


\$

\$\$

\$\$\$

\$\$\$\$

Remote Products



	APWR	SRP	SRM	SRPA
				
Series	APWR	SRP	SRM	SRPA
Material	Plastic	Polycarbonate	Sheet Metal	Polycarbonate
Source	LED	LED	LED	LED
Number of heads	1 or 2	1 or 2	1 or 2	2
Adjustable	Yes	Yes	Yes	Yes, with forward throw
Coverage	15 feet	13 to 60 feet	13 to 60 feet	29 feet
Voltage input	3.6 volts	4.8 through 12 volts	4.8 through 12 volts	4.8 through 6 volt
Color	White,Black	White,Black,Grey	White,Black,Grey	White,Black,Silver,Grey
Temp Range	0 C to 40 C	-30 C to 60 C	-30 C to 60 C	-30 C to 55 C
UL Rating	Wet location	Wet Location	Wet Location	Wet Location
Availability	Stock	Stock	Stock	Stock
	\$	\$\$	\$\$\$	\$\$\$\$